

Distributed by:

**JAMECO**<sup>®</sup>  
ELECTRONICS

**www.Jameco.com ♦ 1-800-831-4242**

The content and copyrights of the attached  
material are the property of its owner.

Jameco Part Number 240717

## 3296 cermet trimmer potentiometer

**Electrical characteristics:**

Standard resistance range: 10(Ohms) -2M(Ohms)

Resistance tolerance:  $\pm 5\%$ ,  $\pm 10\%$

Terminal resistance:  $\leq 1\%R$  or 2(Ohms)

Contact resistance variation:  $\leq 3\%R$  or 3(Ohms)

**Environment characteristics:**

Rated power:  $+70^\circ$  0.5W,  $+125^\circ$  0W

Temperature range:  $-55^\circ$   $+125^\circ$

**Physical characteristics:**

Total mechanical travel:  $30 \pm 2$  cycles

Starting torque:  $\leq 36$  mN.m

Clutch torque:  $\leq 36$  mN.m

Standard packaging: 50 pcs/tube

Model	Resistance ( $\Omega$ )
3296Y-1-101	100
3296Y-1-102	1,000
3296Y-1-103	10,000
3296Y-1-104	100,000
3296Y-1-105	1,000,000
3296Y-1-200	20
3296Y-1-201	200
3296Y-1-202	2,000
3296Y-1-203	20,000
3296Y-1-205	2,000,000
3296Y-1-253	25,000
3296Y-1-500	50
3296Y-1-501	500
3296Y-1-502	5,000
3296Y-1-503	50,000
3296Y-1-504	500,000

