

Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 29197 Ver 2

SPECIFICATION OF CARBON COMPOSITION VARIABLE RESISTORS

CUSTOMER				CODE No	
PART No		TYPE CODE	SAMPLES	SPEC No	
MODEL No		24N- 5KB.15R		DRWG No	
DRWG No			KITS/PCS	DATE	
E 01	NOMINAL RESISTANCE	5 K OHMS ± 20 %			<p style="text-align: center;">TAPER B CURVE</p>
E 02	TAPER CURVE	FIGURE AT RIGHT →			
E 03	POWER RATINGS	125 V 0.05 W			
E 04	RESIDUAL	T1-T2	LESS THAN 20 OHMS		
E 05	RESISTANCE	T2-T3	LESS THAN 20 OHMS		
E 06	TRACKING ERROR (dBm) FOR GANG TYPE ONLY	VOLUME	± FOR TO		
			± FOR TO		
		TONE	± AT 50% TRAVEL		
E 07	SWITCH	RATINGS	V A		
		CONTACT	LESS THAN OHMS		
E 08	SLIDING NOISE	LESS THAN 47 mV			
E 09	INSULATION RESISTANCE	DC 500V 100M OHMS			
E 10	DIELECTRIC STRENGTH	AC 1000V FOR 1 MINUTE			
M 01	DIMENSIONS	FIGURE ATTACHED			
M 02	STOPPER STRENGTH	MORE THAN 7 Kg			
M 03	OVERALL TRAVEL	ROTATION	300 ± 5 °		
		STROKE	± mm		
M 04	TORQUE	SLIDING	50 - 350 gcm		
M 05		SWITCH	- gcm		
M 06	SWITCH	ROTATION	± °		
	TRAVEL	STROKE	± mm		
M 07	SWITCH TYPE	P. T.			
L 01	WORKING LIFE	MORE THAN 15,000 CYCLES			
AUTHORIZED	APPROVED	CHECKED	WRITTEN		

ACCESSORIES	NUT	OD	T	PC
	WASHER	OD	T	PC
	SCREW	M1.7 PO	L	PC

NOTES

BUSHING — 3/8