

PC Board Drill Bits

- Shaft diameter: .125"
- Use for drilling holes in glass PC boards



Part No.	Size	Dia.	1	10	100
1919537	1/8	.125"	\$.99	\$.75	\$.59
1919588	31	.120"	.99	.75	.59
1919300	32	.116"	.99	.75	.59
1919609	33	.113"	.99	.75	.59
1919553	35	.110"	.99	.75	.59
1919570	38	.102"	.99	.75	.59
1919502	45	.082"	.99	.75	.59
1919596	46	.081"	.99	.75	.59
1919561	48	.076"	.99	.75	.59
16580	59	.040"	1.75	1.49	.99
16619	75	.021"	1.75	1.49	.99

High-Speed Steel Step Drill Bit

Drill multiple holes in thin material with the same bit, faster and easier. Each bit does the work of many drill bit sizes. You can drill holes in most materials such as plastic, metal, and wood up to 1/8" thick.



- Shank size: 3/8" • 2.4" long

Part No.	Description	1	10	50
229657	3/16" - 7/8" 13-step ...	\$14.95	\$13.49	\$11.95

*Drill Bits — Enter Web Code NEJ

Need special orders or pricing?
Call us at 1-800-831-4242



32-Piece Security Bit Set

These bits match the security fasteners commonly used in today's electronic products.

Includes: Torx bits: #6, #8 and #10; Tri-wing bits: #1, #2, #3 and #4; Security hex bits: 5/64", 3/32", 7/64", 1/8", 9/64", 5/32" 3/16" and 1/4"; Security Torx bits: T8, T10, T15, T20, T25, T27, T30, T35 and T40; Spanner bits: 4, 6, 8 and 10mm; Phillips bits: #1, #2, #3 and #4; and 60mm magnetic bit extension that fits 1/4" hex driver



Part No.	Description	1	10
223829	32-piece security bit set	\$10.95	\$9.95



Ball-End, Hex Key and Screwdriver Sets

Bondhus/Telo Products: Inferior tools cost money when something goes wrong. The cost of removing a stripped or broken screw head from a tight location, or replacing a damaged tool exceeds the cost of purchasing a superior tool in the first place.

- Material: Protanium high torque steel
- Ergonomically designed anti roll handle
- Bondhus: made in USA; Telo: made in Germany
- Ball-end inserts quickly into screw head up to 250
- Delivers perfect balance between tip strength and working angle
- Life time warranty

*Web Code: CAQ

Part No.	Mfr.	Description	1	10
34041	BenchPro	6-pc. precision screwdriver set (slotted - 3/64", 1/16", 5/64", 5/32", 1/8", 9/64")	\$2.95	\$2.59
34059	BenchPro	6-pc. precision screwdriver set (Phillips #0 - 1/16", 5/64", 3/32", #1 - 1/8", 9/64")	2.95	2.59
2096229	Telo	6-pc. screwdriver set (slotted - 9/64"; 5/32"; 7/32"; 1/4"; Phillips - #1; #2)	37.95	35.95
99451	BenchPro	6-pc. long neck screwdriver set (slotted - (Dia. x L) 3/32" x 6 5/8", 1/8" x 7 5/8", 5/32" x 9 5/8", Phillips - #00 x 6 5/8"L, #0 x 7 5/8"L, #1 x 9 5/8")	8.95	7.95
226106	BenchPro	6-pc. precision 50 mm torx screwdriver set (Torx - T5, T6, torx hex - T7, T8, T9, T10)	13.95	11.95
2096350	Bondhus	8-pc. ball-end screwdriver set (.05", 1/16", 5/64", 3/32", 7/64", 1/8", 9/64", 5/32", 3/16", 7/32", 1/4", 5/16")	21.95	19.95
2096499	Bondhus	16-pc. folding hex key set (5/64", 1/4"; 2mm to 8mm)	13.95	12.49
2096173	Bondhus	12-pc. ball-end hex key set (.05", 1/16"; 5/64"; 3/32"; 7/64"; 1/8"; 9/64"; 5/32"; 3/16"; 7/32"; 1/4"; 5/16"	12.95	11.95
261999	BenchPro	7-pc. 1000V insulated magnetic screwdriver set (slotted - 2.5mm)	15.95	14.49
2096456	Telo	7-pc. 1000V insulated screwdriver set (slotted - 3/32"; 1/8"; 9/64"; 5/32"; 7/32"; Phillips - #1; #2)	32.95	29.95
99565	BenchPro	6-pc. screwdriver & plier set (slotted - (Dia. x L) 0.09" x 7 5/8", 0.312 x 9 1/2", Phillips - #2 0.09" x 7 5/8", #0 0.12" x 9 1/2", pliers - micro nipper cutter, micro flat nose pliers)	14.95	13.49
261842	BenchPro	7-pc. SAE nut driver set w/ colored handles (sizes: 3/16", 1/4", 5/16", 11/32", 3/8", 7/16", 1/2")	6.95	5.95
226094	BenchPro	11-pc. magnetic AWL prec. screwdriver set (slotted - .9, 1.2, 1.4, 1.8, 2.4, 3 mm, Phillips - #00, #0, #1)	3.95	2.95
2096165	Bondhus	12-pc. screwdriver bit set w/ screwdriver (slotted - 1/8"; 5/32"; 7/32"; 9/32"; POZI - #1; #2; Phillips - #0; #1; #2; Torx - #15; #20)	24.95	22.95



34041 2096229 99451 226106



2096350 2096499 2096173



261999 2096456 99565 261842



226094 2096165



Pocket Screwdriver

Phillips & Flat head

*Web Code: CAQ

- Pen clip for pocket storage



Part No.	Description	1	10	100
127271	6" long pocket screwdriver	\$1.95	\$1.59	\$1.39

Automatic Center-Punch Tool

Adjustable


- Precision instrument
- Alloy steel point
- Knurled steel body
- Size: 5.0"L x 0.5"Dia.



Part No.	Description	1	10
160282	Center punch tool	\$5.95	\$5.49

30 AWG Wire Wrap/Strip Tools

Recommended for use on 0.025" (0.63mm) square posts on 0.100" (2.54mm) center grids. The first 1-1/2 loop on the modified tool has wire insulation while all loops on a regular tool have bare wires.



Part No.	Description	1	5
242801	Tool (regular)	\$19.95	\$18.95
242798	Tool (modified)	22.95	21.95
242827	Replacement tip (242801)	7.95	7.29
242819	Replacement tip (242798)	7.95	7.29
242835	Replace stripper assembly	5.95	5.49



Regular Modified



Strip-Wrap-Unwrap Tools

- Tool tip made of tempered steel
- Spring steel cutter
- Use with 30 AWG wire on .025" square posts
- No solder necessary, see pg 57 for wire
- Wrap 1 to 2 turns of insulated portion of wire for secure connections • 4.5" long



34585

*Web Code: BBC

Part No.	Product No.	1	5
34585	HSM30 (Modified)	\$49.95	\$44.95
236785	HSR30 (Regular)	29.95	25.95

1/4-Watt & 1/2-Watt Resistor & Capacitor Lead Forming Tool

- Watt size indicates appropriate package size
- Bends lead length in 0.05" increments
- Lead spacing: 1/4W: 0.4"-1.5"; 1/2W: 0.5"-1.5"
- Size: 5.4"L x 1.5"W



Part No.	Description	1	10
106884	1/4W & 1/2W	\$4.95	\$4.49

*For Complete Specs & Additional Product Listings Search www.Jameco.com/More and Enter Web Code Listed Above