

Powered Project Breadboards

- Solderless breadboard with 2420 tie points
- Power switch with light • Outputs are short-circuit protected

Includes: Power cord

*Web Code: XAT

- 136259:**
- Fixed power: +5V @ 1A; variable power: 0 to ±15VDC @ 500mA
 - Edge plate for non-DIP size components
 - Input power: 120/220VAC @ 50-60Hz (switchable)
 - Replacement fuse: P/N 103908, pg 40
- 1942163:**
- Input power: 110VAC or 220VAC @ 50-60Hz (switch selectable)
 - Triple output power supply: fixed 5VDC @ 1A; 0 to +16VDC @ 500mA (adjustable); 0 to -16VDC @ 500mA (adjustable)
 - Grounded case
 - Fuse protection

- One-year warranty
- Breadboard size: 7.4"L x 6.8"W
- Back panel has ground terminal
- Overload protection
- Lighted power switch



136259



1942163

Part No.	Description	Overall Size	Wt. (lbs.)	1	5
136259	15VDC @ 500mA	9.8"L x 8.0"W x 2.6"H	6.8	\$175.95	\$159.95
1942163	5VDC @ 1A & 16VDC @ 500mA	10.3"L x 8.8"W x 3.3"H	6.0	99.95	89.95

Wire Jumper Kits

- 0.1" to 5.0" lengths (14 sizes)
- Pre-stripped/preformed
- Clear plastic durable case
- 22 AWG solid wire jumpers in 10 colors

19290



2096018: 140 pieces, 10 of each length

19290: 350 pieces, 25 of each length

20080: 350 pieces, refill for 19290

*Web Code: LAS

Part No.	Description	1	10	50	100
20080	Refill for 19290	\$11.95	\$10.95	\$8.95	\$6.95
19290	350-piece kit	16.95	14.95	12.95	10.95
2096018	140-piece kit	7.95	7.29	6.59	5.95

Reinforced Jumper Wires

- 24 AWG-300 volts
- Reinforced pin ends for durability
- 10 pack assortment: 2 each yellow, white, red, black & blue

126342



*Web Code: LAS

Part No.	Cross Ref. No.	Length (mm/inch)	1	10	100
126360	JW50	50/1.97	\$3.95	\$3.59	\$3.19
126342	JW100	100/3.94	5.95	5.39	4.95
126325	JW200	200/7.87	6.95	6.29	5.49

Stackable Banana Test Lead Cables



*Web Code: TLC

Part No.	Mfr. P/N	Description	1	10	25
159901	B-24-02	(2) 24" leads	\$9.95	\$8.95	\$8.29
159919	B-36-02	(2) 36" leads	10.95	9.95	8.95

Test Leads & Clips

See pages 154-155 for our selection



Bug Boxes

- Anti-static plastic
- Fits in bug cage (P/N 11332, below)
- Box size: 4.9"L x 3.3"W x 0.6"H
- Color: blue

11375



11341

11341: Stores sixty 8-pin or thirty 16-pin DIPs
11375: Designed to store all types of components

Part No.	Description	1	10	100
11341	30 compartments	\$5.95	\$5.49	\$4.95
11375	3 compart./3 vertical & 3 horizontal dividers	5.95	5.49	4.95

Bug Tray

- Fits in bug cage (P/N 11332, below)
- 10 compartments
- 3.2"L x 0.4"W x 0.4"H ea.
- Tray size: 4.8"L x 3.6"W x 0.5"H



Part No.	Description	Color	1	10	100
11800	Divided bug tray	Blue	\$4.95	\$4.49	\$3.95

Bug Cage

- Holds bug boxes or trays
- Modular and interlocking
- Case size: 5.0"L x 3.9"W x 5.1"H



Boxes/Trays not included

Part No.	Description	Color	1	10	100
11332	Bug cage	Blue	\$8.95	\$7.95	\$6.95

Plastic Fliptop Case for SMDs

- 128 compartments
- 8 rows x 16 columns grid
- Fliptop openings on each bin
- Padded cover locks bins closed
- Perfect match to store P/N 156882 SMD resistor assortment, pg 52
- Size: 11.0"L x 8.3"W x 1.7"Thick • Color: gray

JAMECO EXCLUSIVE



Part No.	Description	1	10
164267	SMD fliptop case	\$49.95	\$44.95

Helping You Find What You Need

Can't find the product you're looking for?
Call us at 1-800-831-4242.

Resistance & Capacitance Decade Substitution Boxes

Wide-range decade substitution boxes for product design or calibration checks.

- Light durable construction
- Case may be grounded separately
- Three binding posts permit isolated substitutions
- Size: 4.7"W x 5.7"H x 1.4"D • Wt: 0.7 lbs.



- 211668: 1% resistance substitution from 1Ω to 11.111110MΩ
- 7 decade ranges of resistance
- Values can be changed in 1Ω increments • @ 3 watts

- 211676: 5% capacitance substitution from 100pF to 11.111µF
- 5 decade ranges of capacitance • @ 50VDC

Part No.	Description	1	5
211668	Resistance	\$99.95	\$89.95
211676	Capacitance	129.95	119.95

Component Cabinet

JAMECO ValuePro EXCLUSIVE



319600



Drawer (319601) Divider (319611)

319601 Components not included

319600:

- Drawer can be divided into 3 sections (clear)
- Wall mountable cabinet (ABS black)
- Cabinet size: 6.0"D x 14.7"W x 7.4"H

Includes: 20 clear plastic drawers, 20 dividers and 30 adhesive I.D. labels

319601: 5.5"L x 2.7"W x 1.5"H; 319611: 2.5"W x 1.2"H

2108605:

- Counter-top design (ABS blue)
- Cabinet size: 7.0"D x 17.625"W x 9.75"H



2108605

Includes:

- 14 clear plastic drawers in 3 sizes: 10 ea. 6.375"L x 3.375"W x 1.5"H, 3 ea. 6.375"L x 8.75"W x 1.5"H, 1 ea. 6.375"L x 8.75"W x 3.25"H, and 20 adhesive I.D. labels

* Order in multiples of 10

Part No.	Description	1	10	100
319600	20-drawer cabinet	\$16.95	\$15.49	\$13.95
2108605	14-drawer cabinet	24.95	22.95	19.95
319601	Drawer for cabinet	.49	.45	.39
319611	Divider for cabinet	*	.12	.10

Plastic Fliptop Boxes

- Clear plastic box with a clear plastic lid and removable dividers

- 100256: Size: 8.4"L x 4.5"W x 1.4"H • 18 compartments (1.4" x 1.5" each)
- 148902: Size: 10.2"L x 4.7"W x 1.6"H • 12 compartments (1.7" x 2.3" each)
- 2095955: Size: 7.7"L x 5.3"W x 1.4"H • 11 individual rounded compartments



100256

Part No.	Description	1	10	100
100256	18 compartments	\$2.29	\$1.95	\$1.79
148902	12 compartments	3.95	3.49	2.95
2095955	11 compartments	2.95	2.69	2.39

* For Complete Specs & Additional Product Listings Search www.Jameco.com/More and Enter Web Code Listed Above