



1/2-Watt 24mm Linear Taper (±20%)

- Rotational angle: 300° (±5°)
- Max. volt.: 500V • Shaft Dia.: 0.25"
- Withstanding voltage for 1 minute: 500VAC

*Web Code: **NBQ**



Qty.	1	10	100	500
Price	\$1.49	\$1.29	\$1.15	\$0.99

Part No.	Manufacturer Part No.	Shaft Length (L)	Ohms
255477	RV24AF-10-15R1-B52	0.335"	500
255485	RV24AF-10-15R1-B13	0.335"	1k
255493	RV24AF-10-15R1-B23	0.335"	2k
255514	RV24AF-10-15R1-B53	0.335"	5k
255522	RV24AF-10-15R1-B14	0.335"	10k
255531	RV24AF-10-15R1-BF4	0.335"	25k
255549	RV24AF-10-15R1-B54	0.335"	50k
255557	RV24AF-10-15R1-B15	0.335"	100k
255565	RV24AF-10-15R1-BF5	0.335"	250k



2 & 5-Watt Linear Taper Wirewound (±20%)

- Temp. range: -10°C to +70°C
- Non-rotational key



Includes: Mounting hardware

123960

2-Watt (±20%) • Length: 0.825"

*Web Code: **WAR**

- Shaft diameter: 0.25"
- Mounting hole: 0.375" • Base length: 0.25"

Part No.	Cross Ref. No.	Ohms	1	10	100	500
123960	PT1K	1k	\$3.95	\$3.49	\$3.09	\$2.69
123968	PT5K	5k	4.95	4.49	3.95	3.59

5-Watt (±20%)

- Shaft length/diameter: 0.67"/0.23" (6mm)
- Mounting hole: 0.32"
- Maximum panel thickness: 0.1"



Part No.	Cross Ref. No.	Ohms	1	10	100	500
140514	PW5B100	100	\$2.75	\$2.49	\$2.25	\$1.75

Bourns® 2-Watt 10-Turn Wirewound (±5%)

- Insulation resist.: (500VDC) 1000MΩ min.
- Absolute min. resist.: 1Ω or 0.1% maximum
- Operating temp. range: +1°C to +125°C

*Web Code: **JBE**



- 3540S-1 Series: 2W @ 70°C; metal
- 3590S-1 Series: 2W @ 40°C; plastic
- 3540S-1 Series: 2W @ 40°C; metal

Part No.	Mfr. Part No.	Ohms	1	10	50
183548	3540S-1-502L	5k	\$16.95	\$15.49	\$13.95
855818	3590S-2-502L	5k	9.95	8.95	8.25
183521	3540S-1-103	10k	14.49	12.95	11.49
771121	3590S-1-103L	10k	9.95	8.95	8.25
771155	3590S-2-103L	10k	9.95	8.95	8.25
771139	3590S-1-104L	100k	12.95	11.75	10.75

Bourns® 1/4-Watt, 4mm Square SMD, Trim Potentiometers (±10%)

3314 Series Top Adjustment

854330

- Adjustment angle: 210°
- End resistance: 1% or 2Ω max.
- Power rating: 0.25W @ 70°C • Straight slot



Part No.	Product No.	Ohms	1	10	100
854330	3314J-1-502E	5K	\$1.25	\$1.09	\$0.95
854284	3314G-1-103E	10K	1.25	1.09	.95

Part No.	Manufacturer Part No.	Shaft Length (L)	Ohms
255573	RV24AF-10-15R1-B55	0.335"	500k
255582	RV24AF-10-15R1-B16	0.335"	1M
255600	RV24AF-10-15R1-B26	0.335"	2M
264373	RV24AF-10-20K-B52	0.531"	500
264382	RV24AF-10-20K-B13	0.531"	1k
264400	RV24AF-10-20K-B23	0.531"	2k
264402	RV24AF-10-20K-B53	0.531"	5k
264411	RV24AF-10-20K-B14	0.531"	10k
264429	RV24AF-10-20K-B54	0.531"	50k
264437	RV24AF-10-20K-B15	0.531"	100k
264445	RV24AF-10-20K-BF5	0.531"	250k
264462	RV24AF-10-20K-B16	0.531"	1M
264480	RV24AF-10-20K-B26	0.531"	2M
255611	RV24AF-10-40R1-B52	1.32"	500
255629	RV24AF-10-40R1-B13	1.32"	1k
255662	RV24AF-10-40R1-B14	1.32"	10k
255696	RV24AF-10-40R1-B15	1.32"	100k

1/4-Watt Miniature Linear (±20%)

X201 (19/32") Vertical Mount

- 15mm thick • Volt. rating: 350VDC
- Power rating: below 5kΩ - 1/4 watt @ 40°C; 5kΩ & above - 1/4 watt @ 55°C
- Total rotation: 260° ±5°



Cross Ref. Chart

Equivalent to:	
CTS	X201R
Bourns	3355X
PIHER	PT15

Qty.	1	10	100	500
Price	\$0.55	\$0.45	\$0.39	\$0.35

Part No.	Cross Ref. No.	Ohms	Part No.	Cross Ref. No.	Ohms
94693	X201R1K	1k	94714	X201R10K	10k
35503	X201R252B	2.5k	94722	X201R50K	50k
94706	X201R5K	5k	94731	X201R100K	100k

3/4-Watt, 3/4" Rectangular, 15-Turn Cermet Potentiometers Side Adjustment (±10%)

3006P Series Value Equivalents

*Web Code: **FDG**

- Low PC board profile
- Temp. range: -55°C to 125°C
- Absolute min. resist.: 1% or 2Ω
- Contact resist.: 1% or 1Ω max.
- Power rating: 0.75W @ 70°C (400V max.)

Cross Ref. Chart

Equivalent to:	
Allen Bradley	94P
Beckman	89PR
Bourns	3006P
Littlon	6034Y
Meppcopal	8034
Murata	2101P
Spectrol	43P
VRN	961-20
Weston	830P

Qty.	1	10	100	500
Price	\$1.49	\$1.29	\$1.09	\$0.95

Part No.	Cross Ref. No.	Ohms	Part No.	Cross Ref. No.	Ohms
241235	3006P-101	100	241307	3006P-203	20k
241242	3006P-201	200	241314	3006P-253+	25k
41937	3006P-501	500	41911	3006P-503	50k
241252	3006P-501	500	241323	3006P-503	50k
241269	3006P-102+	1k	41849	3006P-104	100k
41865	3006P-202	2k	241332	3006P-104	100k
241278	3006P-202	2k	63001	3006P-204	200k
41890	3006P-502	5k	241350	3006P-204	200k
241286	3006P-502	5k	41953	3006P-504	500k
41822	3006P-103	10k	41806	3006P-105	1M
241294	3006P-103	10k	241374	3006P-105	1M
41873	3006P-203	20k			



1/2-Watt 24mm Linear Taper with SPST Switch (±20%)

- Shaft diameter: 0.25"
- Maximum voltage: 500V
- Terminal type: solder lugs
- Switch rating: 125VAC, 1A
- Rotational angle: 300° (±5°)

*Web Code: **KBR**

Blue Part No. = Limited Quantity Available

Qty.	1	10	100	500
Price	\$1.95	\$1.75	\$1.49	\$1.35

Part No.	Manufacturer Part No.	Shaft Length	Ohms
263759	RV24A01F-10-15R1-B52	0.335"	500
263768	RV24A01F-10-15R1-B13	0.335"	1k
263784	RV24A01F-10-15R1-B5K	0.335"	5k
263792	RV24A01F-10-15R1-B14	0.335"	10k
263805	RV24A01F-10-15R1-BF4	0.335"	25k
263813	RV24A01F-10-15R1-B54	0.335"	50k
263822	RV24A01F-10-15R1-B100K	0.335"	100k
263848	RV24A01F-10-15R1-B55	0.335"	500k

1/2-Watt, 1/4" Round, Cermet Potentiometers (±10%)

3329P Series Value Equivalents

- Sealed to withstand wave soldering and immersion cleaning process
- Terminals: solderable pins
- TO-5 grid
- Top adjustment
- Extended temp. range: -55°C to +150°C

Cross Ref. Chart

Equivalent to:	
Beckman	82M
Bourns	3329P
Meppcopal	8050
MEC	471
Murata	3321P
Spectrol	62-3
VRN	171
Weston	567

Qty.	1	10	100	500
Price	\$1.75	\$1.49	\$1.25	\$0.99

Part No.	Cross Ref. No.	Ohms	Part No.	Cross Ref. No.	Ohms
254465	3329P-101	100	254538	3329P-203	20k
254473	3329P-201	200	95484	3329P-104	100k
95441	3329P-102	1k	254570	3329P-204	200k
95450	3329P-502	5k	254597	3329P-105	1M
96719	3329P-103	10k			



1/4-Watt, 1/4" Square Trim Potentiometers Top Adjustment (±10%)

Bourns 3266W Series Value Equivalents

- 12 turns nominal
- Contact resist. variation: 3% or 3Ω max. (whichever is greater)
- Absolute min. resist.: 1% or 2Ω max. (whichever is greater)
- Power rating: 0.25W @ 70°C (300V max.)
- Insulation resistance: (500VDC) 1,000mΩ min.

*Web Code: **JBQ**

Qty.	1	10	100	500
Price	\$2.49	\$2.25	\$1.95	\$1.75

Part No.	Cross Ref. No.	Ohms	Part No.	Cross Ref. No.	Ohms
254609	3266W-500	50	254677	3266W-103	10k
254617	3266W-101	100	254692	3266W-253	25k
254626	3266W-201	200	254706	3266W-503	50k
254633	3266W-501	500	254714	3266W-104	100k
254642	3266W-102	1k	254722	3266W-204	200k
254651	3266W-202	2k	254730	3266W-504	500k
254669	3266W-502	5k	254749	3266W-105	1M

Pocket Trim Potentiometer Adjustment Tool

- Glass-filled body
- Stainless steel blade



Part No.	Description	Size	1	10	100
153315	Trimmer tool	5.2"L	\$1.75	\$1.49	\$1.25

*For Complete Specs & Additional Product Listings Search www.Jameco.com/More and Enter Web Code Listed Above