

JAMECO ValuePro

Hook-Up Wire – UL1007 (Single Rated) UL1007 & UL1569 (Dual Rated, UL/CSA)

- Applications: Interconnection circuits, wiring of computer and data processing equipment, applications and automotive
- Tinned copper • PVC insulation • Stranded • Sold in 100' rolls

NEW
MARKED IN PINK

*Web Code: JAS



Single Rated (UL1007): -40° to 80°: 300V peak

Dual Rated (UL1007 & UL1569): -40° to 105°C: 600V peak

Appliance Wiring Material (AWM) is UL recognized covering of insulated wire & cable intended for internal wiring of appliances & equipment.

Manufacturer	AWG	Stranding	UL1007	UL1569	Black P/N	Red P/N	White P/N	Green P/N	Yellow P/N	Blue P/N	1	5	10
ValuePro	28	7 x 36	x	x	734611	734603	734610	734606	734605	734614	\$6.95	\$6.49	\$5.95
ValuePro	26	7 x 34	x	x	734511	734503	734510	734506	734505	734514	7.95	7.29	6.49
ValuePro	24	7 x 32	x	x	734411	734403	734410	734406	734405	734414	8.95	7.95	6.95
ValuePro	22	7 x 30	x		126085	126034	126077	310852	310878	310886	6.95	5.95	4.95
ValuePro	22	7 x 30	x	x	734311	734303	734310	734306	734305	734314	9.95	8.95	7.95
ValuePro	20	10 x 30	x		125840	125795	125831+	310894	310915	310922	9.95	8.95	7.95
ValuePro	20	10 x 30	x	x	734211	734203	734210	734206	734205	734214	12.95	11.95	10.95
ValuePro	18	16 x 30	x		125787	125736	125752	310932	310949+	310958	13.95	12.95	11.95
ValuePro	18	16 x 30	x	x	734111	734103	734110	734106	734105	734114	16.95	15.49	13.95
ValuePro	16	26 x 30	x	x	734011	734003	734010	734006	734005	734014	19.95	17.95	15.95

Solid Hook-Up Wire – 22 AWG

*Web Code: PAF

- Temperature range: -55°C to +105°C
- Passes UL VW-1 flame test • MIL-W-16878D type B
- For use with breadboards such as the JE20 series, pg 168



100 Foot		Pricing		1000 Foot		Pricing	
Part No.	Color	1	5	Part No.	Color	1	5
36768	Blue	\$6.95	\$6.29	36776	Blue	\$59.95	\$54.95
36792	Black	6.95	6.29	36805	Black	59.95	54.95
36822	Green	6.95	6.29	36840	Green	59.95	54.95
36856	Red	6.95	6.29	36864	Red	59.95	54.95
36881	White	6.95	6.29	36899	White	59.95	54.95
36920	Yellow	6.95	6.29	36928	Yellow	59.95	54.95

Bus Bar Hook-Up Wire

*Web Code: BBV

- Solid soft drawn annealed bare copper
- Tinned & enameled
- Single conductor
- Sold in 100' rolls
- Approvals: QQ-W-343 type S, Mil-W-3861 type S, ASTM B-33, UL, CAS, OSHA



JAMECO ValuePro

NEW
MARKED IN PINK

Part No.	Mfr.	Gauge	O.D. (in.)	Amps	1	5	10
2098478	ValuePro	24 AWG	0.020	5	\$9.95	\$8.95	\$7.95
734169	Belden	24 AWG	0.020	5	22.95	20.95	18.95
2098486	ValuePro	22 AWG	0.025	7	11.95	10.95	9.95
2098494	ValuePro	20 AWG	0.032	8.5	13.95	12.95	11.95
734165	Belden	20 AWG	0.032	8.5	29.95	27.95	25.95
2098507	ValuePro	18 AWG	0.040	16	16.95	14.95	12.95
2098515	ValuePro	16 AWG	0.061	19	19.95	17.95	15.95

Ⓢ Blue Part No. = Limited Quantity Available

JAMECO ValuePro

1/4 Lb. Magnet Wire

Magnetic wire is perfect for custom winding applications: coils, inductors, transformers, motors, balasts, relays, speakers and timers.

- Solid bare copper conductor • Solderable @ 806 F/430°C
- Temp range: -22° to 266°F, -30° to 130°C
- Polyurethane/Polyamide (nylon) insulation
- Approvals: MIL JW-1177/42, MW 80-C, Class C

NEW
MARKED IN PINK



Part No.	Description	Nom. O.D	Length (ft.)	1	5	25
2098371	16 AWG	.0524"	32	\$5.49	\$4.95	\$4.49
2098380	18 AWG	.0418"	51	5.75	5.25	4.75
2098398	20 AWG	.0334"	81	5.95	5.49	4.95
2098401	22 AWG	.0265"	129	6.49	5.95	5.49
2098419	24 AWG	.0213"	205	6.95	6.49	5.95

JAMECO ValuePro

Twisted Paired Cable – 24 AWG

- PVC insulation
- Use for hook-up wire
- Stranded tinned wire (7 x 32)
- Reduced EMI
- 80°C
- 300 V

*Web Code: EBC



100 Foot Reel		Pricing		1000 Foot Reel		Pricing	
Part No.	Color	1	5	Part No.	Color	1	5
173164	Black/white	\$8.95	\$7.95	173172	Black/white	\$79.95	\$69.95
105912	Grn/white	8.95	7.95	105807	Grn/white	79.95	69.95
173148	Red/white	8.95	7.95	173156	Red/white	79.95	69.95

JAMECO ValuePro

Modular Telephone Cable – 28 AWG

- Color coded conductors
- Flat modular cable • Gray
- 7 x 43 stranded • PVC jacket

*Web Code: LCG

JAMECO EXCLUSIVE



Part No.	Cross Ref. No.	Conductors	Length (ft.)	1	5	10
644666	300-840SL-100	4	100	\$5.95	\$5.49	\$4.95
644674	300-840SL-1000	4	1000	49.95	44.95	39.95
644691	300-860SL-100	6	100	8.95	7.95	6.95
644703	300-860SL-1000	6	1000	69.95	64.95	59.95
644720	300-880SL-100	8	100	9.95	8.95	7.95
644738	300-880SL-1000	8	1000	89.95	84.95	79.95



Composite Data, Audio, Video Security and Control Cable

Two RG6 18 AWG solid bare copper conductors and Two 4-pair UTP 24 AWG solid bare copper conductors

- Gas injected FPR insulation coax cable, polyolefin insulation CAT5e cable and F-R PVC jackets
- Banana Peel™ jacketless cable
- Component nominal outer diameter: 200"



Part No.	Mfr. Part No.	Description	Color	Price
734164	7913S-500	500' reel	Black	\$299.95
234162	7913S-1000+	1000' reel	Black	395.95

Kynar™ Wire-Wrap Wire – 30 AWG

*Web Code: NAC

- Polyvinylidene fluoride insulation
- Silver plated copper (solid conductor)
- Temperature: -40°C to +125°C
- Wire wrap tools, pg 159
- Used for prototyping
- UL 1423
- Passes UL VW-1 flame test
- See pg 18 for sockets



100 Foot Reel		Pricing		1000 Foot Reel		Pricing	
Part No.	Color	1	5	Part No.	Color	1	5
22542	Blue	\$6.95	\$6.29	22551	Blue	\$49.95	\$44.95
22577	Black	6.95	6.29	22585	Black	49.95	44.95
22631	Red	6.95	6.29	22649	Red	49.95	44.95
22665	White	6.95	6.29	22673	White	49.95	44.95
22606	Green	6.95	6.29	22614	Green	49.95	44.95
22700	Yellow	6.95	6.29	22702	Yellow	49.95	44.95



Bonded-Pair Cable Prep Tool

The bonded-pair cable preparation tool makes it faster and easier to prepare cables for connector termination. Ideal for use with Belden's IBDN's DataTwist® 350 bonded pair cables, providing special features that help separate twisted pairs. It can be used to prepare any unbonded-pair cable for installation.



Part No.	Mfr. Part No.	Description	1	5
1941241	1797B009	Bonded-pair cable prep tool	\$10.95	\$9.95

*For Complete Specs & Additional Product Listings Search www.Jameco.com/More and Enter Web Code Listed Above