

Cat 5e/6 Network Crossover Cables

- Connect 2 PCs without a hub
- 24AWG (7 x 43) stranded
- Strain relief RJ45 connectors
- 4-pair • 8P8C • UTP

*Web Code: CAE



Part No.	*Mfr.	Length	Description	1	10	100
681109	◆	3 ft.	Cat 5e gray	\$2.75	\$2.49	\$2.25
302041	JVP	7 ft.	Cat 5e gray	3.75	3.35	2.95
685812	◆	7 ft.	Cat 5e yellow	3.75	3.35	2.95
169261	JVP	10 ft.	Cat 5e gray	6.95	6.25	5.65
203781	JVP	12 ft.	Cat 5e black	2.95	2.65	2.35
679762	◆	3 ft.	Cat 6 gray	1.49	1.35	1.19
681096	◆	7 ft.	Cat 6 gray	3.75	3.35	2.95


Modular Telephone/Printer Sharing Cables (Gray)

- RJ11 – 6P4C for telephone or network
- RJ11 – 6P6C for telephone or printer sharing
- RJ45 – 8P8C for telephone or modem-dial-up use

*Web Code: EBF



- Style 1 – Reverse wiring for telephone systems
- Style 2 – Straight wiring for networking/printer sharing



Part No.	Conn. Style	Type	Length	Pricing		
				1	10	100
196227	1	RJ11-6P4C	7ft.	\$1.75	\$1.59	\$1.39
115554	2	RJ11-6P4C	7ft.	1.75	1.59	1.39
115545	1	RJ11-6P4C	25ft.	2.95	2.65	2.35
201232	2	RJ11-6P4C	35ft.	1.75	1.59	1.39
115588	1	RJ11-6P6C	7ft.	1.49	1.35	1.19
115617	2	RJ11-6P6C	7ft.	1.95	1.75	1.59
355653	2	RJ11-6P6C	14ft.	.75	.69	.55
115677	2	RJ45-8P8C	7ft.	1.95	1.75	1.59

Keystone-Type RJ11 & RJ45 Jacks

Modular Punchdown Type

- CAT 5e classification
- Punchdown type wiring connections with color coding
- Size: 0.57"W x 1.23"D x 0.63"H

*Web Code: MBV



Part No.	*Mfr.	Description	Color	1	10	50
213517	◆	6P6C (RJ11)	White	\$2.75	\$2.49	\$2.25
615048	GCE	8P8C (RJ45)	Black	4.75	4.25	3.79
195630	◆	8P8C (RJ45)	Black	2.25	1.95	1.75
212951	◆	8P8C (RJ45)	Blue	2.25	1.95	1.75
212944	◆	8P8C (RJ45)	White	2.95	2.65	2.39
195637	◆	8P8C (RJ45)	Ivory	1.95	1.75	1.69
636130	FST	8P8C (RJ45)	Almond	2.75	2.49	2.25
615144	GCE	Tool-less	Ivory	2.49	2.25	1.95

Blue Part No. = Limited Quantity Available

RJ45-Plug Color Caps (Boots)

- Round strain relief
- Order in multiples of 10

*Web Code: JBG



Part No.	Color	10	100	500	1000
204410	Black	\$.19	\$.17	\$.15	\$.11
204353	Gray	.19	.17	.15	.11
204362	Blue	.19	.17	.15	.11

Cisco Wall Jack DSL Filter

- Filters out DSL
- Dimension: 4.7" x 3.0"

Part No.	Description	Color	1	10
15077	6P4C (RJ11)	White	\$2.95	\$2.65

Modular Plugs

*Web Code: FBB

P = No. of positions
C = No. of contacts



Part No.	Description	Size (L" x W" x H")	1	10	100	1000
103491	4P4C (RJ14) handset	.485 x .30 x .26	*.13	\$.12	\$.09	
79290	6P4C (RJ11)	.487 x .38 x .26	*.14	.13	.10	
79273	6P6C (RJ11)	.487 x .38 x .26	.25	.23	.20	.18
79281	8P8C (RJ45) (for stranded wire)	.845 x .46 x .31	.47	.43	.38	.29
119343	8P8C (RJ45) unshielded (for solid wire)	.845 x .46 x .31	.45	.39	.35	.29
116611	8P8C (RJ45) shielded	.866 x .46 x .33	1.09	.99	.89	.79
204231	8P8C (RJ45) shielded (for STP stranded wire)	.484 x .455 x .285	.75	.69	.59	.49
116602	8P8C (RJ45) shielded (for solid wire)	.845 x .46 x .31	.99	.89	.79	.59
180646	10P10C (RJ50) for stranded wire	.849 x .46 x .31	.39	.35	.29	.25
524411	8P8C, unshielded flat oval solid	.850 x .464 x .314	.55	.49	.45	.39

Modular Jacks

*Web Code: NEL



Part No.	*Mfr.	Description	Panel Mount	Size (L" x W" x H")	1	10	100	1000
115128	JVP	4P4C (RJ14) handset side entry, center latch	No	.51 x .40 x .57	\$4.45	\$3.95	\$3.55	\$2.99
852836	AMP	4P4C (RJ14) side entry, center latch, flangeless	No	.82 x .44 x .63	.75	.69	.59	.49
199620	JVP	4P4C (handset) side entry, center latch	Yes	.51 x .55 x .57	.35	.29	.25	.19
105945	JVP	6P4C (RJ11) side entry, center latch, top flange	Yes	.48 x .48 x .71	*.19	.17	.15	
524277	AMP	6P6C (RJ11) top entry, center latch, flangeless	No	.53 x .64 x .63	.65	.59	.55	.49
2077781	JVP	6P4C (RJ11) side entry, center latch	No	.72 x .51 x .45	.45	.39	.35	.29
2077221	◆	6P6C (RJ11) side entry, front latch, PCB ground	Yes	.73 x .55 x .58	.69	.59	.49	.45
115837	JVP	6P6C (RJ11) side entry, center latch	Yes	.51 x .48 x .57	.85	.75	.65	.59
151766	JVP	6P4C (RJ11) side entry, center latch	Yes	.80 x .52 x .59	.65	.59	.55	.49
852449	AMP	6P6C (RJ25) side entry, center latch, SMT, low profile	Yes	.72 x .63 x .50	.89	.79	.69	.59
204178	JVP	6P6C (RJ11) dual entry, center latch	Yes	.62 x 1.1 x .60	1.35	1.19	.99	.79
124039	JVP	6P6C (RJ11) top entry, 6' leads, panel mount	Yes	.54 x .59 x .72	1.25	1.09	.99	.89
800315	MOL	6P6C (RJ11) side entry, center latch, unshielded, ganged	No	.92 x .85 x .52	2.95	2.65	2.39	2.15
115844	JVP	8P8C (RJ45) side entry, center latch	No	.53 x .60 x .57	.69	.59	.55	.49
2078240	◆	8P8C (RJ45) side entry, center latch	Yes	.81 x .60 x .59	.69	.59	.49	.45
203449	JVP	8P8C (RJ45) side entry, center latch, shielded	No	.84 x .63 x .53	.95	.85	.75	.65
204215	JVP	8P8C (RJ11) side entry, center latch, low profile	No	.81 x .60 x .50	.95	.85	.75	.65
2078258	◆	8P8C (RJ45) side entry, center latch, low profile	No	.71 x .60 x .46	.49	.45	.39	.35
524461	AMP	8P8C (RJ45) side entry, front latch, low profile	No	.72 x .61 x .50	.55	.49	.45	.39
524251	AMP	8P8C (RJ45) side entry, center latch	Yes	.82 x .61 x .64	.65	.59	.49	.45
2078266	◆	8P8C (RJ45) side entry, front latch, low profile	No	.68 x .59 x .49	.49	.45	.39	.35
1537416	KYC	8P8C (RJ45) side entry, front latch, low profile	Yes	.72 x .60 x .50	.59	.45	.35	.29
524488	AMP	8P8C (RJ45) top entry, top latch	No	.66 x .62 x .63	.65	.59	.55	.49
2077790	◆	8P8C (RJ45) top entry, bottom latch	Yes	.64 x .61 x .62	.59	.55	.49	.45
889129	AMP	6P6C (RJ25) top entry, center latch SMT	No	.55 x .53 x .50	1.65	1.49	1.35	1.19

RS-232-to-RJ11/RJ45 Modular Jack Adapters

Simplify networking applications when changing your RS-232 port to an RJ11 or RJ45 modular jack. Comes with all necessary hardware and wiring.

*Web Code: RDR



Part No.	*Mfr.	Description	1	10	100
66181	JVP	DB9 M to RJ11 (6P6C)	\$2.49	\$2.25	\$1.95
204265	JVP	DB9 M to RJ11 (6P6C)	.75	.69	.59
66191	JVP	DB9 M to RJ45 (8P8C)	2.75	2.49	2.25
614977	GCE	DB9 M to RJ45 (8P8C)	2.75	2.49	2.25
614985	GCE	DB9 F to RJ11 (4P4C)	1.95	1.75	1.59
114738	JVP	DB9 F to RJ11 (6P4C)	2.35	2.09	1.89
66203	JVP	DB9 F to RJ11 (6P6C)	2.75	2.49	2.25

Part No.	*Mfr.	Description	1	10	100
66212	JVP	DB9 F to RJ45 (8P8C)	\$2.95	\$2.65	\$2.39
615005	GCE	DB9 F to RJ45 (8P8C)	2.45	2.19	1.95
66229	JVP	DB25 M to RJ11 (6P6C)	2.75	2.49	2.25
2099681	JVP	DB15 F to RJ-11 (6P6C)	2.49	2.25	1.95
66237	JVP	DB25 M to RJ45 (8P8C)	1.85	1.69	1.49
615021	GCE	DB25 M to RJ45 (8P8C)	2.75	2.49	2.25
204273	JVP	DB25F - RJ11 (6P4C)	.65	.59	.55
66254	JVP	DB25 F to RJ45 (8P8C)	1.85	1.69	1.49

EZ-RJ45 Category 5 & 6 Modular Plugs

Strip the wire and insert into the plug & pull out the wire on the other side. This ensures correct conductor order and uniformity in crimping. No wire bar and no wasted cable.

Part No.	Mfr.	Part No.	Description	1	10	100	1000
158115		300568EZ	8P8C CAT5 EZ-Plug	\$1.65	\$1.49	\$1.35	\$1.19
2099278		300668EZ	8P8C CAT6 EZ-Plug	1.75	1.59	1.45	1.29

NEW MARKED IN PINK

* AMP = AMP | FST = FutureSmart | GCE = GC Electronics | JVP = Jameco ValuePro | KYC = Kyccon | MOL = Molex | ◆ Manufacturer Varies

*For Complete Specs & Additional Product Listings Search www.Jameco.com/More and Enter Web Code Listed Above