

For complete specifications visit www.Jameco.com

General Purpose Power Relays

Part No.	Mfr.	Product No.	Contact Form	Rating	Contact Rating	Coil Resis.	Contact Type	1	10	50
454571	Omron	G7L-1A-TUB-CB-DC24	SPST-NO	24VDC @ 79mA	25A, 220VAC	303Ω	.250" quick connect	\$7.95	\$6.95	\$5.95
611928	P&B	T9AP1D52-48-03	SPST-NO	48VDC @ 21mA	30A, 240VAC	2304Ω	Quick connect: .187" for coil/.250" for contacts	3.95	3.69	3.39
137358	ValuePro	953-1C12DM-R [Ⓜ]	SPDT	12VDC @ 77mA	20A, 240VAC/28VDC	155Ω	Quick connect: .110" for coil/.250" for contacts	2.49	2.19	1.95
552462	P&B	PRD-7AG0-120	DPST-NO	120VAC @ 85mA	30A, 240VAC	290Ω	Screw: #8-32 for main; #6-32 for contacts	29.95	27.49	25.95
183791	Master	GH-2C-12D	DPDT	12VDC @ 170mA	30A, 240VAC	70Ω	Screw down terminals	12.95	11.49	10.95
551881	P&B	PRD-11AG0-120	DPDT	240VAC @ 43mA	30A, 240VAC	1200Ω	Screw: #8-32 for main; #6-32 for contacts	44.95	39.95	34.95



General Purpose Blade and Octal Relays

- UL/CSA approved
- Industry standard termination for quick installation
- Wide range of coil voltages for industrial and commercial applications

*Web Code: ACF



Part No.	*Mfr.	Product No.	Fig.	Contact Form	Coil Voltage	Contact Rating	Coil Resis. (Ω)	Coil Current (mA)	Mating Socket*		Pricing		
									Standard	DIN Rail	1	10	50
2096122	Magnecraft	781XAXM4L-12D [Ⓜ]	1	SPDT [†]	12VDC	20A @ 1200VAC/28VDC	188	100	—	—	\$5.95	\$5.49	\$4.95
282440	P&B	KRPA-5DG-24	2	SPDT	24VDC	10A @ 240VAC	472	51	282132	282159	17.95	16.95	15.95
2119996	Omron	G2R-1-E-ASI [†]	3	SPDT	24VDC	16A @ 250VAC; 16A @ 30VDC	1100	21.8	—	—	4.95	4.49	3.95
2096131	Magnecraft	781XAXM4L-24A [Ⓜ]	1	SPDT [†]	24VAC	20A @ 120VAC/28VDC	180	100	—	—	5.95	5.49	4.95
498671	P&B	KUEP-11D15-12	4	DPDT	12VDC	3A @ 150VDC; 10A @ 240VAC	80	150	282124	282175	6.95	6.29	5.75
2093079	Omron	LY2F-DC12 [Ⓜ]	1	DPDT	12VDC	10A @ 24VDC; 10A @ 110VAC	160	75	P108	175531	5.95	5.39	4.79
139766	Rayex	MK2P-I	5	DPDT	12VDC	10A @ 28VDC; 10A @ 240VAC	120	10	141145	141145	6.95	6.29	5.75
282378	P&B	KRPA-11DG-12 [Ⓜ]	2	DPDT ^G	12VDC	10A @ 240VAC	120	100	282132	282159	11.95	10.95	9.95
172719	ValuePro	LB2-12DS-R [Ⓜ]	1	DPDT	12VDC	12A @ 30VDC; 12A @ 240VAC	160	75	175531	282191	5.95	5.49	4.95
2095875	Magnecraft	782XBXM4L-12D [Ⓜ]	3	DPDT [†]	12VDC	12A @ 28VDC; 15A @ 120VAC	160	100	—	—	7.95	7.25	6.49
282255	P&B	K10P-11D15-12 [Ⓜ]	6	DPDT	12VDC	15A @ 30VDC; 15A @ 120VAC	160	75	282191	282191	7.95	7.29	6.49
282386	P&B	KRPA-11DG-24 [Ⓜ]	2	DPDT ^G	24VDC	10A @ 240VAC	472	51	282132	282159	11.95	10.95	9.95
2095867	Magnecraft	782XBXM4L-24D [Ⓜ]	3	DPDT [†]	24VDC	12A @ 28VDC; 15A @ 120VAC	650	100	—	—	7.95	7.25	6.49
175565	ValuePro	LB2-24DS-R [Ⓜ]	1	DPDT	24VDC	12A @ 30VDC; 12A @ 240VAC	650	37	175531	282191	5.95	5.49	4.95
282263	P&B	K10P-11D15-24 [Ⓜ]	6	DPDT	24VDC	15A @ 30VDC; 15A @ 120VAC	650	37	282191	282191	7.95	7.29	6.49
301073	P&B	KRPA-11DG-110 [Ⓜ]	2	DPDT ^G	110VDC	10A @ 240VAC	10,000	11.5	282132	282159	10.95	9.95	9.49
175573	ValuePro	LB2-110AS [Ⓜ]	1	DPDT ^G	110VAC	12A @ 30VDC; 12A @ 240VAC	3,900	28	175531	282191	6.95	6.29	5.49
139740	Beta	BTAG-2C-J-CW-120VAC [Ⓜ]	5	DPDT	120VAC	10A @ 28VDC; 10A @ 240VAC	1,700	122	141145	141145	6.95	6.29	5.49
2095859	Magnecraft	782XBXM4L120A [Ⓜ]	3	DPDT [†]	120VAC	12A @ 28VDC; 15A @ 120VAC	4,430	100	—	—	8.95	7.95	6.95
282247	P&B	K10P-11A15-120 [Ⓜ]	6	DPDT	120VAC	15A @ 30VDC; 15A @ 120VAC	3,900	11	282191	282191	7.95	7.29	6.49
282503	P&B	KUP-14D15-24	7	3PDT	24VDC	10A @ 28VDC or 240VAC	472	51	282124	282175	9.95	8.95	8.49
301217	P&B	KRPA-14DN-24	2	3PDT	24VDC	10A @ 28VDC; 6A @ 250VAC	472	51	282141	282167	12.95	11.95	10.95
301170	P&B	KRPA-14AY-120 [Ⓜ]	2	3PDT ^Y	120VAC	5A @ 120VAC; 3A @ 240VAC	2,250	8.75	282141	282167	15.95	14.95	13.95
282301	P&B	KHAU-17D11-12 [Ⓜ]	8	4PDT	12VDC	3A @ 120VAC/28VDC (max)	160	100	496958	282183	6.95	6.29	5.75
291507	ValuePro	LB4H-120-R [Ⓜ]	1	4PDT	12VDC	5A @ 30VDC; 5A @ 240VAC	160	75	175557	175557	4.95	4.49	3.95
2095891	Magnecraft	7782XDX2M4L-12D [Ⓜ]	3	4PDT [†]	12VDC	8A @ 28VDC; 10A @ 120VAC	160	100	—	—	7.95	7.25	6.49
175602	ValuePro	LB4H-24DS-R [Ⓜ]	1	4PDT	24VDC	5A @ 30VDC; 5A @ 240VAC	650	37	175557	175557	4.95	4.49	3.95
282319	P&B	KHAU-17D12-24 [Ⓜ]	8	4PDT	24VDC	5A @ 120VAC/28VDC (max)	650	52	496958	282183	6.95	6.29	5.75
2095939	Magnecraft	782XDX2M4L-24D [Ⓜ]	3	4PDT	24VDC	8A @ 28VDC; 10A @ 120VAC	650	100	—	—	7.95	7.25	6.49
282280	P&B	KHAU-17A11-24 [Ⓜ]	8	4PDT	24VAC	3A @ 120VAC/28VDC (max)	160	52	496958	282183	6.95	6.29	5.49
2095921	Magnecraft	782XDX2M4L-24A [Ⓜ]	3	4PDT	24VAC	8A @ 28VDC; 10A @ 120VAC	180	100	—	—	9.95	8.95	7.95
175611	ValuePro	LB4H-110AS-R [Ⓜ]	1	4PDT ^G	110VAC	5A @ 30VDC; 5A @ 240VAC	3,900	28	175557	175557	4.95	4.49	3.95
2095912	Magnecraft	782XDX2M4L-120A [Ⓜ]	3	4PDT	120VAC	8A @ 28VDC; 10A @ 120VAC	4,430	100	—	—	7.49	6.75	5.95

* For sockets see below † PCB G = Silver-cadmium oxide, no lamp Y = Silver contacts, no indicator lamp 1 = Push to test button, bi-polar LED status lamp, ID write-on label, flag indicator
 Ⓜ Blue Part No. = Limited Quantity Available

Blade and Octal Relay Sockets

Part No.	Mfr.	Product No.	Relay Series	Pins	Contact Form	Type	1	10	50
141145	Beta	PF-083A	BTA1	8	DPDT	Combo [†]	\$3.95	\$3.69	\$3.39
175531	ValuePro	27E895 [Ⓜ]	K10	8	DPDT	Combo [†]	3.95	3.69	3.39
282191	P&B	27E895 [Ⓜ]	K10	8	DPDT	DIN Rail	4.95	4.79	4.59
282132	P&B	27E122 [Ⓜ]	KRP/KRPA	8	DPDT	Standard	4.95	4.69	4.39
282167	P&B	27E892 [Ⓜ]	KRP/KRPA	11	3PDT	DIN Rail	9.95	8.95	7.95
282175	P&B	27E121 [Ⓜ]	KUP/KUEP/KUMP	11	3PDT	Din Rail	10.95	9.95	8.95
282141	P&B	27E123 [Ⓜ]	KRP/KRPA	11	3PDT	Standard	6.95	6.29	5.59
282124	P&B	27E121 [Ⓜ]	KUP/KUEP/KUMP	11	3PDT	Standard	6.95	6.29	5.59
175557	ValuePro	27E894 [Ⓜ]	KHUA	14	4PDT	DIN Rail	3.49	3.19	2.79
282183	P&B	27E894 [Ⓜ]	KHA/KHS/PT	14	4PDT	DIN Rail	8.95	7.95	7.29
496958	P&B	27E166 [Ⓜ]	KHA/KHUA	14	4PDT	Standard	11.95	10.95	9.95

*Web Code: TEM



† Combo: DIN Rail or Screw Terminal

* For Complete Specs & Additional Product Listings Search www.Jameco.com/More and Enter Web Code Listed Above

