

DC Brushless Tubeaxial Fans & Blowers

3 LEVELS OF SAVINGS
NAME BRANDS HOUSE BRANDS FACTORY OVERRUN

Call for additional OEM PRICING - we carry major manufacturers.

DC Brushless Tubeaxial Fans & Blowers (Continued)



* 12V Web Code: LBZ



1585291

1950446

mm to Inches Conversion Chart

125006

114682

mm	6.8	10	15	20	25	28	30	32	35	38	40	45	51	60	76	80	92	95	97	120	127	150	172
Inches	0.27	0.40	0.60	0.80	1.00	1.10	1.18	1.26	1.40	1.50	1.60	1.80	2.00	2.36	2.99	3.15	3.63	3.74	3.82	4.69	5.00	5.90	6.77

Part No.	Manufacturer	Mfr. Part No.	Voltage (VDC)	Size mm (W x H x D)	Air Flow (CFM)	Bearing	Current (mA)	Power (Watts)	Agency Approvals	Noise (dBA)	Connection (Leads)	Pricing			
												1	10	50	100
1950526	Sunon	KD1204PFS3H	12	40 x 40 x 10	4.2	Sleeve	60	0.7	UL/TUV	22	12"	\$5.95	\$5.35	\$4.79	\$4.29
2095314	Adda	AD0412LX-G70	12	40 x 40 x 10	4.7	Hypro	70	0.84	UL/CUL/TUV/CE	14	12"	6.95	6.25	5.59	4.95
210797	Sunon	KD1204PFV3	12	40 x 40 x 10	4.9	Vapo	60	0.6	UL/CUL/TUV/CE	24	12"	6.95	6.25	5.59	4.95
279611	Toyo	T401012VH	12	40 x 40 x 10	5.8	Ball	90	1.1	UL/CUL/TUV/CE	33.5	12"	4.95	4.49	3.95	3.59
1585469	Y.S. Tech	FD1240107B-2N	12	40 x 40 x 10	6.6	Ball	90	1.08	UL/CUL/TUV	29	6"	5.95	4.95	4.49	3.95
1928054	Adda	AD0412HB-G70	12	40 x 40 x 10	6.7	Ball	100	1.2	UL/CUL/TUV/CE	25	2.5" w/conn	5.95	5.35	4.79	4.29
2100380	Adda	AD0412HX-G71-LF	12	40 x 40 x 10	6.7	Hypro	100	1.2	UL/CUL/TUV/CE	25	10" 2	7.95	6.95	6.25	5.59
290010	Adda	AD0412HB-G70	12	40 x 40 x 10	6.7	Ball	100	1.2	UL/CUL/TUV/CE	25	10" w/conn	9.95	8.95	7.95	6.95
212717	Sunon	KDE1204PFV2.11.MS.A.GN	12	40 x 40 x 10	7.0	Vapo	80	1.0	UL/CUL/TUV/CE/DE	27	12"	6.95	6.25	5.59	4.95
1950139	Sunon	KDE1204PFS2-11	12	40 x 40 x 10	7.0	Sleeve	92	1.1	UL/CUL/TUV/CE	27	12"	6.95	6.25	5.59	4.95
2081924	Sunon	KDE1204PFB2	12	40 x 40 x 10	7.5	Ball	90	1.1	UL/CUL/TUV/CE	30	12"	8.95	7.95	6.95	5.95
189691	Sunon	KD1204PFS1-11.GN	12	40 x 40 x 10	8.0	Sleeve	60	0.7	UL/CUL/TUV/CE	30	12"	7.95	7.19	6.49	5.79
212725	Sunon	KDE1204PFV1	12	40 x 40 x 10	8.3	Vapo	110	1.4	UL/CUL/TUV/CE/DE	34.4	12"	6.95	6.25	5.59	4.95
1708473	Sunon	KDE1204PFVX11.MS.A	12	40 x 40 x 10	9.5	Vapo	150	1.8	UL/CUL/TUV	39	12"	6.95	6.25	5.59	4.95
136178	Adda	AD0412MS-C70	12	40 x 40 x 20	5.0	Sleeve	110	1.32	UL/CSA	23	9"	5.95	5.39	4.79	4.29
1809856	Sunon	GM1204PKV3-A	12	40 x 40 x 20	6.3	Vapo	50	0.6	UL/CSA/TUV	18	12"	6.95	6.25	5.59	4.95
195899	Sunon	KDE1204PKS2	12	40 x 40 x 20	6.5	Sleeve	70	0.9	UL/CSA/TUV	25.5	12"	5.95	5.39	4.79	4.29
279620	Toyo	T402012H	12	40 x 40 x 20	6.7	Ball	70	0.84	UL/CUL/TUV/CE	26.2	12"	6.95	6.25	5.59	4.95
210065	Sunon	KD1204PKB2(2)GN	12	40 x 40 x 20	7.7	Dual ball	62	0.7	UL/CSA/TUV	22	12"	6.95	6.25	5.59	4.95
687754	Sunon	KDE1204PKSX-8	12	40 x 40 x 20	9.5	Sleeve	90	1.1	UL/CSA	28	11"	6.95	6.25	5.59	4.95
2099518	Adda	AD0412UB-C51	12	40 x 40 x 20	9.9	Ball	180	2.16	UL/CUL/TUV/CE	36.1	11"	7.95	6.95	6.25	5.59
2082100	Sunon	KDE1204PKBX-8	12	40 x 40 x 20	10	Ball	90	1.1	UL/TUV/CE	29.4	4"	7.95	6.95	6.25	5.59
2099841	Delta	EFB0412VHD-R00	12	40 x 40 x 20	10.1	Dual ball	120	1.4	UL/CSA/VDE/CE	32.5	12" 2	9.95	8.95	7.95	6.95
1928118	Adda	AD4012HB-C50	12	40 x 40 x 20	10.5	Ball	100	1.2	UL/CUL/TUV/CE	31.9	12"	9.95	8.95	7.95	6.95
1585291	Sunon	GM1204PKVX-A	12	40 x 40 x 20	10.8	Vapo	130	1.6	UL/CUL/CSA	27.5	5"	6.95	6.25	5.59	4.95
2082089	Sanyo Denki	109P0412H302	12	40 x 40 x 28	11.3	Ball	195	2.3	UL/CSA/TUV	37	3.75"	6.95	6.25	5.59	4.95
2095162	Sunon	PMD1204PQBX-A(2)F	12	40 x 40 x 28	23.5	Ball	570	6.8	UL/CE	51.5	3" w/conn 1	12.95	11.49	9.95	8.95
1951246	Sunon	PMD1204PQBX-A(2)	12	40 x 40 x 28	23.5	Ball	570	6.8	UL/CE	51.5	12"	14.95	13.49	11.95	10.95
1951254	Sunon	PMD1204PQBX-A(2)F	12	40 x 40 x 28	23.5	Ball	570	6.8	UL/CE	51.5	12" 1	14.95	13.49	11.95	10.95
1950753	Comair Rotron	CR4512MB-G70	12	45 x 45 x 10	6.9	Ball	70	0.8	UL/CUL/CE/TUV	21.6	12"	6.95	6.25	5.59	4.95
2095322	Adda	AD4512HX-G70	12	45 x 45 x 10	9.1	Hypro	90	1.08	UL/CUL/TUV/CE	27.4	11"	7.95	6.95	6.25	5.59
2100371	Adda	AD0512LX-G70LF	12	51 x 51 x 10	9.0	Hypro	60	0.72	UL/CSA/TUV/CE	20	11"	5.95	5.35	4.79	4.29
1918809	Jamicon	KF0510B1M	12	51 x 51 x 10	9.27	Ball	80	0.8	UL/CUL/TUV/CE	26.6	10.5"	5.95	5.35	4.79	4.29
2095331	Adda	AD0512HX-G70	12	51 x 51 x 10	10.5	Hypro	120	1.4	UL/CUL/TUV/CE	24	11"	5.95	5.35	4.79	4.29
2095349	Adda	AD0512MB-G76	12	51 x 51 x 10	10.5	Ball	120	1.4	UL/CUL/TUV/CE	24	11" 1	7.95	6.95	6.25	5.59
1950446	Sunon	KD1205PFB1(2)H	12	51 x 51 x 10	11.4	Ball	130	1.6	UL/TUV	34.7	12"	7.95	6.95	6.25	5.59
2100419	Adda	AD0512HB-G70-LF	12	51 x 51 x 10	11.8	Ball	90	1.08	UL/CSA/TUV/CE	27	11"	8.95	7.95	6.95	6.25
125006	Nidec	A33999-16 71	12	51 x 51 x 15	4.0	Ball	170	2.04	UL/CE	46	11"	8.95	7.95	6.95	6.25
139601	Adda	AD0512HS-D71	12	51 x 51 x 15	12	Sleeve	100	1.2	UL/CSA/CE	29	5"	6.95	6.25	5.59	4.95
2099534	Adda	AD5012MX-D71	12	51 x 51 x 15	12.6	Hypro	100	1.2	UL/CUL/TUV/CE	29	5.5"	7.95	6.95	6.25	5.59
1809813	Sunon	GM1205PHV1-AR	12	51 x 51 x 15	17	Vapo	130	1.5	UL/CUL/TUV/CE	33	12" 2	7.95	6.95	6.25	5.59
2095357	Adda	AD0612HB-G70	12	60 x 60 x 10	14.5	Ball	150	1.8	UL/CUL/TUV/CE	32	11"	9.95	8.95	7.95	6.95
1946025	Evercool	EC6010M12CA	12	60 x 60 x 10	15.5	Ball	160	1.9	UL/CE/TUV	30	9" 1	8.95	7.95	6.95	6.25
2115522	Everflow	R126010DU	12	60 x 60 x 10	19.41	Ball	250	3	UL/CE/TUV	37	9" w/conn 1	8.95	7.95	6.95	6.25
1928046	Adda	AD0612LX-D70GL	12	60 x 60 x 15	12	Hypro	90	1.08	UL/CUL/TUV/CE	27.2	8"	5.95	5.59	4.95	4.49
2078178	Delta	AFB0612MB	12	60 x 60 x 15	13.4	Ball	80	0.96	UL/CUL/TUV/CE	29	12"	7.95	6.95	6.25	5.59
195945	Adda	AD612MS-D71GL	12	60 x 60 x 15	14.2	Sleeve	110	1.32	UL/CSA/TUV/CE	28.8	6"	8.95	7.95	6.95	6.25
249069	Jamicon	JF0615B1H-000-243	12	60 x 60 x 15	15.7	Ball	170	2.04	UL/CUL/TUV/CE	34	12"	9.95	8.95	7.95	6.95
2121308	Adda	AD0612HB-D70GL	12	60 x 60 x 15	16.6	Ball	130	1.56	UL/CSA/TUV/CE	32.4	11" w/conn	9.95	8.95	7.95	6.95
687771	Sunon	KDE1206PHS1	12	60 x 60 x 15	21	Sleeve	150	1.8	UL/CSA/TUV/CE	36	11"	8.95	7.95	6.95	6.25
1585400	Sunon	KDE1206PHB1	12	60 x 60 x 15	21	Ball	150	1.8	UL/CSA/CE	37.5	11"	10.95	9.95	8.95	7.95
144161	Adda	AD0612LB-C70GL	12	60 x 60 x 20	12.6	Ball	80	1.0	UL/CSA/TUV	22.7	6"	9.95	8.95	7.95	6.95
1928126	Adda	AD0612HB-C70GL	12	60 x 60 x 20	16.3	Ball	160	1.92	UL/CSA/TUV/CE	31	12"	9.95	8.95	7.95	6.95
189595	Sunon	KD1206PKS2	12	60 x 60 x 20	16.5	Sleeve	150	1.8	UL/CSA/TUV/CE	31	12"	7.95	6.95	6.25	5.59
119635	Delta/Fonsan	DFD0612H	12	60 x 60 x 20	17.7	Ball	110	1.3	UL/CE/CSA/VDE	30	12"	6.95	6.25	5.59	4.95
1951182	Sunon	KDE1206PKV2.MS.A.GN	12	60 x 60 x 20	18.5	Vapo	90	0.8	UL/CE	27.5	11"	7.95	6.95	6.25	5.59
2120073	Sunon	KD1206PKB2(2)F.GN	12	60 x 60 x 20	19	Dual ball	88	1.1	UL/CUL/TUV	29	12" 1	7.95	6.95	6.25	5.59
114682	Delta	AFB0612VHD	12	60 x 60 x 20	30	Ball	270	2.4	UL/CE/CSA/VDE	39.5	12"	8.95	7.95	6.95	6.25
2120081	Sunon	KDE1206PTV3.13.MS.AF.GN	12	60 x 60 x 25	16	Vapo	110	0.7	UL/CSA/TUV	21	12" 1	7.95	6.95	6.25	5.59
1810101	Japan Servo	TUDC12Z4F-022	12	60 x 60 x 25	19	Ball	140	1.8	UL/CSA/TUV	32	5" w/conn	5.95	5.39	4.79	4.29
2095197	Delta	DFB0612H	12	60 x 60 x 25	19.4	Ball	120	1.4	UL/CE/CSA/VDE	30	12"	7.95	6.95	6.25	5.59

1 3 leads; speed sensor 2 3 leads; locked rotor protection (These functions are optional, if needed) † Blower Blue Part No. = Limited Quantity Available Fans continued on next page

RoHS compliant product + This product is available in both RoHS and non-RoHS versions. Add an "R" before part number for RoHS version. Details on page 197.