

DC Brushless Tubeaxial Fans, Blowers, Power Cords, Guards & Filters

Call for additional OEM PRICING – we carry major manufacturers.



153411



212661

DC Brushless Tubeaxial Fans & Blowers (Continued)

* 24V Web Code: QEF



* 48V Web Code: MAJ



1952960



1952775

Part No.	Manufacturer	Mfr. Part No.	Voltage (VDC)	Size mm (W x H x D)	Air Flow (CFM)	Bearing	Current (mA)	Power (Watts)	Agency Approvals	Noise (dBA)	Connection (Leads)	Pricing			
												1	10	50	100
1928302	Adda	AD0924US-A71GL	24	92 x 92 x 25	57.8	Sleeve	210	5.04	UL/CUL/TUV/CE	38.6	12"	\$10.95	\$9.95	\$8.95	\$7.95
104890	EBM Pabst	3314/12	24	92 x 92 x 32	47.1	Ball	140	3.4	UL/CE/TUV	37	12" ¹	11.95	10.95	9.95	8.95
1951465	Delta	FFB0924VHE	24	92 x 92 x 38	85	Ball	280	6.7	UL/CSA/VDE/CE	47	12"	12.95	11.49	9.95	8.95
2115557	Sunon	KD2412PTB3-6A.GN	24	120 x 120 x 25	69	Ball	120	2.9	UL/CUL/TUV/CE	35.5	12"	12.95	11.49	9.95	8.95
1809881	Sunon	KD2412PTB1-6A	24	120 x 120 x 25	90	Ball	220	5.3	UL/CUL/TUV/CE	44.5	12"	13.95	12.49	10.95	9.95
1951115	Nidec	TA450DC-A34350-16	24	120 x 120 x 25	92	Ball	180	4.32	UL/CSA	40.4	10"	11.95	10.95	9.95	8.95
2120129	Sunon	PMD2412PTB3-A(2).GN	24	120 x 120 x 25	120	Dual ball	280	6.7	UL/CSA/TUV	48	12"	12.95	11.49	9.95	8.95
153411	Sunon	KD2412PMB2-6A	24	120 x 120 x 38	98	Ball	230	5.5	UL/CSA/TUV	36.5	12"	17.95	15.95	14.49	12.95
694444	Jamicon	JF1238S2MR-R	24	120 x 120 x 38	101.3	Sleeve	220	5.28	UL/CSA/TUV/CE	39.1	9"	13.95	12.49	10.95	9.95
694524	Jamicon	JF1238B2MR-R	24	120 x 120 x 38	101.3	Ball	220	5.28	UL/CSA/TUV/CE	39.1	9"	15.95	14.49	12.95	11.49
107394	EBM Pabst	4294GH	24	120 x 120 x 38	108	Sleeve	220	5.3	UL/CE/CSA/TUV	49	Terminals	14.95	13.49	11.95	10.95
694532	Jamicon	JF1238B2HR-R	24	120 x 120 x 38	118.7	Ball	310	7.44	UL/CSA/TUV/CE	43.8	9.5"	17.95	15.95	14.49	12.95
1809910	Sunon	KD2412PMSX-6A	24	120 x 120 x 38	119	Sleeve	300	7.2	UL/CUL/TUV/CE	45	12"	13.95	12.49	10.95	9.95
297959	Delta	BFB1224AHE	24	125 x 126 x 34	27.2	Ball	340	8.1	UL/CE/CSA/TUV	50.5	12"	14.95	13.49	11.95	10.95
212662	EBM Pabst	6424R-139	24	172 x 150 x 51	241	Ball	750	18	UL/CUL/TUV	57	24" ⁶	19.95	17.95	15.95	14.49
212661	EBM Pabst	6224N/8HT	24	172 Round x 51	241.3	Ball	750	18	UL/CE/CSA/VDE	55	12" ⁶	19.95	17.95	15.95	14.49
212644	Delta	AFB0948L	48	92 x 92 x 25	37	Ball	50	2.44	UL/CSA/TUV/CE	25	12"	14.95	13.49	11.95	10.95
2120137	Sunon	PMD4809PMB3-A(2).GN	48	92 x 92 x 38	91.7	Dual ball	120	5.8	UL/CSA/TUV	50.3	12"	15.95	14.49	12.95	11.49
212653	Delta	BFB1248HH	48	120 x 120 x 32	35.3	Ball	220	10.5	UL/CSA/CE/VDE	54	12"	14.95	13.49	11.95	10.95
1952960	Comair Rotron	MC48B6QDNX	48	120 x 120 x 32	102	Ball	180	8.4	UL/CSA/TUV/CE	48	11" w/ conn. ¹	15.95	14.49	12.95	11.49
1951457	Delta	EFB1248HHF	48	120 x 120 x 32	120	Ball	140	6.72	UL/CSA/TUV/CE	50.5	6" w/ conn.	14.95	13.49	11.95	10.95
1952775	Orion	OD1232-48HB	48	120 x 120 x 32	120	Ball	180	8.6	UL/TUV/CE	51	12" ⁵	15.95	14.49	12.95	11.49
2120145	Sunon	PMD4812PMB1-A(2).GN	48	120 x 120 x 38	190	Dual ball	400	19.2	UL/CSA/TUV	54	12"	17.95	15.95	14.95	12.95
1951422	Delta	FFB1248EHE-ROO	48	120 x 120 x 38	190	Ball	500	24	UL/CSA/TUV/CE	59	12" w/ conn. ²	17.95	15.95	14.49	12.95
689063	EBM Pabst	WZG115-AG75-85	48	127 x 127 x 38	155	Ball	310	15	UL/CUL	52	10" ¹	17.95	15.95	14.49	12.95
1954711	Delta	EFB1348HHE-SV06	48	127 x 127 x 38	185	Ball	360	17.28	UL/CSA/VDE/CE	55.5	26" ¹	17.95	15.95	14.95	12.95

¹ 3 leads; speed sensor ² 3 leads; locked rotor protection ⁵ 4 Leads wired for Dell proprietary PWM circuit control w/ tach (blue), lock rotor (yellow) & fan guard

⁶ 5 leads; locked rotor with 2 separate ground if needed (These functions are optional, if needed) † Blower * Blue Part No. = Limited Quantity Available

DC & AC Plug Fan Power Cords

* Web Code: GAE

For Fans w/ Terminal Connection

Part No.	Description	Fig.	Length	1	10	100	250
28564	Straight pigtail fan cord	1A	24"	\$1.49	\$1.25	\$.99	\$.89
2076658	Straight pigtail fan cord	1A	36"	1.49	1.25	.89	.79
1952548	45° pigtail fan cord	2A	24"	1.25	1.19	1.09	.99
104192	90° pigtail fan cord	3A	24"	1.25	1.19	1.09	.99
1952572	Straight AC plug fan cord	1B	72"	2.95	2.69	2.39	2.19
2117245	45° AC plug fan cord*	2B	24"	11.95	10.95	9.95	8.95
1952581	45° AC plug fan cord	2B	72"	2.95	2.69	2.39	2.19

* Green cord, thermal controlled


Fan Guards & Aluminum Washable Filters

* Web Code: UAR

Guards and filters fit all fans. Please match by size dimension.
Example: P/N 300557 fan (80mm) matches P/N 31924 metal guard (80mm).

Part No.	mm	Description	Fig.	1	10	50	100
123502	40	Metal (chrome) guard+	1	\$.59	\$.55	\$.49	\$.45
120038	60	Metal (chrome) guard	1	.65	.59	.55	.49
687666	60	Metal (black anodized) guard	2	.85	.79	.75	.69
31924	80	Metal (chrome) guard	1	.69	.65	.59	.55
1928433	80	Metal (black anodized) guard	2	.79	.69	.65	.59
123511	92	Metal (chrome) guard+	1	.75	.69	.65	.59
25735	120	Metal (chrome) guard	1	.79	.75	.69	.65
695068	120	Metal (black anodized) guard	2	1.09	.99	.89	.79
695076	127	Metal (chrome) guard	1	1.25	1.09	.99	.89
1811198	172	Metal (chrome) guard	1	1.25	1.09	.99	.89
1952644	40	Plastic guard only	3	.55	.49	.45	.39
1952652	60	Plastic guard only	3	.65	.59	.55	.49
1952290	80	Plastic guard only	3	.69	.59	.55	.49

Part No.	mm	Description	Fig.	1	10	50	100
1952661	92	Plastic guard only	3	\$.89	\$.85	\$.75	\$.69
1952679	120	Plastic guard only	3	.99	.89	.79	.75
1952687	150	Plastic guard only	3	1.29	1.19	1.09	.99
1952695	40	Plastic guard w/ mesh	4	1.29	1.19	1.09	.99
1952708	60	Plastic guard w/ mesh	4	1.95	1.79	1.59	1.39
138562	80	Plastic guard w/ mesh	4	1.65	1.49	1.39	1.29
229665	92	Plastic guard w/ mesh+	4	1.95	1.75	1.49	1.35
196817	120	Plastic guard w/ mesh	4	2.19	2.09	1.95	1.79
1952716	172	Plastic guard w/ mesh	4	2.79	2.49	2.29	2.19
1952724	60	Alum. washable filter	5	1.95	1.75	1.59	1.45
138580	80	Alum. washable filter	5	2.09	1.95	1.75	1.59
1952732	92	Alum. washable filter	5	2.25	1.95	1.75	1.59
130105	120	Alum. washable filter	5	2.95	2.75	2.49	2.25



* For Complete Specs & Additional Product Listings Search www.Jameco.com/More and Enter Web Code Listed Above



Order by Phone 24/7 at 1-800-831-4242 or Online at www.Jameco.com