

# AC-to-AC & AC-to-DC Regulated Switching Wall Adapters



## AC-to-AC Wall Adapters

Input: 120VAC @ 60Hz



\*Web Code: ABO

We specialize in Wall Adapters – Call for additional OEM PRICING.  
We are happy to change any listed DC wall adapter power plug to a connector of your choice (see pg 130) for just \$2.50 each. A 100 pc. minimum order applies.

Part No.	Manufacturer	Product No.	Output Rating		Output Connector ID x OD mm Female/Male	Size (H" x W" x D")	Case Color	Output Cord Length	Wt. (lbs.)	Agency Approvals	Pricing			
			Voltage (VAC)	Current (mA)							1	10	50	100
2082521	Atlinks	5-2634	5	400	2.1mm x 5.5mm right angle F	2.0 x 1.4 x 1.3	White	6'	0.4	UL/CSA	\$3.95	\$3.59	\$3.25	\$2.95
2082530	Atlinks	5-2633	5	400	2.1mm x 5.5mm right angle F	2.0 x 1.4 x 1.3	Black	6'	0.4	UL/CSA	4.95	4.49	3.95	3.59
249017	ReliaPro	ACU070150	7	1500	2.5mm x 5.5mm F	2.5 x 2.0 x 1.7	Black	6'	0.5	UL/CSA	9.95	8.95	7.95	7.29
100061	ReliaPro	ACU090050	9	500	2.1mm x 5.5mm F	2.7 x 1.9 x 1.7	Black	6'	0.6	UL/CUL	7.95	7.29	6.59	5.95
1950921	ITI	AM-9700ALF	9	700	Screw terminals	2.8 x 2.0 x 1.7	White	—	0.6	UL	4.95	4.49	3.95	3.59
236814	ReliaPro	ACU090080	9	800	3.5mm M	2.5 x 2.0 x 1.7	Black	6'	0.5	UL/CUL	7.95	6.95	6.25	5.59
1581281	OEM	AA-091A	9	1000	2.1mm x 5.5mm F	2.2 x 2.1 x 1.6	Black	6'	0.6	UL/CSA	6.95	6.25	5.59	4.95
102234	ReliaPro	ACU090100Z8182	9	1000	2.1mm x 5.5mm F	3.2 x 2.2 x 1.9	Black	6'	0.6	UL/CSA	8.95	7.95	7.29	6.49
1586154	Arndt	AA091A	9	1000	2.5mm x 5.5mm F	2.6 x 2.1 x 1.6	Black	6'	0.6	UL/CSA	7.95	6.95	6.25	5.59
157041	ReliaPro	ACU090100E8942	9	1000	2.5mm x 5.5mm F	2.1 x 2.1 x 1.6	Black	6'	0.6	UL/CSA	8.95	7.95	7.29	6.49
112336	ReliaPro	ACU090150	9	1500	2.5mm x 5.5mm F	2.5 x 2.2 x 2.0	Black	6'	0.9	UL	10.95	9.95	8.95	7.95
688634	Arndt	PP-1012-A	10	1200	2.5mm x 5.5mm F	3.5 x 2.5 x 1.9	Black	6'	1.3	UL	7.95	6.95	6.25	5.59
2076543	Radio Shack	15-1963	12	400	2.1mm x 5.5mm F	2.6 x 1.7 x 1.6	Black	6'	0.6	UL/CSA	5.95	5.35	4.79	4.29
101258	ReliaPro	ACU120050	12	500	2.1mm x 5.5mm F	2.5 x 2.0 x 1.7	Black	6'	0.6	UL/CSA	6.95	6.25	5.59	4.95
2076666	CIC	48A12-500Q	12	500	2.5mm x 5.5mm right angle F	3.3 x 2.6 x 2.0	Black	6'	1.0	CSA	4.95	4.49	3.95	3.59
10081	ReliaPro	ACU120100J0920	12	1000	2.1mm x 5.5mm F	2.6 x 2.4 x 2.0	Black	6'	0.7	UL/CSA	9.95	8.95	7.95	7.29
100167	ReliaPro	A411201000U	12	1000	2.5mm x 5.5mm F	3.2 x 2.4 x 2.0	Black	6'	0.7	UL/CSA	9.95	8.95	7.95	7.29
10428	ReliaPro	ACU120100Z9121	12	1000	3.5mm M	2.6 x 2.4 x 2.0	Black	6'	0.6	UL/CUL	9.95	8.95	7.95	7.29
167151	ReliaPro	ADU120150	12	1500	2.1mm x 5.5mm F	3.4 x 2.7 x 2.2	Black	6'	1.5	UL/CUL	10.95	9.95	8.95	7.95
307838	ReliaPro	ADU120160H4120	12	1600	2.5mm x 5.5mm F	2.9 x 2.3 x 1.9	Black	6'	1.0	UL/CUL	11.95	10.95	9.95	8.95
153761	ReliaPro	ADU120160C2521	12	1600	3.5mm M	2.5 x 2.2 x 1.9	Black	6'	0.9	UL	10.95	9.95	8.95	7.95
206404	Arndt	MGT1220	12	1670	Screw terminals with green LED	3.2 x 2.2 x 1.9	White	—	0.9	UL/CSA	9.95	8.95	7.95	7.29
2082564	ReliaPro	GPU1355000	13.5	5000	2.1mm x 5.5mm F (Table-Top style)	4.7 x 3.2 x 2.5	Black	6'	2.4	—	22.95	20.49	18.95	16.95
171408	ReliaPro	ACU140050	14	500	2.1mm x 5.5mm F	2.8 x 2.0 x 1.6	Black	6'	0.6	UL/CSA	9.95	8.95	7.95	6.95
318684	Horizon	ACU140085	14	850	2.5mm x 5.5mm right angle F	2.5 x 2.0 x 1.7	Black	6'	0.6	UL/CUL	12.95	11.49	9.95	8.95
100108	ReliaPro	ADU160100	16	1000	2.1mm x 5.5mm F	3.1 x 2.7 x 1.9	Black	6'	0.9	UL/CSA	10.95	9.95	8.95	7.95
163053	ReliaPro	ADU160110	16	1100	2.5mm x 5.5mm F	3.2 x 2.3 x 1.8	Black	6'	1.1	UL/CSA	10.95	9.95	8.95	7.95
176604	ReliaPro	BHU160400	16	4000	2.1mm x 5.5mm F (Table-Top style)	4.4 x 3.1 x 2.5	Black	6'/6'	2.8	—	19.95	17.95	15.95	13.95
2082142	Ault	308-2018	18	900	Screw terminals	1.88 x 2.18 x 1.95	Beige	—	0.7	UL	9.95	8.95	7.95	6.95
121216	ReliaPro	ADU180100	18	1000	2.1mm x 5.5mm F	3.1 x 2.7 x 1.9	Black	6'	1.1	UL/CUL	10.95	9.95	8.95	7.95
185439	ReliaPro	AFU180185	18	1850	2.1mm x 5.5mm right angle F	3.3 x 2.7 x 2.2	Black	6'	1.7	—	11.95	10.95	9.95	8.95
2076631	Ault	T57-182200	18	2200	2.1mm x 5.5mm F	3.2 x 2.6 x 2.2	Black	5'6"	1.2	UL/CSA	11.95	10.95	9.95	8.95
87581	ReliaPro	ADU240050	24	500	2.1mm x 5.5mm F	2.5 x 2.2 x 1.9	Black	6'	0.9	UL/CSA	8.95	7.95	7.29	6.49
206439	Arndt	MGT2420	24	830	Screw terminals with green LED	3.2 x 2.2 x 1.9	White	—	0.9	UL/CSA	10.95	9.95	8.95	7.95
140599	ReliaPro	ADU240100D5531	24	1000	2.1mm x 5.5mm F	3.0 x 2.2 x 1.9	Black	6'	1.2	UL/CSA	10.95	9.95	8.95	7.95
10102	ReliaPro	ADU240100E0461	24	1000	3.5mm M	3.0 x 2.2 x 1.9	Black	6'	1.2	UL/CSA	10.95	9.95	8.95	7.95
2100195	ReliaPro	GPU572401500WA00	24	1500	2.1mm x 5.5mm F	3.3 x 2.6 x 2.3	Black	6'	1.7	UL/CUL	14.95	13.49	11.95	10.95



## AC-to-DC "Slim Line" Regulated Switching Wall Adapters

Output connector: 2.1mm x 5.5mm F2 (center positive)

Compact in size and lightweight, they are the perfect power solution in all those applications where space is critical. And their high efficiency satisfies requirements for minimizing power losses. You no longer have to deal with traditional wall adapters that block unused outlets in wall plates and power strips/surge protectors.

- 2-wire AC input
- Output cord length: 6'
- Input voltage: 100 – 240VAC @ 47-63Hz
- Color: black
- One-year warranty



\*Web Code: CBO



We'll Brand the Adapters  
With Your Company Name  
Call 1-800-831-4242 for Details



CEC: Equivalent Available Below

Choose from 2 Models!		Output Rating		Size (H"xW"xD")	Wt. (lbs.)	Pricing			
Non-CEC P/N	CEC Part No.	Volt (VDC)	Curr. (mA)			1	10	50	100
—	251565	3.3	1500	2.5x1.1x1.7	0.2	\$11.95	\$10.95	\$9.49	\$8.49
—	251600	3.3	2500	2.9x1.1x1.7	0.3	12.95	11.49	9.95	8.95
252701	—	5	500	2.9x1.1x1.7	0.3	10.95	9.95	8.95	7.95
—	252720	5	1000	2.5x1.1x1.7	0.2	12.95	11.49	9.95	8.95
252727	252728	5	1500	2.5x1.1x1.7	0.2	13.95	12.49	10.95	9.95
—	252736	5	2500	2.9x1.3x2.2	0.3	14.95	13.49	11.95	10.49
2082222	—	5	3000	2.9x1.3x2.2	0.3	14.95	12.95	10.95	8.95
—	252753	9	500	2.5x1.1x1.7	0.2	11.95	10.95	9.95	8.95
—	1950841	9	1000	2.5x1.1x1.7	0.2	13.95	12.49	10.95	9.95
—	252779	9	1200	2.9x1.3x2.2	0.3	13.95	12.49	10.95	9.95
252786	—	9	1500	2.9x1.3x2.2	0.3	15.95	14.49	12.95	11.49

Choose from 2 Models!		Output Rating		Size (H"xW"xD")	Wt. (lbs.)	Pricing			
Non-CEC P/N	CEC Part No.	Volt (VDC)	Curr. (mA)			1	10	50	100
252794	252795	12	250	2.5x1.1x1.7	0.2	\$8.95	\$7.95	\$6.95	\$6.25
—	252808	12	500	2.5x1.1x1.7	0.2	10.95	9.95	8.95	7.95
—	252816	12	600	2.5x1.1x1.7	0.2	9.95	8.95	7.95	6.95
—	252824	12	1000	2.9x1.3x2.2	0.3	12.95	11.49	9.95	8.95
—	252833	12	1250	2.9x1.3x2.2	0.3	13.95	12.49	10.95	9.95
254757	—	15	800	2.9x1.3x2.2	0.2	12.95	11.49	10.49	9.49
—	252904	15	1000	2.9x1.3x2.2	0.3	13.95	12.49	10.95	9.95
252858	—	24	250	2.5x1.1x1.7	0.2	9.95	8.95	7.95	6.95
252866	—	24	500	2.9x1.3x2.2	0.3	11.95	10.95	9.95	8.95
—	2076341	24	630	2.9x1.3x2.2	0.3	12.95	11.49	10.49	9.49

✓ CEC equivalent available    ✓ CEC    ⚙ Blue Part No. = Limited Quantity Available

\*For Complete Specs & Additional Product Listings Search [www.Jameco.com/More](http://www.Jameco.com/More) and Enter Web Code Listed Above



Order by Phone 24/7 at 1-800-831-4242 or Online at [www.Jameco.com](http://www.Jameco.com)