

# AC-to-DC Regulated Wall Adapters



## Energy Star Worldwide Interchangeable AC-to-DC Regulated Switching Wall Adapters

Meets US and European Energy Star compliance. Approved for European high-efficiency power applications.

- Field changeable AC Plug Clips (sold separately, see below)
- Input voltage: 90-264VAC @ 47-63Hz
- Output connector: 2.1mm x 5.5mm female center positive; except P/N 1918702: 2.5mm x 5.5mm female right angle center positive
- Load regulation: ±5%
- Class B EMI
- Color: black
- Applications: wireless communications, portable equipment, digital camera, peripherals and networking



\*Web Code: NBH



Phihong & Mean Well AC Plug Clips (below)



Shown w/o AC Plug Clip  
AC Plug Clips Not Included

### Wall Adapters (AC Plug Clip required, not included)

Part No.	Manufacturer	Mfr. Part No.	Output Volt. (VDC)	Current (A)	Power (W)	Ripple (mVp-p)	Line Regulation	Efficiency (%)	Dimensions (L" x W" x H")	Pricing			
										1	10	50	100
1950761	Phihong	PSA05R-050PA	5	1.0	5	50	±1%	60 - 75	2.8 x 1.8 x 1.2	\$5.95	\$5.49	\$4.95	\$4.49
2082302	Mean Well	GE12105-P1J	5	2.0	10	50	+5%	70	2.8 x 1.6 x 1.5	14.95	13.49	11.95	10.95
2095429	Phihong	PSMIIR-060	6	1.66	10	100	±5%	73	2.8 x 1.8 x 1.2	14.95	13.49	11.95	10.95
1918702	Globtek	GT-41052-1506	6	2.5	15	100	±1%	76	2.9 x 1.7 x 1.5	22.95	19.95	17.95	15.95
2082311	Mean Well	GE18109-P1J	9	2.0	18	100	+5%	75	3.2 x 1.7 x 1.6	16.95	15.49	13.95	12.95
228770	Phihong	PSA05R-120	12	0.42	5	120	+5%	60	2.8 x 1.8 x 1.2	12.95	11.49	10.49	9.49
2108656	Phihong	PSC12R-120	12	1.0	12	240	+5%	78	2.8 x 1.8 x 1.2	14.95	13.49	11.95	10.95
2100179	Phihong	PSAA20R-120R	12	1.67	20	120	+5%	81	2.8 x 2.0 x 1.3	19.95	18.95	16.95	15.95
2082329	Phihong	PSC30R-120	12	2.5	30	180	±1%	80	3.8 x 2.1 x 1.2	23.95	21.49	18.95	16.95
2114423	APS*	PA1050-120-1	12	3.33	40	120	±1%	75	4.3 x 2.1 x 1.3	22.95	20.49	17.95	15.95
2114458	APS*	PA1050-120-1	12	4.16	50	120	±1%	75	4.3 x 2.1 x 1.3	24.95	22.49	19.95	17.95
2082337	Mean Well	GE12115-P1J	15	0.8	12	150	+3%	76	2.8 x 1.6 x 1.5	13.95	12.49	10.95	9.95
2082345	Mean Well	GE12124-P1J	24	0.63	15	240	+3%	80	2.8 x 1.6 x 1.5	13.95	12.49	10.95	9.95
2114431	APS*	PA1050-240-1	24	1.67	40	240	±1%	75	4.3 x 2.1 x 1.3	22.95	20.49	17.95	15.95
2114466	APS*	PA1050-240-1	24	2.08	50	240	±1%	75	4.3 x 2.1 x 1.3	24.95	22.49	19.95	17.95
2114440	APS*	PA1050-480-1	48	0.83	40	480	±1%	75	4.3 x 2.1 x 1.3	24.95	22.49	19.95	17.95

† Comes with USA AC plug clip (RPA) # 2.5mm x 5.5mm female right angle center positive plug \*Kit includes US, UK, EU, AUS plugs

### Phihong AC Plug Clips (sold separately, required for above adapters)

Part No.	Mfr. P/N	Description (see above for photos)	1	10	50	100
229155	RPA	USA AC plug only	\$.69	\$.65	\$.59	\$.55
229163	RPE	European AC plug only	.69	.65	.59	.55
229171	RPK	United Kingdom AC plug only	1.05	.99	.95	.89
2081422	RPS	Australia AC plug only	1.75	1.69	1.65	1.59
229181	RPKIT	Kit includes RPA/RPE/RPK/RPS clips (4)	3.49	2.95	2.69	2.39

### Mean Well Plug AC Clips (sold separately, required for above adapters)

Part No.	Mfr. P/N	Description (see above for photos)	1	10	50	100
2082353	AC-Plug-US	USA AC plug only	\$.69	\$.65	\$.62	\$.59
2082361	AC-Plug-EU	European AC plug only	.89	.85	.79	.75
2082370	AC-Plug-UK	United Kingdom AC plug only	1.09	1.05	.99	.95
2082388	AC-Plug-AU	Australia AC plug only	.95	.89	.85	.79
2082396	AC-Plug-MIX	Kit includes US, EU, UK & AU clips (4)	3.49	2.95	2.69	2.39



## AC-to-DC Regulated Linear Wall Adapters

\*Web Code: WAZ

We specialize in Wall Adapters - Call for additional OEM PRICING.

♦ Polarity figures & photos on next page

Part No.	Manufacturer	Product No.	Output Rating		Output Connector ID x OD mm Female/Male; Polarity ♦	Input VAC @ Hz	Size (H" x W" x D")	Case Color	Output Cord Length	Wt. (lbs.)	Agency Approvals	Pricing			
			Voltage (VDC)	Current (mA)								1	10	50	100
164101	ReliaPro	GPU410500	5	500	2.1mm x 5.5mm F 2	120@60	2.8 x 2.0 x 1.6	Black	6'	0.6	UL/CUL	\$9.95	\$8.95	\$7.95	\$6.95
220935	ReliaPro	DDU050060	5	600	2.1mm x 5.5mm F 1	120@60	2.7 x 2.2 x 1.9	Black	6'	0.8	UL/CUL	10.95	9.95	8.95	7.95
319986	DVE	DV-580R	5	800	2.5mm x 5.5mm F 2	120@60	3.2 x 2.2 x 2.0	Black	6'	1.0	UL/CUL	10.95	9.95	8.95	7.95
2081609	Condor	RWP480505	5	1000	2.1mm x 5.5mm F 2	120@60	3.2 x 2.2 x 1.9	Black	6'	1.2	UL/CSA	12.95	11.49	9.95	8.95
1953612	ReliaPro	DBU0501000	5	1000	2.1mm x 5.5mm F 2	120@60	3.3 x 2.2 x 1.9	Black	6'	1.2	UL/CSA	12.95	11.49	9.95	8.95
168605	ReliaPro	DBU0501000	5	1000	2.5mm x 5.5mm F 2	120@60	3.3 x 2.2 x 1.9	Black	6'	1.2	UL/CSA	12.95	11.49	9.95	8.95
681571	ITE	RWP480505-2	5	1000	2.5mm x 5.5mm right angle F 2	120@60	3.3 x 2.2 x 1.9	Black	6'	1.0	UL/CUL	12.95	11.49	9.95	8.95
1919220	Friwo	FE4823	5	1200	2.5mm x 5.5mm F 2	120@60	3.5 x 2.4 x 1.9	Black	6'	1.2	UL/CUL	14.95	13.49	11.95	10.95
190512	ReliaPro	DBU60020-H3570	6	200	2.1mm x 5.5mm F 2	120@60	2.2 x 1.7 x 1.5	Black	6'	0.4	UL/CUL	9.95	8.95	7.95	6.95
283573	ReliaPro	ADR-6V500MA-2.1	6	500	2.1mm x 5.5mm F 2	120@60	3.1 x 2.0 x 1.7	Black	6'	0.6	UL/CSA	10.95	9.95	8.95	7.95
1953701	ReliaPro	ADR-6V500MA-2.5	6	500	2.5mm x 5.5mm F 2	120@60	3.1 x 2.0 x 1.7	Black	6'	0.6	UL/CSA	9.95	8.95	7.95	6.95
1953719	ReliaPro	DBU0601000	6	1000	2.1mm x 5.5mm F 2	120@60	3.2 x 2.3 x 2.0	Black	6'	1.3	UL/CSA	12.95	11.49	9.95	8.95
190529	ReliaPro	AD9123	9	250	2.5mm x 5.5mm right angle F 2	120@60	2.5 x 2.0 x 1.6	Black	6'	0.5	UL/CSA	9.95	8.95	7.95	6.95
1953639	ReliaPro	DCU09050	9	500	2.1mm x 5.5mm F 2	120@60	3.3 x 2.2 x 1.9	Black	6'	0.9	UL/CSA	10.95	9.95	8.95	7.95
1953647	ReliaPro	DCU09050	9	500	2.5mm x 5.5mm F 2	120@60	3.3 x 2.2 x 1.9	Black	6'	0.9	UL/CSA	10.95	9.95	8.95	7.95
220898	ReliaPro	DCU120020	12	200	2.1mm x 5.5mm F 1	120@60	2.5 x 2.0 x 1.7	Black	6'	0.5	UL/CUL	9.95	8.95	7.95	6.95
1953655	ReliaPro	DDU120050H	12	500	2.1mm x 5.5mm F 1	120@60	2.9 x 2.2 x 1.9	Black	6'	1.3	UL/CSA	10.95	9.95	8.95	7.95
162996	ReliaPro	DDU120050	12	500	2.1mm x 5.5mm F 2	120@60	3.2 x 2.2 x 1.9	Black	6'	0.9	UL/CUL	10.95	9.95	8.95	7.95
170245	ReliaPro	RDU120100	12	1000	2.1mm x 5.5mm F 2	120@60	3.2 x 2.3 x 2.0	Black	6'	1.2	UL/CUL	14.95	13.49	11.95	10.95
1953663	ReliaPro	DCU1201000	12	1000	2.5mm x 5.5mm F 2	120@60	3.3 x 2.3 x 2.0	Black	6'	1.2	UL/CSA	14.95	13.49	11.95	10.95
174861	ReliaPro	DFU240050	24	500	2.1mm x 5.5mm F 2	120@60	3.4 x 2.7 x 2.2	Black	6'	1.3	UL/CUL	12.95	11.49	9.95	8.95
1953680	ReliaPro	DFU240500W	24	500	2.5mm x 5.5mm F 1	120@60	3.1 x 2.2 x 2.0	Black	6'	1.2	UL/CUL	11.95	10.95	9.95	8.95
174879	ReliaPro	DCU090025	24	500	2.5mm x 5.5mm F 2	120@60	3.4 x 2.7 x 2.2	Black	6'	1.3	UL/CUL	12.95	11.49	9.95	8.95
1953698	ReliaPro	DFU2401000	24	1000	2.1mm x 5.5mm F 2	120@60	3.4 x 2.7 x 2.2	Black	6'	1.3	UL/CSA	16.95	14.95	13.49	11.95
1953671	ReliaPro	MPC-2400107	24	1000	2.5mm x 5.5mm F 2	120@60	3.4 x 2.7 x 2.2	Black	6'	1.3	UL/CSA	16.95	14.49	11.95	10.95

\*For Complete Specs & Additional Product Listings Search [www.Jameco.com/More](http://www.Jameco.com/More) and Enter Web Code Listed Above



Order by Phone 24/7 at 1-800-831-4242 or Online at [www.Jameco.com](http://www.Jameco.com)