


Save 10% or more on most batteries!

Lithium, NiCd & NiMH Batteries

Applications: personal computers, workstations, test equipment, feature telephones, copiers, fax machines, video scramblers/descramblers and remotes.



NEW
MARKED IN PINK

*Web Code: GCF

Lithium

Part No.	Product No.	Manufacturer	Fig.	Size	Volts	mAh	Terminals/Connection	Dimensions	1	10	25
673627	NB4414/F9D	Panasonic	1	Coin cell	2.0	1.0	4.8mm body w/ tabs (2)	0.18"Dia. x 0.06"Thick	\$.49	\$.45	\$.39
673601	NBL621/F9DE	Panasonic	1	Coin cell	2.0	4.0	Vertical PC mount	0.27"Dia. x 0.10"Thick	.85	.75	.65
2119865	CR1632	Various	2	Coin cell	3	120	Clock/memory/watch	0.63"Dia. x 0.13"Thick	1.09	.95	.85
11789	CR2325	Various	2	Coin cell	3	165	Clock/memory/watch	0.91"Dia. x 0.13"Thick	1.79	1.59	1.45
14162	CR2032	Various	2	Coin cell	3	180	Clock/memory/watch	0.79"Dia. x 0.13"Thick	1.25	1.09	.99
1585451	DL2032	Duracell	2	Coin cell	3	180	Clock/memory/watch	0.79"Dia. x 0.13"Thick	1.49	1.35	1.19
689071	DL2450	Various	2	Coin cell	3	600	Clock/memory/watch	0.95"Dia. x 0.18"Thick	2.25	1.95	1.75
2113691	BR2330	Dantona	3	Coin cell	3	255	Clock/memory/watch (w/ legs)	0.90"Dia. x 0.12"Thick	2.45	2.19	1.95
2119873	CR2	Various	4	Cylinder	3	750	Consumer tip/digital camera	1.66"L x 0.61"Dia.	4.95	4.49	4.09
2119881	2CR5	Various	5	Dual cyl.	6	1400	(2) term. on one end	1.76"L x 1.33"Dia.	7.95	7.29	6.95
126754	TL5101S	Tadiron	4	Sub-AA	3.6	850	Macintosh*	0.95"L x 0.56"Dia.	4.75	4.25	3.55
263898	ER14250	ReliaPro	4	Sub-AA	3.6	1000	With axial leads	1.00"L x 0.55"Dia.	4.75	4.25	3.85
240266	ER14250	ReliaPro	4	Sub-AA	3.6	1000	Consumer tip	1.00"L x 0.55"Dia.	4.25	3.95	3.55
673635	CA1/2AA	Various	6	1/2 AA	3	950	Barrel w/ leads (2)	1.0"L x 0.58"Dia.	2.49	2.29	1.95
33371	TL5101P	Tadiron	7	1/2 AA	3.6	850	Barrel w/ leads (clock/mem.)	0.93"L x 0.56"Dia.	6.25	5.65	4.95
33398	TL5104P	Tadiron	8	AA	3.6	1900	Barrel w/ leads (clock/mem.)	1.88"L x 0.56"Dia.	6.95	6.25	5.65
146114	TL5104/S	Tadiron	9	AA	3.6	1900	Barrel pressure (clock/mem.)	1.91"L x 0.56"Dia.	6.95	6.25	5.65
263935	ER14505	ReliaPro	10	AA	3.6	2400	With solder tabs	2.00"L x 0.55"Dia.	5.95	5.35	4.95
240258	CR123A	ReliaPro	11	A	3	1300	Photo/computer	1.36"L x 0.65"Dia.	2.75	2.49	2.25

NiCd - Rechargeable

Part No.	Product No.	Manufacturer	Fig.	Size	Volts	mAh	Terminals/Connection	Dimensions	1	10	25
261657	AA-700-CT	ReliaPro	12	AA	1.2	700	Consumer tip	1.90"L x 0.55"Dia.	\$1.69	\$1.49	\$1.35
244515	AA-1000-CT	ReliaPro	12	AA	1.2	1000	Consumer tip	1.90"L x 0.55"Dia.	2.75	2.49	2.25
126720	351FT	Various	13	N/A	3.6	60	2-lead (pin), barrel	0.72"L x 0.61"Dia.	4.49	3.95	3.55
119116	3/V60R	Dantona	13	N/A	3.6	60	3-lead (pin), barrel	0.72"L x 0.61"Dia.	3.35	2.95	2.65
101653	NA101-1	Various	14	N/A	3.6	60	2-lead (eyelet), barrel	0.72"L x 0.61"Dia.	3.95	3.55	3.19

NiMH - Rechargeable

Part No.	Product No.	Manufacturer	Fig.	Size	Volts	mAh	Terminals/Connection	Dimensions	1	10	25
231095	AAA-750NM	Dantona	15	AAA	1.2	600	Consumer tip	1.70"L x 0.40"Dia.	\$3.45	\$3.09	\$2.79
244822	AA-1800-CT	ReliaPro	16	AA	1.2	1800	Consumer tip	1.90"L x 0.55"Dia.	3.55	3.19	2.89
231087	AA-1800NM	Dantona	17	AA	1.2	1600	Consumer tip	1.90"L x 0.55"Dia.	3.95	3.55	3.19
244620	9V-200	Bao Tong USA	18	9V	9	200	Snaps	1.94"L x 0.65"Dia.	9.75	8.75	7.95
231108	9V-8.4NM	Dantona	19	9V	9	150	Snaps	1.94"L x 0.61"Dia.	10.95	9.95	8.95
231124	D-900NM	Dantona	20	D	1.2	9000	Consumer tip	2.30"L x 1.30"Dia.	14.95	13.49	11.95



- Use with UPS Backup Systems, Security Fire Alarms, Wheel Chairs, Scooters
- Sealed • UL approved
- Rechargeable • Two-year warranty



Lead Acid Batteries

*Web Code: LBR



Lead Acid Chargers on next page

Part No.	Mfr. Part No.	Nominal Voltage	Amp-Hrs.	Cross Reference				Terminal Size	Size (L" x W" x H")	Wt. (lbs.)	Pricing	
				Panasonic	YUASA	Eagle Picher	Tempest				1	10
138692	K9120-REVC	6	1.3	Honeywell	—	—	—	Quick connect 0.187"	2.1 x 1.0 x 3.8	0.7	\$3.49	\$2.95
264014	TY-6-4.5	6	4.5	LCR6VP	NP4-6	CF16V4	TR-4-6	Quick connect 0.187"	2.8 x 1.9 x 4.0	1.9	11.95	10.75
317024	LA-TY-6-12	6	12.0	—	—	—	—	Quick connect 0.187"	5.9 x 1.9 x 3.7	4.6	19.95	17.95
318844	LA-TY-12-1.2	12	1.2	—	—	—	—	Quick connect 0.187"	3.8 x 1.7 x 2.1	1.3	14.95	13.45
264031	TY-12-2.3	12	2.3	LCR12V2.2P	NP2.3-12	CF12V1.5	TR2.3-12	Quick connect 0.187"	7.0 x 1.3 x 2.4	2.1	19.95	17.95
318924	LA-TY-12-3.2	12	3.2	—	—	—	—	Quick connect 0.187"	5.3 x 2.7 x 2.4	3.1	22.95	20.65
264057	TY-12-7.5	12	7.5	LCR12V7.2BP	NP712	CFM12V65	TR7.5-12	Quick connect 0.187"	5.9 x 2.6 x 3.7	5.6	22.95	20.65
264065	TY-12-12	12	12.0	PS12120	—	CFM12V12	TR12-12	Quick connect 0.187"	5.9 x 3.9 x 3.9	9.0	39.95	35.95
264073	TY-12-18	12	18.0	LCR12V17BP	NPG18-12	CF12V18	TR18-12	Quick connect 0.472"	7.1 x 3.0 x 6.6	13.3	47.95	42.95
318852	LA-TY-12-35	12	35.0	—	—	—	—	Nut & bolt	7.6 x 5.1 x 6.3	27.6	79.95	75.95

*For Complete Specs & Additional Product Listings Search www.Jameco.com/More and Enter Web Code Listed Above

3 LEVELS OF SAVINGS
NAME BRANDS HOUSE BRANDS FACTORY OVERRUN

Order by Phone 24/7 at 1-800-831-4242 or Online at www.Jameco.com