

Pomona 100MHz Probe Set

- Complete accessory kit included
- Compensation range: 10-60pF
- Bandwidth: 15/100MHz (-3dB)
- Attenuation: x1/x10 • 48" cable
- Rise time: 23.33/3.5ns
- Input resistance: 1/10MΩ • Capacitance: 64/10.5pF



Part No.	Mfr. Part No.	1	5
156451	4550B (100MHz)	\$56.95	\$53.95

PROBE MASTER 1000 Volt Probe Kit


- Rating: 1000V 10A
- Gold tips and contacts
- Electronic deluxe probe kit includes leads with shrouded right angle banana plug, probes, sprung hook probes, alligator clips, spade lugs, extender probes, minigator leads, .025" wire wrap leads, pico hooks and pincer hooks



Part No.	Description	1	5
212249	High voltage test probe	\$74.95	\$71.95

DV3100 Digital Logic Analyzer

From a new aluminum case to advanced triggering, adjustable threshold, more memory and a wider voltage range, the new DV3100 is the best value in a portable logic analyzer.



- 18 channels @ 100MHz (10ns)
- Automatic real time hardware compression (Tri-mode) • Eliminates res. vs. depth tradeoffs
- +0.5 to +2.8V adjust. threshold
- Ground current protection ±12V
- USB 2.0 & 1.1 compatible

DiGiView

NEW MARKED IN PINK

Includes: All cables, clips (quantity 20) and software

Part No.	Mfr. Part No.	1	5
2115776	DV3100	\$499.95	\$469.95

High Voltage Test Probe

- Maximum voltages: DC:40kV, AC: 40kV peak, 28kVrms
- Accuracy: DC:±1.5%, AC:±5%
- 10MΩ meter input impedance required
- Input/output impedance: 1,000MΩ/1.1MΩ
- Probe length: 14" • Cable length: 39"



Part No.	Product No.	Weight	1	5	25
132290	HV-40	0.8 lbs.	\$79.95	\$73.95	\$69.95

17MHz Logic Pulser

- Compatible with TTL, DTL and CMOS ICs
- Pulse repetition rate: 0.5pps/400pps
- 1MΩ sync input impedance
- Pulse width output at 100mA load: 10µs
- Pulse mode output current: 10mA
- Square wave current output: 5mA
- "One shot" or continuous 5Hz pulse train



*Web Code: MAQ

Part No.	Product No.	1	5	25
24601	LP540H	\$29.95	\$26.95	\$23.95

108-Watt Desktop Power Supply

- Load reg.: ±2%
- Input volt.: 88 132VAC/176-264VAC @ 47-63Hz (switch selectable)
- Ripple and noise max.: 120mVp-p
- Line regulation: ±5% • Efficiency (typical): 81%
- Vol. adjustment range: 12VDC to 15VDC
- Front panel on/off switch and 3 color LED loading indicator • Size: 5.9"W x 5.5"D x 3.3"H
- Short-circuit/overload/ overvoltage/overtemperature protection • Weight: 3.3 lbs.
- Back panel 3-prong AC receptacle and banana plugs



Part No.	Mfr. Part No.	1	5
673230	ESP-120-13.5	\$49.95	\$44.95

17MHz Logic Probe

- Max input freq.: 17MHz
- Minimum pulse width: 30ns
- Pulse flash time: 500ms
- Audible tones for high & low
- Input impedance: 1MΩ
- Power supply protection: ±20V
- TTL threshold: Lo = 0.8V ±0.2V, Hi = 2.3V ±0.2V
- CMOS threshold: Lo = 30% VCC, Hi = 70% VCC



Part No.	Product No.	1	5	25
149930	LP3500	\$39.95	\$35.95	\$32.95

PC Cable-Check® Pro

This powerful universal cable tester troubleshoots and maps 20 types of computer cables for opens, shorts, crosses, and good connections. Tests any combination of D-sub 9-pin, D-sub 15-pin, D-sub 25-pin, Centronics 36-pin printer, USB-A and USB-B, Mini USB, PS/2, RJ-11, RJ-45, BNC female-female cables and Firewire.



- Auto power off, auto & manual scan
- Includes: 9V battery

Paladin Tools®

Part No.	Mfr. Part No.	1	5	25
652480	1577	\$185.95	\$169.95	\$159.95

90-Watt Digital DC Power Supply

- 30V @ 3A
- Input voltage: 110/220VAC @ 50-60Hz
- Resolution: 1% ±1 digit accuracy
- Constant volt. and current operation
- Size: 5.1"W x 10.1"D x 5.9"H

JAMECO EXCLUSIVE



Part No.	Product No.	1	5
489184	DRP-303D	\$199.95	\$189.95

Single Output Benchtop Power Supplies

*Web Code: SAX



301920



175257



645600



301971



207618



1939626



207706



175249

- Voltage and current adjustable

Part No.	Mfr.	Mfr. Part No.	Voltage (VDC)/ Current (A)	Power (W)	Displays (Digits)	Input Voltage (VAC)	Short Circuit Protection	Overload Protection	Size (W" x H" x D")	Weight (lbs.)	Pricing	
											1	5
301920	Mastech	HY1503C	15/3	45	2-Analog	115/230 ±10%	Y	N	3.8 x 6.3 x 9.1	9	\$99.95	\$89.95
175265	Various	DPS150A	15/10	150	2-Analog	110 @ 60Hz	Y	Y	6.2 x 4.0 x 5.7	12	149.95	129.95
175257	Various	SPS250A	15/15	225	2-Analog	110/220 @ 47-63Hz	Y	Y	6.2 x 4.0 x 5.6	3.8	149.95	129.95
681221	Extech	382202	18/3	54	2-Digital LCD (4)	120 @ 60 Hz	Y	Y	9.4 x 6.1 x 4.3	6.6	139.95	129.95
645600	Extech	382200	30/1	30	2-Digital LCD (4)	100/240 @ 47-63Hz	Y	Y	9.4 x 6.1 x 4.3	4.4	129.95	119.95
301971	Lascar	PSU130	30/1	30	2-Digital LCD (4)	100/240 @ 47-63Hz	Y	Y	5.5 x 1.6 x 5.2	1.2	89.95	84.95
301866	Mastech	HY3003D	30/3	90	2-Digital LCD (4)	115/230 ±10%	Y	N	5.4 x 6.2 x 11.5	10	159.95	135.95
207618	Mastech	HY3005C	30/5	150	2-Analog	115/230 ±10%	Y	N	5.4 x 6.2 x 11.5	14	159.95	135.95
301911	Mastech	HY3005D	30/5	150	2-Digital LCD (4)	115/230 ±10%	Y	N	5.4 x 6.2 x 11.5	13	199.95	179.95
2112858	SKMI	LP-3010	30/10	300	1-Digital LED (3)	115 @ 50Hz	Y	Y	9.3 x 5.4 x 13.6	26.5	599.95	549.95
207626	Mastech	HY3010C	30/10	300	2-Analog	115/230 ±10%	Y	N	10.4 x 6.5 x 14.4	31	299.95	269.95
207635	Mastech	HY3010R	30/10	300	2-Digital LED (4)	115/230 ±10%	Y	N	10.4 x 6.5 x 14.4	31	319.95	289.95
207686	Mastech	HY3020R	30/20	600	2-Digital LED (4)	115/230 ±10%	Y	N	10.4 x 6.5 x 14.4	42	499.95	449.95
1939626	Extech	382290	30/30	900	2-Digital LED (4)	110-240 @ 50-60Hz	Y	Y	9.8 x 3.8 x 13.4	13.2	749.95	699.95
207694	Mastech	HY5002R	50/2	100	2-Digital LED (4)	115/230 ±10%	Y	N	5.4 x 6.2 x 11.5	13	149.95	134.95
163723	Various	DPS-3050	50/3	150	2-Analog	110 @ 60Hz	Y	Y	4.8 x 7.5 x 9.0	12.3	129.95	115.95
207706	Mastech	HY5003	50/3	150	2-Digital LED (4)	115/230 ±10%	Y	N	5.4 x 6.2 x 11.5	13	199.95	179.95
207600	Mastech	HY5005	50/5	250	2-Digital LED (4)	115/230 ±10%	Y	N	10.4 x 6.5 x 14.4	17	279.95	249.95
175249	Various	DPS5050	50/5	250	2-Analog	110 @ 50-60Hz	Y	Y	7.7 x 6.7 x 4.9	13.8	179.95	159.95

RoHS compliant product + This product is available in both RoHS and non-RoHS versions. Add an "R" before part number for RoHS version. Details on page 197.