



## Ball-End, Hex Key and Screwdriver Sets

**Bondhus/Felo Products:** Inferior tools cost money when something goes wrong. The cost of removing a stripped or broken screw head from a tight location, or replacing a damaged tool exceeds the cost of purchasing a superior tool in the first place.

- Material: Protanium high torque steel
- Ergonomically designed anti roll handle
- Bondhus: Made in USA; Felo: Made in Germany
- Ball-end inserts quickly into screw head up to 250
- Delivers perfect balance between tip strength and working angle
- Life time warranty

\*Web Code: CAQ

Part No.	Mfr.	Description	1	10
34041	BenchPro	6-pc. precision screwdriver set (slotted - 3/64", 1/16", 5/64", 5/32", 1/8", 9/64")	\$2.95	\$2.59
34059	BenchPro	6-pc. precision screwdriver set (Phillips #0 - 1/16", 5/64", 3/32", #1 - 1/8", 9/64")	2.95	2.59
2096229	Felo	6-pc. screwdriver set (slotted - 9/64"; 5/32"; 7/32"; 1/4"; Phillips - #1; #2)	37.95	35.95
99451	BenchPro	6-pc. long neck screwdriver set (slotted - (Dia. x L) 3/32" x 6 5/8", 1/8" x 7 5/8", 5/32" x 9 5/8", Phillips - #00 x 6 5/8"L, #0 x 7 5/8"L, #1 x 9 5/8")	8.95	7.95
226106	BenchPro	6-pc. precision 50 mm torx screwdriver set (Torx - T5, T6, torx hex - T7, T8, T9, T10)	13.95	11.95
2096350	Bondhus	8-pc. ball-end screwdriver set (.05", 1/16", 5/64", 3/32", 7/64", 1/8", 9/64", 5/32")	21.95	19.95
2096499	Bondhus	16-pc. folding hex key set (5/64", 1/4", 2mm to 8mm)	13.95	12.49
2096173	Bondhus	12-pc. ball-end hex key set (.05", 1/16", 5/64", 3/32", 7/64", 1/8", 9/64", 5/32", 3/16", 7/32", 1/4", 5/16")	12.95	11.95
261999	BenchPro	7-pc. 1000V insulated magnetic screwdriver set (slotted - 2.5mm)	15.95	14.49
2096456	Felo	7-pc. 1000V insulated screwdriver set (slotted - 3/32", 1/8", 9/64", 5/32", 7/32"; Phillips - #1; #2)	32.95	29.95
99565	BenchPro	6-pc. screwdriver & plier set (slotted - (Dia. x L) 0.09" x 7 5/8", 0.312 x 9 1/2", Phillips - #2 0.09" x 7 5/8", #0 0.12" x 9 1/2", pliers - micro nipper cutter, micro flat nose pliers)	12.95	11.95
261842	BenchPro	7-pc. SAE nut driver set w/ colored handles (sizes: 3/16", 1/4", 5/16", 11/32", 3/8", 7/16", 1/2")	6.95	5.95
226094	BenchPro	11-pc. magnetic AWL prec. screwdriver set (slotted - .9, 1.2, 1.4, 1.8, 2.4, 3 mm, Phillips - #00, #0, #1)	3.95	2.95
2119005	BenchPro	8-pc. ratcheting screwdriver bit set (3-slotted, 3 philips, 1 square)	7.95	6.95
2096165	Felo	12-pc. screwdriver bit set w/ screwdriver (slotted - 1/8"; 5/32"; 7/32"; 9/32"; POZI - #1; #2; Phillips - #0; #1; #2; Torx - #1; #20)	24.95	22.95



## Automatic Center-Punch Tool

**Adjustable**

- Precision instrument
- Alloy steel point
- Knurled steel body



• Size: 5.0"L x 0.5"Dia.

Part No.	Description	1	10
160282	Center Punch Tool	\$5.95	\$5.49

## 30 AWG Wire Wrap/Strip Tools

Recommended for use on 0.025" (0.63mm) square posts on 0.100" (2.54mm) center grids. The first 1-1/2 loop on the modified tool has wire insulation while all loops on a regular tool have bare wires.



Regular Modified

- Knurled handle for easy grip
- 5" long

Part No.	Description	1	5
242801	Tool (regular)	\$19.95	\$18.95
242798	Tool (modified)	22.95	21.95
242827	Replacement tip (242801)	7.95	7.29
242819	Replacement tip (242798)	7.95	7.29
242835	Replace stripper assembly	4.95	4.49

## Deluxe Precision Knife Set

- Three different knife handles - fine work, medium and heavy duty power grip
- Size: 6.3"L x 2.8"W x 1.4"H




Includes: 13 types of blades

Part No.	Description	1	10	100
72768	13 blade knife set	\$8.95	\$7.95	\$6.95

## 5" Steel Hemostats

- Grade 410 A.I.S.I. stainless steel
- Three locking positions



Part No.	Cross Ref. No.	Description	1	10	100
115107	HEM01	Straight	\$3.95	\$2.95	\$2.49
115115	HEM02	Curved	3.95	2.95	2.49

## Strip-Wrap-Unwrap Tools

- Tool tip made of tempered steel
- Spring steel cutter
- Use with 30 AWG wire on .025" square posts
- No solder necessary, see pg 58 for wire
- Wrap 1 to 2 turns of insulated portion of wire for secure connections
- 4.5" long



34585 \*Web Code: BBC

Part No.	Product No.	1	5
34585	HSM30 (Modified)	\$49.95	\$44.95
236785	HSR30 (Regular)	29.95	25.95

## 1/4-Watt & 1/2-Watt Resistor & Capacitor Lead Forming Tool

- Watt size indicates appropriate package size
- Bends lead length in 0.05" increments
- Lead spacing: 1/4W: 0.4"-1.5"; 1/2W: 0.5"-1.5"



Part No.	Description	Size (L" x W")	1	10
106884	1/4W & 1/2W	5.4 x 1.5	\$4.95	\$4.49

## IC Pin Straightener

- Straighten bent pins safely and easily w/ Jameco's IC pin straightener.
- Straightens 8/14/16/18/20/24/28/40/42-pin ICs
  - Materials: black plastic
  - Size: 3.3"L x 1.5"W x 0.4"H
- Includes: Ground terminal



Part No.	Description	1	10	100
99363	IC straightener	\$7.95	\$6.95	\$5.95

## 24" Joubert Bungee Cord

- Braided jacket cover
- 2.75" steel hook height
- 0.81" steel hook opening
- 0.16" thick PVC coated steel hook
- Blue cord with black coated hook
- Stretches easily to 48"



Part No.	Product No.	1	10	100
2081668	JBC24	\$.75	\$.69	\$.59

\*Calipers - Enter Web Code PAQ

## Nibbling Tool

- Perfect for cutting, trimming, or notching sheet metal up to 18 AWG
- Time-saver when working on prototyping, chassis, and circuit boards
- Minimum .375" hole required
- Size: 7.8"L



Part No.	Mfr. P/N	Description	1	10
18810	HT204	Nibbling Tool	\$7.95	\$6.95
29331	HT204B	Replace. bit	3.95	3.55

## Metal Dial Calipers

- Choose Metric or Inches
- Measures outside, inside & depth
  - Accurate measurements every time
  - Easy-to-read dial gauge
  - Materials: metal
  - Color: silver
  - Length: 6" (150mm)



Includes: Fitted plastic storage case

Part No.	Description (min. reading)	1	5	25
116134	Metric (.02 mm)	\$25.95	\$23.95	\$21.95
116126	Inches (.001 inch)	25.95	23.95	21.95
684449	Metric/Inches	27.95	25.95	23.95

## Digital Display Caliper

- Metric and Inches
- Hardened stainless steel
  - Display: inches to 0.001; mm to 0.01
  - Instructions for making internal, external, depth & step measurements
  - Calipers measure to 6 inches/150mm
- Includes: Fitted case and 1.5V silver oxide battery (replacement battery, P/N 140783, pg 149)



Part No.	Description	1	5
127482	Digital Display Caliper	\$39.95	\$36.95

## Precision Caliper (Micrometer)

- Precision measurement to 0.0001"
- Measure 0 to 1"
- Sturdy steel construction
- Weight: 7.4 oz.



Part No.	Description	1	5
2118969	Micrometer	\$19.95	\$17.95

\*For Complete Specs & Additional Product Listings Search [www.Jameco.com/More](http://www.Jameco.com/More) and Enter Web Code Listed Above