

General Purpose Illuminated 3X Magnifier

- 3.5" Dia. x 7.5"L
- Great for magnifying fine print
- 90mm diameter lens
- Light requires 2 AA batteries (not included, recommend P/N 198707, pg 149)



Part No.	Description	1	5
149542	Illuminated magnifier	\$4.95	\$4.49

3X Flexible Neck Magnifier

- 3.5" diameter
- 3x diopter lens
- Flexible gooseneck with workbench clamp
- Arm length: 20"
- Weight: 1.8 lbs.



Part No.	Description	1	5
239548	Flexible neck magnifier	\$10.95	\$8.95

Glue Gun and Glue Sticks

- Adheres to PCBs, cardboard, wires, metal and cloth
- Silicon nozzle
- Electronic heating
- Trigger action
- Utilizes 100mm long glue sticks (2 sticks included) • Size: 7.3"L x 6.3"W



Part No.	Description	1	5	25
72696	Glue gun	\$7.95	\$7.29	\$6.49
78633	Glue sticks (6/pk)	2.95	2.49	1.95

Butane Powered Mini-Trigger Torch

- Adjustable gas flow up to 2500°F
- Self-igniting piezo electric ignition
- Meets child safety requirements
- Slide lock for continuous use
- 60 min. burn time



Part No.	Mfr.	Part No.	1	5
2097483	MT-70		\$19.95	\$17.95
2097491	5 1/8 oz. butane		5.49	4.95

Table-Top Micro Torch

- Flame temp. approx. 2500°F
- Self-igniting system w/ safety lock
- Safety lock to prevent unintentional ignition and for storage
- Wide stable base, perfect for lab use
- Educational lab burner applications
- Slide lock for continuous use • 60 min. burn time



Part No.	Mfr.	Part No.	1	5
2097467	MT-30		\$36.95	\$34.95
2097491	5 1/8 oz. butane		5.49	4.95

Magna-Lite Butane Table-Top Torch

- Flame temperature: 2500°F (1300°C)
- Waterproof piezo ignition
- Adjustable flame control
- Refills in 20 seconds with standard butane gas
- Run time: 60 minutes (@ middle flame setting)
- Child-resistant ignition for safety
- Uses: brazing, soldering, heat shrink tubing, industrial maintenance



Part No.	Mfr.	Part No.	1	5
1943001	ML200		\$29.95	\$26.95

Heat Guns and Strippers

All Master® products are made in the US from superior quality materials and the finest craftsmanship. Heat guns are ideally suited for drying, heating, welding, shrinking, soldering, desoldering, and many other applications where heat is required.



- 2076578: • CFM selectable • Includes 4 attachments & case
• Weight: 1.0 lb.
- 2076501: • No slip adjustable stand
• Weight: 4.0 lbs.
- 191943: • 3-pos. switch (hot/off/cool)



Web Code: QAJ



Part No.	Mfr.	Product No.	Description	Watts	Heat Setting (°F)	Temp. (°F max.)	1	5
2117413	NTE	HG300-D	Mini heat gun	350	482-662	662	\$19.95	\$18.95
254925	BenchPro	1001A	Economical heat gun	1000	600 & 1000	1000	39.95	35.95
76865	BenchPro	G1HG1	Heat gun/stripper	1500	600 & 1100	1100	39.95	35.95
2076578	Master	EC-100K	Economical heat gun (7 & 9 CFM)	1200	500 & 1000	1000	54.95	51.95
2076501	Master	HG-501A	Industrial heat gun (23 CFM)	1680	750	750	114.95	104.95
191943	Weller	6996C	Industrial heat gun	250	750-800	800	139.95	129.95
2007062	BenchPro	1004	Tool kit for 254925	—	—	—	12.95	11.95
217816	BenchPro	HG018-AO	Heat shrink attach for 76865	—	—	—	1.95	1.69
217832	BenchPro	HG018-CO	Air spreader for 76865	—	—	—	1.95	1.69

Butane Powered Cordless Soldering Iron

- Built-in on-off switch
- Can be used as a torch or hot blower
- Length: 8.5"
- Maximum temperature: 450°C (842°F)
- Average use of 40 minutes on a full load



Part No.	Mfr.	Part No.	1	5
645520	GASIRON2		\$29.95	\$26.95

16 to 30-Watt Variable Soldering Iron & Stand

- 116572: Length: 7.5"
36329: • Black anodized steel base - 5.3"L x 3.3"W
- See below for replacement sponge (P/N 134631)
 - Fits most soldering irons .85" dia.
- Includes: Sponge



Part No.	Description	1	5	25
116572	258VL soldering iron	\$19.95	\$17.95	\$15.95
36329	Soldering stand	4.95	4.45	3.95
134631	Sponge (for P/N 36329)	2.95	2.59	2.29

25-Watt Thermally Balanced Soldering Iron

- The XY200GX is a thermally balanced soldering iron for the professional or hobbyist.
- 120VAC; 6' cord • 25-watt power consumption
 - Interchangeable tips (pg 168) • UL listed
 - Length: 8.0" • One-year warranty




Includes: 1.6mm conical tip

Part No.	Mfr.	Part No.	1	5	25
129040	200GX-25W		\$13.95	\$11.95	\$9.95

50-Watt SMD Tweezer Iron

- 168401 Includes: 0.078" tip 168401
- 236460: Replacement sponge
- 168583: 0.078" replacement tip (see above)
- 168591: 0.59" replacement tip (see above)
- | Part No. | Mfr. | Part No. | For Use With | 1 | 5 |
|----------|-----------|----------|--------------|---------|---------|
| 168401 | TW250ESD | XY9-60A | | \$44.95 | \$39.95 |
| 236460 | 78-744615 | XY9-60A | | 2.95 | 2.59 |



40-60-Watt High-Performance, Economical Soldering Irons

High-quality soldering irons that are suitable for both professional & do-it-yourself applications.

- Length: 9"
- 120VAC; 6' cord with 3-prong plug
- Tips for P/N 224602; P/N 226018/226000
- Tip for P/N 195223; P/N 226026
- For additional tips see pg 168



Part No.	Mfr.	Part No.	1	5	25
224602	200PHG-40W		\$11.95	\$10.95	\$9.95
195223	200PHG-60W		12.95	11.49	10.49
226018	44-240513 conical tip		1.95	1.59	1.29
226000	44-240517 chisel tip		1.95	1.59	1.29
226026	44-240617 chisel tip		1.95	1.59	1.29

35-Watt SMD Tweezer Iron

- Max. temp.: 760°F
- 120VAC
- Max. efficiency ceramic heating elements insures rapid heat-up and instant heat recovery
- Heater insulation exceeds 100MΩ
- Heater power consumption: 35W ea.



Includes: 0.078" tip

Part No.	Description	1	5	25
168410	Tweezer iron	\$54.95	\$49.95	\$44.95
168583	Tip .078"	9.95	8.95	7.95
168591	Tip .590"	11.95	10.95	9.95

Weller® 25 & 35-Watt High-Quality Soldering Irons

- 120VAC @ 60Hz
 - Interchangeable heater elements
 - Lightweight handle with cushioned grip
 - Quick change knurled collar • Length: 9"
- Includes: Power cord & ST3 tip (pg 166)



Part No.	Mfr.	Part No.	Description	1	5
170587	WP25		25W solder iron	\$39.95	\$37.95
192102	WP35		35W solder iron	47.95	45.95
146608	ST1		Screwdriver tip 1/16"	5.95	4.95
146616	ST3		Screwdriver tip 1/8"	5.95	4.95
192145	ST6		Screwdriver tip .031"	5.95	4.95
146624	ST7		Conical tip 1/32"	5.49	4.49

* For Complete Specs & Additional Product Listings Search www.Jameco.com/More and Enter Web Code Listed Above