

70-80 Watt Soldering Stations

- Input: 110-120VAC @ 60Hz
- Nichrome heating element on soldering iron
- Soldering iron assembly w/ nichrome heating element & K-type thermocouple sensor
- Adjustable knob for temp. setting • Weight: 5.3 lbs.
- Includes: soldering station, soldering stand with cleaning pad, soldering iron, manual



1950711

- 1950711: Analog 70-Watt** • Size: 8"L x 5.2"W x 3.8"H
- LED to indicate power (green), heater on (red)
 - Temp. acc.: ±3°C • Uses model 209 soldering iron
 - Temp. range: 200°C to 450°C (329°F to 842°F)

2099180: Digital 80-Watt

- Temp. accuracy: ±3°C
- Temp range: 200°C to 480°C (392°F to 896°F)
- Size: 4.2"W x 3.6"H x 5.0"D • ESD safe
- Uses 108ESD soldering iron assembly

* Web Code: GEJ

Part No.	Mfr. Part No.	Description	1	5
1950711	169	Analog	\$99.95	\$89.95
2099180	LF-1600	Digital	89.95	79.95

80-Watt High-Power Stained Glass Soldering Station

- 100-120VAC @ 60Hz or 220-240VAC @ 50Hz
- On/off switch with "power on" indicator light
- Temperature range: 482-923°F (250-500°C)
- Variable power control
- Safety guard iron holder • Cushioned foam grip



NEW
MARKED IN PINK

Part No.	Mfr. Part No.	Description	1	5
2118467	LT-80		\$49.95	\$44.95

Weller® 80-Watt Soldering Station

- 120V @ 60Hz
- Lighted on/off switch
- Adjustable power from 5 to 80 watts
- Temperature is electronically controlled from 350° to 900°F
- Size: 5.5"L x 4.5"W x 3.5"H
- Weight: 2.1 lbs.



2082775

* Web Code: GEJ

Includes: MTG21 1/4" chisel tip and manual

Part No.	Mfr. Part No.	Description	1	5
2082775	WLC200	Soldering station	\$69.95	\$65.95
2082812	MTG21	1/4" chisel tip	7.95	7.49
2082821	MTG22	3/8" cone tip	8.95	8.49
2082783	WCC104	Sponge	1.75	1.59

Weller® 85-Watt Digital Soldering Station

- Extensive special functions menu allows you to use setback, lockout, standby, auto-off time and more
- Heating element is contained in pencil rather than tip
- Micro pencil with short tip-to-grip (37mm) puts you close to the work
- Iron stand has adjustable tilt angle in 4 positions ranging from 30° to 80°
- Uses WMP soldering pencil and WDH20 iron stand
- Size: 15.9"L x 10.9"W x 5.8"H • Weight: 7.5 lbs.



* Web Code: GEJ

Part No.	Mfr. Part No.	Description	1	5
684781	WD1001		\$309.95	\$294.95

Weller® 85-Watt Digital Soldering Station

- New WP80 soldering pencil with short tip-to-grip (52mm)
- Barrel can be exchanged with optional longer version to work at standard length (65mm)
- Unique silver heater allows fast, efficient soldering
- Uses WP80 soldering pencil and WDH10 soldering stand
- Size: 15.4"L x 10.2"W x 5.2"H



* Web Code: GEJ


Part No.	Mfr. Part No.	Description	1	5
684772	WD1002		\$309.95	\$299.95

Weller® Soldering Tips

Replacement Tips for WES51 & WESD51

- Tip leakage: less than 2mV
- Tip to ground resist.: less than 2Ω
- Additional tips can be special ordered

* Web Code: NAB



Part No.	Mfr. P/N	Description	1	5
16774	ETA	Screwdriver 1/16"	\$6.95	\$6.29
16782	ETJ	Long screwdriver 1/32"	6.95	6.29
16803	ETR	Narrow screwdriver 1/16"	6.95	6.29
16811	ETS	Long conical 1/64"	6.95	6.29
2082783	WCC104	Replacement sponge	1.75	1.59

Replacement Sponges for Legacy Model Soldering Stations

- 134640: For 138-3
- 134631: For XY-60D, XY-379 & XYT379-C

Part No.	Mfr. Part No.	Description	1	5	25
134640	SP815		\$1.95	\$1.75	\$1.59
134631	SP715		2.95	2.59	2.29

Desoldering Tips

- Replacement tips for LF7000 P/N 1919107 and LF8000 P/N 1919115



Part No.	Description	1	5	25
2095496	Desolder tip 1mm	\$8.95	\$7.95	\$6.95
2095509	Desolder tip 1.2mm	8.95	7.95	6.95
2095517	Desolder tip 1.5mm	8.95	7.95	6.95

CHIPQUIK® SMD Removal Kit

- Quick and easy to use
- Potential damage to printed circuit boards is eliminated
- 2.5" of CHIPQUIK® material removes 1250-1500 SMD pins
- Uses simple equipment and materials for application & clean-up



Part No.	Description	1	5
141305	SMD removal kit	\$15.95	\$14.49

Vacuum Pen Tools

- ESD safe body
- Picks up components with weight of 1.1 lbs. or less

Part No.	Description	1	5
207239	Handivac tool (4 tips/cups)	\$19.95	\$17.95
207247	Pen vac tool (6 tips/cups)	39.95	33.95

90-Watt Analog Soldering & Desoldering Station

- Soldering iron: 32VAC output, 90 watt, 200°C to 480°C (400°F to 900°F) temperature range with 1.6mm/1/16" tip
- Input voltage: 100 - 120VAC @ 60Hz
- Desoldering iron (DIA80): 32VAC output, 80 watt, 300°C to 450°C (570°F to 850°F) temp. range, with 1.2mm/0.048" tip • Temp. stability: ±3°C (6°F)
- Pump controlled by a finger actuated thyristor on desoldering iron
- Automatic power down after 15 minutes of idle as indicated by pause LED
- Dials for temperature settings on both soldering and desoldering iron
- Analog readout for vacuum pressure
- Self-contained vacuum pump engineered to provide continuous, maintenance free operation
- Zero voltage switching and full grounded design
- Adjustable temperature without changing tips
- Size: 10.8"W x 12.5"D x 4.1"H



- Includes:** 104A/105A soldering stands, A-2000-1 soldering stand, DIA80 desoldering iron with #44-915412 tip, 210ESD soldering iron with #44-415404 tip, 5pc. 5" high precision tweezers, AX205 5" micro cutting pliers, steel brush/cotton/foam replacement filters, power cable, and instruction manual

Part No.	Mfr. Part No.	Description	1	5
1919107	LF-7000		\$339.95	\$319.95

100-Watt High-Powered Soldering & Desoldering Station

- Input voltage: 100 - 120VAC @ 60Hz
- Soldering iron (heater output, power and temp. range): 32VAC, 100W, 200°C to 450°C (400°F to 850°F)
- Desoldering iron (heater output, power, and temperature range): 32VAC, 80W, 300°C to 450°C (570°F to 850°F)
- Temp. stability: ±3°C (6°F)
- Pump controlled by a finger actuated thyristor on desoldering iron
- Zero voltage switching & fully grounded design
- Adjustable temperature w/o changing tips
- Auto power down after 15 min. of idle
- Detachable soldering iron and desoldering wand
- Self-contained vacuum pump engineered to provide continuous, maintenance free operation
- Digital readout for temperature
- Analog readout for vacuum pressure
- Size: 10.8"W x 12.5"D x 6.1"H



- Includes:** 104A/105A soldering stands, DIA80 desoldering iron, 210ESD soldering iron, steel brush, foam filters, power cord, diagonal wire cutters, 5 high precision tweezers and instruction manual

Part No.	Mfr. Part No.	Description	1	5
1919115	LF-8000		\$489.95	\$464.95

* Soldering/Desoldering Stations — Enter Web Code GEJ

Large Quantities Heavily Discounted
Factory Overruns - Jameco Excess Inventory
Discontinued Product Lines
www.Jameco.com/Clearance

* For Complete Specs & Additional Product Listings Search www.Jameco.com/More and Enter Web Code Listed Above