

Solder Spool & Iron Stand

- 4 pc. spool stand (some assembly required)
- Size: 6"L x 3.5"W x 3.1"H
- Sponge size: 1.6"W x 2.4"L
- Shaft diameter: 0.6"



Part No.	Description	Wt. (lbs.)	1	5	25
169551	Spool & iron stand	2.0 \$9.95	\$8.95	\$7.95

* Solder Spool Stand — Enter Web Code YAU

JAMECO ValuePro Solder Spool Stand

- 12 pc. solder spool stand (some assembly required)
- Size: 3.6"W x 3.9"D x 4.3"H
- Shaft dia.: 0.6"



Part No.	Description	Wt. (lbs.)	1	5	25
141761	Solder spool stand	1.6 \$10.95	\$9.95	\$8.95

Soldering Tip Cleaner with Stand

- For cleaning soldering iron tips without the use of water and sponge
- Metal wool for cleaning
- Rubberized base for stability



Part No.	Description	Wt. (lbs.)	1	5	25
156777	Tip cleaner & stand	0.5	... \$4.95	\$4.49	\$3.95
160004	Metal wool replacement	0.1 2.49	2.29	1.95

150-Watt Solder Pot

- On-off switch on handle
- Input voltage: 120VAC
- Maintains pot temp. of 450°C to 480°C (842°F to 896°F)
- 3-conductor power cord: 5' long
- Pot size: 400mm deep x 400mm Dia.



Part No.	Product No.	Wt. (lbs.)	1	5
2115418	RD-7339	1.2 \$59.95	\$53.95

300-Watt Solder Pot

Temperature Regulated Between 420°C and 450°C

- HI/LO temperature switch
- 2 conductor power cord: 5' 9" long
- Holds up to 1 bar of P/N 176057 or 170465, pg 170
- Input volt.: 110VAC @ 2.7A; 50-60Hz
- Size: (unit) 4.8"H x 5.5" Dia. (base)
- Size: (tub) 2.4"Dia. x 1.6"D
- One-year warranty



Part No.	Description	Wt. (lbs.)	1	5
1951625	300W solder pot	5.9 \$89.95	\$79.95

* Solder Pots — Enter Web Code HAW

600-Watt Solder Pot

Temperature Adjustable

- 2-wire power cord (5'5")
- Temperature: 0°C to 500°C
- Self-regulating temperature
- Input voltage: 110VAC @ 5.5A
- On-off power switch and LED indicator for heat
- Holds up to 3 bars of P/N 176057 or 170465, pg 170
- Size (unit): 6.8"L x 5.5"W x 2.8"H
- Size (tub): 3.9"L x 1.6"D



Includes: Skimmer and removable dross tray

Part No.	Description	Wt. (lbs.)	1	5
172276	600W solder pot	7.4 \$149.95	\$139.95

2000-Watt Solder Pot

- Thermostat control for setting temp. from 50°C to 300°C
- Holds up to 48 bars of P/N 176057 or 170465, pg 170
- 3 conductor pigtail power cord: 5'L
- Input voltage: 110VAC @ 18A, 50-60Hz single phase
- Size (unit): 18.1"L x 11.5"W x 6.0"H
- Size (tub): 12.0"L x 8.0"W x 2.9"H
- One-year warranty



Power cord not included
Recommend 37997

Part No.	Description	Wt. (lbs.)	1	5
149876	2000W solder pot	23.1 \$329.95	\$299.95

22-Watt Fume Extractor

Absorbs noxious lead fumes using activated-carbon filter and a high-efficiency fan

- Operate continuously providing filtered air
- Static ground jack • Fuse protected
- Air flow: 115 CFM • Noise: 49dB fan
- 20VAC, 60Hz, 22 watts
- Aerodynamic hood design for effective removal of solder fumes
- Removable carbon-impregnated filter
- Size: 6.4"W x 4.6"D x 7.9"H
- Weight: 4.6 lbs. • One-year warranty



Includes: Detachable power cord

Part No.	Description	Wt. (lbs.)	1	5
120150	Fume extractor	4.6 \$49.95	\$45.95
127183	Replace. filters (2/pk)	0.05 9.95	8.95

* Fume Extractors — Enter Web Code HAR

320-Watt Fume Extractor System

Compact & Portable

The HV-2E replaces smaller less powerful counter top extractors and creates more work space in crowded labs & stations. The main unit features strong fan performance with both a pre-filter and standard filter. The internal pump system utilizes a brushless centrifugal fan motor that efficiently and quietly removes fumes.



- 7' long, 6.5" Dia. exhaust tubes
- Lockable metal casters
- Airflow: 175m³/hour • Noise level: <50dB
- Voltage: 110V/220V • Size: 13"W x 12"D x 17"H

Part No.	Mfr. Part. No.	Wt. (lbs.)	1	5
2099235	HV-2E	30.0 \$599.95	\$549.95

Weller® 20-Watt Fume Extractor

This fume extractor removes flux fumes from the soldering workbench by drawing smoke through an activated carbon filter. With its exceptionally quiet fan, it can process up to 1.37 cubic meters of air per minute and its stand is adjustable allowing it to be set-up in multiple positions.



- Voltage: 120VAC • Sound level: 45-50dB
- Air consumption: 87-107CFM • ESD safe
- Power consumption: 20W • UL/CUL listed
- Absorption capacity: 1.25 cubic meters to 1.37 cubic meter per minute
- Size: 10"L x 6.5"W x 11"H

Part No.	Mfr. Part No.	Wt. (lbs.)	1	5
684810	WSA350	4.2 \$54.95	\$52.95
684828	WSA350F (carbon filter)	0.02 7.95	6.95

42-Watt Combination Soldering Station and Fume Extractor

- Power consumption: 42W @ 650°F (soldering iron)
- Adjustable knob for temperature control: 500°F to 800°F
- Stability @ idle: ±9°F
- Max. air volume: 95/115CFM
- LED indicator for pilot light
- Electronic zero-voltage switching
- Input voltage: 100-120VAC @ 60Hz
- Size: 6.4"W x 7.8"H x 4.7"D



Includes: Soldering iron, iron holder, sponge, carbon activated filter, power cord and manual

Part No.	Mfr. Part No.	Wt. (lbs.)	1	5
183169	456DLX	5.2 \$79.95	\$74.95

Vacuum Base Vise

- Features the patented "split ball" that tilts, turns and rotates through three planes
- Powerful suction pad for quick and easy set-up
- Nylon jaws open 2.25"
- Size: 5.0"L x 4.0"W x 6.3"H
- One-year warranty

262116



* Web Code: TAD

Part No.	Mfr.	Product No.	Wt. (lbs.)	1	5
262116	ValuePro	GV-300	3.3	... \$39.95	\$35.95
27131	PanaVise	M381	3.3 61.95	59.95

Third Hand Tools

- Two adjustable arms with alligator clip jaws
- Quick and easy rotation
- Sturdy, heavy base



681002

Part No.	Description	Size	Wt. (lbs.)	1	5
72865	With holder/sponge	2.0"	1.4	... \$8.95	\$7.95
681002	With holder/sponge	3.5"	1.7 9.95	8.95
26690	Third hand	2.0"	1.4 5.95	5.49

PANA VISE Multi-Purpose Work Center

- Jaws open to 9"
- Double action extra wide self-centering heads allow fast opening and closing; centered weight allows jaws to hold heavier objects; plates can be reversed to close together; reversible jaw pads feature ribbing on one side and a V groove on the other
- Base has three 1/4" countersunk mounting holes
- Overall base diameter is 8.5"



Part No.	Mfr. Part No.	Wt. (lbs.)	1	5
684852	350	5.0 \$99.95	\$89.95

PANA VISE Electronic Work Center

- Circuit board holder, standard base, tray base mount, solder station, sponges and wire holder included
- Size: 8.5"W x 7.8"H
- One-year warranty



Part No.	Mfr. Part No.	Wt. (lbs.)	1	5
27060	324	5.3 \$99.95	\$89.95

PANA VISE Vacuum Base Vise

- Head moves through three planes: 210° tilt, 360° turn and rotation
- Grooved jaws are made of reinforced thermal alloy and open up to 2.9"
- Fine/coarse adjustment • Base dia.: 3.4"
- Jaw size: 2"H x 1"W • Height: 7.5"H



Part No.	Mfr. Part No.	Wt. (lbs.)	1	5
251791	209	0.8 \$39.95	\$35.95

* For Complete Specs & Additional Product Listings Search www.Jameco.com/More and Enter Web Code Listed Above