

Vises, Soldering Accessories & Tape Products

3 LEVELS OF SAVINGS
NAME BRANDS **HOUSE BRANDS** **FACTORY OVERRUN**

PANA VISE PV Jr. Vise

- Jaw size: 1" wide x 2" long; opening: 2.8"
- Jaw heat tolerance: 350°F
- Vertical/horizontal jaw grooves
- Fine/course adjusting knob
- The vise neck tilts, turns and rotates
- Vise height: 6.8" • Weight: 1.4 lbs.
- Base bolt is 4.3" and fits all PanaVise base mounts



Part No.	Mfr. Part No.	1	5
134439	PVJR 201	\$26.95	\$24.95

Rapid Assembly Circuit Board Holder

- 8 positions rotating adjustment, six positive lock positions in the vertical plane and height adjustment for quick board rotation speeds
- Holds circuit boards from 1/8" (3.2mm) to 12" (304.8mm) wide and up to 5/32" (4mm) thick
- Arms move independently
- 10" high (from base to top of vertical shaft)



Part No.	Mfr. Part No.	Weight	1	5
684844	333	6.4 lbs.	\$79.95	\$75.95

Clamp Vise

- No tools needed — finger turn to tighten
- Ball cup allows vise to adjust to any angle
- Size: 10.0"L x 2.5"W



- Nylon jaws open 2"
- Weight: 2.1 lbs.

Part No.	Mfr. Part No.	1	5
127167	OR-307	\$19.95	\$17.95

Thornton Clear Plastic Vials with White Lid

- Crystal polystyrene vials
- White polyethylene snap-caps
- Uses: hobby, home, education and science/medical labs

NEW
 MARKED IN PINK



Part No.	Volume (oz.)	Dia. (inch)	Inside Height (inch)	Price		
				1	10	100
2120858	1.13	1	2-5/8 ...	\$.35	\$.29	\$.25
2120866	2.50	1-1/2	2-11/1655	.45	.39
2120874	5.00	1-7/8	3-5/1665	.55	.49

OPTRONIC Plastic Pump Bottle

- 6 oz. bottle
- ESD compliant
- Plastic bottle with dispenser cover



Part No.	Mfr. Part No.	1	10	100
158131	450	\$9.95	\$8.95	\$7.95

3M Tape Products

★ Web Code: TPS



285587



285464



652172



285907



645159



651882

Part No.	Description	Color	Width (in.)	Length (yards)	Thickness (in.)	Price		
						1	10	50
285587	Vinyl electrical tape, Tartan 1710, UL	Black	.75	20	.0070	\$1.19	\$1.09	\$.99
285464	Vinyl electrical tape, Super 33+, UL	Black	.75	20	.0070	4.95	4.79	4.49
652156	Vinyl electrical tape, Super 35, UL	Yellow	.75	22	.0070	4.95	4.79	4.49
652172	General purpose masking tape, Scotch	Tan	.95	60	.0060	4.95	4.49	3.95
285907	Double sided foam tape	White	1.0	4	.1250	15.95	14.95	13.95
645159	Vinyl tape, clean removal	Red	2.0	36	.0051	19.95	18.95	17.95
651882	Safety stripe tape	Yellow/Black	2.0	36	.0050	29.95	28.95	27.95

RoHS compliant product + This product is available in both RoHS and non-RoHS versions. Add an "R" before part number for RoHS version. Details on page 197.

Solder Bars, Rolls and Pocket Packs

★ Web Code: ABD

Part No.	Manufacturer	% Composition					Dia. "	L"	Weight	Type†	Pricing	
		Tin	Lead	Silver	Copper	Gold					1	10
73576	Kester	60	40	—	—	—	0.031	—	0.5 oz.	2	\$2.79	\$2.55
32117	Kester	60	40	—	—	—	0.031	—	1.0 lb.	1	25.95	22.95
141786	Super	60	40	—	—	—	0.031	—	1.1 lbs.	1	19.95	17.95
176057	ValuePro	60	40	—	—	—	—	13	1.1 lbs.	4	20.95	18.95
94570	Kester	60	40	—	—	—	0.05	—	1.3 oz.	2	3.15	2.85
73605	Kester	62	36	2	—	—	0.02	—	0.35 oz.	2	2.85	2.59
2119101	ChipQuik	63	37	—	—	—	0.02	—	4 oz.	1	6.95	6.49
2119110	ChipQuik	63	37	—	—	—	0.031	—	4 oz.	1	6.25	5.49
151474	Kester*	63	37	—	—	—	0.031	—	1 lb.	1	27.95	24.95
115433	Kester	63	37	—	—	—	0.039	—	0.14 oz.	3	.99	.75
170465	ValuePro	96.3	37	—	0.7	—	—	13	2.1 lbs.	4	19.95	18.95
668262	ValuePro	96.3	—	3.2	0.5	—	0.04	—	7.2 oz.	1	25.95	23.95
668297	ValuePro	96.3	—	3.2	0.5	—	0.04	—	1.1 lbs.	1	49.95	44.95
2119128	ChipQuik	96.5	—	3	0.5	—	0.02	—	4 oz.	1	7.75	6.95
1945858	Various	96.5	—	3.0	0.5	—	0.02	—	1.1 lbs.	1	27.95	25.95
2113172	Kester	96.5	—	3.0	0.5	—	0.031	—	0.43 oz.	2	2.49	2.29
2119136	ChipQuik	96.5	—	3	0.5	—	0.031	—	4 oz.	1	6.95	6.49
668271	ValuePro	96.5	—	3.5	—	—	0.04	—	9.6 oz.	1	29.95	26.95
668318	ValuePro	96.5	—	3.5	—	—	0.04	—	1.1 lbs.	1	49.95	44.95
668422	ValuePro	96.5	—	—	—	3.5	—	13	2.2 lbs.	4	49.95	44.95
170457	Various	99.3	—	—	0.7	—	0.031	—	0.8 oz.	2	2.49	2.25
668078	ValuePro	99.3	—	—	0.7	—	0.04	—	7.2 oz.	1	15.95	13.95
209075	Various	99.3	—	—	0.7	—	0.031	—	1 lb.	1	19.95	18.95
668406	ValuePro	99.3	—	—	0.7	—	—	13	2.2 lbs.	4	34.95	31.95

* Organic core † 1. Roll 2. Packet 3. Coil 4. Bar \$ 2.2% Rosin core Blue Part No. = Limited Quantity Available



141786



115433



170465



668297



2113172



170457



139951



263695



2113130



2113156

5' Desolder Braids

★ Web Code: DAG

Part No.	Manufacturer	Mfr. Part No.	Description	Width (ins.)	1	10
139951	Techspray	1814-5F	No-Clean, Military & NASA certified	.030	\$3.59	\$3.29
124126	Techspray	1815-5F	No-Clean, Military & NASA certified	.055	3.59	3.29
124118	Techspray	1816-5F	No-Clean, Military & NASA certified	.075	3.59	3.29
263708	Techspray	1817-5F	No-Clean, Military & NASA certified	.098	3.95	3.59
263695	Techspray	1803-5F	Pro wick, pure rosin	.075	2.95	2.59
263599	Techspray	1804-5F	Pro wick, pure rosin	.098	3.29	2.95
263581	Techspray	1511-5F	Pro wick, pure rosin with bobbin	.098	3.29	2.95
41082	ValuePro	GISW20	Solder braid	.079	1.89	1.69
41100	ValuePro	GISW25	Solder braid	.098	1.99	1.79
153462	ValuePro	GSR104D	Solder braid	.120	2.25	1.95
2113130	Chemtronics	60-3-5	Soder-wick no clean size 3	0.08	3.75	3.49
2113148	Chemtronics	60-4-5	Soder-wick no clean size 4	0.11	4.49	3.95
2113156	Chemtronics	40-3-5	Soder-wick, lead free size 3	0.08	4.25	3.75
2113164	Chemtronics	40-4-5	Soder-wick, lead free size 4	0.11	4.75	4.25

Acid Brush

- Used for application of reactive solvents



Part No.	Description	1	10	100
153322	Metal handle, 6" R	\$.65	\$.55	\$.45

JAMECO ValuePro

Clip-On Heat Sink

- Absorbs and dissipates heat during soldering and desoldering sensitive parts



Part No.	Product No.	Size	1	10	100
159126	HT156	2.7"L x 0.7"W	\$2.95	\$2.59	\$2.29

Tech Closeout Center

Small Quantities Priced Near Cost New Products and Accessories That Didn't Make The Catalog Discontinued Consumer Products And a few surprises...



www.Jameco.com/TechCenter