

## USB 3.0 2-Port PCI Express Card

Can be inserted into an expansion slot of a computer motherboard to add functionality to a computer system.



**NEW**  
MARKED IN PINK

- Supports high-speed data transfer rate up to 5 Gbps (10x faster than USB 2.0)
- Supports USB 3.0 hot-swapping and Plug-and-Play capability
- Dimensions: 3.2"L x 2.7"W x 1.6"H

**System Requirements:** Windows® 2000, XP, Vista, Windows® 7/Mac® OS 10.3 or higher

Part No.	Description	1	10
2119620	USB 3.0 2-port PCI card	\$39.95	\$35.95

## USB 3.0 2-Port PCMCIA Express Card

- Supports high-speed data transfer rate up to 5 Gbps
- Supports USB 3.0 hot-swapping and Plug-and-Play capability
- Dimensions: 4.6"L x 1.6"W x 0.6"H



**NEW**  
MARKED IN PINK

**System Requirements:** Windows® XP, Vista, Windows® 7/Mac® OS 10.3 or higher

Part No.	Description	1	10
2119638	USB 3.0 express card	\$34.95	\$32.95

## USB 2.0 to SATA/IDE Combo Adapter

Keep the existing IDE drive while at the same time migrating to the new SATA technology, which provides a transfer rate of up to 150Mbps. Any SATA or IDE drives can be turned into an external USB 2.0 storage device.



- SATA 1.0a and USB 2.0 compliant
- Dual-headed IDE connector (4- and 44-pin) plus one SATA connector that supports 2.5"/3.5"/5.5"
- Operates one IDE and one SATA HDD simultaneously
- External power supply provided

**System Requirements:** IBM compatible Pentium® 233MHz, USB, Windows® 98SE/ME/XP, MAC OS 8.6 or later

Part No.	Mfr. Part No.	1	5
2075815	AS1200	\$49.95	\$44.95

## USB 2.0 Ethernet Adapter

A high performance, highly integrated USB 2.0 bus Ethernet controller with embedded 7k x 16 bit SRAM.



**\*Web Code: SDR**

- USB 2.0 and 1.1 compliant
- IEEE802.3 (10Base-T) & 802.3u (100Base-TX)
- Supports suspend mode and remote wake up via link-up
- Supports full-duplex and half-duplex operations
- Size: 2.8"L x 2.0"W x 1.3"H

**System Requirements:** IBM compatible Pentium® 233MHz or faster, 64MB or more, USB port available, Windows® XP/2000/Vista 32/64-bit, Mac® OS 10.x

Part No.	Mfr. Part No.	1	5
1944513	AE2201	\$21.95	\$19.95

## USB-A to Mini USB Adapters



2119769      2119777      2119689

- USB 2.0 compliant
- **USB-A to Mini USB 5-Pin Female**
- Data transfer speed: up to 200 Mbps
- Fully shielded to reduce EMI interference sources
- Dimensions: 1.4"L x 0.7"W x 0.4"H

Part No.	Description	1	10
2119769	A male to mini USB	\$2.69	\$2.55
2119777	A female to mini USB	2.69	2.55

**NEW**  
MARKED IN PINK

### USB-A to Mini USB 5-Pin Male

- Metal neck with nickel plating
- Dimensions: 2.0"L x 0.7"W x 0.4"H

Part No.	Description	1	10
2119689	A male to mini USB	\$1.95	\$1.75
2119697	A female to mini USB	1.95	1.75

## USB Gender Adapter

- USB-A female to USB-A female
- Dimensions: 1.5"L x 0.7"W



Part No.	Description	1	10	25
316806	USB-A female	\$2.95	\$2.65	\$2.39

## USB 2.0 Active Repeater Cable

- This is an active repeater cable and not a passive extension cable for connecting USB devices to your computer. The repeater cable regenerates the USB signal for maximum reliability and performance over extended distances at maximum transfer rates of 480Mbps.
- Repeater cable length: 5m (16.4 ft.)
  - Cascaded up to 5 to extend distance to 25m (81 ft.) between USB device and computer
  - Regenerates the USB signal for maximum reliability and performance over extended distances



**Requirements:** Desktop or laptop with available USB port, Windows® 98SE/ME/2000/XP or Mac OS X

Part No.	Cross Ref. No.	1	5
2075840	AR2500	\$13.95	\$12.55

JAMECO ValuePro

## USB 2.0 Cables



- Higher transfer rate up to 480Mbps
- Backward compatible with USB 1.1 products

### USB-A Male to USB-A Male

**\*Web Code: NAV**

Part No.	Description	1	10	25
326474	3' cable beige	\$1.95	\$1.75	\$1.59
229682	6' cable beige	2.05	1.85	1.65
222033	6' cable black	2.05	1.85	1.65
229690	10' cable beige	2.35	2.09	1.85
229569	10' cable clear	2.35	2.09	1.85
222050	15' cable black	3.25	2.95	2.65
229577	15' cable clear	3.25	2.95	2.65

### USB-A Male to USB-B Male

Part No.	Description	1	10	25
229711	3' cable beige	\$1.95	\$1.75	\$1.59
222608	3' cable black	1.95	1.75	1.59
229585	3' cable clear	1.95	1.75	1.59
229730	6' cable beige	2.05	1.85	1.65
222010	6' cable black	2.05	1.85	1.65
229594	6' cable clear	2.05	1.85	1.65
229738	10' cable beige	2.35	2.09	1.85
222018	10' cable black	2.35	2.09	1.85
229607	10' cable clear	2.35	2.09	1.85
229762	15' cable beige	3.25	2.95	2.65
222026	15' cable black	3.25	2.95	2.65
229614	15' cable clear	3.25	2.95	2.65

### USB-A Male to USB-A Female

Part No.	Description	1	10	25
326482	3' cable beige	\$1.95	\$1.75	\$1.59
229771	6' cable beige	2.05	1.85	1.65
222068	6' cable black	2.05	1.85	1.65
229623	6' cable clear	2.05	1.85	1.65
229789	10' cable beige	2.45	2.19	1.95
222076	10' cable black	2.45	2.19	1.95
229631	10' cable clear	2.25	1.95	1.75
229797	15' cable beige	3.25	2.95	2.65
222084	15' cable black	3.25	2.95	2.65

### USB-A Male

- For use w/ digital cameras, memory card readers, etc.
- Color: black



Part No.	Description	1	10	25
673715	6' mini 4-pin	\$3.95	\$3.59	\$3.39
2081481	5'6" mini 5-pin	2.25	1.95	1.65
673694	6' mini 5-pin	2.75	2.45	2.25

## USB 3.0 Cables

### USB-A Male to USB-B Male

- SuperSpeed with 5Gbps data transfer rate
- 10X performance increase over USB 2.0
- Hot syncing
- SuperSpeed USB is backwards compatible with USB 2.0



Part No.	Description	1	10	25
2095218	6' cable black	\$6.95	\$6.25	\$5.49
2095226	10' cable black	7.95	7.15	6.49

## Helping You Find What You Need



Can't find the product you're looking for?

Call us at  
1-800-831-4242.

**\*For Complete Specs & Additional Product Listings Search [www.Jameco.com/More](http://www.Jameco.com/More) and Enter Web Code Listed Above**