

High Speed USB Extender Cable

An active device where the USB signals going in and out of the extension cable are buffered to assure signal quality and adherence to electrical and timing specs.




- Full compliance with USB spec Ver. 2.0/1.1
- Supports 480Mbit/s high speed 12Mbit/s full speed, and 1.5Mbit/s low speed serial data communication
- One upstream port and one downstream port
- Windows® 98 & higher or Mac® OS compatible
- Supports plug & play and hot-swap functions
- USB-A male to USB-A female
- Bus power mode • Length: 16 ft.

Part No.	Cross Ref. No.	1	5
1919174	10U2-24116	\$18.95	\$16.95

JAMECO ValuePro Serial Null Modem Cables

- Molded type connectors
- Color: gray
- 181404/180698 Pin outs: 1 & 6-4, 2-3, 3-2, 4-6 & 1, 5-5, 7-8, 8-7



- 181438 Pin outs: 2-2; 3-3; 5 & 6-4; 7-5; 8-7; 20-6 & 8 (Serial printer null modem)



- 180582 Pin outs: 2-2; 3-3; 4-5 & 6; 5-7; 6 & 8-20; 7-8; (Serial printer null modem)



- 180742 Pin outs: 1-4 & 5; 2-2; 3-3; 4-6; 5-7; 6-20; 7-8; 8-8



Part No.	Mfr.	Description	1	10	50
181404	ValuePro	6' DB9 F to DB9 F	\$5.55	\$4.95	\$4.49
180698	ValuePro	10' DB9 F to DB9 F	6.75	5.95	5.45
181438	Various	6' DB25 M to DB9 F	5.55	4.95	4.49
180742	ValuePro	10' DB25 F to DB9 F	6.95	6.25	5.65
180582	ValuePro	10' DB25 M to DB9 F	5.95	5.35	4.75

JAMECO ValuePro IEEE Firewire Cables



- IEEE-1394 compliant
- Length: 6'
- UL approved
- Male to male

*Web Code: FAE

Part No.	Cross Ref. No.	Description	1	5	25
1944134	10E4-991-06-C	9-pin/9-pin	\$16.95	\$15.25	\$13.75
175848	10E3-01106-R	6-pin/6-pin	5.95	5.35	4.75
175839	10E3-02106-R	4-pin/6-pin	2.95	2.65	2.39

JAMECO ValuePro IEEE 488 Cables

A variety of cable lengths are offered to ensure that IEEE system requirements are met (20 meters max. length with a maximum of 15 devices). These cables are standard IEEE 488 with stackable 24-pin GPIB connectors on both ends.



*Web Code: EAJ

Part No.	Description	Color	1	5	25
73155	1 meter	Gray	\$39.95	\$35.95	\$31.95
115782	2 meter	Gray	41.95	36.95	32.95
115802	4 meter	Gray	42.95	37.95	33.95

19" Rack Mount Enclosures

- Ventilation holes on all sides
- Front and back panels are steel w/ aluminum, pre-punched face plates
- 0.12" thick black front panel
- Top, bottom and sides are durable 0.035" steel
- All enclosures have handles except P/N 132813



Includes: Mounting screws

Part No.	Dimensions (In.)			Wt. (lbs.)	Pricing	
	H1	H2	D		1	5
132813	1.73	1.25	9.75	6.2	\$39.95	\$35.95
132822	3.46	3.00	9.75	7.9	51.95	46.95
132840	3.46	2.88	11.75	9.1	54.95	49.95
132848	5.22	4.75	11.75	10.6	59.95	53.95
132864	8.56	8.00	13.50	15.4	109.95	99.95

*Rack Mounts Available Online — Enter Web Code GAT

19" Rack Mount Cat 5 Patch Panel

These Cat 5 patch panels feature 110D punch locks that are compatible with KRONE or 110D tools. UL and CUL listed and certified. Cat 5 certified and can be used with T568 A/B installations, color coded blocks for T568 color coding.



*Web Code: GBK

Part No.	Description	1	5
208785	24-port patch panel	\$24.95	\$22.49

19" Rack Mount Enclosure for 14" Monitor

- Clear glass front panel
- Hinged door for accessing monitor controls
- Color: gray
- Size: 19.0"W x 15.1"D x 14.0"H
- Weight: 30 lbs.



Monitor not included

Part No.	Product No.	Price
136021	IAC-C910	\$119.95

QuickNetwork Install Can

- Type: Install can for QuickNetwork panels
- Feature: power supply and cover installed
- Size: 24"



Part No.	Mfr. Part No.	1	5
636607	QN24	\$59.95	\$49.95

Cable Assemblies

Part No.	Mfr.	Length	1	10	50
262730/262748	ValuePro	25'	\$6.95	\$6.25	\$5.49
262748	ValuePro	50'	8.95	7.95	7.25

Part No.	Mfr.	Length	1	5
1581409	Elyssa	100'	\$24.95	\$22.45

Part No.	Mfr.	Length	1	5
1581409	Elyssa	100'	\$24.95	\$22.45

Part No.	Mfr.	Length	1	10
85585	ValuePro	3'	\$.49	\$.45

Cabinet Mounting Plate for 19" Cabinet

- Use as industrial chassis mounting plate for servers, PCs or patch panels
- Size: 19.0"W x 15.8"D x 3.5"H
- Made of industrial grade steel and aluminum



Part No.	Product No.	1	10
149500	UP02	\$34.95	\$31.95

JAMECO ValuePro USB-A Cables w/ Bracket

- Supports data transfer rates of 12Mbps
- Allows connection of two devices
- Dual USB-A female connectors • 8" long



Part No.	Description	1	10	25
144813	Female panel mount	\$4.25	\$3.75	\$3.25
319652	Male panel mount	1.49	1.35	1.19

JAMECO ValuePro USB-to-DB9 Serial Adapters

- USB-A to DB9 male
- Length: 13"
- Supports automatic handshake mode
- Over 230kpbs data transfer rate
- 96 byte buffer each for upstream and downstream data flow
- Works with cellphones, PDA, digital cameras, modems and ISDN terminal adapters



Part No.	Description	1	10	5
387954	With jack screws	\$18.95	\$16.95	
2115346	With thumbscrews	18.95	16.95	

JAMECO ValuePro SCSI Cable


- 50-pin header socket ribbon cable SCSI-I



Part No.	Description	1	10	100
32715	18" ribbon cable	\$3.75	\$3.49	\$2.95

Ribbon Cable Assemblies

- Metal connector
- 28 AWG flat cable
- 105°C rating
- 300V rating
- Tin-plated contacts



Part No.	Description	1	10	100
12408	4' DB25 M-F	\$4.95	\$4.45	\$3.95
208582	6' DB9 M-F (ValuePro)	4.95	4.45	3.95

AT/ATX Power Supply Extension Cable

- For use with ATX power supplies
- 20-pin ATX male and female connectors
- Color coded to ATX power supply



Part No.	Length	AWG	1	10	100
170238	15"	18	\$8.95	\$7.95	\$6.95

JAMECO ELECTRONICS Product Search

Quick and Easy Search

Our enhanced website offers thousands of datasheets and photos to assist you in finding the products you need.