

# Electrolytic & Dipped Tantalum Capacitors


3 LEVELS OF SAVINGS  
NAME BRANDS HOUSE BRANDS FACTORY OVERRUN

JAMECO ValuePro

## Aluminum Axial-Lead Electrolytic Capacitors (±20%) 85°C



Operating temperature range	-40°C to +85°C
Leakage Current (After 2 minutes 20°C)	0.02CV or 2µA, whichever is greater



\* Web Code: GAA

\* Order in multiples 10

Part No.	Product No.	Mfr.	Value (µF)	Voltage	Size (mm)* D x H	Pricing			
						1	10	100	500
10866	A1/50	◆	1	50V	5 x 13	*	\$.17	\$.14	\$.11
10868	A1/50	JVP	1	50V	5 x 12	.29	.22	.17	.14
93569	A2.2/50	◆	2.2	50V	6 x 13	*	.15	.12	.09
11076	A4.7/50	◆	4.7	50V	6 x 13	*	.17	.14	.11
1946201	A10/16A	◆	10	16V	5 x 13	*	.06	.04	.03
1946199	A10/16	◆	10	16V	4 x 7	*	.08	.04	.03
10882	A10/50	◆	10	50V	6 x 12	*	.15	.12	.09
10884	A10/50	JVP	10	50V	6 x 12	*	.15	.12	.09
331425	AB10/450	JVP	10	450V	13 x 25	.95	.75	.59	.49
1946210	A22/16	◆	22	16V	5 x 11	*	.09	.05	—
199268	A22J/25	JVP	22	25V	6 x 12.5	*	.15	.12	.09
331433	AB22/450	JVP	22	450V	16 x 26.5	1.75	1.49	1.25	.99
2081730	A33/35	JVP	33	35V	7 x 14	*	.12	.09	.07
135319	A47/25	◆	47	25V	8 x 16	*	.17	.14	.11
199188	A100J/16	JVP	100	16V	6 x 12.5	.29	.22	.17	.14
199284	A100J/25	JVP	100	25V	8 x 15	*	.19	.15	.12
93551	A100/35	◆	100	35V	8 x 16	.29	.22	.17	.14
10911	A100/50	◆	100	50V	8 x 20	.29	.22	.17	.14
10913	A100/50	JVP	100	50V	8 x 16	.32	.25	.19	.15
331380	AB100/100	JVP	100	100V	10 x 20.5	.45	.39	.35	.29

\* Capacitor dimensions and styles may vary on items with various manufacturers

Part No.	Product No.	Mfr.	Value (µF)	Voltage	Size (mm)* D x H	Pricing			
						1	10	100	500
331417	AB100/250	JVP	100	250V	16 x 31	\$2.49	\$2.25	\$1.95	\$1.75
11019	A220/50	JVP	220	50V	10 x 17	.49	.39	.32	.27
199217	A470J/16	JVP	470	16V	8 x 17	.35	.29	.22	.17
199381	A470J/35	JVP	470	35V	10 x 21	.39	.32	.25	.19
11123	A470/50	JVP	470	50V	13 x 22	.75	.59	.49	.39
93633	A1000/16	JVP	1000	16V	10 x 21	.35	.29	.25	.19
10954	A1000/25	◆	1000	25V	13 x 31	.65	.49	.39	.32
10956	A1000/25	JVP	1000	25V	10 x 20	.75	.59	.49	.39
93649	A1000/35	◆	1000	35V	13 x 26	.75	.59	.49	.39
93651	A1000/35	JVP	1000	35V	13 x 22	.85	.69	.59	.49
147256	A1000/50	◆	1000	50V	16 x 31	.75	.59	.49	.39
11033	A2200/16	◆	2200	16V	16 x 40	.85	.69	.59	.49
93658	A2200/35	JVP	2200	35V	16 x 30	1.25	.99	.79	.65
199479	A2200J/50	JVP	2200	50V	18 x 33	1.95	1.75	1.49	1.25
93666	A3300/25	JVP	3300	25V	16 x 30	.85	.65	.55	.49
199487	A3300J/50	JVP	3300	50V	22 x 43	2.49	2.25	1.95	1.75
93673	A4700/25	JVP	4700	25V	22 x 39	1.35	1.15	.95	.75
158811	A4700A50	JVP	4700	50V	22 x 43	2.49	2.25	1.95	1.75
93681	A10000/16	◆	10000	16V	22 x 51	1.95	1.75	1.49	1.25
93683	A10000/16	JVP	10000	16V	16 x 40	1.95	1.75	1.49	1.25


Passives

JAMECO ValuePro

## Resin Dipped Solid Tantalum Capacitors (±10%)

- Operating temperature range: -55°C to +85°C (+125°C with derating)
- Exceptional temperature stability
- Flame retardant coating
- Designed for entertainment and commercial equipment
- Rated voltage DC: ≤ +85°C
- Moisture-resistant
- Low leakage current

\* Web Code: VAE



\* Order in multiples 10

Part No.	Product No.	Mfr.	Value (µF)	Voltage (V)	Size (mm)* D x H x L.S.	Pricing			
						1	10	100	500
33486	TM.1/35	◆	.10	35	4.5 x 7.0 x 5.2	\$.32	\$.25	\$.19	\$.15
33488	TM.1	JVP	.10	35	4.5 x 7.0 x 2.5	.39	.32	.25	.19
545561	TAP104K035SCS	JVP	.10	35	4.0 x 6.0 x 2.5	.39	.32	.25	.19
545570	TAP104K050SCS	JVP	.10	50	4.0 x 6.0 x 2.5	*	.19	.15	.12
33507	TM.22/35	◆	.22	35	4.5 x 7.0 x 5.0	.32	.25	.19	.15
33523	TM.33/35	◆	.33	35	4.5 x 7.0 x 2.5	.32	.25	.19	.15
33525	TM.33	JVP	.33	35	4.5 x 7.0 x 2.5	.39	.32	.25	.19
33531	TM.47/35	◆	.47	35	4.5 x 7.0 x 2.7	.32	.25	.19	.15
33533	TM.47	JVP	.47	35	4.5 x 7.0 x 2.5	.39	.32	.25	.19
61102	TM.68	JVP	.68	35	4.5 x 7.0 x 2.5	*	.12	.09	.07
546142	TAP684K050SCS	JVP	.68	50	4.3 x 7.0 x 2.5	*	.19	.15	.12
154860	TM1/25	◆	1	25	4.5 x 7.0 x 4.7	.32	.25	.19	.15
545588	TAP105K025SCS	JVP	1	25	4.3 x 7.0 x 2.5	.39	.32	.25	.19
154862	TM1/25	JVP	1	25	4.5 x 7.0 x 2.5	.39	.32	.25	.19
33662	TM1/35	◆	1	35	4.5 x 7.0 x 2.7	.35	.29	.22	.17
545596	TAP105K035SCS	JVP	1	35	4.3 x 7.0 x 2.5	.39	.32	.25	.19
33664	TM1	JVP	1	35	4.5 x 7.0 x 2.5	.39	.32	.25	.19
545609	TAP105K050SCS	JVP	1	50	4.7 x 7.5 x 2.5	.59	.55	.45	.29
94001	TM2.2/16	◆	2.2	16	4.5 x 7.0 x 4.7	.32	.25	.19	.15
94003	TM2.2/16	JVP	2.2	16	4.5 x 7.0 x 2.5	.35	.25	.22	.17
33736	TM2.2/35	JVP	2.2	35	5.0 x 8.0 x 2.5	.35	.29	.22	.17
332152	TDR2.2/50	JVP	2.2	50	6.5 x 11 x 2.5	.49	.45	.39	.35
545941	TAP335K025SCS	JVP	3.3	25	4.3 x 7.0 x 2.5	.45	.35	.29	.22
545967	TAP335K050SCS	JVP	3.3	50	5.4 x 8.0 x 2.5	.59	.49	.39	.35
94035	TM4.7/16	◆	4.7	16	5.0 x 8.0 x 2.5	.35	.29	.22	.17

Note: Above case sizes may have ± tolerances

\* Capacitor dimensions and styles may vary

\* Order in multiples 10

Part No.	Product No.	Mfr.	Value (µF)	Voltage (V)	Size (mm)* D x H x L.S.	Pricing			
						1	10	100	500
94043	TM4.7/25	◆	4.7	25	5.0 x 8.0 x 4.7	\$.45	\$.35	\$.29	\$.22
546071	TAP475K025SCS	JVP	4.7	25	4.3 x 7.0 x 2.5	.55	.45	.35	.29
33806	TM4.7/35	◆	4.7	35	5.5 x 9.5 x 2.5	.49	.39	.32	.25
546089	TAP475K035SCS	JVP	4.7	35	4.7 x 7.5 x 2.5	.59	.49	.39	.32
546185	TAP685K025SCS	JVP	6.8	25	4.7 x 7.5 x 2.5	.49	.39	.32	.25
33873	TM6.8/35	◆	6.8	35	6.5 x 9.0 x 4.7	.45	.35	.29	.22
545617	TAP106K006SCS	JVP	10	6.3	4.3 x 7.0 x 2.5	.32	.25	.19	.15
545625	TAP106K010SCS	JVP	10	10	4.7 x 7.5 x 2.5	.49	.39	.32	.25
94060	TM10/16	◆	10	16	4.6 x 7.5 x 3.2	.49	.39	.32	.25
94062	TM10/16	JVP	10	16	5.0 x 8.0 x 2.5	.55	.45	.35	.29
545633	TAP106K020SCS	JVP	10	20	5.4 x 8.0 x 2.5	.45	.35	.29	.25
94078	TM10/25	◆	10	25	5.5 x 9.5 x 2.8	.55	.45	.35	.29
545641	TAP106K025SCS	JVP	10	25	5.4 x 8.0 x 2.5	.55	.45	.35	.29
94080	TM10/25	JVP	10	25	5.5 x 9.5 x 2.5	.59	.49	.39	.32
33689	TM10/35	◆	10	35	6.5 x 11.0 x 4.7	.99	.79	.65	.49
545650	TAP106K035SCS	JVP	10	35	5.4 x 8.0 x 2.5	1.15	.95	.79	.65
33691	TM10	JVP	10	35	5.5 x 11.0 x 2.5	1.15	.95	.79	.65
332161	TDR10/50	JVP	10	50	8.5 x 13.0 x 2.5	2.49	2.25	1.95	1.75
545721	TAP156K010SCS	JVP	15	10	4.7 x 7.5 x 2.5	*	.15	.12	.09
545748	TAP156K020SCS	JVP	15	20	5.4 x 8.0 x 2.5	.35	.29	.25	.19
33719	TM15/25	JVP	15	25	4.5 x 8.0 x 2.5	.79	.65	.49	.39
597468	TAP156K035SCS	JVP	15	35	5.5 x 9.5 x 4.7	.99	.89	.79	.69
33751	TM22/6.3	◆	22	6.3	4.7 x 7.5 x 2.5	.29	.25	.19	.15
94094	TM22/16	◆	22	16	5.5 x 9.5 x 4.1	.55	.45	.35	.29
94095	TM22/16	JVP	22	16	5.5 x 9.5 x 2.5	.55	.45	.35	.29
545852	TAP226K016SCS	JVP	22	16	5.4 x 8.0 x 2.5	.69	.55	.45	.35

Capacitors continued on next page

\* JVP = Jameco ValuePro | ◆ Manufacturer Varies

RoHS compliant product + This product is available in both RoHS and non-RoHS versions. Add an "R" before part number for RoHS version. Details on page 197.