

Paired & Flat Ribbon Cable

3 LEVELS OF SAVINGS
NAME BRANDS **HOUSE BRANDS** **FACTORY OVERRUN**



Paired Cable

*Web Code: HCS

Part No.	Product No.	Fig.	AWG/Drain Wire	# of Pairs	Length	Jacket	Wire Color	Insul.	Pricing	
									1	5
733172	8720 060100	1	14 / 16	1	100' Reel	Chrome/PVC	Black/Clear	B	\$84.95	\$79.95
733190	8720 060500	1	14 / 16	1	500' Reel	Chrome/PVC	Black/Clear	B	369.95	349.95
734066	8720 060U500	1	14 / 16	1	500' Unreel	Chrome/PVC	Black/Clear	B	369.95	349.95
233146	8714 060100	1	16 / 18	1	100' Reel	Chrome/PVC	Black/Clear	B	69.95	63.95
734065	8719 060U500	1	16 / 18	1	500' Unreel	Chrome/PVC	Black/Clear	B	259.95	239.95
733163	8719 0601000	1	16 / 18	1	1000' Reel	Chrome/PVC	Black/Clear	B	549.95	529.95
734185	8790 060100	1	18 / 24	1	100' Reel	Chrome/PVC	Black/Clear	B	41.95	39.95
234194	8762 060100	1	20 / 20	1	100' Reel	Chrome/PVC	Black/Clear	B	29.95	26.95
734197	8762 060500	1	20 / 20	1	500' Reel	Chrome/PVC	Black/Clear	B	129.95	119.95
733112	8451 010100	3	22 / 22	1	100' Reel	Black/PVC	Black/Red	A	26.95	24.95
734063	8451 010U500	3	22 / 22	1	500' Unreel	Black/PVC	Black/Red	A	129.95	115.95
734180	8723 060100	2	22 / 24	2	100' Reel	Chrome/PVC	Black/Red, Green/White	A	49.95	46.95
734184	8723 060U500	2	22 / 24	2	500' Unreel	Chrome/PVC	Black/Red, Green/White	A	199.95	189.95
734181	8723 0601000	2	22 / 24	2	1000' Reel	Chrome/PVC	Black/Red, Green/White	A	399.95	379.95
734179	1419A 060100	4	24 / 24	2	100' Reel	Chrome/PVC	Wh/Blue Str, Blue/Wh Str, Wh/Org Str, Org/Wh Str	D	29.95	26.95
734085	1419A 0601000	4	24 / 24	2	1000' Reel	Chrome/PVC	Wh/Blue Str, Blue/Wh Str, Wh/Org Str, Org/Wh Str	D	279.95	259.95



Fig. 1



Fig. 2



Fig. 3



Fig. 4



Fig. 5

A = Polypropylene
 B = Polyethylene
 C = Semi-rigid PVC
 D = Datalene E = Standard PVC
 Wh = White Blk = Black
 Org = Orange Str = Stripe

Wire & Cable



Flat Ribbon Cable

Gray Cable — 28AWG (7 x 36)

*Web Code: WBX



- Insulation: polyvinyl chloride (PVC)
- Single edge red stripe for pin 1 orientation

Part No.	Cross Ref. No.	Conductors	Length	1	5	25
643794	171-10-10	10	10'	\$2.79	\$2.49	\$2.19
643807	171-10-25	10	25'	5.49	5.25	4.99
643815	171-10-100	10	100' reel	17.95	15.95	14.95
689311	9L2801000RH*	10	100' reel	25.95	23.95	21.95
643831	171-16-10	16	10'	3.95	3.59	3.29
643840	171-16-25	16	25'	7.95	6.95	6.29
643858	171-16-100	16	100' reel	23.95	21.95	19.95
643874	171-20-10	20	10'	3.95	3.59	3.29
643882	171-20-25	20	25'	8.95	7.95	6.95
643891	171-20-100	20	100' reel	32.95	29.95	26.95
643911	171-25-10	25	10'	4.95	4.49	3.95
643920	171-25-25	25	25'	10.95	8.95	7.95
643938	171-25-100	25	100' reel	36.95	33.95	29.95
643962	171-26-10	26	10'	5.95	5.49	4.95
643971	171-26-25	26	25'	11.95	10.95	9.95
643989	171-26-100	26	100' reel	39.95	36.95	33.95
644033	171-34-10	34	10'	6.49	5.95	5.49
644041	171-34-25	34	25'	12.95	11.95	10.95
644050	171-34-100	34	100' reel	51.95	49.95	47.95
644076	171-37-10	37	10'	6.95	6.29	5.59
644084	171-37-25	37	25'	12.95	11.95	10.95
644092	171-37-100	37	100' reel	49.95	44.95	42.95
644113	171-40-10	40	10'	7.95	6.95	6.29
644121	171-40-25	40	25'	15.95	14.49	12.95
644130	171-40-100	40	100' reel	55.95	52.95	49.95
644156	171-50-10	50	10'	8.95	7.95	6.95
644164	171-50-25	50	25'	17.95	16.49	14.95
644172	171-50-100	50	100' reel	59.95	56.95	52.95
689426	9L28050008H100*	50	100' reel	119.95	109.95	99.95
644199	171-60-10	60	10'	9.95	8.95	7.95
644201	171-60-25	60	25'	17.95	16.95	14.95
644210	171-60-100	60	100' reel	64.95	59.95	54.95

*Belden: -40°C to +105°C

• Prepackaged and priced in lengths listed below

Multicolor Cable — 28AWG (7 x 36)



- Standard 10-color repeat sequence
- Voltage rating: 300V • Stranded copper wire
- Center spacing: 0.05" • Temp. rating: -20°C to +80°C

*Web Code: WCF

Part No.	Cross Ref. No.	Conductors	Length	1	5	25
639672	28RC10-10	10	10'	\$3.95	\$3.59	\$3.19
643508	28RC10-25	10	25'	8.95	7.95	6.95
643516	28RC10-100	10	100' reel	29.95	27.95	24.95
643532	28RC16-10	16	10'	5.95	5.49	4.95
643541	28RC16-25	16	25'	12.95	11.95	10.95
643559	28RC16-100	16	100' reel	49.95	44.95	39.95
643575	28RC20-10	20	10'	6.95	6.49	5.95
643583	28RC20-25	20	25'	16.95	15.49	13.95
643591	28RC20-100	20	100' reel	64.95	59.95	54.95
643612	28RC25-10	25	10'	8.95	7.95	6.95
643621	28RC25-25	25	25'	22.95	20.95	18.95
643639	28RC25-100	25	100' reel	69.95	64.95	59.95
643655	28RC34-10	34	10'	10.95	9.95	8.95
643663	28RC34-25	34	25'	25.95	23.95	21.95
643671	28RC34-100	34	100' reel	89.95	84.95	79.95
643698	28RC40-10	40	10'	12.95	11.95	10.95
643701	28RC40-25	40	25'	33.95	29.95	26.95
643719	28RC40-100	40	100' reel	119.95	109.95	99.95
643735	28RC50-10	50	10'	19.95	17.95	15.95
643743	28RC50-25	50	25'	39.95	36.95	33.95
643751	28RC50-100	50	100' reel	145.95	135.95	129.95

⊕ Blue Part No. = Limited Quantity Available

Flat Ribbon Cable – Gray

*Web Code: WBX

.100" (2.54mm) — 24AWG

- Capacitance: 31pF/m
- Insulation resist.: 100MΩ • Temp. rating: 105°C
- Insulation material: 7mm polyvinyl chloride (PVC) gray



Part No.	Mfr.	Cross Ref.	Conductor	Length	1	5	25
363813	Various	H24G-10-10	10	10'	\$9.95	\$8.95	\$7.95
363856	ValuePro	H24G-10-100	10	100'	69.95	63.95	59.95

Ⓡ RoHS compliant product + This product is available in both RoHS and non-RoHS versions. Add an "R" before part number for RoHS version. Details on page 197.

