

Cable Accessories, Braided Sleeves & Heat Shrink Tubing

3 LEVELS OF SAVINGS
NAME BRANDS **HOUSE BRANDS** **FACTORY OVERRUN**

Cable Tie Mounts & Cable Clamps

- Tie mount and screw tab cable clamps
- Material: UL approved nylon 66, 94V-2

RU *Web Code: **FBE**



Part No.	Cross Ref. No.	Description	* Order in multiples of 10	1	10	100	1000
182942/171214/71408/71395/71386	70595	182301/173761	182334	173737	71062		
182942	0505HC-101S	4-way cable tie mount, self-adhesive, .75"D	*	\$1.10	\$0.09	\$0.08	
171214	HC-100	4-way cable tie mount, self-adhesive, use w/ 0.1"W max., 0.5" square	*	.16	.14	.13	
71408	HC-101	4-way cable tie mount, self-adhesive, use w/ 0.1"W max., 0.9" square	*	.19	.17	.15	
71395	HC-102	4-way cable tie mount, self-adhesive, use w/ 0.2"W max., 1.1" square	*	.25	.23	.19	
71386	HC-103	4-way cable tie mount, self-adhesive, use w/ 0.4"W max., 1.1" square	*	.37	.33	.29	.27
70595	HC-0	4-way cable tie, screw type, use w/ 0.2"W max., 0.8"L x 0.4"W	*	.19	.17	.15	
182301	0510HC-2	Cable tie mount, 1/4" screw hole, 0.5"D	*	.17	.15	.14	
173761	HC-1	Cable tie, saddle type, 0.6"L x 0.4"W	*	.10	.09	.08	
182318	0519ATC-17	2-way adjustable tie mount, #6 flat head screw, 0.7"D	*	.29	.27	.25	
182376	0519ATC-22	2-way adjustable tie mount, #6 flat head screw, 0.9"D	*	.21	.19	.15	
182334	0520FC-1	Cable tie mount, self-adhesive, 0.1"D	*	.19	.17	.14	
173729	UC0.5	Cable clamp for 3/16" cable	*	.08	.06	.04	
173737	UC1	Cable clamp for 1/4" cable	*	.11	.10	.09	
71062	MCV-100R	Cable ID tie (4"L x 0.1"W) with tab (.98"W x .31"H)	*	.29	.27	.23	

Wire & Cable

Polyolefin Heat Shrink Tubing

alpha FIT221/FIT221B Series

Insulation from environment and resistance from water fungus and UV light. Use for insulation and repair, wire and cable harnessing/bundling, cable and connector protection, and wire and tubing splicing and connecting.

- Operating temp: -55°C to 135°C
- Shrinkage ratio: 2:1 @ 121°C
- Dielectric strength: 500V/mil (197kV/cm)
- Volume resistivity: 10¹⁴Ω-cm

*Web Code: **VAH**

Clear (4-foot pieces)

Part No.	Mfr. Part No.	Before/After ID (in.)	1	10	100
419119	FIT221-3/64	.046/.023	\$.85	\$.79	\$.65
419135	FIT221-1/16	.063/.031	.95	.85	.75
419178	FIT221-1/8	.125/.062	1.19	1.05	.95
419215	FIT221-1/4	.250/.125	2.25	1.95	1.75
419231	FIT221-3/8	.375/.187	1.79	1.59	1.39
419274	FIT221-3/4	.750/.375	2.69	2.49	—
2113682	TT-100	1.00/.500	3.95	3.69	—

Black (4-foot pieces)

419101	FIT221B-3/64	.046/.023	\$.89	\$.79	\$.69
419127	FIT221B-1/16	.063/.031	.99	.89	.79
419143	FIT221B-3/32	.093/.046	.99	.89	.79
419160	FIT221B-1/8	.125/.062	.99	.89	.79
419186	FIT221B-3/16	.187/.093	1.25	1.09	.99
419207	FIT221B-1/4	.250/.125	1.85	1.69	1.49
419223	FIT221B-3/8	.375/.187	1.95	1.75	1.59
419240	FIT221B-1/2	.500/.250	1.95	1.75	1.59

Black (6-inch pieces)

Part No.	Mfr. Part No.	Before/After ID (in.)	Bags of	1	5
419400	FIT221B-1/16	.063/.031	36	\$14.75	\$13.29
419549	FIT221B-3/4	.750/.375	12	14.75	13.29

FLEXO® Braided Sleeve

- Color: black
- Length: 25 feet
- Cut and abrasion resistant
- Maintains properties across wide temperature range
- UV resistant

Flexo® Clean-Cut Braided

*Web Code: **EQC**

- Dense braid structure provides fuller coverage
- Fray resistant when cut w/ scissors

Part No.	Mfr. Part No.	Min/Max Flex (in.)	Inside Dia. (in.)	Outside Dia. (in.)	1	5
162157	CCP0.25BK25	5/32 - 7/16	0.250	0.440	\$15.95	\$14.49
162165	CCP0.50BK25	1/4 - 3/4	0.500	0.750	17.95	15.95

Flexo® Pet Braided

*Web Code: **TFP**

- Braided from 10 mil polyethylene terephthalate monofilament yarns
- UL recognized component
- Conforms to FMVSS 302
- High tensile strength

Part No.	Mfr. Part No.	Min/Max Flex (in.)	Inside Dia. (in.)	Outside Dia. (in.)	1	5
693679	PTNO.25BK25	1/8 - 7/16	0.250	0.440	\$7.95	\$6.95
693687	PTNO.38BK25	3/16 - 5/8	0.375	0.425	11.95	10.95
695383	PTNO.50BK25	1/4 - 3/4	0.500	0.550	11.95	10.75

Low Profile Conduit

No more tripping or running over cables and cords. This low profile conduit hides cables/cords and provides cable management at the same time.

Simply install on any wall or floor with its double-sided tape.

- 5 feet long



Part No.	Description	1	5
2112479	Low profile conduit	\$19.95	\$17.95

Round-Type Strain Relief Bushings

- UL approved nylon 66, 94V-2
- Used extensively for protecting cords and to prolong cord life
- Order in multiples of 10



Part No.	Cable Type	Length (in.)	10	100	1000
182351	SVI/SVT	.43	\$.08	\$.07	\$.05
182369	SJ/SJT; 16 AWG	.58	.12	.10	.08

Part No.	Description	1	10
73471	Bushing tool	\$34.95	\$29.95

Blue Part No. = Limited Quantity Available

Heat Shrink Tubing Kits

A selection of heat shrinkable flexible polyolefin tubing that offers an outstanding balance of electrical, physical and chemical properties for a wide variety of industrial and military applications. Rated for 275°F (135°C).

2095971		2095963		285481		2095947		645976	
Size	Pieces	Size	Pieces	Size	Pieces	Size	Pieces	Size	Pieces
1/8"	12	1/16"	56	3/16"	30	1/16"	56	3/32"	35
1/4"	10	3/32"	35	1/4"	28	3/32"	35	1/8"	28
3/8"	6	1/8"	28	3/8"	20	1/8"	28	3/16"	21
1/2"	4	3/16"	18	1/2"	14	3/16"	18	1/4"	21
3/4"	3	1/4"	9	3/4"	6	1/4"	9	3/8"	14
1"	2	3/8"	8	1"	4	3/8"	8	1/2"	14

Part No.	Mfr.	Description	Pieces	Length	1	5
2095971	ValuePro	Black, dual wall, moisture resistant	37	4	\$24.95	\$22.49
2095963	ValuePro	Black	154	4	19.95	17.95
285481	3M	Black	102	6	65.95	58.95
2095947	ValuePro	Black/red/white/yellow/blue/green/clear	154	4	19.95	17.95
645976	3M	Black/red/white/yellow/blue/green/clear	133	6	65.95	58.95



*Web Code: **HST**

Heat Shrink Tubing

- 2:1 uniform shrink ratio
- Shrink temp.: 90°C
- Color: black

Polyolefin Tubing

- Only sold in 10' & 100' lengths

*Web Code: **HST**

Part No.	Dia. Before (mm)	Length (ft.)	1	10
644834	0.12" (3)	10	\$1.95	\$1.75
644851	0.12" (3)	100	12.65	11.49
644869	0.16" (4)	10	2.15	1.95
644877	0.16" (4)	100	19.95	17.95
644906	0.20" (5)	10	2.45	2.19
644914	0.20" (5)	100	21.45	19.29
644931	0.24" (6)	10	2.55	2.29
644949	0.24" (6)	100	21.75	19.59
644957	0.31" (8)	10	2.95	2.65
644965	0.31" (8)	100	31.95	28.75
644973	0.43" (11)	10	3.95	3.55
644981	0.43" (11)	100	35.95	32.35
644990	0.59" (15)	10	4.95	4.45

Polyolefin Flexible Tubing

- Dielectric strength: 1300V
- Temp. range: -45°C to +125°C
- Flame retardant
- Precut 39" length (1 meter)

Part No.	Dia. Before (mm)	1	10	100
71327	.059" (1.5)	\$.55	\$.49	\$.45
71871	.079" (2.0)	.55	.49	.45
71280	.098" (2.5)	.95	.85	.75
72063	.197" (5.0)	.85	.75	.69

RoHS compliant product + This product is available in both RoHS and non-RoHS versions. Add an "R" before part number for RoHS version. Details on page 197.