

D-Subminiature Connectors

3 LEVELS OF SAVINGS
NAME BRANDS **HOUSE BRANDS** **FACTORY OVERRUN**

D-Subminiature Connectors


Right Angle PCB Mount *Web Code: FAN
 Metal .318" Setback – Tin plated short style



Part No.	Manufacturer	Product No.	Contacts	Gender	1	10	100
1952839	Foxconn	D-SUB-9M+†	9	M	\$.55	\$.45	\$.35
104943	ValuePro	DB9P318R	9	M	\$.69	\$.59	\$.49
614441	AMP	747840-4†	9	M	1.49	1.35	1.19
2076682	Various	DB9S318	9	F	\$.65	\$.55	\$.45
104952	ValuePro	DB9S318R	9	F	\$.75	\$.65	\$.55
614504	AMP	747844-4†	9	F	1.95	1.75	1.49
614125	AMP	745781-4	9	F	1.95	1.75	1.55
71124	ValuePro	DA15P318†	15	M	\$.69	\$.59	\$.49
71125	ValuePro	DA15P318R†	15	M	\$.79	\$.69	\$.59
168743	ValuePro	HDDB15S318*	15	M	\$.59	\$.55	\$.49
77956	ValuePro	DA15S318	15	F	\$.79	\$.69	\$.59
1952273	Kycon	HDDSUB-15S†*	15	F	\$.49	\$.45	\$.39
71466	ValuePro	HDDB15S318R*	15	F	\$.89	\$.79	\$.69
614539	AMP	747845-4†	15	F	1.75	1.55	1.39
15150	ValuePro	DB25P318R	25	M	\$.75	\$.65	\$.55
614230	AMP	745238-4	25	M	3.95	3.69	3.29
265439	Various	DSUB-25F	25	F	\$.75	\$.65	\$.55
15182	ValuePro	DB25S318R	25	F	\$.85	\$.75	\$.65
446483	Cinch	DBKL-25SAT-E25†	25	F	\$.75	\$.65	\$.59
614547	AMP	747846-3†	25	F	1.25	1.09	\$.95
614141	AMP	745783-4	25	F	3.19	2.89	2.59
71706	ValuePro	DC37P318†	37	M	1.15	\$.95	\$.89
78182	ValuePro	DC37S318+†	37	F	1.19	1.05	\$.95

*High Density † Without female jack screws (P/N 172603, pg 69)

Metal Solder-Cup *Web Code: EAB



Part No.	Manufacturer	Product No.	Contacts	Gender	1	10	100
15748	ValuePro	1001-9P-R	9	M	\$.55	\$.45	\$.35
222990	AMP	747904-2	9	M	2.25	1.95	1.75
222957	AMP	747904-4†	9	M	2.25	1.95	1.75
15771	ValuePro	500-109	9	F	\$.65	\$.55	\$.45
223052	AMP	747905-2	9	F	2.25	1.95	1.75
223036	AMP	747905-4†	9	F	2.75	2.35	2.09
15035	ValuePro	1001-15P-R	15	M	\$.69	\$.55	\$.45
15078	ValuePro	1002-15P-R*	15	M	\$.95	\$.75	\$.59
223001	AMP	747908-2	15	M	2.89	2.55	2.25
15052	ValuePro	1001-15S-R	15	F	\$.75	\$.59	\$.49
164823	ValuePro	1002-15S-R*	15	F	\$.95	\$.75	\$.59
223061	AMP	747909-2	15	F	3.95	3.59	3.29
15115	ValuePro	1001-25P-R	25	M	\$.95	\$.79	\$.69
2095091	Amphenol	EDD25ST	25	M	\$.75	\$.65	\$.55
223010	AMP	747912-2	25	M	3.25	2.95	2.65
222973	AMP	747912-4†	25	M	2.95	2.69	2.29
458126	Cinch	DBH-25P	25	M	3.95	3.49	2.95
15157	ValuePro	500-125	25	F	\$.95	\$.79	\$.69
223079	AMP	747913-2	25	F	3.75	3.15	2.65
223044	AMP	747913-4†	25	F	3.95	3.49	2.95
203799	ValuePro	1002-26P*	26	M	\$.85	\$.69	\$.55
203782	ValuePro	1002-26S-R*	26	F	\$.75	\$.65	\$.55
639630	Amphenol	EDC37P	37	M	\$.85	\$.65	\$.55
15473	ValuePro	1002-37P	37	M	1.35	1.15	\$.95
222981	AMP	747916-4†	37	M	3.95	3.49	2.95
482724	Amphenol	EDC37S	37	F	\$.95	\$.75	\$.55
15500	ValuePro	GC028-R	37	F	1.25	1.09	\$.95
223087	AMP	747917-2	37	F	5.49	4.95	3.49
482732	Amphenol	EDD50P	50	M	\$.75	\$.65	\$.55
15676	ValuePro	GC029-R	50	M	1.95	1.69	1.49
482741	Amphenol	EDD50S	50	F	\$.95	\$.75	\$.55
15691	ValuePro	GC030	50	F	1.29	1.15	\$.95

*High Density † Zinc plated shell †† With standard mounting hole

Right Angle PCB Mount *Web Code: HAN

Metal .590" Set Back – Tin plated long style



• Current rating: 1A

Part No.	Manufacturer	Product No.	Contacts	Gender	1	10	100
104970	ValuePro	DB9P590	9	M	\$.95	\$.85	\$.75
104978	ValuePro	DB9S590	9	F	\$.95	\$.85	\$.75
104985	Astron	DA15P590†	15	M	\$.65	\$.55	\$.49
104993	ValuePro	DA15S590+†	15	F	\$.65	\$.55	\$.49
189624	Various	DB25P590††	25	M	\$.75	\$.65	\$.59
105006	ValuePro	DB25P590	25	M	1.29	1.15	\$.95
105013	ValuePro	DB25S590+†	25	F	1.29	1.09	\$.85

† Without female jack screws (P/N 172603, pg 69) †† Without board tabs


Metal Straight PCB Mount *Web Code: SBK



Part No.	Manufacturer	Product No.	Contacts	Gender	1	10	100
111692	ValuePro	DB9PPCB	9	M	\$.55	\$.45	\$.35
15781	ValuePro	DB9SPCB	9	F	\$.59	\$.49	\$.39
176760	ValuePro	DA15PPCB	15	M	\$.65	\$.55	\$.45
2077491	Various	DAH15SPCB*	15	F	\$.55	\$.45	\$.39
176752	ValuePro	DA15SPCB	15	F	\$.65	\$.55	\$.45
15123	ValuePro	DB25PPCB	25	M	\$.75	\$.65	\$.55
15165	ValuePro	DB25PCB	25	F	\$.79	\$.69	\$.59
180013	ValuePro	DC37PPCB	37	M	\$.79	\$.69	\$.59
180021	ValuePro	DC37PCB	37	F	1.25	1.09	\$.95

* High Density

Crimp-Type *Web Code: UBR



Part No.	Manufacturer	Product No.	Contacts	Gender	1	10	100
73189	ValuePro	500-010+	9	M	\$.49	\$.39	\$.35
222640	AMP	205204-1	9	M	1.15	\$.95	\$.85
73197	ValuePro	500-110	9	F	\$.55	\$.45	\$.35
222842	AMP	205203-3R	9	F	\$.85	\$.75	\$.65
222691	AMP	205203-1	9	F	1.09	\$.95	\$.75
73200	ValuePro	G37-15	15	M	\$.55	\$.45	\$.35
180882	ValuePro	1006-15P-R*	15	M	\$.85	\$.75	\$.65
222703	AMP	205205-1R	15	M	\$.79	\$.69	\$.65
222658	AMP	205206-1	15	M	\$.95	\$.85	\$.75
73219	ValuePro	G1G125-R	15	F	\$.65	\$.55	\$.45
180890	ValuePro	1006-15S*	15	F	\$.65	\$.55	\$.49
38789	ValuePro	500-027	25	M	\$.65	\$.55	\$.45
222818	AMP	207464-2R	25	M	\$.79	\$.65	\$.55
38771	ValuePro	500-127	25	F	\$.65	\$.55	\$.45
222922	AMP	207463-1R	25	F	\$.95	\$.85	\$.75

* High Density

IDC Ribbon Cable

• Contact material: phosphor bronze
 • Terminates with standard D-type connectors



Part No.	Manufacturer	Product No.	Shell	Cont.	Gender	1	10	100
109226	ValuePro	MDB9P	Metal	9	M	\$1.75	\$1.49	\$1.25
12504	ValuePro	CDB9P	Plastic	9	M	2.25	1.95	1.75
109218	ValuePro	MDB9S	Metal	9	F	1.85	1.65	1.45
12521	ValuePro	CDB9S	Plastic	9	F	2.49	2.25	1.95
614387	AMP	747318-4††	Plastic	9	F	4.49	3.95	3.49
1577961	3M	8309-6000R	Metal	9	F	3.95	3.69	3.29
614328	AMP	747303-4R	Metal	9	F	4.95	4.49	3.95
117382	ValuePro	MDA15P	Metal	15	M	1.75	1.49	1.29
12299	ValuePro	CDA15P	Plastic	15	M	1.49	1.25	1.09

†† With standard mounting holes

Continued on next page

RoHS compliant product + This product is available in both RoHS and non-RoHS versions. Add an "R" before part number for RoHS version. Details on page 197.