

AC-to-DC Unregulated Linear Wall Adapters

JAMECO ReliaPro

AC-to-DC Unregulated Linear Wall Adapters (Continued)


* Web Code: UAP

120VAC @ 60Hz

We specialize in Wall Adapters - Call for additional OEM PRICING.



123158



We are happy to change any listed DC wall adapter power plug to a connector of your choice (see pg 114) for just \$2.50 each. A 100 pc. minimum order applies.

Part No.	Manufacturer	Product No.	Output Rating		Output Connector ID x OD mm Female/Male; Polarity ◆	Size (H" x W" x D")	Case Color	Output Cord Length	Wt. (lbs.)	Agency Approvals	Pricing			
			Voltage (VDC)	Current (mA)							1	10	50	100
114825	ReliaPro	DCU120050D4740	12	500	Stripped & tinned	2.5 x 2.0 x 1.7	Black	6'	0.6	UL/CUL	\$7.95	\$6.95	\$6.59	\$5.95
15368	ReliaPro	DCU120050Z8698	12	500	2.1mm x 5.5mm F 1	2.5 x 1.9 x 1.6	Black	6'	0.6	UL/CSA	7.95	6.95	6.59	5.95
102496	ReliaPro	DCU120050E8601	12	500	2.1mm x 5.5mm F 2	2.5 x 1.9 x 1.6	Black	6'	0.6	UL/CSA	7.95	7.29	6.59	5.95
131300	ReliaPro	DCU120050E0251	12	500	2.1mm x 5.5mm right angle F 2	2.6 x 1.9 x 1.7	Beige	6'	0.6	UL/CSA	7.95	6.95	5.95	4.95
102277	ReliaPro	DCU120050UE2631	12	500	2.5mm x 5.5mm F 2	2.5 x 2.1 x 1.7	Black	6'	0.6	UL/CSA	7.95	7.29	6.59	5.95
17267	ReliaPro	DCU120050Z5391	12	500	3.5mm M 2	2.5 x 1.9 x 1.6	Black	6'	0.6	UL/CSA	7.95	7.29	6.59	5.95
202219	ReliaPro	DCU120070F2142	12	700	2.1mm x 5.5mm F 2	3.3 x 2.9 x 2.3	Black	6'	0.6	UL/CUL	8.95	7.95	7.29	6.49
117479	ReliaPro	DDU120080E6451	12	800	2.1mm x 5.5mm F 2	3.0 x 2.3 x 2.0	Black	6'	0.9	UL/CSA	8.95	7.95	7.49	6.95
129331	ReliaPro	DDU120080F2412	12	800	2.5mm x 5.5mm F 2	3.0 x 2.3 x 2.0	Black	6'	0.9	UL/CSA	8.95	7.95	7.49	6.95
121232	ReliaPro	DDU120080F2271	12	800	3.5mm M 2	2.6 x 2.4 x 2.0	Black	6'	0.9	UL/CSA	8.95	7.95	7.49	6.95
100870	ReliaPro	DDU120100Z7974	12	1000	2.1mm x 5.5mm F 2	2.6 x 2.4 x 1.9	Black	6'	0.9	UL/CSA	9.95	8.95	7.95	7.29
105478	ReliaPro	DDU120100Z2993	12	1000	2.5mm x 5.5mm F 2	3.1 x 2.4 x 2.0	Black	6'	1.0	UL/CSA	9.95	8.95	7.95	7.29
15392	ReliaPro	DDU120100E7302	12	1000	3.5mm M 2	3.3 x 2.4 x 2.0	Black	6'	1.0	UL/CSA	9.95	8.95	7.95	7.29
2125991	CUI Inc	57-12-1200D	12	1200	2.1mm x 5.5mm F 2	3.6 x 2.6 x 2.1	Black	6'	1.4	UL/CUL	9.95	8.95	7.95	6.95
196779	ReliaPro	DDU120120G0031	12	1200	2.5mm x 5.5mm F 2	3.0 x 2.3 x 1.9	Black	6'	1.0	UL/CUL	11.95	10.95	9.95	8.95
203036	ReliaPro	DDU120150H4530	12	1500	2.1mm x 5.5mm F 1	3.3 x 2.2 x 1.9	Black	6'	1.5	UL/CUL	15.95	14.95	13.49	11.95
136881	ReliaPro	DDU120150K1960	12	1500	2.1mm x 5.5mm F 2	3.4 x 2.7 x 2.2	Black	6'	1.5	UL	15.95	14.95	13.49	11.95
101291	ReliaPro	DDU120150	12	1500	2.5mm x 5.5mm F 2	3.4 x 2.7 x 2.2	Black	6'	1.5	UL/CUL	15.95	14.95	13.49	11.95
2135620	Tamura	425A12400P	12.5	400	2.1mm x 2.5mm right angle F 2	3.3 x 2.2 x 1.6	Black	8'	0.7	UL/CUL	6.95	5.95	5.49	4.95
2077626	Qualcomm	TXACA036	13	1000	2.5mm x 5.5mm F 2 (Switching)	2.7 x 2.4 x 1.6	Black	6'6"	0.6	UL/CE	4.95	3.95	3.49	2.95
308099	ReliaPro	DDU135100H3210	13.5	1000	2.1mm x 5.5mm F 2	2.9 x 2.3 x 1.9	Black	6'	1.0	UL/CUL	10.95	9.95	8.95	7.95
2135582	Ault	P48131000A010G	13.5	1000	2.5mm x 5.5mm right angle F 2	3.2 x 2.2 x 1.9	Black	6'	1.1	UL/CSA	8.95	7.95	6.95	5.95
212812	ReliaPro	DBU140020F6022	14	200	2.1mm x 5.5mm F 2	2.2 x 1.7 x 1.5	Black	6'	0.8	UL/CUL	4.95	4.49	3.95	3.59
212821	ReliaPro	DBU140030F6042	14	300	2.1mm x 5.5mm F 2	2.2 x 1.7 x 1.5	Black	6'	0.8	UL/CUL	6.95	5.95	5.49	4.95
129314	Various	DV-1250	14	360	2.5mm x 5.5mm right angle F 2	2.3 x 2.0 x 1.6	Black	6'	0.6	UL/CSA	4.95	3.95	3.49	2.95
123932	ReliaPro	DDU140070Z7470	14	700	2.1mm x 5.5mm F 2	2.6 x 2.4 x 2.0	Black	6'	1.0	UL/CSA	8.95	7.95	6.95	6.25
202260	ReliaPro	DDU140100F3270	14	1000	2.1mm x 5.5mm F 2	3.9 x 2.9 x 2.4	Black	6'	0.9	UL/CUL	9.95	8.95	7.95	6.95
190001	ReliaPro	DCU150050E3021	15	500	2.1mm x 5.5mm F 2	2.3 x 2.4 x 1.9	Black	6'	0.8	UL/CSA	8.95	7.95	7.29	6.49
189982	ReliaPro	DCU150050E3031	15	500	2.5mm x 5.5mm F 2	2.3 x 2.4 x 1.9	Black	6'	0.8	UL/CSA	8.95	7.95	7.29	6.49
2135427	Ventronics	D48W150900-14/1	15	900	2.1mm x 5.5mm F 2	2.5 x 2.2 x 2.0	Black	6'	0.8	UL/CUL	8.95	7.95	6.95	5.95
203502	ReliaPro	DDU150090F4480	15	900	2.5mm x 5.5mm F 2	2.6 x 2.2 x 1.9	Black	6'	1.0	UL/CSA	9.95	8.95	7.95	6.95
151992	ReliaPro	DDU150100E8181	15	1000	2.1mm x 5.5mm F 1	3.1 x 2.0 x 1.9	Beige	6'	1.5	UL/CSA	7.95	6.95	5.95	4.95
191652	ReliaPro	DDU150100D7051	15	1000	2.1mm x 5.5mm F 2	3.3 x 2.2 x 1.9	Black	6'	1.0	UL/CSA	10.95	9.95	8.95	7.95
681563	Ault	P48151000A020G	15	1000	2.5mm x 5.5mm F 2	3.3 x 2.3 x 1.9	Black	6'	1.2	UL/CSA	7.95	6.95	5.95	4.95
162317	ReliaPro	DDU165050J19910	16	500	2.1mm x 5.5mm F 2	2.5 x 2.0 x 1.7	Black	6'	0.8	UL/CSA	9.95	8.95	7.95	7.29
217541	NiteRider	FE4116168C030	16.8	300	2.5mm x 5.5mm F 2	3.1 x 2.1 x 1.6	Black	6'	0.6	UL/CUL	4.95	3.95	3.49	2.95
2081713	DVE	DV-1790	17	900	2.5mm x 5.5mm F 2	3.2 x 2.2 x 2.0	Black	6'	1.2	UL/CSA	3.95	3.49	2.95	2.59
181729	ReliaPro	DCU180025F8680	18	250	2.1mm x 5.5mm F 2	2.6 x 2.0 x 1.6	Black	6'	0.6	UL	5.95	4.95	4.49	3.95
217568	NiteRider	FE4126180P040	18	400	2.5mm x 5.5mm F 2 (w/ LED indicator)	3.5 x 2.1 x 1.6	Black	6'	0.8	UL/CUL	3.95	3.49	2.95	2.59
163272	ReliaPro	DDU180050C1031	18	500	2.1mm x 5.5mm F 2	2.6 x 2.3 x 1.9	Black	6'	0.8	UL/CUL	7.95	6.95	6.25	5.59
206958	ReliaPro	DDU180100H4551	18	1000	2.5mm x 5.5mm F 2	3.3 x 2.2 x 1.9	Black	6'	1.4	UL/CUL	10.95	9.95	8.95	7.95
102285	ReliaPro	DDU240040Z7860	24	400	2.1mm x 5.5mm F 2	3.0 x 2.3 x 2.0	Black	6'	0.9	UL/CUL	8.95	7.95	7.29	6.49
163635	ReliaPro	DDU240050C1981	24	500	2.1mm x 5.5mm F 1	3.1 x 2.3 x 1.9	Black	6'	1.0	UL/CUL	9.95	8.95	7.95	7.29
191556	ReliaPro	DDU240050E5852	24	500	2.5mm x 5.5mm F 2	3.1 x 2.3 x 1.9	Black	6'	1.0	UL/CUL	9.95	8.95	7.95	7.29
139088	ReliaPro	DDU240050E9160	24	500	3.5mm M 2	3.1 x 2.3 x 1.9	Black	6'	1.0	UL/CUL	9.95	8.95	7.95	7.29
1918930	ReliaPro	DDU240060L260	24	600	2.1mm x 5.5mm F 2	2.9 x 2.2 x 1.9	Black	6'	0.4	UL/CUL	10.95	9.95	8.95	7.95
168495	ReliaPro	DFU240080J3180	24	800	2.1mm x 5.5mm F 2	2.9 x 1.9 x 1.6	Black	6'	0.4	UL/CUL/TUV	12.95	11.95	10.95	9.95
220960	ReliaPro	DFU240100G2300	24	1000	2.1mm x 5.5mm F 1	3.4 x 2.7 x 2.2	Black	6'	1.6	UL/CUL	14.95	13.49	11.95	9.95
249121	ReliaPro	DFU240120G8520	24	1150	2.1mm x 5.5mm F 2	3.4 x 2.7 x 2.2	Black	6'	1.7	UL/CUL	17.95	15.95	14.49	12.95
249113	ReliaPro	DFU240120G8510	24	1150	2.5mm x 5.5mm F 2	3.4 x 2.7 x 2.2	Black	6'	1.7	UL/CUL	17.95	15.95	14.49	12.95
199523	ReliaPro	DDU300050E9340	30	500	2.5mm x 5.5mm F 2	2.9 x 2.3 x 1.9	Black	6'	1.1	UL/CUL	10.95	9.95	8.95	7.95
15309	ReliaPro	900-051	3, 4.5, 6, 7.5, 9, 12	500	1.3 x 3.5, 2.1 x 5.0, 2.5 x 5.5 Female 2.5, 3.5 Male, 9V battery snap (LED ind.)	3.0 x 2.2 x 2.1	Black	6'	0.7	UL/CSA	9.95	8.95	7.95	6.95
123158	ReliaPro	900-100	1.5, 3, 4.5, 6, 7.5, 9, 12	1000	1.3 x 3.5, 2.1 x 5.0, 2.5 x 5.5 Female 2.5, 3.5 Male, 9V battery snap (LED ind.)	3.7 x 2.2 x 2.5	Black	6'	0.9	—	11.95	10.95	9.95	8.95

* For Complete Specs & Additional Product Listings Search www.Jameco.com/More and Enter Web Code Listed Above

4 LEVELS OF SAVINGS

Order by Phone at 1-800-831-4242 or Online at www.Jameco.com