



Enclosed Switching AC-to-DC Power Supplies (Continued)



SP-500

* Web Code: EPS

Part No.	Manufacturer	Mfr. Part No.	Output		Size (L"xW"xH")	Ripple & Noise (mV p-p)*	Load Reg. (±%)*	Line Reg. (±%)*	Additional Info Pg. 121†	Certification	Pricing		
			Voltage @ Current(min-max)	Power							1	5	25
Single Output (Continued)													
202076	Mean Well	S-240-15	+15V @ 0-15A	225W	7.5x3.7x2.6	150	0.5	0.5	2	UL/CUL/TUV/CE/CB/PFC	\$59.95	\$53.95	\$47.95
374993	Mean Well	S-320-15	+15V @ 0-20A	300W	8.5x4.5x2.0	150	0.5	0.5	2	UL/CUL	74.95	64.95	54.95
693610	Mean Well	SP-320-15	+15V @ 0-20A	300W	8.5x4.5x2.0	150	0.5	0.3	3	UL/CUL/TUV/CE/CB/PFC	64.95	59.95	54.95
693652	Mean Well	SP-480-15	+15V @ 0-35A	480W	10.9x5.0x1.7	150	0.5	0.3	3	UL/CUL/TUV/CE/CB/PFC	144.95	134.95	124.95
291522	Mean Well	SE-600-15	+15V @ 0-40A	600W	9.7x5.0x2.5	150	0.5	0.5	2	UL/CUL	114.95	106.95	99.95
374222	Mean Well	PSP-600-15	+15V @ 0-40A	600W	6.7x4.7x3.7	240	0.5	0.5	5	UL/CUL/TUV/CE/CB/PFC	149.95	134.95	124.95
374045	Mean Well	SCN-600-15	+15V @ 0-40A	600W	11.5x5.2x2.7	150	0.5	0.5	4	UL/CUL/CB	149.95	139.95	119.95
2094901	Mean Well	HRPG-600-15	+15V @ 0-43A	645W	8.5x4.1x2.5	150	0.5	0.3	6	UL/CUL/TUV/CE/CB/PFC	189.95	174.95	164.95
694920	Mean Well	RSP-1500-15	+15V @ 0-100A	1500W	10.9x5.0x3.3	150	0.5	0.5	5	UL/CUL/TUV/CE/CB/PFC	424.95	389.95	359.95
1919078	Mean Well	RS-15-24	+24V @ 0-0.625A	15W	2.5x2.0x1.1	200	0.5	0.5	1	UL/CUL/TUV/CE/CB	16.95	12.95	10.95
123272	Mean Well	S-25-24	+24V @ 0-1.1A	26.4W	3.9x3.8x1.4	100	0.5	0.5	2	UL/TUV/CE	19.95	16.95	14.95
323311	Mean Well	RS-25-24	+24V @ 0-1.1A	26.4W	3.0x2.0x1.1	120	0.5	0.5	1	UL/CUL/TUV/CE/CB	19.95	16.49	13.95
323353	Mean Well	RS-35-24	+24V @ 0-1.5A	36W	3.9x3.2x1.4	120	0.5	0.5	1	UL/CUL/TUV/CE/CB	21.95	17.95	14.95
689792	Metapo	1M041C24-1M	+24V @ 0-1.8A	43W	4.8x3.8x1.5	100	0.5	0.5	—	UL/CUL/TUV/CE	14.95	13.49	11.95
123319	Mean Well	S-40-24	+24V @ 0-1.8A	43W	5.1x3.9x1.5	100	0.5	0.5	2	UL/CUL/TUV/CE/CB	22.95	19.95	17.95
2104225	Mean Well	NES-50-24	+24V @ 0-2.2A	52.8W	5.1x3.9x1.5	200	0.5	0.5	—	UL/CUL/CE/CB	24.95	18.95	15.95
323417	Mean Well	RS-50-24	+24V @ 0-2.2A	52.8W	3.9x3.8x1.4	120	0.5	0.5	1	UL/CUL/TUV/CE/CB	23.95	19.95	16.95
123352	Mean Well	S-60-24	+24V @ 0-2.5A	60W	6.3x3.8x1.5	150	0.5	0.5	2	UL/CUL/TUV/CE/CB	26.95	22.95	19.95
323620	Mean Well	RS-75-24	+24V @ 0-3.2A	76.8W	5.1x3.9x1.5	120	0.5	0.5	1	UL/CUL/TUV/CE/CB	28.95	23.95	19.49
2104250	Mean Well	NES-75-24	+24V @ 0-3.2A	76.8W	6.3x3.8x1.5	200	0.5	0.5	—	UL/CUL/CE/CB	29.95	22.95	18.49
194854	Mean Well	SP-75-24	+24V @ 0-3.2A	76.8W	7.0x3.9x1.3	100	0.5	0.5	3	UL/CUL/TUV/CE/CB	42.95	36.95	31.95
194812	Mean Well	SP-100-24	+24V @ 0-4.2A	100.8W	7.0x3.9x1.8	150	0.5	0.5	3	UL/CUL/TUV/CE/CB/PFC	46.95	41.95	36.95
201971	Mean Well	S-100F-24	+24V @ 0-4.5A	108W	7.8x3.9x1.5	150	0.5	0.5	2	UL/TUV/CE/CB	32.95	26.95	23.95
323732	Mean Well	RS-100-24	+24V @ 0-4.5A	108W	6.3x3.8x1.5	120	0.5	0.5	1	UL/CUL/TUV/CE/CB	39.95	32.95	26.95
155651	Power One	MAP110-1024CM	+24V @ 5A or +28V @ 4.3A	110W	7.0x4.3x1.8	240	0.5	1.0	—	UL/CSA/TUV	24.95	22.95	19.95
1945920	APS	RP1150-24C	+24V @ 0-6.25A	150W	7.5x4.2x2.0	100	1.0	1.0	—	UL/CE	34.95	29.95	23.95
173404	Mean Well	SP-150-24	+24V @ 0-6.25A	150W	7.0x3.9x2.0	150	0.5	0.5	3	UL/CUL/TUV/CE/CB/PFC	56.95	49.95	44.95
371012	Potrans	GL150W-24-NC	+24V @ 6.5A	156W	7.8x3.7x2.5	180	2.0	2.0	—	UL/CUL/TUV/CE	26.95	23.95	19.95
123450	Mean Well	S-150-24	+24V @ 0-6.5A	156W	7.0x4.3x2.0	240	0.2	0.2	2	UL/CUL/TUV/CE/CB	34.95	32.49	29.95
323855	Mean Well	RS-150-24	+24V @ 0-6.5A	156W	7.8x3.9x1.5	120	0.5	0.5	1	UL/CUL/TUV/CE/CB	41.95	38.95	35.95
2094864	Mean Well	HRPG-150-24	+24V @ 0-6.5A	156W	6.3x3.8x1.5	150	0.5	0.3	6	UL/CUL/TUV/CE/CB/PFC	94.95	79.95	69.95
2135523	TDK/Lambda	HWS150-24/A	+24V @ 0-6.5A	156W	6.3x1.7x3.2	150	0.5	0.3	—	UL/CSA/CE/EN/IEC	189.95	169.95	125.00
194782	Mean Well	SP-200-24	+24V @ 0-8.4A	201.6W	7.0x3.9x2.0	150	0.5	0.5	3	UL/CUL/TUV/CE/CB/PFC	54.95	49.95	44.95
2104583	Mean Well	S-250-24	+24V @ 0-10A	240W	5.9x5.5x3.4	120	0.5	0.5	2	UL/CUL	55.95	49.95	44.95
2101518	Mean Well	SP-240-24	+24V @ 0-10A	240W	7.5x3.7x2.0	150	0.5	0.2	3	UL/CUL/TUV/CE/CB/PFC	64.95	59.95	55.95
196657	Mean Well	S-320-24	+24V @ 0-12.5A	300W	8.5x4.5x2.0	150	0.5	0.5	2	UL/CUL	74.95	64.95	54.95
244752	Mean Well	SP-320-24	+24V @ 0-13A	312W	8.5x4.5x2.0	150	0.5	0.2	3	UL/CUL/TUV/CE/CB/PFC	64.95	59.95	54.95
2102220	Mean Well	HRP-300-24	+24V @ 0-14A	336W	7.7x4.1x1.6	150	0.5	0.2	3	UL/CUL/TUV/CE/CB/PFC	114.95	104.95	94.95
2094881	Mean Well	HRPG-300-24	+24V @ 0-14A	336W	7.8x4.1x1.6	150	0.5	0.3	6	UL/CUL/TUV/CE/CB/PFC	119.95	114.95	109.95
2101606	Mean Well	SE-450-24	+24V @ 0-18.8A	451.2W	8.9x4.9x2.0	200	0.5	0.2	—	UL/CUL	99.95	92.95	86.95
2122335	Mean Well	HRP-450-24	+24V @ 0-18.8A	451.2W	8.6x4.1x1.6	150	0.5	0.2	6	UL/CUL/TUV/CE/CB/PFC	164.95	148.49	133.95
301322	Mean Well	SP-480-24	+24V @ 0-22A	480W	10.9x5.0x1.7	150	0.5	0.2	3	UL/CUL/TUV/CE/CB/PFC	144.95	134.95	124.95
147054	Mean Well	SP-500-24	+24V @ 0-20A	480W	6.7x4.7x3.7	240	0.5	0.5	3	UL/CUL/TUV/CE/CB/PFC	169.95	149.95	129.95
295902	Mean Well	SE-600-24	+24V @ 0-25A	600W	9.7x5.0x2.5	150	0.5	0.5	2	UL/CUL	114.95	106.95	99.95
374231	Mean Well	PSP-600-24	+24V @ 0-25A	600W	6.7x4.7x3.7	240	0.5	0.5	5	UL/CUL/TUV/CE/CB/PFC	149.95	134.95	119.95
320048	Mean Well	SP-750-24	+24V @ 0-31.3A	750W	10.9x5.0x2.5	120	0.5	0.2	3	UL/CUL/TUV/CE/CB	219.95	199.95	184.95
374310	Mean Well	SCP-800-24	+24V @ 0-33A	792W	11.4x7.7x2.7	240	0.5	0.5	5	UL/CUL/TUV/CE/CB	229.95	209.95	199.95
1585717	Mean Well	RSP-1000-24	+24V @ 0-40A	960W	11.6x5.0x1.6	150	0.5	0.5	5	UL/CUL/TUV/CE/CB/PFC	319.95	299.95	279.95
2101569	Mean Well	RE-1000-24	+24V @ 0-41.7A	1000.8W	10.9x5.0x2.5	200	0.5	0.5	4	UL/CUL	209.95	184.95	164.95
373923	Mean Well	PSP-1500-24	+24V @ 0-56.4A	1353.6W	10.9x5.1x7.5	150	0.5	0.2	5	UL/CUL/TUV/CE/CB/PFC	449.95	424.95	399.95
694938	Mean Well	RSP-1500-24	+24V @ 0-63A	1512W	10.9x5.0x3.3	150	0.5	0.5	5	UL/CUL/TUV/CE/CB/PFC	389.95	369.95	349.95
693409	Mean Well	SP-75-27	+27V @ 0-2.8A	75.6W	7.0x3.9x1.3	100	0.5	0.5	3	UL/CUL/TUV/CE/CB	42.95	36.95	31.95
202033	Mean Well	S-150-27	+27V @ 0-5.6A	151.2W	7.0x4.3x2.0	240	0.2	0.2	2	UL/CUL/TUV/CE/CB	34.95	32.49	29.95
693513	Mean Well	SP-150-27	+27V @ 0-5.6A	151.2W	7.8x3.9x2.0	150	0.5	0.5	—	UL/CUL/TUV/CE/CB/PFC	49.95	44.95	39.95
693548	Mean Well	SP-200-27	+27V @ 0-7.5A	202.5W	7.0x3.9x2.0	150	0.5	0.5	3	UL/CUL/TUV/CE/CB/PFC	54.95	49.95	44.95
693581	Mean Well	S-320-27	+27V @ 0-11.0A	297W	8.5x4.5x2.0	200	0.5	0.5	2	UL/CUL	74.95	64.95	54.95
693628	Mean Well	SP-320-27	+27V @ 0-11.7A	315.9W	8.5x4.5x2.0	200	0.5	0.2	3	UL/CUL/TUV/CE/CB/PFC	64.95	59.95	54.95
190706	Mean Well	SP-500-27	+27V @ 0-18A	486W	6.7x4.7x3.7	200	0.5	0.5	3	UL/CUL/TUV/CE/CB/PFC	169.95	149.95	129.95
295911	Mean Well	SE-600-27	+27V @ 0-22.2A	599.4W	9.7x5.0x2.5	150	0.5	0.5	2	UL/CUL	114.95	106.95	99.95
374257	Mean Well	SP-600-27	+27V @ 0-22.2A	600W	6.7x4.7x3.7	240	0.5	0.5	5	UL/CUL/TUV/CE/CB/PFC	149.95	134.95	119.95
374038	Mean Well	SP-750-27	+27V @ 0-27.8A	750W	10.9x5.0x2.5	120	0.5	0.2	3	UL/CUL/TUV/CE/CB	219.95	199.95	184.95
231652	Mean Well	PSP-1000-27	+27V @ 0-33.6A	907.2W	10.9x5.1x5.0	150	0.5	0.2	5	UL/CUL/TUV/CE/CB/PFC	299.95	279.95	259.95

* Primary Output

More Enclosed Switching Power Supplies on pages 121-122 & 124-126

* For Complete Specs & Additional Product Listings Search www.Jameco.com More and Enter Web Code Listed Above

4 LEVELS OF SAVINGS
 NAME BRANDS HOUSE BRANDS FACTORY OVERRUN DOLLAR SALE

Power