

DC Brushless Tubeaxial Fans & Blowers

Call for additional OEM PRICING – we carry major manufacturers.

DC Brushless Tubeaxial Fans & Blowers

* 5V Web Code: TAS



* 12V Web Code: LBZ



695050



1581249



1809936



2095269

mm to Inches Conversion Chart

mm	6.8	10	15	20	25	28	30	32	35	38	40	45	51	60	76	80	92	95	97	120	127	150	172
Inches	0.27	0.40	0.60	0.80	1.00	1.10	1.18	1.26	1.40	1.50	1.60	1.80	2.00	2.36	2.99	3.15	3.63	3.74	3.82	4.69	5.00	5.90	6.77

Part No.	Manufacturer	Mfr. Part No.	Voltage (VDC)	Size mm (W x H x D)	Air Flow (CFM)	Bearing	Current (mA)	Power (Watts)	Agency Approvals	Noise (dBA)	Connection (Leads)	Pricing			
												1	10	50	100
2095285	Adda	AD1505LX-K90	5	15 x 15 x 6	0.1	Hypro	50	0.25	CE	9.6	5.5"	\$8.95	\$7.95	\$6.95	\$5.95
2095277	Adda	AD2005LX-G70	5	20 x 20 x 10	0.6	Hypro	80	0.4	UL/CUL/CSA/TUV/CE	20	5.5"	7.95	6.95	5.95	4.95
2131872	Adda	AD0205MX-K53-LF	5	25 x 25 x 6	2.2	Hypro	120	0.6	UL/CUL/TUV/CE	26	6" ¹	8.95	7.95	6.95	5.95
131247	Adda	AD0205LX-G50	5	25 x 25 x 10	1.8	Sleeve	100	0.5	UL/CSA/CE	15.6	5.5"	14.95	13.49	11.95	10.95
695050	Sunon	GM0502PFV2-8	5	25 x 25 x 10	3.0	Vapo	80	0.4	UL/CUL	16	5.5"	12.95	11.49	9.95	8.95
1708481	Sunon	KDE0502PHB3-8 (MS)	5	25 x 25 x 15	1.8	Ball	80	0.4	UL/CUL	16	4"	8.95	7.95	6.95	5.95
2131899	Adda	AD0305LX-K70-LF	5	30 x 30 x 6.8	2.5	Hypro	90	0.45	UL/CSA/TUV/CE	20	6"	5.95	5.35	4.79	3.95
1928311	Adda	AD0305LB-K70	5	30 x 30 x 6.8	2.5	Ball	60	0.3	UL/CUL/TUV/CE	30	6"	5.95	4.95	3.95	3.49
2099497	Adda	AD0305MX-K70	5	30 x 30 x 6.8	3.3	Hypro	120	0.6	UL/CSA/TUV/CE	27.9	5.5"	5.95	4.95	4.49	3.95
1951211	Sunon	KDE0503PEV1-8 (MSN)	5	30 x 30 x 6.8	4.9	Vapo	180	0.9	UL/TUV/CE	28	6"	7.95	6.95	6.25	5.59
1951220	Sunon	KDE0503PEB3-8 (MSN)	5	30 x 30 x 6.8	4.9	Ball	180	0.9	UL/TUV/CE	28	6"	8.95	7.95	6.95	5.95
2099489	Adda	AD0305HX-G50	5	30 x 30 x 10	4.2	Hypro	170	0.85	UL/CUL/TUV/CE	30.7	5.5"	6.95	5.95	4.95	3.95
1950534	Sunon	KDE0503PFB1-8V	5	30 x 30 x 10	5.1	Ball	180	0.7	UL/TUV	22.5	5"	8.95	7.95	6.95	5.95
2120031	Sunon	GM0503PEV1-8N.GN	5	30 x 30 x 10	5.5	Vapo	140	0.7	UL/CSA/TUV	23	6"	6.95	5.95	4.95	3.95
2095293	Adda	AD305HB-D50	5	30 x 30 x 15	3.7	Ball	130	0.65	UL/CUL/TUV/CE	22.5	11"	5.95	5.39	4.79	4.29
1708457	Sunon	KDE0504PEB3-8 (MS)	5	40 x 40 x 6.8	3.5	Ball	90	0.45	UL/CUL/TUV	20	6"	5.95	5.35	4.79	3.95
1928361	Adda	AD0405MB-K90 (S)	5	40 x 40 x 6.8	5.5	Ball	90	0.45	UL/TUV/CE	25	6"	7.95	6.95	6.25	5.59
2132031	Adda	AD0405HX-KC3(Y14X)LF	5	40 x 40 x 6.8	5.9	Hypro	60	0.6	UL/CSA/TUV/CE	27	5.5" ¹	7.95	6.95	6.25	5.59
1928353	Adda	AD0405HB-K90	5	40 x 40 x 6.8	6.0	Ball	120	0.6	UL/CUL/TUV/CE	30	5"	8.95	7.95	6.95	5.95
1581249	Sunon	KDE0504PFB3-8	5	40 x 40 x 10	4.6	Ball	70	0.35	UL/CUL	23.5	12"	6.95	6.25	5.59	4.95
2138628	Adda	AD0405MB-G70	5	40 x 40 x 10	5.7	Ball	110	0.55	UL/CUL/TUV/CE	20	12"	9.95	8.95	8.49	7.95
2131928	Adda	AD0405MX-G76-LF	5	40 x 40 x 10	5.7	Hypro	110	0.55	UL/CUL/TUV/CE	20	11" ²	6.95	6.25	5.59	4.95
2121295	Adda	AD0405MB-G76	5	40 x 40 x 10	5.7	Ball	110	0.40	UL/CSA/TUV/CE	20	11" ¹	8.95	7.95	6.95	5.95
1581265	Sunon	KDE0504PFS1-8	5	40 x 40 x 10	7.0	Sleeve	110	0.6	UL/CUL	27	12"	6.95	6.25	5.59	4.95
2100013	Delta	AFB0405LD	5	40 x 40 x 20	5.6	Ball	210	1.05	UL/CSA/VDE/CE	25	13" ²	4.95	4.49	3.49	2.95
1952741	Elina	KDC050420MB	5	40 x 40 x 20	6.8	Ball/Sleeve	210	1.0	UL/CUL/TUV	25.5	12"	6.95	5.95	5.49	4.95
2131910	Adda	AD0405MX-C50-LF	5	40 x 40 x 20	8.1	Hypro	160	0.8	UL/CUL/TUV/CE	27	5.5"	6.95	6.25	5.59	4.95
1951406	Delta	AFB0405HD-ROO	5	40 x 40 x 20	8.5	Ball	400	2.0	UL/CUL/TUV/CE	33	12" ¹	6.95	6.25	5.95	4.95
2095251	Adda	AD4505MX-K90	5	45 x 45 x 6	7.1	Hypro	120	0.6	CE	25.5	5.5"	7.95	6.95	5.95	4.95
136494	Delta	AFB0505LA	5	51 x 51 x 10	7.4	Ball/Sleeve	80	0.4	UL/CE/CSA/VDE	26	11"	6.95	6.25	5.59	4.95
1950500	Sunon	KDE0505PFB1-8	5	51 x 51 x 10	10.2	Ball	170	0.9	UL/TUV	31.5	12"	8.95	7.95	6.95	6.25
136275	Delta	BFB0505L [†]	5	51 x 51 x 15	2.5	Ball	140	0.7	UL/CE/CSA/VDE	26.5	12"	9.95	8.95	7.95	6.95
136283	Elina	KDC050515MB	5	51 x 51 x 15	12.7	Ball/Sleeve	380	4.0	UL/CE/CUL/TUV	28	11"	6.95	6.25	5.59	4.95
1809936	Sunon	KD0505PHB2 (GN)	5	51 x 51 x 15	12.7	Ball	180	0.8	UL/CUL/TUV/CE	27.8	12"	8.95	7.95	6.95	6.25
2131961	Adda	AD0605MX-D71GL-LF	5	60 x 60 x 15	14.2	Hypro	250	1.25	UL/CSA/TUV/CE	28.8	5"	6.95	6.25	5.59	4.95
2131952	Adda	AD0605MB-D71GL-LF	5	60 x 60 x 15	14.2	Ball	250	1.25	UL/CSA/TUV/CE	28.8	6"	7.95	6.95	6.25	5.59
1809944	Sunon	KDE0506PHB3	5	60 x 60 x 15	15.2	Ball	240	1.2	UL/CUL/TUV/CE	26.5	12"	6.95	5.95	5.25	4.95
2081756	Adda	AD0605HB-D71GL	5	60 x 60 x 15	16.6	Ball	370	1.8	UL/CUL/CE	32	6"	5.95	5.49	4.95	4.49
1708431	Sunon	KD0506PHB2	5	60 x 60 x 15	18.5	Ball	380	1.9	UL/CUL/TUV/CE	32	12"	8.95	7.95	6.95	6.25
1951414	Delta	AFB0605HD	5	60 x 60 x 20	16.6	Ball	240	1.2	UL/CUL/TUV/CE	28	12"	7.95	6.95	5.95	4.95
355493	Sunon	KD0506PTS3	5	60 x 60 x 25	15.9	Sleeve	230	1.2	UL/CUL/CE	26.7	6.5" w/conn	5.95	5.25	4.59	3.95
134869	Delta	AFB0605M	5	60 x 60 x 25	16.2	Ball	220	1.1	UL/CE/CSA/TUV	24.5	12"	7.95	6.95	6.25	5.59
2131944	Adda	AD0605HB-A70	5	60 x 60 x 25	23.2	Ball	450	2.25	UL/CUL/TUV/CE	32	11"	7.95	6.95	6.25	5.59
1951078	Mechatronics	F8025E05B2-FS	5	60 x 60 x 25	24	Ball	700	3.5	UL/CUL	36	12" ²	8.95	7.95	6.95	6.25
1951086	Mechatronics	F8025E05B2-FS	5	80 x 80 x 25	46	Ball	800	4.0	UL/CUL	32	12" ²	9.95	8.95	7.95	6.95
1951094	Mechatronics	E9225M05B2-FS	5	92 x 92 x 25	44	Ball	560	2.8	UL/CUL	32	12" ²	6.95	5.95	4.95	4.49
1951107	Mechatronics	F1238L05B2-FS	5	120 x 120 x 38	94	Ball	800	4.0	UL/CUL	36	12" ²	10.95	9.95	8.95	7.95
2095269	Adda	AD2012LX-K70	12	20 x 20 x 6	0.6	Hypro	60	0.72	CE	19.5	5.5"	7.95	6.95	5.95	4.95
2100363	Adda	AD0212LX-K50-LF	12	25 x 25 x 6	1.8	Hypro	60	0.3	UL/CUL/TUV/CE	20.5	5.5"	8.95	7.95	6.95	5.95
2131881	Adda	AD0212MX-K53-LF	12	25 x 25 x 6	2.2	Hypro	80	0.4	UL/CSA/TUV/CE	23	6" ¹	8.95	7.95	6.95	5.95
2095306	Adda	AD0212MB-K50 (S)	12	25 x 25 x 6	2.4	Ball/Sleeve	90	1.08	UL/CUL/TUV/CE	26	5.5"	11.95	10.95	9.95	8.95
1951641	Adda	AD0212LB-G50 (GL)	12	25 x 25 x 10	1.8	Ball	70	0.84	UL/CUL/CE	15.6	5.5"	8.95	7.95	6.95	5.95
2121316	Adda	AD0212MX-G50GL	12	25 x 25 x 10	2.3	Hypro	80	0.4	UL/CUL/TUV/CE	23.1	5.5"	8.95	7.95	6.95	5.95
1708449	Sunon	KDE1202PFB1-8 (V)	12	25 x 25 x 10	3.1	Ball	83	1.0	UL/CUL	33	6"	10.95	9.95	8.95	7.95
2131901	Adda	AD0312MB-G50-LF	12	30 x 30 x 10	4.1	Ball	120	0.6	UL/CSA/TUV/CE	28	6"	7.95	6.95	5.95	4.95
1708465	Sunon	KDE1203PFB2-8 (MS)	12	30 x 30 x 10	4.2	Ball	66	0.8	UL/CUL	25	6"	5.95	5.35	4.79	4.29
212784	Sunon	KDE1203PFB1-8V	12	30 x 30 x 10	5.1	Ball	75	0.9	UL/CUL/TUV/CE/VDE	27	4"	6.95	5.95	4.95	3.95
212783	Sunon	KDE1203PFB1-8	12	30 x 30 x 10	5.1	Ball	75	0.9	UL/CUL/TUV/CE/VDE	27	5.9"	7.95	6.95	5.95	4.95

¹ 3 leads; speed sensor

² 3 leads; locked rotor protection

(All fans operate to their specs with or without the additional optional wire functions)

[†] Blower

Fans continued on next page

* For Complete Specs & Additional Product Listings Search www.Jameco.com More and Enter Web Code Listed Above

4 LEVELS OF SAVINGS