

## FireWire Adapter Card

- 4-port (2 Firewire and 2 USB 2.0) • PCI bus
- Firewire 800 and hi-speed USB combo/Firewire adapter

\* Web Code: VBB

Part No.	Mfr. Part No.	1	10
2209238	NN-8IS212-S2	\$9.95	\$8.95

## Computer Switchbox

- 2-port switchbox
- DB25 female (2 PCs to 1 printer)
- Size: 6.0"L x 5.8"W x 2.3"H • Weight: 1.4 lbs.

\* Web Code: CAK

Computer Cables on page 137

Part No.	Cross Ref. No.	1	10
20095	40D3-17602	\$17.95	\$15.95

## 19" Rack Mount Enclosures

- Ventilation holes all side
- Finish: Flat black
- Front and back panels are steel with aluminum, pre-punched face plates
- 0.12" thick black front panel
- Need to assemble
- Top, bottom and sides are durable 0.035" steel
- All enclosures have handles except P/N 132813



Includes: Mounting screws

Part No.	RU	Dimensions (In.)			Wt. (lbs.)	Pricing	
		H1	H2	D		1	5
149500*	2U	3.50	1.70	15.80	8.0	\$29.95	\$27.95
132813	1U	1.73	1.25	9.75	6.2	49.95	44.95
132840	2U	3.46	2.88	11.75	9.1	59.95	53.95
2203590†	2U	3.50	3.50	15.50	9.1	39.95	35.95
132848	3U	5.22	4.75	11.75	10.6	64.95	59.95
132864	5U	8.56	8.00	13.50	15.4	109.95	99.95

\*2U fixed rack shelf (beige) †Assembled with 2 fans

\* Rack Mount Products — Enter Web Code GAT

## Wireless Keyboard with Touchpad

Connect with PCs, tablets, Android TV, Google TV boxes, XBOX360 & PS3 game consoles, Raspberry Pi and more.



- 92 keys, audio and web buttons
- 2.4-2.48 GHz, ≤45 ft. range
- Slick, compact design
- Mini wireless QWERTY keyboard with touchpad

Includes: Li-ion battery, charging cable and USB receiver

NEW MARKED IN PINK

Part No.	Mfr. Part No.	1	5
2240112	DFR0330	\$24.95	\$22.49

## LED BRIGHT STICK

Rechargeable 29-LED flashlight is perfect for shop use or roadside emergencies.

- 29 LED work light
- 3 LED flashlight
- Magnetized end and 360° hook for safe and convenient hands-free mounting
- Water and oil resistant

Includes: Bright stick, 12VDC wall power



Part No.	Mfr. Part No.	Price
2202175	2417	\$9.95



JAMECO ValuePro

## 6-Outlet Surge Protector

- Heavy-duty power cord (14AWG x 3)
- Size: 9.5"L x 1.7"W x 1.4"H
- 4' cord
- Clamping voltage: 400V
- Max. surge voltage: 6500V
- RESET/OFF switch with built-in 15A circuit breaker



Part No.	Cross Ref. No.	Spike Current (Max.)	1	10	25
216485	51W1-10206	4500A, 150 joules	\$11.95	\$10.95	\$9.95

\* DIN Mounting Rails Accessories — Enter Web Code MBM

Audio Cables & Adapters on pages 48-49

JAMECO ValuePro

## USB-A Cable with Bracket

- Add additional USB ports to your PC
- Dual USB-A female ports
- Supports data transfer rates of 12Mbps
- 8'L cable



Part No.	Description	1	10	25
144813	(2) 1x5-pin connectors	\$4.95	\$4.49	\$3.95

## Analog DIN Rail Timer

- DIN rail/ back panel mount (17.5mm)
- 10 time ranges
- 13 timing functions
- Output contact: SPDT (1C/0)
- Contact rating: 5A (NO), 3A @ 250VAC (NC)
- Faceplate (IP50), housing (IP40), terminals (IP20)



Part No.	Size	1	5	25
2193862	17.5mm	\$31.95	\$29.95	\$27.95

MW

## 8GB USB Flash Drive

USB flash drive in the shape of a Mean Well power supply! Perfect for storing, transporting and sharing your presentations, documents, photos, music, and more.

- Compatible with Windows® 2000, XP, Vista and 7; Linux; Mac® OS



Part No.	Description	1	10
2155356	Mini USB flash drive	\$6.95	\$5.95

BACO

## Mini Pan & Tilt Kit

- For horizontal surface mount
- Aluminum multifunction bracket
- 15kg/cm @ 4.8V
- Rotation: 0-180°



Part No.	Mfr.	Mfr. Part No.	1	5
2157870	Dagu	RS002B	\$15.95	\$13.95

## 6-Outlet Power Strips

- 10 ft. 14/3 AWG power cord
- 6 grounded outlets
- Combination circuit
- Breaker ON/OFF switch
- 125V/15A/1875W



2258460/2132200: 6 ft. cord

2258697: 10 ft. cord

Part No.	Mfr. Part No.	1	10	25
2258460	PS08-12-WHITE*	\$6.95	\$5.95	\$5.49
2258697	PS08-12-BEIGE	7.95	6.95	5.95
2132200	ALG242**	2.95	2.59	2.39

\*Protective socket covers \*\*Wall mount

## USB 2.0 4-Port Hub

Add multiple high performance USB 2.0 devices to your computer or laptop. Unique design allows for easy storage and use.

- Stylish compact size and light weight
- USB 2.0 up to 480 Mbps
- Plug-and-play, bus powered
- 1 upstream, 4 downstream ports



Part No.	Cross Ref. No.	1	5
2184085	HU2Z40	\$9.95	\$8.95

## Waterproof USB Video Borescope

Allows for easy surveying of hard-to-reach places with 4 adjustable LEDs on the top on the camera.

- Flexible 16' cord
- 9.8mm camera
- Webcam and photo snap function
- Works with Windows® XP, 7, Vista and Mac iOS



Part No.	Cross Ref. No.	1	5
2177707	INSPECTOR-T1	\$34.95	\$31.95

\* Computer Brackets — Enter Web Code RAX

\* Surge Protectors — Enter Web Code CAC

## 6-CHANNEL USB SERVO CONTROLLER

The six-channel serial servo controller features a native USB interface and internal scripting control. The channels can be configured as servo outputs for use with radio control or electronic speed controls, as analog inputs, or as digital outputs.

- Three control methods: USB, TTL (5V) serial and internal scripting
- Free configuration and control application for Windows® available
- Individual speed and acceleration control for each channel
- Uses USB 5-pin mini-B interface (cable not included)
- Size: 1.2" x 0.85"



Part No.	Mfr. Part No.	Pulse Range	Pulse Rate	PWM Res.	1	5
2128180	1350	64 to 3280µs	33-100Hz	0.25µs	\$19.95	\$18.95

