

Spacers

NEW

Aluminum Round Spacers

- 3/16" OD • #4 ID (0.115")
- Iridite clear finish

* Prepackaged: order in increments of 10, 100 or 1000

Part No.	Product No.	Length	1	10	100	1000
392850CJ	1107-4-A-7	1/8"	*	\$.177	\$.169	\$.159
392868CJ	1108-4-A-7	3/16"	*	.195	.186	.176
392876CJ	1109-4-A-7	1/4"	.20	.194	.19	.185
392884CJ	1110-4-A-7	5/16"	.26	.214	.203	.193
392892CJ	1111-4-A-7	3/8"	.26	.214	.203	.193
392905CJ	1112-4-A-7	7/16"	.34	.288	.274	.26
392913CJ	1113-4-A-7	1/2"	.29	.233	.221	.21
392921CJ	1115-4-A-7	5/8"	.30	.242	.23	.218
392930CJ	1116-4-A-7	11/16"	.44	.37	.35	.34
392948CJ	1117-4-A-7	3/4"	.33	.279	.265	.252

Aluminum Round Spacers

- 1/4" OD • #4 ID (0.115")
- Iridite clear finish

Part No.	Product No.	Length	1	10	100	1000
393051CJ	1122-4-A-7	1/8"	\$.24	\$.205	\$.194	\$.185
393060CJ	1123-4-A-7	3/16"	.24	.205	.194	.185
393078CJ	1124-4-A-7	1/4"	.24	.205	.194	.185
393086CJ	1125-4-A-7	5/16"	.24	.205	.194	.185
393094CJ	1126-4-A-7	3/8"	.30	.242	.23	.218
393107CJ	1127-4-A-7	7/16"	.39	.326	.309	.294
393115CJ	1128-4-A-7	1/2"	.30	.242	.23	.218
393123CJ	1133-4-A-7	13/16"	.39	.326	.309	.294
393131CJ	1134-4-A-7	7/8"	.39	.326	.309	.294
393140CJ	1136-4-A-7	1"	.39	.326	.309	.294

Aluminum Round Spacers

- 1/4" OD • #6 ID (0.140")
- Iridite clear finish

Part No.	Product No.	Length	1	10	100	1000
393254CJ	1122-6-A-7	1/8"	\$.24	\$.205	\$.194	\$.185
393262CJ	1123-6-A-7	3/16"	.24	.205	.194	.185
393271CJ	1124-6-A-7	1/4"	.24	.205	.194	.185
393289CJ	1125-6-A-7	5/16"	.24	.205	.194	.185
393297CJ	1126-6-A-7	3/8"	.30	.242	.23	.218
393300CJ	1127-6-A-7	7/16"	.39	.326	.309	.294
393318CJ	1128-6-A-7	1/2"	.30	.242	.23	.218
393326CJ	1133-6-A-7	13/16"	.39	.326	.309	.294
393334CJ	1134-6-A-7	7/8"	.39	.326	.309	.294

Brass Round Spacers

- 3/16" OD • #4 ID (0.115")
- Zinc clear chromate finish

Part No.	Product No.	Length	1	10	100	1000
392956CJ	1107-4-B-7	1/8"	\$.79	\$.67	\$.64	\$.60
392964CJ	1108-4-B-7	3/16"	.85	.68	.64	.61
392972CJ	1109-4-B-7	1/4"	.86	.74	.70	.67
392981CJ	1110-4-B-7	5/16"	.87	.74	.71	.67
392999CJ	1111-4-B-7	3/8"	.89	.75	.72	.68
393001CJ	1112-4-B-7	7/16"	.91	.77	.73	.70
393019CJ	1113-4-B-7	1/2"	.93	.78	.74	.70
393027CJ	1115-4-B-7	5/8"	1.12	.95	.90	.86
393035CJ	1116-4-B-7	11/16"	1.14	.96	.91	.87
393043CJ	1117-4-B-7	3/4"	1.16	.98	.93	.88

Brass Round Spacers

- 1/4" OD • #4 ID (0.115")
- Zinc clear chromate finish

Part No.	Product No.	Length	1	10	100	1000
393158CJ	1122-4-B-12	1/8"	\$.24	\$.205	\$.194	\$.185
393166CJ	1123-4-B-12	3/16"	.22	.186	.177	.168
393174CJ	1124-2-B-12	1/4"	.26	.214	.203	.193
393182CJ	1125-4-B-12	5/16"	.31	.26	.247	.23
393191CJ	1126-4-B-12	3/8"	.32	.26	.247	.235
393203CJ	1127-4-B-12	7/16"	.77	.65	.62	.59
393211CJ	1128-4-B-12	1/2"	.34	.288	.274	.26
393220CJ	1133-4-B-12	13/16"	.97	.82	.78	.74
393238CJ	1134-4-B-12	7/8"	.66	.56	.53	.504
393246CJ	1136-4-B-12	1"	.74	.63	.60	.57

Brass Round Spacers

- 1/4" OD • #6 ID (0.140")
- Zinc clear chromate finish

Part No.	Product No.	Length	1	10	100	1000
393351CJ	1122-6-B-12	1/8"	\$.24	\$.205	\$.194	\$.185
393369CJ	1123-6-B-12	3/16"	.22	.186	.177	.168
393377CJ	1124-6-B-12	1/4"	.26	.214	.203	.193
393385CJ	1125-6-B-12	5/16"	.31	.26	.247	.235
393393CJ	1126-6-B-12	3/8"	.32	.26	.247	.235
393406CJ	1127-6-B-12	7/16"	.77	.65	.62	.59
393414CJ	1128-6-B-12	1/2"	.34	.288	.274	.26
393422CJ	1133-6-B-12	13/16"	.97	.818	.78	.74
393431CJ	1134-6-B-12	7/8"	.66	.56	.53	.504
393449CJ	1135-6-B-12	1"	.74	.63	.60	.57

Standoffs, Male-Female

Male-Female Hex Aluminum Standoffs

- 3/16" Hex • 4-40 thread
- Iridite clear finish
- Thread length : 1/4"



Part No.	Product No.	Length	1	10	100	1000
393457CJ	4501-440-A-7	1/4"	\$.35	\$.298	\$.283	\$.269
393465CJ	4502-440-A-7	3/8"	.35	.298	.283	.269
393473CJ	4505-440-A-7	1/2"	.35	.298	.283	.269
393490CJ	4509-440-A-7	3/4"	.39	.326	.309	.294
393502CJ	4513-440-A-7	1"	.39	.326	.309	.294

Male-Female Hex Brass Standoffs

- 1/4" Hex • Zinc clear chromate finish
- 4-40 thread • Thread length : 3/16"

Part No.	Product No.	Length	1	10	100	1000
393836CJ	4530-440-B-12	1/4"	\$.73	\$.61	\$.58	\$.55
393844CJ	4532-440-B-12	3/8"	.75	.63	.60	.57
393852CJ	4534-440-B-12	1/2"	.81	.69	.65	.62
393861CJ	4536-440-B-12	5/8"	.83	.70	.66	.63
393879CJ	4538-440-B-12	3/4"	.78	.66	.63	.60
393887CJ	4542-440-B-12	1"	.78	.66	.63	.60
393895CJ	4546-440-B-12	1-1/4"	.85	.72	.68	.65
393908CJ	4550-440-B-12	1-1/2"	1.24	1.05	1.00	.95

Standoffs, Female-Female

Female-Female Hex Brass Standoffs

- 1/4" Hex • 4-40 thread
- Zinc clear chromate finish



Part No.	Product No.	Length	1	10	100	1000
393684CJ	2100-440-B-12	1/4"	\$.24	\$.205	\$.194	\$.185
393692CJ	2102-440-B-12	3/8"	.37	.307	.292	.277
393705CJ	2103-440-B-12	7/16"	.71	.60	.57	.55
393713CJ	2104-440-B-12	1/2"	.44	.372	.353	.336
393721CJ	2104-440-B-12	5/8"	.61	.512	.486	.462
393730CJ	2108-440-B-12	3/4"	.69	.58	.55	.52
393748CJ	2112-440-B-12	1"	.81	.69	.65	.62

Male-Female Hex Aluminum Standoffs

- 3/16" Hex • 6-32 thread
- Iridite clear finish
- Thread length : 3/8"

Part No.	Product No.	Length	1	10	100	1000
393537CJ	4501-632-A-7	1/4"	\$.35	\$.298	\$.283	\$.269
393545CJ	4503-632-A-7	3/8"	.35	.298	.283	.269
393553CJ	4505-632-A-7	1/2"	.35	.298	.283	.269
393570CJ	4509-632-A-7	3/4"	.39	.326	.309	.294
393588CJ	4513-632-A-7	1"	.39	.326	.309	.294

Male-Female Hex Brass Standoffs

- 1/4" Hex • Zinc clear chromate finish
- 6-32 thread • Thread length : 3/16"

Part No.	Product No.	Length	1	10	100	1000
393916CJ	4530-632-B-12	1/4"	\$.73	\$.61	\$.58	\$.55
393924CJ	4532-632-B-12	3/8"	.75	.63	.60	.57
393932CJ	4534-632-B-12	1/2"	.81	.69	.65	.62
393941CJ	4538-632-B-12	3/4"	.78	.66	.63	.60
393959CJ	4542-632-B-12	1"	.78	.66	.63	.60
393967CJ	4546-632-B-12	1-1/4"	.85	.72	.68	.65

Female-Female Hex Brass Standoffs

- 1/4" Hex • 6-32 thread • Zinc clear chromate finish

Part No.	Product No.	Length	1	10	100	1000
393756CJ	2100-632-B-12	1/4"	\$.24	\$.205	\$.194	\$.185
393764CJ	2102-632-B-12	3/8"	.37	.307	.292	.277
393772CJ	2104-632-B-12	1/2"	.44	.372	.353	.336
393781CJ	2106-632-B-12	5/8"	.61	.512	.486	.462
393799CJ	2108-632-B-12	3/4"	.69	.58	.548	.52
393801CJ	2112-632-B-12	1"	.81	.69	.65	.62
393810CJ	2120-632-B-12	1-1/2"	.77	.65	.62	.59

Washer-Face Aluminum Thumbscrews



Part Number	Product Number	Thread	Length	Length	Pricing			
					1	10	100	1000
393975CJ	7100-A	4-40	5/16"	5/8"	\$1.55	\$1.47	\$1.40	\$1.33
393983CJ	7101-A	4-40	3/8"	11/16"	1.55	1.47	1.40	1.33
393991CJ	7105-A	4-40	1/2"	13/16"	1.55	1.47	1.40	1.33
394003CJ	7106-A	8-32	3/8"	11/16"	1.69	1.61	1.53	1.45
394011CJ	7107-A	8-32	1/2"	13/16"	1.75	1.66	1.58	1.50
394020CJ	7109-A	10-32	3/8"	11/16"	1.69	1.61	1.53	1.45
394038CJ	7111-A	10-32	5/8"	15/16"	1.75	1.66	1.58	1.50
394046CJ	7112-A	1/4-20	3/8"	3/4"	1.79	1.70	1.62	1.54

Plain Aluminum



Part Number	Product Number	Thread	Length	Length	Pricing			
					1	10	100	1000
394054CJ	7120-A	4-40	5/16"	1/2"	\$1.55	\$1.47	\$1.40	\$1.33
394062CJ	7125-A	6-32	3/8"	9/16"	1.49	1.42	1.35	1.28
394071CJ	7128-A	8-32	3/8"	9/16"	1.65	1.56	1.49	1.41
394089CJ	7135-A	10-32	1/2"	11/16"	1.69	1.60	1.52	1.44
394097CJ	7138-A	1/4-20	1/2"	3/4"	1.79	1.71	1.63	1.55
394100CJ	7140-A	1/4-20	5/8"	7/8"	1.85	1.76	1.67	1.59

Visit Our Website at www.Jameco.com

**Order Anytime,
Day or Night**

Our friendly sales department will take your order 24x7x365 by phone, fax, web or email.

1-800-831-4242