

DC Brushless Fans

Call for additional OEM PRICING – we carry major manufacturers.



234894CJ



102955CJ

- Low profile
- Ball and sleeve bearings
- Power input by lead wires or terminals
- PBT black thermo plastic frame and impeller
- Agency approved
- Low power consumption
- Low acoustical noise rating

NEW



Quantity SAVE



227900CJ



163619CJ

Part Number	Manufacturer	Product Number	Voltage (VDC)	Size (W" x H" x D")* See metric below	Air Flow (CFM)	Bearing	Current (mA)	Power (Watts)	Agency Approvals	Noise (dBA)	Connection (Leads)	Pricing			
												1	10	50	100
237075CJ	Nidec	TA225DC-B33399-55	12	2.36 x 2.36 x 1.00	12	Ball	110	1.3	UL/CSA	17.2	10"	\$5.95	\$5.36	\$4.28	\$3.21
75352CJ	Common Wealth	FP108FDC12VS2	12	2.36 x 2.36 x 1.00	15.5	Sleeve	110	1.3	UL/CSA/TUV/CE	25	12"	5.79	5.21	4.17	3.13
136143CJ	Delta	SBO612M	12	2.36 x 2.36 x 1.00	17.7	Sleeve	110	1.8	UL/CSA/VDE	26.5	5"	5.95	5.36	4.28	3.21
279646CJ	Toyo	T602512H	12	2.36 x 2.36 x 1.00	18.1	Ball	140	1.7	UL/CUL/TUV/CE	34	12"	5.89	5.30	4.24	3.18
102947CJ	Jamicon	JF0625S1H	12	2.36 x 2.36 x 1.00	20.5	Sleeve	230	2.7	UL/CSA/TUV	30.5	11"	6.49	5.84	4.67	3.50
150421CJ	Jamicon	JF0625B1H	12	2.36 x 2.36 x 1.00	20.5	Ball	230	2.7	UL/CSA/TUV	30.5	10"	6.95	6.26	5.00	4.29
195910CJ	Sunon	KD1206PTS1	12	2.36 x 2.36 x 1.00	21.7	Sleeve	190	2.3	UL/CSA/TUV	34	12"	6.49	5.84	5.26	4.73
109081CJ	Adda	AD0812HS-D71	12	3.15 x 3.15 x 0.60	29	Sleeve	190	2.3	UL/CSA/TUV/CE	31.4	12"	9.95	8.99	8.09	7.25
141920CJ	Adda	AD0812HB-C70	12	3.15 x 3.15 x 0.80	27.3	Ball	240	2.9	UL/CSA/CE	34	12"	6.35	5.95	5.75	5.55
16993CJ	Various	FAN7315SL1*	12	3.15 x 3.15 x 1.00	25-40*	Sleeve	120-200*	1-2*	UL/CSA*	25*	4-12**	6.95	6.26	5.00	3.75
75361CJ	Various	FAN6315BL*	12	3.15 x 3.15 x 1.00	25-40*	Ball	120-200*	1-2*	UL/CSA*	25*	4-12**	5.95	5.36	4.28	3.21
234894CJ	Adda	AD0812LB-A70GL	12	3.15 x 3.15 x 1.00	27.6	Ball	120	1.44	UL/CSA/TUV/CE	22.5	11.5"	8.19	6.39	5.89	5.49
286926CJ	Toyo	USTF802512MW	12	3.15 x 3.15 x 1.00	29	Ball	180	2.16	UL/CSA/CE/VDE	24.8	4.5"	6.99	6.29	5.05	3.79
154288CJ	Sunon	KDE1208PTS3-6	12	3.15 x 3.15 x 1.00	29.4	Sleeve	120	1.4	UL/CSA/TUV/CE	24.5	5.5"	4.55	4.10	3.28	2.46
195952CJ	Panasonic	FMB-08A12M	12	3.15 x 3.15 x 1.00	30	Sleeve	124	1.5	UL/CSA	28	11"	4.55	4.10	3.28	2.46
123529CJ	Adda	AD0812MS-A70GL	12	3.15 x 3.15 x 1.00	32	Sleeve	150	1.8	UL/CSA/TUV	28.3	12"	6.95	6.26	5.00	3.75
265578CJ	Yate Loon	D80SH-12	12	3.15 x 3.15 x 1.00	33	Ball	190	2.28	UL/CUL/TUV/CE	35.0	5"	7.29	7.18	7.07	6.96
166959CJ	NMB (Smart Fan)	3110NL-0120340-00†	12	3.15 x 3.15 x 1.00	35	Ball	290	3.5	UL/CSA	35	2"	8.95	8.06	6.44	4.83
191599CJ	NMB	3110KL-04W-B50	12	3.15 x 3.15 x 1.00	39	Ball	230	2.7	CSA	34	10"	7.49	6.74	5.39	4.04
185834CJ	Panafan	FBM08A12H	12	3.15 x 3.15 x 1.00	39.6	Sleeve	220	2.1	None	32	11"	6.95	6.26	5.00	3.75
206181CJ	Sunon	KDE1208PTS1-6	12	3.15 x 3.15 x 1.00	42	Sleeve	220	2.6	UL/CSA/TUV/CE	34	9"	5.95	5.36	4.28	3.21
355400CJ	ReliaPro	JR-DCF128025B1	12	3.15 x 3.15 x 1.00	42	Ball	230	2.8	UL/CUL/TUV/CE	28.6	11.5"	7.05	5.10	4.80	4.56
102955CJ	Sunon	KD1208PTB1	12	3.15 x 3.15 x 1.00	42.5	Ball	220	2.6	UL/CSA/TUV/CE	33.5	12"	6.49	5.85	5.29	4.75
249148CJ	Sunon	KDE1208PTB1-6	12	3.15 x 3.15 x 1.00	42.5	Ball	220	2.6	None	33.5	12"	6.49	5.85	5.29	4.75
172460CJ	Nidec	TA300DCM33406-68‡	12	3.15 x 3.15 x 1.00	43	Ball	290	3.5	UL/CSA	41	11/3 leads	9.95	8.99	7.19	5.39
189755CJ	Cheng	CHA8012DB	12	3.15 x 3.15 x 1.00	44.3	Ball	300	3.6	UL	37	2" w/ conn.	5.49	4.94	3.95	2.96
323897CJ	Mechatronics	F8025E12B1‡	12	3.15 x 3.15 x 1.00	46	Ball	240	2.88	UL/CUL/TUV	32	3/3 leads	6.99	5.09	4.79	4.45
196015CJ	Cheng	CHA9212CB	12	3.63 x 3.63 x 1.00	44.1	Ball	190	2.3	UL/CSA	31	12"	5.25	4.73	3.78	2.84
75441CJ	Common Wealth	FP108BDC12VS1	12	3.63 x 3.63 x 1.00	45	Sleeve	320	3.1	UL/CSA/TUV	32	10"	3.19	2.87	2.58	2.33
154641CJ	Nidec	TA350DC-M33422-16	12	3.63 x 3.63 x 1.00	48	Ball	290	3.5	UL/CSA	43	12"	7.55	6.80	5.44	4.08
190983CJ	Sunon	KD1209PTB1-6A	12	3.63 x 3.63 x 1.00	51	Ball	220	2.6	UL/CSA/TUV	34	12"	7.25	6.52	5.22	3.92
162739CJ	NMB (Smart Fan)	3610KL-04W-B56†	12	3.63 x 3.63 x 1.00	55	Ball	430	3.8	UL/CSA/VDE/CE	37	10/3 leads	7.95	7.16	6.44	5.80
102963CJ	Nidec	TA350DC-M33503-55	12	3.63 x 3.63 x 1.00	56	Ball	400	4.8	UL/CSA	45	8"	7.95	6.95	6.25	5.59
319193CJ	Pabst	3312-177	12	3.63 x 3.63 x 1.26	54.7	Ball	290	3.5	UL/CSA/CE/VDE	43	12"	7.95	7.16	5.72	4.29
213567CJ	Nidec	A34124-33‡	12	3.83 x 3.72 x 1.30	25	Ball	650	7.8	UL/CUL	60	11.5/3 leads	19.95	17.95	14.36	10.77
174140CJ	Common Wealth	FP108MS3	12	4.68 x 4.68 x 1.00	54	Sleeve	140	1.7	UL/CSA/TUV/CE	25	12"	6.95	6.26	5.00	3.75
227900CJ	Common Wealth	FP-108M-S1-B	12	4.68 x 4.68 x 1.00	80	Ball	330	4.0	UL/CSA/VDE/CE	42	12"	10.95	9.85	8.89	7.99
363848CJ	Mechatronics	E1225H12B	12	4.68 x 4.68 x 1.00	82	Ball	385	4.62	UL/CUL/TUV	40	3.5"	16.09	14.48	11.58	8.69
174924CJ	Globe Motors	D47-B10A-04T3-000	12	4.68 x 4.68 x 1.00	90	Ball	740	6.8	UL/CSA	39	Terminals	6.95	6.26	5.00	3.75
163619CJ	NMB (Smart Fan)	4710NL012P535P0†	12	4.68 x 4.68 x 1.00	90	Ball	740	8.9	None	38.5	12"	4.95	4.46	3.56	2.67
159020CJ	Sunon	KDE1212PMS1-6A	12	4.68 x 4.68 x 1.50	107	Sleeve	570	6.8	UL/CSA/TUV	41	12"	11.95	10.76	8.60	6.45
94625CJ	Sunon	KD1212PMB1-6A	12	4.68 x 4.68 x 1.50	108	Ball	570	6.8	UL/CSA/TUV/CE	42	12"	11.95	10.76	8.60	6.45
285966CJ	Delta	AFB1212VHE	12	4.68 x 4.68 x 1.50	130	Ball	900	10.8	UL/CSA/VDE/CE	48	6"	14.95	13.45	10.75	8.09
355655CJ	Panaffo	FBA12G12U	12	4.68 x 4.68 x 1.50	114.7	Sleeve	650	7.8	UL/CSA	45.5	9.5" w/ conn.	11.55	10.40	8.32	6.24
206201CJ	Sunon	KDE2404PKB3	24	1.60 x 1.60 x 0.80	6	Ball	30	0.7	UL/CSA/TUV/CE	24	12"	7.49	6.74	5.39	4.04
100909CJ	Sunon	KD2404PKS2	24	1.60 x 1.60 x 0.80	6.5	Sleeve	50	1.2	UL/CSA/TUV/CE	25.5	12"	7.95	7.16	6.44	5.36

‡ 16993CJ: Replacement for the PC/XT computer power supply fan ‡ 172460CJ: Locked rotor alarm ‡ 185826CJ/323897CJ: Speed sensor ‡ 213567CJ: Blower type
 † Temperature control: P/N 166959CJ (40°C); P/N 162739CJ (50°C, 3 leads); P/N 163619CJ (35°C) * Manufacturer & specifications may vary † Blue Part No. = Limited Quantity Available

DC Brushless Fans continued on page 158

♦ Size Conversion: Inches to mm

Inches	0.25	0.40	0.47	0.60	0.80	0.90	1.00	1.18	1.26	1.40	1.50	1.60	1.80	2.00	2.36	2.98	3.15	3.63	3.72	3.83	4.68	5.00	5.90	6.75
mm	6	10	12	15	20	23	25	30	32	35	38	40	45	50	60	75	80	92	95	97	120	127	150	170

Color Code Legend
New Sale Lower\$ QtySave

Order 24/7 Toll Free 1-800-831-4242