

Mount your video camera almost anywhere

As steady as a tripod, the Window Camera Mount lets you anchor that video camera to any glass surface at any height.



Mount your video or CCTV camera on any window or other non-porous surface, and capture what you've never been able to before. This heavy-duty metal mounting bracket attaches securely to any glass surface with a strong lever-activated 3.25" neoprene suction cup. Mount your camera onto the tripod-style screw. Adjust to any position, and you're ready to shoot hands-free. It's perfect for temporary surveillance of your business or home. For cameras up to 3 lbs.

Part No.	Description	1	5
222746CJ	CCTV camera window mount	\$33.19	\$29.87

Mini Indoor Pan & Tilt Mechanism Continuous Pan

- Automatic scanning: 0° - 355° angular travel; pan clockwise and counter-clockwise
- Manual tilt: 0° - 90°
- Pan speed: 5"/sec.
- Maximum load: 4.4 lbs.
- Power consumption: 1 watt
- Size: 2.5"Dia. x 2.4"H
- Warranty: 2 years continuous use • Weight: 0.4 lbs.



Camera not included

Includes: 24V @ 150mA power supply, wall mount bracket and mounting hardware

Part No.	Description	1	10
215407CJ	Mini pan/tilt	\$49.95	\$44.95

Outdoor Metal Camera Enclosures

- Plate glass: 3mm thick
- Outdoor use
- 170931CJ: without heater**
- Clear window area: 2.5"W x 2.3"H
- Max. camera size: 4.0"L x 2.4"W x 2.4"H
- Size: 16.0"L x 4.9"W x 4.9"H • Weight: 2.8 lbs.
- 170940CJ: w/ heater (keeps optics from fogging)**
- Clear window area: 3.5"W x 3.1"H
- Max. camera size: 6.5"L x 3.2"W x 3.2"H
- Size: 11.0"L x 3.6"W x 3.6"H • Weight: 6.8 lbs.



Part No.	Description	1	10
170931CJ	Camera housing	\$28.45	\$26.55
170940CJ	Camera housing w/ heater	62.95	59.89

Indoor Metal Camera Enclosure

- Clear window area: 2.2"W x 1.8"H
- Maximum camera size: 7.1"L x 2.6"W x 2.4"H
- Overall size: 11.7"L x 3.1"W x 2.7"H • Weight: 1.5 lbs.



Part No.	Description	1	10
310691CJ	Camera housing	\$27.49	\$26.15

Camera Mounting Bracket

- Aluminum construction (white coated)
- Maximum load: 6.5lbs.
- Overall height: 5.1"
- Base diameter: 1.8"
- 360 degree tilt swivel
- 120 degree tilt angle
- Base mounted w/ 3 screws (included)



Part No.	Description	1	10
311191CJ	15-B009	\$6.65	\$6.19

Mounting Brackets for Enclosed Camera

- Material: plastic
- Base mounted w/ 3 screws
- Swivel angle: 360°
- Tilt angle: 90°
- For use w/ enclosed cameras (P/N 150404CJ, pg 220)



Part No.	Max Load (lbs.)	Ht. (in.)	1	10
171002CJ	11 lbs.	6.4	\$4.69	\$4.08
170982CJ	6.6 lbs	2.0	5.49	4.94

Heavy Duty Camera Mounting Bracket

- Steel construction (white coated)
- Maximum load: 22 lbs.
- Overall length: 11.2"
- Base size: 3.8"L x 33.3"W
- 360° swivel angle, 90° tilt angle



Part No.	Product No.	1	10
320151CJ	15-B006	\$16.65	\$14.95

Monitor/TV Wall Mount Bracket

- 95° swivel
- Assembly required **SALE**
- Requires unit base to be mounted securely to wall stud
- Wall mount screws not included
- Supports up to 66 lbs. • Weight: 9.0 lbs.



Part No.	Description	1	10
181817CJ	12"-18" TV wall mount	\$23.69	\$21.55

Mini Alarm Siren

- Sound pressure: 108dB
- Output frequency: 3000Hz
- Rated: 2-12VDC @ 300mA
- Adjustable mounting plate
- 16" color coded connector wires, tinned
- Size: 2.8"Dia. x 2.5"L



Part No.	Description	1	10	50
148152CJ	Alarm siren	\$8.95	\$7.99	\$6.35

Free Technical Support

Our knowledgeable Tech Support department is ready to answer your questions. Just call us!
1-800-831-4242

EyeD Hamster USB Fingerprint Scanner

The EyeD Hamster fingerprint recognition tool for computers focuses on both security and convenience. This unit, which can be connected to the USB port of a computer and separate from the mouse, provides a simple, convenient and reliable security system instead of using passwords which are hard to remember or can be stolen. Applications such as computer networks, computer security, business IT solutions, E-commerce, banking and financial security and medical information systems are some of the environments where security plays an essential part.



- Assures computer security through fingerprint recognition
- Provide fast matching • USB interface
- Compact in size, takes up less than 3" of desk space

Includes: Installation manual and CD-ROM drivers
System requirements: Windows® 95/98/NT4.0/2000/ME/XP, available USB port

Blue Part No. = Limited Quantity Available

Part No.	Description	1	5
262713CJ	EyeD Hamster	\$115.95	\$104.35

EyeD USB OptiMouse with Biometric Recognition Software

With security and convenience of its fingerprint recognition module, this is the world's smartest mouse. No need to memorize passwords—the simple yet unique touch of your finger securely protects your PC, network, and the Internet all at once.

SALE



- Surface enhanced irregular reflection optical design
- Fingerprint extraction and verification technology
- Applications: PC and network security, Enterprise IT solution, secure files and folders within your PC, E-commerce

System requirements: Windows® 95/95/NT/2000/ME/XP, available USB port

Part No.	Description	1	10
262625CJ	EyeD USB OptiMouse	\$115.95	\$110.19

Notebook Computer Security Cable

This security cable uses a unique lock slot that is built into most of today's leading notebook computers.

NEW



If your computer is from Apple, Compaq, Dell, Digital, HP, IBM or Toshiba, among others, you probably have the built-in security lock slot at the side of your computer. Safeguard your laptop, desktop, and other valuable equipment.

- Length: 6 feet

Part No.	Description	1	10
355573CJ	Security cable	\$26.85	\$24.19