


### JAMECO BenchPro Mini Test Clips

- Two lengths
- Blue Part No. = Limited Quantity

**Includes:** One black and one red hooked probe clip



Part No.	Description	1	10	100
114809CG	1.75" mini test clips	\$1.89	\$1.49	\$1.35
114817CG	3.5" mini test clips	\$1.75	\$1.55	\$1.39

### JAMECO BenchPro Alligator Clip Leads

- 24 AWG wire
- Color-coded, 15" long
- Insulated alligator clip on each end
- 10 per pkg. in assorted colors



Part No.	Description	1	10	100
10444CG	Alligator leads	\$4.39	\$3.95	\$3.56

### JAMECO BenchPro BNC to Alligator Clip Test Cable

Permits BNC assembly to be used as a test cable.

- Upper connection: two alligator clips - red 5.5" 22AWG wire; black 9" 22AWG wire
- Lower connection: 23" RG/58U cable with BNC connector



**NEW**

Part No.	Description	1	10	100
11384CG	BNC cable	\$3.49	\$2.49	\$2.25

### JAMECO BenchPro Insulated Alligator Clips

- Color-coded
- Insulated barrel
- Jaw opening .375"-0.5"
- Solder strap and pre-drilled hole for 6-32 self threading screw
- Size: 2.3"L x 0.5"W
- Blue Part No. = Limited Quantity

**Includes:** One red and one black clip




Part No.	Description	1	10	100
70990CG	Alligator clips	\$0.39	\$0.36	\$0.33

### JAMECO BenchPro 1 1/4" Banana Plugs

- Set-screw connection
- Standard banana spring plug
- Additional 6-32 threaded hole for connection reliability
- Insulating sleeve is threaded to banana plug body
- .1875" lead opening
- Size: 1.6"L x 0.4"Dia.
- Blue Part No. = Limited Quantity

**Includes:** One red and one black plug




Part No.	Description	1	10	100
72194CG	Banana plugs	\$1.59	\$1.49	\$1.25

### JAMECO BenchPro 2 1/4" Banana Plugs

- Nine rib spring plug
- Will accept up to 0.1" dia. wire
- Each plug equipped with hole for interconnection
- Insulating sleeve fits snugly over copper post
- Size: 2.3"L x 0.3"W
- Set-screw connection

**Includes:** One red and one black connector




**NEW**

Part No.	Description	1	10	100
137526CG	Banana plugs	\$2.95	\$2.12	\$1.84

### JAMECO BenchPro Claw Clips and Alligator Clips

- Sold in increments of 2, 4 or 10
- Blue Part No. = Limited Quantity Available

Part No.	Description	Size (L"xW")	2	4	10
248920CG	Mini-alligator clip solder/crimp	1.2 x 0.3	\$.28	\$.25	\$.23
248954CG	Red insulator for 248920CG	—	.15	.13	.11
248946CG	Black insulator for 248920CG	—	.15	.13	.11
256525CG	Alligator clip, barrel/screw	1.9 x 0.2	.45	.38	.35
248938CG	Alligator clip, solder/crimp	1.6 x 0.3	.52	.48	.42
248971CG	Red ins. for 248938CG/256525CG	—	.29	.27	.25
248962CG	Blk. ins. for 248938CG/256525CG	—	.23	.21	.18
248989CG	Claw clip 10A, screw terminal	2.1 x 0.4	.55	.49	.45



### JAMECO BenchPro BNC Female Connector with 20AWG Lead Wires

Solder the 20AWG wires onto your protoboard, plug the BNC female connector into your test equipment and you have an instant testing board for varied applications.

- BNC female connector
- 7" 20AWG lead wires




Part No.	Cross Ref. No.	1	10	100
256831CG	CBB-069	\$5.39	\$5.15	\$4.89

### JAMECO BenchPro Micro Test Clip

- One piece per package

Part No.	Description	1	10	100
153162CG	1.6" micro test clip	\$.95	\$.87	\$.69



### JAMECO BenchPro Mini-Clip Test Leads

These spring loaded mini-clips hook easily to IC pins for testing.


- Set of five: red, blue, green, black and yellow
- 14"L; clips on both ends
- 26 AWG to 300V CSA/UL approved wire
- Blue Part No. = Limited Quantity



Part No.	Description	1	10	100
135298CG	Mini test leads	\$11.49	\$10.39	\$9.29

### JAMECO BenchPro Mini-Clip to Banana Test Cables

- Plunger-type action
- Available in black or red
- Positive connection that won't disconnect from components
- Banana plug connection on opposite end
- 20 AWG insulated wire
- Length: 3.5'




**NEW**

Part No.	Description	1	10	100
21857CG	Black test cable	\$3.95	\$3.55	\$2.99
21865CG	Red test cable	3.95	3.49	2.99

### JAMECO BenchPro Banana-to-Banana Test Leads

- Stackable
- Color coded: 2 each red, yellow, blue, black, white
- 9.8" long
- 10 per package
- 18 AWG wire



Part No.	Description	1	10	25
77841CG	Test leads	\$22.95	\$20.69	\$18.59

### Scowell Test Clip

- Hexnut for adjusting tension
- Rapid easy connectors
- Threaded stud standard

Part No.	Prod. No.	Description	1	10	100
469087CG	02-0	Threaded std	\$2.35	\$2.28	\$2.21

▲ This product ships from a separate warehouse and may require up to 4 days to ship. Each warehouse will accrue separate shipping charges. Sorry, we're unable to ship COD.

### 0.025" (0.64mm) Square Pin To Straight Banana Plug Adapter

- Excellent for use as a jumper on circuit cards with 0.6mm (0.025") square pins and equipment with 4.2mm (0.166") diameter pin jacks
- Plug body: brass alloy
- Insulation: polypropylene
- Connector: in-line banana plug
- Spring material: beryllium copper alloy
- Wire: 22AWG stranded (26 x 36) PVC insulated, 36" long
- Pin connector: 0.64mm (0.025") square pin receptacle, phosphor bronze gold plated



Part No.	Product No.	Color	1	5	10
684553CG	4771-36-0	Black	\$6.09	\$5.95	\$5.79
684570CG	4771-36-2	Red	6.09	5.95	5.79

### Pomona Micro SMD Oscilloscope Tip Adapter

- Adapter attaches to monolithic type oscilloscope probes
- Interface with pomona's micro SMD grabbers
- Adapter provides electrical connection to probe tip and probe head grounding area
- Dual leads allows oscilloscope probe to attach to 0.025" (0.64mm) diameter posts



Part No.	Product No.	1	5	10
684588CG	6443	\$56.69	\$55.19	\$53.65

Over 99% of Our Catalog Products Are In Stock

Place your order by 6PM EST for same business-day shipment.



Test Tools