

JAMECO ValuePro



**EXCLUSIVE**

## Miniature Toggle Switches

**Quantity SAVE**

• Mounting hole diameter: 1/4"



Fig. 1



Fig. 2




Fig. 3



Fig. 4



Fig. 5



Fig. 6



Fig. 7

Includes: Mounting hardware

Part No.	Cross Ref. No.	Fig.	Pins	Type ( ) Momentary	Dimensions L" x W" x D"	Lead Spacing			Contact Rating (A @ VAC)	Lead Type	Lever Type	Pricing				
						A"	B"	C"				1	10	100	500	1000
76523	JMT113	1	2	SPST on-off	.52 x .32 x .38	—	.185	—	6 @ 125 & 3 @ 250	Solder lugs	Round	\$1.15	\$1.03	\$ .93	\$ .75	\$ .65
21936	JMT123	1	3	SPDT on-on	.52 x .32 x .38	—	.185	—	5 @ 125 & 2 @ 250	Solder lugs	Round	1.15	1.03	.93	.75	.65
21910	JMT121	1	3	SPDT on-off-on	.52 x .32 x .38	—	.185	—	5 @ 125 & 2 @ 250	Solder lugs	Round	1.35	1.25	1.09	.95	.71
22833	LFH123	2	3	SPDT on-on	.52 x .28 x .36	—	.185	—	5 @ 125 & 2 @ 250	Solder lugs	Flat	1.15	1.05	.95	.85	.75
75854	SWM132	1	3	SPDT on-on	.52 x .32 x .38	—	.185	—	6 @ 125 & 3 @ 250	Solder lugs	Round	1.29	1.16	1.04	.94	.69
75889	SWM129	1	3	SPDT (on)-off-(on)	.52 x .32 x .38	—	.185	—	6 @ 125 & 3 @ 250	Solder lugs	Round	1.99	1.85	1.55	1.09	.95
26331	MPC123	1	3	SPDT on-on	.52 x .32 x .37	—	.185	—	6 @ 125 & 3 @ 250	PC straight	Round	1.39	1.25	1.12	.95	.78
26315	MPC121	1	3	SPDT on-off-on	.52 x .32 x .37	—	.185	—	5 @ 125 & 2 @ 250	PC straight	Round	1.29	1.15	1.05	.95	.72
71597	SWM148	3	3	SPDT on-on	.52 x .32 x .38	—	.185	.20	5 @ 125 & 2 @ 250	PC right angle	Round	1.19	1.09	.91	.73	.55
75871	SWM145	4	3	SPDT on-on	.52 x .32 x .38	—	.185	.20	6 @ 125 & 3 @ 250	PC right angle	Round	1.49	1.35	1.09	.86	.79
22841	LFH221	6	6	DPDT on-off-on	.52 x .52 x .38	.20	.185	—	3 @ 125 & 1 @ 250	Solder lugs	Flat	1.45	1.35	1.19	1.09	.95
21979	JMT223	5	6	DPDT on-on	.52 x .52 x .38	.20	.185	—	5 @ 125 & 2 @ 250	Solder lugs	Round	1.49	1.29	1.15	.99	.59
22859	LFH223	6	6	DPDT on-on	.52 x .52 x .38	.20	.185	—	5 @ 125 & 2 @ 250	Solder lugs	Flat	1.29	1.19	1.05	.95	.71
75900	SWM133	5	6	DPDT on-on	.52 x .52 x .38	.20	.185	—	6 @ 125 & 3 @ 250	Solder lugs	Round	1.49	1.34	1.14	.91	.68
21952	JMT221	5	6	DPDT on-off-on	.52 x .52 x .38	.20	.185	—	6 @ 125 & 3 @ 250	Solder lugs	Round	1.29	1.16	.99	.79	.59
75951	SWM130	5	6	DPDT (on)-off-(on)	.52 x .52 x .38	.20	.185	—	6 @ 125 & 3 @ 250	Solder lugs	Round	1.49	1.35	1.25	.99	.89
26367	MPC223	5	6	DPDT on-on	.52 x .52 x .38	.20	.185	—	5 @ 125 & 2 @ 250	PC straight	Round	1.49	1.35	1.25	.99	.89
26358	MPC221	5	6	DPDT on-off-on	.52 x .52 x .38	.20	.185	—	5 @ 125 & 2 @ 250	PC straight	Round	1.29	1.16	1.04	.89	.75

### Other Manufacturers

105814	SWA208	5	6	DPDT on-(on)	.52 x .52 x .38	.20	.185	—	5 @ 125 & 2 @ 250	Solder lugs	Round	\$1.59	\$1.45	\$1.29	\$1.03	\$ .77
202964	WI24	7	6	DPDT on-off-(on)	.50 x .50 x .46	.15	.15	.20	6 @ 125 & 3 @ 250	PC right angle	Round	1.59	.79	.68	.54	.41



## Toggle Switches

### E Series Sealed Miniature

- Contact rating: 7.5A @ 125VAC or 28VDC; 3A @ 250VAC
- UL 94V-0 Nylon case and bushing
- Sealed against solder and cleaning process contaminants
- Operating temp.: -30°C to +85°C
- Insulation resistance: 10,000MΩ min.



E Series

### GT Series Sealed Ultraminiature

- Contact rating: 0.4VA max. @ 20VAC or DC max.
- Sealed against solder and cleaning process contaminants
- Insulation resistance: 10,000MΩ min.
- Operating temp.: -30°C to +85°C
- Ultraminiature size, smallest footprint available



GT Series

### T Series Subminiature

- Operating temp.: -30°C to +85°C
- Insulation resistance: 10,000MΩ min.
- Contact rating: 0.4 VA max. @ 20VAC/VDC max; 3A @ 120VAC or 28VDC
- Compact size, small footprint



T Series

### 7000 Series Miniature

- Epoxy sealed terminals prevent contamination
- Insulation resistance: 10,000MΩ min.
- Contact rating: 0.4VA max. @ 20VAC/VDC max; 5A @ 120VAC or 28VDC; 2A @ 250VAC
- Operating temp.: -30°C to +85°C



7000 Series

### 9000 Series Power

- Contact rating: 6A @ 120VAC/28VDC; 3A @ 250VAC or 10A @ 125VAC/ 28VDC; 5A @ 250VAC
- Insulation resistance: 10,000MΩ min.
- Operating temp.: -30°C to +85°C

### MIL-S-83731 Series Military/Aerospace/Hi-Rel

- Contact rating: 0.4VA max. @ 28VAC/DC max.
- Operating temp.: -25°C to +71°C

These products ship from a separate warehouse and may not ship the same day. Each warehouse will accrue separate shipping charges. Sorry, we're unable to ship COD.

See Our Complete C&K Rocker Switch Offering at [www.Jameco.com/Prod/CKRocker](http://www.Jameco.com/Prod/CKRocker)

## Alcoswitch Toggle Switches

### Gemini A Series Miniature

- Insulation resistance: 1000MΩ @ 500VDC
- Dielectric strength: 1000 volts RMS @ sea level
- Contact rating: gold: 0.4VA @ 20VAC/DC; silver: 2A @ 250VAC, 5A @ 125VAC
- Operating temp.: -20°C to 85°C



A Series

### AE Series Washable

- Dielectric strength: 1000 volts RMS @ sea level
- Operating temp.: -20°C to +85°C
- Contact rating: gold: 0.4VA @ 20VAC/DC; silver: 2A @ 250VAC, 5A @ 125VAC
- Insulation resistance: 1000MΩ @ 500VDC



MT Series

### MT Series

- Dielectric strength: 1500VAC
- Operating temp.: -20°C to +80°C
- Contact rating: gold: 6A @ 125VAC, 3A @ 250VAC
- Insulation resistance: 1000MΩ @ 500VDC min. for 1 minute

### TT Series

- Insulation resistance: 1000MΩ min. @ 500VDC min.
- Dielectric strength: 1000 volts RMS @ sea level
- Contact rating: 0.4VA @ 20VDC or peak AC or 3A @ 125VAC
- Operating temp.: -30°C to +85°C



7320 Series

### 7320/7360/7402 Series Power

- Operating temp.: 0°C to 55°C
- Screw terminals
- Contact rating: 7320 series: 16A @ 125VAC, 8A @ 250VAC; 7360 series: 20A @ 125VAC, 10A @ 250VAC; 7402 series: 20A @ 125/250VAC

These products ship from a separate warehouse and may not ship the same day. Each warehouse will accrue separate shipping charges. Sorry, we're unable to ship COD.

See Our Alcoswitch Toggle Switch Offering at [www.Jameco.com/Prod/AlcoToggle](http://www.Jameco.com/Prod/AlcoToggle)

[www.Jameco.com](http://www.Jameco.com)

Our enhanced website offers over 65,000 new products. Find products quickly and order them easily.