


JAMECO ValuePro

## Aluminum Radial-Lead Electrolytic Capacitors (±20%) (Continued)



Leakage Current (20°C)	After 1 min.	0.03CV or 4µA, whichever is greater
	After 2 min.	0.01CV or 3µA, whichever is greater



† CROSS REFERENCES: Elna: RC2/RE2; IC: RAR/RSS; Marcon: SEM/SSM; Nichicon: LB/VX/USA/SR/SA; Rubycon: MS7/TWSS; Sprague: 501D/513D; UCC: SME/SRE/SRA/SRG; Panasonic: KA/KS/SU

### 105°C – HT Type General Purpose (Continued)

**Quantity SAVE**

\* Prepackaged: please order in increments of 10

\* Prepackaged: please order in increments of 10

Part No.	Cross Ref. No. †	Value (µF)	Voltage	Size (mm) D x H x L.S.	Pricing			
					1	10	100	500
609983	UVZ2E2R2MED	2.2	250V	6.3 x 11 x 2.5	\$.30	\$.211	\$.149	\$.096
610052	UVZ2W2R2MPD	2.2	450V	10 x 12.5 x 5	.38	.284	.208	.144
607961	UPW1H3R3MDD	3.3	50V	5 x 11 x 2	* .122	.091	.068	
609799	UVZ2A3R3MDD	3.3	100V	5 x 11 x 2	.20	.138	.10	.068
608382	UPW2A3R3MDD	3.3	100V	5 x 11 x 2	.25	.17	.125	.094
609861	UVZ2C3R3MED	3.3	160V	6.3 x 11 x 2.5	.30	.203	.149	.108
609932	UVZ2D3R3MED	3.3	200V	6.3 x 11 x 2.5	.30	.211	.144	.096
610001	UVZ2E3R3MPD	3.3	250V	8 x 11.5 x 3.5	.30	.211	.149	.102
610079	UVZ2W3R3MPD	3.3	450V	10 x 16 x 5	.44	.332	.25	.17
609596	UVZ1H3R3MDD	3.6	50V	5 x 11 x 2	.20	.13	.091	.06
607996	UPW1H4R7MDD	4.7	50V	5 x 11 x 2	* .122	.091	.068	
330781	RB4.7/50	4.7	50V	5 x 11 x 2	* .056	.046	.036	
609810	UVZ2A4R7MDD	4.7	100V	5 x 11 x 2	.20	.138	.10	.068
609887	UVZ2C4R7MED	4.7	160V	6.3 x 11 x 2.5	.30	.211	.149	.102
609941	UVZ2D4R7MPD	4.7	200V	8 x 11.5 x 3.5	.31	.229	.174	.12
330851	RB4.7/250	4.7	250V	8 x 11 x 3.5	* .14	.122	.105	
610087	UVZ2W4R7MPD	4.7	450V	10 x 20 x 5	.55	.413	.315	.219
330692	RB10/16	10	16V	5 x 11 x 2	* .039	.034	.029	
607849	UPW1H100MDD	10	50V	5 x 11 x 2	.20	.138	.10	.075
330799	RB10/50	10	50V	5 x 11 x 2	* .056	.046	.036	
609641	UVZ1J100MDD	10	63V	5 x 11 x 2	* .126	.096	.064	
608331	UPW2A100MED	10	100V	6.3 x 11 x 2.5	.27	.203	.149	.112
158529	R10B100	10	100V	6 x 11 x 2.5	* .08	.07	.055	
330844	RB10/160	10	160V	8 x 11 x 3.5	* .149	.127	.095	
609908	UVZ2D100MPD	10	200V	10 x 12.5 x 5	.39	.292	.216	.144
330861	RB10/250	10	250V	10 x 17 x 5	.22	.207	.181	.162
610036	UVZ2W100MHD	10	450V	12.5 x 20 x 5	.84	.65	.493	.349
608059	UPW1J120MDD	12	63V	5 x 11 x 2	.26	.178	.125	.094
606926	UHE1J150MDD	15	63V	5 x 11 x 2	* .111	.08	.072	
607110	UHE2A150MED	15	100V	6.3 x 11 x 2.5	* .146	.108	.081	
608067	UPW1J180MDD	18	63V	5 x 11 x 2	.26	.194	.141	.106
607401	UPW1A220MDD	22	10V	5 x 11 x 2	* .13	.094	.071	
158326	R22B35	22	35V	5 x 11 x 2	* .07	.05	.03	
607890	UPW1H220MDD	22	50V	5 x 11 x 2	.26	.178	.125	.094
606811	UHE1H220MDD	22	50V	5 x 11 x 2	* .113	.083	.062	
330801	RB22/50	22	50V	6 x 11 x 2.5	* .067	.055	.04	
609650	UVZ1J220MDD	22	63V	5 x 11 x 2	.24	.17	.125	.077
608083	UPW1J220MED	22	63V	6.3 x 11 x 2.5	.26	.194	.141	.106
609828	UVZ2C220MPD	22	160V	10 x 16 x 5	.45	.332	.241	.179
609975	UVZ2E220MHD	22	250V	12.5 x 20 x 5	.51	.387	.288	.211
610044	UVZ2W220MHD	22	450V	16 x 25 x 7.5	1.19	.91	.70	.47
607929	UPW1H270MDD	27	50V	5 x 11 x 2	.26	.178	.125	.094
609713	UVZ1V330MDD	33	35V	5 x 11 x 2	.21	.154	.108	.077
608243	UPW1V330MDD	33	35V	5 x 11 x 2	.25	.17	.116	.087
607072	UHE1V330MDD	33	35V	5 x 11 x 2	* .113	.083	.062	
609570	UVZ1H330MDD	33	50V	5 x 11 x 2	.24	.162	.116	.077
607945	UPW1H330MED	33	50V	6.3 x 11 x 2.5	.26	.194	.141	.106
609684	UVZ1J330MED	33	63V	6.3 x 11 x 2.5	.26	.178	.133	.094
608104	UPW1J330MED	33	63V	6.3 x 11 x 2.5	.27	.21	.149	.112
606969	UHE1J330MED	33	63V	6.3 x 11 x 2.5	* .146	.108	.081	
609781	UVZ2A330MPD	33	100V	8 x 11.5 x 3.5	.30	.235	.166	.125
608374	UPW2A330MPD	33	100V	8 x 15 x 3.5	.44	.324	.241	.181
609991	UVZ2E330MHD	33	250V	12.5 x 20 x 5	.59	.442	.32	.235
610061	UVZ2W330MHD	33	450V	16 x 35.5 x 7.5	1.49	1.15	.89	.64
608286	UPW1V390MDD	39	35V	5 x 11 x 2	.26	.178	.125	.094
607144	UHE2A390MPD	39	100V	8 x 15 x 3.5	.22	.17	.133	.108
609502	UVZ1C470MDD	47	16V	5 x 11 x 2	* .138	.10	.068	
606723	UHE1E470MDD	47	25V	5 x 11 x 2	* .113	.083	.062	

Part No.	Cross Ref. No. †	Value (µF)	Voltage	Size (mm) D x H x L.S.	Pricing			
					1	10	100	500
158246	R47B25	47	25V	5 x 11 x 2	* .046	\$.039	\$.029	
609730	UVZ1V470MDD	47	35V	5 x 11 x 2	* .105	.075	.051	
607970	UPW1H470MED	47	50V	6.3 x 11 x 2.5	.27	.205	.144	.112
607988	UPW1H471MHD	47	50V	6.3 x 11 x 2.5	.82	.62	.48	.36
330820	RB47/50	47	50V	6 x 11 x 2.5	* .102	.08	.057	
608139	UPW1J470MPD	47	63V	8 x 11.5 x 3.5	.31	.23	.167	.125
609801	UVZ2A470MPD	47	100V	10 x 12.5 x 5	.35	.267	.191	.143
608391	UPW2A470MPD	47	100V	10 x 16 x 5	.48	.365	.274	.206
607161	UHE2A470MPD	47	100V	10 x 12.5 x 5	.22	.17	.133	.10
609879	UVZ2C470MHD	47	160V	12.5 x 20 x 5	.59	.435	.32	.235
610010	UVZ2E470MHD	47	250V	12.5 x 25 x 5	.86	.65	.488	.348
607822	UPW1E560MDD	56	25V	5 x 11 x 2	.25	.17	.125	.094
608008	UPW1H560MED	56	50V	6.3 x 15 x 2.5	.29	.211	.158	.119
606862	UHE1H560MED	56	50V	6.3 x 11 x 2.5	* .146	.116	.087	
608155	UPW1J680MPD	68	63V	8 x 11.5 x 3.5	.40	.292	.216	.162
607507	UPW1A820MDD	82	10V	5 x 11 x 2	.21	.138	.10	.075
607671	UPW1C820MDD	82	16V	5 x 11 x 2	.23	.154	.116	.087
607005	UHE1J820MPD	82	63V	8 x 15 x 3.5	.28	.227	.174	.131
609300	UVZ0J101MDD	100	6.3V	5 x 11 x 2	* .138	.10	.068	
609414	UVZ1A101MDD	100	10V	5 x 11 x 2	* .122	.09	.06	
330705	RB100/16	100	16V	6 x 11 x 2.5	* .056	.047	.035	
606686	UHE1E101MED	100	25V	6.3 x 11 x 2.5	* .142	.112	.088	
330740	RB100/25	100	25V	6 x 11 x 2.5	* .067	.057	.048	
607700	UPW1E101MED	100	25V	6.3 x 11 x 2.5	.28	.211	.158	.111
330748	RB100/35	100	35V	8 x 11 x 3.5	.20	.084	.08	.074
158394	R100B50	100	50V	8 x 11 x 3.5	* .09	.07	.055	
607857	UPW1H101MPD	100	50V	8 x 11.5 x 3.5	.40	.292	.216	.162
606774	UHE1H101MPD	100	50V	8 x 11.5 x 3.5	.26	.211	.158	.119
608024	UPW1J101MPD	100	63V	10 x 12.5 x 5	.45	.335	.245	.184
608032	UPW1J101MPD	100	63V	8 x 15 x 3.5	.44	.324	.241	.181
330827	RB100/63	100	63V	10 x 13 x 5	* .13	.104	.078	
609748	UVZ2A101MPD	100	100V	10 x 20 x 5	.50	.373	.274	.204
609916	UVZ2D101MHD	100	200V	16 x 31.5 x 7.5	1.45	1.10	.83	.59
609967	UVZ2E101MHD	100	250V	16 x 31.5 x 7.5	1.55	1.21	.94	.70
607523	UPW1C121MED	120	16V	6.3 x 11 x 2.5	.26	.178	.125	.094
606619	UHE1C121MED	120	16V	6.3 x 11 x 2.5	* .113	.083	.062	
607726	UPW1E121MED	120	25V	6.3 x 12 x 2.5	.29	.211	.158	.119
606791	UHE1H121MPD	120	50V	8 x 15 x 3.5	.28	.227	.174	.131
606900	UHE1J121MPD	120	63V	8 x 20 x 3.5	.34	.275	.208	.156
607101	UHE2A121MPD	120	100V	10 x 31.5 x 5	.32	.288	.23	.173
608198	UPW1V151MPD	150	35V	8 x 11.5 x 3.5	.31	.24	.166	.125
607048	UHE1V151MPD	150	35V	8 x 11.5 x 3.5	.21	.162	.125	.094
606803	UHE1H151MPD	150	50V	10 x 12.5 x 5	.28	.227	.174	.131
608340	UPW2A151MHD	150	100V	12.5 x 25 x 5	1.10	.84	.67	.50
607540	UPW1C181MED	180	16V	6.3 x 12 x 2.5	.26	.194	.141	.106
607881	UPW1H181MPD	180	50V	8 x 20 x 3.5	.48	.365	.274	.206
608075	UPW1J181MHD	180	63V	12.5 x 15 x 5	.70	.53	.39	.293
606934	UHE1J181MPD	180	63V	10 x 20 x 5	.45	.365	.282	.212
607128	UHE2A181MHD	180	100V	12.5 x 25 x 5	.40	.36	.288	.216
609334	UPW0J221MDD	220	6.3V	5 x 11 x 2	.22	.146	.108	.077
607259	UPW0J221MED	220	6.3V	6.3 x 11 x 2.5	.26	.178	.125	.094
607419	UPW1A221MED	220	10V	6.3 x 11 x 2.5	.26	.194	.141	.106
606555	UHE1A221MED	220	10V	6.3 x 11 x 2.5	* .138	.11	.083	
311758	R220B10	220	10V	6 x 11 x 2.5	.45	.39	.36	.33
609481	UPW1C221MED	220	16V	6.3 x 11 x 2.5	.26	.194	.141	.102
158263	R220B25	220	25V	8 x 11 x 3.5	* .12	.09	.07	
608201	UPW1V221MPD	220	35V	10 x 12.5 x 5	.45	.33	.255	.191
608219	UPW1V221MPD	220	35V	8 x 15 x 3.5	.45	.332	.241	.181

RoHS compliant product This product is available in both RoHS and non-RoHS versions. Add an "R" before part number for RoHS version. Details on page 1.