



Belden Coaxial Cable

Compare Belden coaxial cables with those from the other companies who produce them and you will discover the obvious: Belden has no equal. That's because Belden coaxial cables are time-tested for performance that guarantees outstanding value. Belden guarantees this level of performance because every cable is tested with equipment that simulates every known environmental and electrical performance condition. As a result, Belden coaxial cable can be counted on for positive, reliable, and trouble-free operation. Engineered in a wide selection of sizes and materials, with each offering the benefits needed for physical, electrical and cost-requirement applications. Cable choices include broadband, standard analog, precision video for analog and digital, and more. For our complete line of Belden products, please visit www.Jameco.com/Belden.

75Ω Standard Analog Video Cable RG59/U Type

- 23 AWG solid .023" bare copper
 • 95% bare copper braid shield
 • Polyethylene insulation and black PVC jacket • Nominal outer diameter: .242"
 • Nominal capacitance: 67.3pF/m • Nominal impedance: 75Ω • Color: black

Part No.	Product No.	Description	1	5	10
732902	8241-100-10	100' reel	\$64.50	\$60.56	\$55.83
732911	8241-500-10	500' reel	169.86	159.38	158.20



Standard Analog Video Cable 75Ω Miniature Coax

- 27 AWG stranded (7x35) .017" bare copper-covered steel
 • Polyethylene insulation and black PVC jacket
 • Nominal capacitance: 67.3pF/m • Color: black
 • Nominal impedance: 75Ω • Nominal outer diameter: .100"

Part No.	Product No.	Description	1	5	10
734174	8218-U500-10	500' unreel box	\$256.99	\$239.99	\$233.65
734173	8218-U1000-10	1000' unreel box	397.39	386.99	371.15



Broadband Coax (Headend/Video Cables)

- 20 AWG solid .031" bare copper
 • Nominal capacitance 68.9pF/m • Color: black
 • Nominal outer diameter: .305" • Nominal impedance: 75Ω
 • 98% tinned copper double braid shield • Polyethylene insulation and jacket

Part No.	Product No.	Description	1	5	10
732962	8281-100-10	100' reel	\$99.99	\$89.99	\$79.99
732980	8281-500-10	500' reel	552.25	501.82	484.72
732988	8281-1000-10	1000' reel	1,087.67	948.18	900.77



- 20 AWG solid .032" solid bare copper
 • Duofoil® +95% tinned copper braid shield
 • Gas injected foam HDPE insulation and PVC jacket
 • Nominal capacitance: 53.5pF/m • Nominal impedance: 75Ω
 • Nominal outer diameter: .234" • Color: black

Part No.	Product No.	Description	1	5	10
734087	1505A-100-10	100' reel	\$49.99	\$47.49	\$44.99
734089	1505A-500-10	500' reel	214.35	192.80	183.62
734088	1505A-1000-10	1000' reel	435.29	382.27	364.07



Belden Paired Cable

Belden paired cables allow balanced signal transmission, which results in lower cross talk through common mode rejection. Due to the improved noise immunity of twisted pairs, they generally permit higher data speeds than other multi-conductor cables. For our complete line of Belden products, please visit www.Jameco.com/Belden.

- Chrome PVC jacket • Tinned copper
 • Twisted pairs • Tinned copper drain wire
 • Overall 100% BELDFOIL® shield (for shielded cables)

Audio, Control, and Instrumentation Cable Non-Plenum

- 22 AWG stranded (7 x 30) shielded with 22 AWG stranded TC drain wire
 • Polypropylene insulation • Paper wrap
 • Black PVC jacket • Nominal capacitance: 111pF/m
 • Nominal outer diameter: 0.138"

Part No.	Product No.	No. of Pairs	Description	1	5	10
733112	8451-100-10	1	100' reel (black).....	\$23.99	\$22.31	\$21.76
734063	8451-U500-10	1	500' unreel box (black) ..	118.75	107.91	93.75
733139	8451-1000-10	1	1000' reel (black)	197.09	177.39	159.65
734062	8451-U1000-10	1	1000' unreel box (blk) ..	243.42	223.14	205.95



Audio, Control, and Instrumentation Cable Non-Plenum (Cont.)

- 20 AWG stranded (7 x 28) shielded with 22 AWG stranded TC drain wire
 • Semi-rigid PVC insulation and overall chrome PVC jacket
 • Nominal capacitance: 180pF/m
 • Nominal outer diameter: 0.300" • Color: chrome

Part No.	Product No.	No. of Pairs	Description	1	5	10
734260	9402-100-60	2	100' reel	\$77.99	\$74.99	\$69.99
734262	9402-U500-60	2	500' unreel box	491.15	458.39	425.64
734261	9402-1000-60	2	1000' reel	1,190.49	1,090.47	1,054.55



- 18 AWG stranded (16 x 30) shielded with 20 AWG stranded TC drain wire
 • Tinned copper, twisted pair • Color: chrome
 • Polyethylene insulation with chrome PVC jacket
 • Nominal capacitance: 79pF/m • Nominal outer diameter: 0.222"

Part No.	Product No.	No. of Pairs	Description	1	5	10
734185	8760-100-60	1	100' reel	\$34.99	\$32.49	\$29.99
734187	8760-500-60	1	500' reel	166.19	150.81	143.26
734189	8760-U500-60	1	500' unreel box	150.39	143.26	136.44
734186	8760-1000-60	1	1000' reel	341.49	326.29	312.89



- 22 AWG stranded (7 x 30) shielded with 24 AWG stranded TC drain wire
 • Polypropylene insulation
 • Nominal capacitance: 115pF/m
 • Nominal outer diameter: 0.168"
 • Color: chrome

Part No.	Product No.	No. of Pairs	Description	1	5	10
734180	8723-100-60	2	100' reel	\$32.69	\$31.15	\$29.67
734182	8723-500-60	2	500' reel	173.99	140.99	130.69
734181	8723-1000-60	2	1000' reel	272.65	267.32	262.08
734183	8723-U1000-60	2	1000' unreel box ..	324.59	306.79	289.79



Paired Line Level Analog Audio Cable

- 14 AWG stranded (19 x 27) shielded with 16 AWG stranded TC drain wire
 • Polyethylene insulation
 • Nominal capacitance: 79pF/m
 • Nominal outer diameter: 0.355" • Color: chrome

Part No.	Product No.	Pairs	Description	1	5	10
733172	8720-100-60	1	100' reel	\$64.99	\$59.99	\$54.99
733190	8720-500-60	1	500' reel	376.55	363.57	346.27
734066	8720-U500-60	1	500' unreel box	500.39	467.74	435.11



www.Jameco.com

For additional Belden Coaxial and Paired Cable visit our website today.