

Additional Cable is available online at [www.Jameco.com/Cable](http://www.Jameco.com/Cable)

### JAMECO ValuePro 2-Conductor Power/Speaker Cable – 24 AWG

- Black wire with white polarity stripe
- Stranded copper wire (7 x 32)
- Operating voltage: 300V
- Temperature rating: 20°C to 60°C

**JAMECO EXCLUSIVE**

Part No.	Cross Ref. No.	Length	1	10	25
100280	224BK/C	100'	\$7.19	\$6.84	\$5.13
100299	224BK/K	1000'	49.99	44.89	39.59

### JAMECO ValuePro RG Type Bulk Coaxial Cable

**JAMECO EXCLUSIVE**

- For ethernet, oscilloscopes
- Nominal capacitance: 27pF/ft.; center resistance: 10.4Ω/1000ft. @ 77°F
- Nominal capacitance: 30.8pF/ft.; center resistance: 97Ω/1000ft. @ 77°F

**NEW MARKED IN PINK**


Part No.	Cross Ref No.	Type	Description	Length	1	25	50
644754	RG58/U-100	RG58/U	20 AWG solid	100'	\$11.99	\$11.39	\$10.79
644762	RG58/U-1000	RG58/U	20 AWG solid	1000'	108.49	103.05	97.89
644771	10X1-041TH-100	RG58A/U	20 AWG stranded	100'	23.75	22.49	21.35
644789	10X1-041TH-1000	RG58A/U	20 AWG stranded	1000'	187.49	178.19	169.19
644797	RG59/U-100	RG59/U	22 AWG solid	100'	12.99	12.35	11.75
644800	RG59/U-1000	RG59/U	22 AWG solid	1000'	130.89	124.34	118.10
644818	RG174/U-100	RG174/U	26 AWG stranded	100'	23.75	20.19	15.14
644826	RG174/U-1000	RG174/U	26 AWG stranded	1000'	234.25	222.53	166.90

## 30-Day Money-Back Guarantee

If you're not completely satisfied with your purchase, simply return the product within 30 days for a refund or exchange. Details on page 175.

## Computer Cables

### Disk Drive & SCSI Cables



32918 185076 32715

- 32918: 34-pin header socket ribbon cable for floppy to card
- 185076: 40-pin IDE hard drive cable to card
- 32715: 50-pin header socket ribbon cable SCSI-I

Part No.	Length	1	10	100
32918	23"	\$3.49	\$2.97	\$2.22
185076	14"	.95	.71	.53
32715	18"	4.29	3.80	3.22

**QUANTITY SAVE**

### 3.5" Disk Drive Power Adapter Cable

- IBM PC/XT and higher compatibles
- Allows connection of standard 3.5" disk drives to power supplies

Part No.	Length	AWG	1	10	100
28397	3.5"	22	\$3.95	\$3.36	\$2.86

### Serial Null Modem Cables

- Molded type connectors
- Color: gray

181404/180698 Pin outs: 1 & 6-4, 2-3, 3-2, 4-6 & 1, 5-5, 7-8, 8-7

181438 Pin outs: 2-2; 3-3; 5 & 6-4; 7-5; 8-7; 20-6 & 8 (Serial printer null modem)

180582 Pin outs: 2-2; 3-3; 4-5 & 6; 5-7; 6 & 8-20; 7-8; (Serial printer null modem)

180742 Pin outs: 1-4 & 5; 2-2; 3-3; 4-6; 5-7; 6-20; 7-8; 8-8

Part No.	Description	1	10	50
181404	6' DB9 F to DB9 F	\$5.69	\$5.09	\$4.59
180698	10' DB9 F to DB9 F	6.79	6.09	5.49
181438	6' DB25 M to DB9 F	4.95	4.49	3.95
180582	10' DB25 M to DB9 F	6.69	6.05	5.45
180742	10' DB25 F to DB9 F	7.39	6.65	5.99

### Ribbon Cable Assemblies

- Metal connector
- 300V rating • 105°C rating
- 28 AWG flat cable
- Tin-plated contacts

12408

Part No.	Description	1	10	100
12408	4' DB25 M-F	\$5.09	\$4.33	\$3.25
208582	6' DB9 M-F	4.75	4.26	3.83

**QUANTITY SAVE**

### AT/ATX Power Supply Extension Cable

- For use with ATX power supplies
- 20-pin ATX male and female connectors
- Color coded to ATX power supply

Part No.	Length	AWG	1	10	100
170238	15'	18	\$6.49	\$6.16	\$5.83

### 3.5" & 5.25" Disk Drive Power Splitters

- IBM PC/XT and higher compatibles
- Splits 4-line Molex male into 2 females

28354

Part No.	Drive	AWG	Length	1	10	100
28354	5.25"	18	5"	\$3.15	\$2.67	\$2.04
277528	5.25"	20	6"	1.95	1.75	1.49
72304	3.5"	22	5"	3.29	2.99	2.63

**QUANTITY SAVE**

### PS/2 Keyboard Extension Cables

- 6-pin mini DIN female-to-male
- Color: beige

Part No.	Description	1	10	100
28549	PS/2 6' non-coiled	\$4.35	\$3.70	\$2.78
111053	PS/2 10' non-coiled	5.49	4.67	3.50

**QUANTITY SAVE**

### Macintosh® Printer and Keyboard Cables

**NEW MARKED IN PINK**

Part No.	Mfr.	Description	1	10	50
10604	ValuePro	6' DIN8M	\$3.39	\$3.22	\$3.05
130025	ValuePro	10' DIN8M	5.99	5.39	4.85
1944994	Various	40' DIN8M w/ EMI	2.95	2.49	2.25

### IEEE 488 Cables

A variety of cable lengths are offered to ensure that IEEE system requirements are met (20 meters maximum length with a maximum of 15 devices). These cables are standard IEEE 488 with stackable 24-pin GPIB connectors on both ends.

- Color: gray

Part No.	Description	1	10	25
73155	1 meter	\$39.39	\$35.41	\$31.85
115781	2 meter	38.35	34.53	31.25
115802	4 meter	42.85	39.81	35.15

### VGA Monitor Extension Cables

- Extends VGA monitor cable; HDDB15 male-to-female
- IBM PC/XT and higher compatibles

134042:

- HDDB15 female w/ hex nuts and HDDB15 male w/ thumbscrews

66165/148532:

- Thumbscrews on each end

Part No.	Description	1	10	100
134042	6' screws/hex nuts	\$4.75	\$4.04	\$3.03
66165	6' thumbscrews	7.49	6.78	6.10
148532	10' thumbscrews	8.45	7.66	6.76

**QUANTITY SAVE**

### VGA Monitor Cables

- Connects video card to VGA monitor
- IBM PC/XT and higher compatibles
- HDDB15 male to male

Part No.	Description	1	10	100
66174	6' monitor cable	\$7.79	\$7.07	\$6.35
148523	10' monitor cable	7.25	6.49	5.79

### RGB Video Cable

- 75Ω coaxial cable
- Length: 6'
- Pin 1 red, pin 2 green, pin 3 blue, pin 14 white/black vertical, pin 13 gray horizontal
- Color: black
- 5 BNCs to HDDB15-pin male

Part No.	Description	1	10	25
73648	RGB video cable	\$19.95	\$16.99	\$12.74

**QUANTITY SAVE**

RoHS compliant product This product is available in both RoHS and non-RoHS versions. Add an "R" before part number for RoHS version. [Details on page 175.](#)

3 LEVELS OF SAVINGS

FRANCHISE SOURCED GENERIC & NON-FRANCHISED JAMECO HOUSE BRANDS FACTORY OVERRUN