

Powered Project Breadboards

- Solderless breadboard with 2420 tie points
- Power switch with light • Outputs are short-circuit protected

Includes: Power cord

***Web Code: XAT**

- 136259:**
- Fixed power: +5V @ 1A; variable power: 0 to ±15VDC @ 500mA
 - Edge plate for non-DIP size components
 - Input power: 120/220VAC @ 50-60Hz (switchable)
 - Replacement fuse: P/N 103908, pg 40
- 1537264:**
- Fixed power: +5V @ 1A; variable power: 0 to ±16VDC @ 300mA
 - Front panel has color coded terminals for DC output power supply, adjustable knobs & ground terminal
 - Input voltage: 110/220VAC @ 50-60Hz switchable

- One-year warranty
- Breadboard size: 7.4"L x 6.8"W
- Back panel has ground terminal
- Breadboard size: 5.8"W x 6.5"L
- Fuse protection



136259



1942163

- 1942163:**
- Input power: 110VAC or 220VAC @ 50-60Hz (switch selectable)
 - Triple output power supply: fixed 5VDC @ 1A; 0 to +16VDC @ 500mA (adjustable); 0 to -16VDC @ 500mA (adjustable)
 - Grounded case
 - Fuse protection
 - Overload protection
 - Lighted power switch

Part No.	Product No.	Overall Size	Wt. (lbs.)	1	5
136259	PP272-ROHS	9.8"L x 8.0"W x 2.6"H	6.8	\$175.95	\$159.95
1537264	PBB-4060	10.0"L x 7.8"W x 2.4"H	6.8	89.95	69.95
1942163	PBB-4060B	10.3"L x 8.8"W x 3.3"H	6.0	99.95	89.95

Wire Jumper Kit (350 pcs.)

- 25 each 0.1" to 5.0" lengths (14 sizes)
- Pre-stripped/preformed 22 AWG solid wire jumpers
- Clear plastic durable case
- 350 assorted lengths in 13 colors



***Web Code: LAS**

20080: 350-piece refill for 19290

Part No.	Description	1	10	50	100
19290	Wire jumper kit	\$16.95	\$14.95	\$13.95	\$10.95
20080	Refill for 19290	11.95	10.95	8.95	6.95

Reinforced Jumper Wires

- 24 AWG-300 volts
- Reinforced pin ends for durability
- 10 pack assortment: 2 each yellow, white, red, black & blue



***Web Code: LAS**

Part No.	Cross Ref. No.	Length (mm/inch)			
			1	10	100
126360	JW50	50/1.97	\$3.95	\$3.55	\$3.15
126342	JW100	100/3.94	5.95	5.29	4.49
126325	JW200	200/7.87	6.95	5.95	4.95

Resistance & Capacitance Decade Substitution Boxes

Wide-range decade substitution boxes for product design or calibration checks.

- Light durable construction
- Case may be grounded separately
- Three binding posts permit isolated substitutions
- Size: 4.7"W x 5.7"H x 1.4"D • Wt: 0.7 lbs.



211668

- 211668:** 1% resistance substitution from 1Ω to 11.111110MΩ
- 7 decade ranges of resistance
 - Values can be changed in 1Ω increments
 - @ 3 watts



211676

- 211676:** 5% capacitance substitution from 100pF to 11.111μF
- 5 decade ranges of capacitance
 - @ 50VDC

Part No.	Description	1	5
211668	Resistance	\$99.95	\$89.95
211676	Capacitance	129.95	119.95



Bug Boxes

- Anti-static plastic
- Fits in bug cage (P/N 11332, below)
- Box size: 4.9"L x 3.3"W x 0.6"H
- Color: blue
- P/N 11341: stores sixty 8-pin or thirty 16-pin DIPs
- P/N 11375: designed to store all types of components




Part No.	Description	1	10	100
11341	30 compartments	\$5.95	\$5.49	\$4.95
11375	3 compart./3 vertical & 3 horizontal dividers	5.95	5.49	4.95



Bug Tray

- Fits in bug cage (P/N 11332, below)
- 10 compartments
- 3.2"L x 0.4"W x 0.4"H ea.
- Tray size: 4.8"L x 3.6"W x 0.5"H



Part No.	Description	Color	1	10	100
11800	Divided bug tray	Blue	\$4.95	\$4.49	\$3.95



Bug Cage

- Holds bug boxes or trays
- Modular and interlocking
- Case size: 5.0"L x 3.9"W x 5.1"H



Boxes/Trays not included

Part No.	Description	Color	1	10	100
11332	Bug cage	Blue	\$8.95	\$8.29	\$7.49



Stackable Drawers

- Case size: 4.5"L x 4.4"W x 2.3"H
- Drawer size: 4.4"L x 4.0"W x 0.9"H
- Color: blue/white



Part No.	Description	1	10	100
11906	Case/drawers	\$2.49	\$2.29	\$1.95

Stackable Banana Test Lead Cables



159901

159919

- 159901:** Two 24" leads
159919: Two 36" leads

***Web Code: TLC**

Part No.	Prod. No.	Description	1	10	25
159901	B-24-02	Patch cord	\$9.95	\$8.95	\$8.29
159919	B-36-02	Patch cord	10.95	9.95	8.95

JAMECO ValuePro Component Cabinet



319600

Component Cabinet



319611 Components not included

- Drawer can be divided into 3 sections (clear)
- Wall mountable cabinet (ABS black)
- Cabinet size: 6.0"D x 14.7"W x 7.4"H

Includes: 20 clear plastic drawers, 20 dividers and 30 adhesive I.D. labels

319601: 5.5"L x 2.7"W x 1.5"H; **319611:** 2.5"W x 1.2"H

* Order in multiples of 10

Part No.	Description	1	10	100
319600	Component cabinet	\$16.95	\$15.49	\$13.95
319601	Drawer for cabinet	.49	.45	.39
319611	Divider for cabinet	*	.12	.10

JAMECO ValuePro Plastic Flip Top Boxes

- Clear plastic box with a clear plastic lid and removable dividers
- 100256:** Size: 8.4"L x 4.5"W x 1.4"H
- 18 compartments (1.4" x 1.5" each)
- 148902:** Size: 10.2"L x 4.7"W x 1.6"H
- 12 compartments (1.7" x 2.3" each)



100256

Part No.	Description	1	10	100
100256	18 compartments	\$2.29	\$1.95	\$1.79
148902	12 compartments	3.95	3.49	2.95

JAMECO ValuePro Plastic Flip Top Case for SMDs

- 128 compartments • Color: gray
- 8 rows x 16 columns grid
- Flip top openings on each bin
- Padded cover locks bins closed
- Perfect match to store P/N 156882 SMD resistor assortment, pg 44
- Size: 11.0"L x 8.3"W x 1.7"Thick



164267

Part No.	Description	1	10
164267	SMD flip top case	\$49.95	\$44.95

The Best Warranty in the Industry

All Jameco purchases are guaranteed for a full 90 days and even longer for Jameco House Brands.

RoHS compliant product + This product is available in both RoHS and non-RoHS versions. Add an "R" before part number for RoHS version. Details on page 189.