

## High Voltage Test Probe

- Maximum voltages: DC:40kV, AC: 40kV peak, 28kVrms
- Accuracy: DC:±1.5%, AC:±5%
- 10MΩ meter input impedance required
- Input/output impedance: 1,000MΩ/1.1MΩ
- Probe length: 14" • Cable length: 39"



Part No.	Description	Weight (lbs.)	1	5	25
132290	High voltage test probe	0.8	\$79.95	\$73.95	\$69.95

## 17MHz Logic Probe

- Max input freq.: 17MHz
- Pulse flash time: 500ms
- Input impedance: 1MΩ
- TTL threshold: Lo = 0.8V ±0.2V, Hi = 2.3V ±0.2V
- CMOS threshold: Lo = 30% VCC, Hi = 70% VCC
- Minimum pulse width: 30ns
- Audible tones for high & low
- Power supply protection: ±20V



Part No.	Description	Size	1	5	25
149930	Logic probe	7.7"L x 1.0"W x 0.6"H	\$39.95	\$35.95	\$32.95

## 17MHz Logic Pulser

- Compatible with TTL, DTL and CMOS ICs
- Pulse repetition rate: 0.5pps/400pps
- 1MΩ sync input impedance
- Pulse width output at 100mA load: 10µs
- Pulse mode output current: 10mA
- Square wave current output: 5mA
- "One shot" or continuous 5Hz pulse train



\* Web Code: MAQ

Part No.	Description	1	5	25
24601	Logic pulser	\$29.95	\$26.95	\$23.95

## PC Cable-Check® Pro

This powerful universal cable tester troubleshoots and maps 20 types of computer cables for opens, shorts, crosses, and good connections. Tests any combination of D-sub 9-pin, D-sub 15-pin, D-sub 25-pin, Centronics 36-pin printer, USB-A and USB-B, Mini USB, PS/2, RJ-11, RJ-45, BNC female-female cables and Firewire.



- Auto power off, auto and manual scan
- Includes: 9V battery

Paladin Tools®

Part No.	Mfr. Part No.	Description	1	5	25
652480	1577	LED indicators	\$185.95	\$169.95	\$159.95

## Single & Multiple Output Benchtop Power Supplies

\* Web Code: SAX



301920



175257



645600



301971



1939626



207618



207706



175249

### Single Output Benchtop Power Supplies • Voltage and current adjustable

Part No.	Mfr.	Mfr. Part No.	Voltage (VDC)/ Current (A)	Power (W)	Displays (Digits)	Input Voltage (VAC)	Short Circuit Protection	Overload Protection	Size (W" x H" x D")	Weight (lbs.)	Pricing	
											1	5
301920	Mastech	HY1503C	15/3	45	2-Analog	115/230 ±10%	Y	N	3.8 x 6.3 x 9.1	9	\$99.95	\$89.95
175265	Various	DPS150A	15/10	150	2-Analog	110 @ 60Hz	Y	Y	6.2 x 4.0 x 5.7	12	149.95	129.95
175257	Various	SPS250A	15/15	225	2-Analog	110/220 @ 47-63Hz	Y	Y	6.2 x 4.0 x 5.6	3.8	149.95	129.95
681221	Extech	382202	18/3	54	2-Digital LCD (4)	120 @ 60 Hz	Y	Y	9.4 x 6.1 x 4.3	6.6	139.95	129.95
645600	Extech	382200	30/1	30	2-Digital LCD (4)	100/240 @ 47-63Hz	Y	Y	9.4 x 6.1 x 4.3	4.4	129.95	119.95
301971	Lascar	PSU130	30/1	30	2-Digital LCD (4)	100/240 @ 47-63Hz	Y	Y	5.5 x 1.6 x 5.2	1.2	89.95	84.95
301866	Mastech	HY3003D	30/3	90	2-Digital LCD (4)	115/230 ±10%	Y	N	5.4 x 6.2 x 11.5	10	159.95	135.95
207618	Mastech	HY3005C	30/5	150	2-Analog	115/230 ±10%	Y	N	5.4 x 6.2 x 11.5	14	159.95	135.95
301911	Mastech	HY3005D	30/5	150	2-Digital LCD (4)	115/230 ±10%	Y	N	5.4 x 6.2 x 11.5	13	199.95	179.95
207626	Mastech	HY3010C	30/10	300	2-Analog	115/230 ±10%	Y	N	10.4 x 6.5 x 14.4	31	299.95	269.95
207635	Mastech	HY3010A	30/10	300	2-Digital LED (4)	115/230 ±10%	Y	N	10.4 x 6.5 x 14.4	31	319.95	289.95
207686	Mastech	HY3020A	30/20	600	2-Digital LED (4)	115/230 ±10%	Y	N	10.4 x 6.5 x 14.4	42	499.95	449.95
1939626	Extech	382290	30/30	900	2-Digital LED (4)	110-240 @ 50-60Hz	Y	Y	9.8 x 3.8 x 13.4	13.2	749.95	699.95
207694	Mastech	HY5002A	50/2	100	2-Digital LED (4)	115/230 ±10%	Y	N	5.4 x 6.2 x 11.5	13	179.95	159.95
163723	Various	DPS-3050	50/3	150	2-Analog	110 @ 60Hz	Y	Y	4.8 x 7.5 x 9.0	12.3	129.95	115.95
207706	Mastech	HY5003	50/3	150	2-Digital LED (4)	115/230 ±10%	Y	N	5.4 x 6.2 x 11.5	13	199.95	179.95
207600	Mastech	HY5005	50/5	250	2-Digital LED (4)	115/230 ±10%	Y	N	10.4 x 6.5 x 14.4	17	279.95	249.95
175249	Various	DPS5050	50/5	250	2-Analog	110 @ 50-60Hz	Y	Y	7.7 x 6.7 x 4.9	13.8	179.95	159.95



211693



301962



301947



197991



197982



1939618

### Multiple Output Benchtop Power Supplies • Voltage and current adjustable

Part No.	Mfr.	Mfr. Part No.	Voltage (VDC)/ Current (A)	Power (W)	Input Voltage	Displays	Short Circuit Protection	Overload Protection	Size (W" x H" x D")	Weight (lbs.)	Pricing	
											1	5
211722	Mastech	HY3002-2A	0-30/2; 0-30/2	120	115/230 ±10%	2-Digital LED	Y	N	10.4 x 6.5 x 14.4	23	\$219.95	\$199.95
211705	Mastech	HY3002D-2	0-30/2; 0-30/2	120	115/230 ±10%	4-Digital LCD	Y	N	10.4 x 6.5 x 14.4	23	239.95	219.95
211693	Mastech	HY3003D-2A	0-30/3; 0-30/3	180	115/230 ±10%	4-Digital LCD	Y	N	10.4 x 6.5 x 14.4	28	299.95	269.95
211731	Mastech	HY3003-2A	0-30/3; 0-30/3	180	115/230 ±10%	2-Digital LED	Y	N	10.4 x 6.5 x 14.4	28	299.95	269.95
301962	Mastech	HY5003-2	0-50/3; 0-50/3	300	115/230 ±10%	2-Digital LED	Y	N	10.4 x 6.5 x 14.4	26	299.95	269.95
301947	Mastech	HY3005D-2A	0-30/5; 0-30/5	300	115/230 ±10%	4-Digital LCD	Y	N	10.4 x 6.5 x 14.4	26.5	299.95	269.95
211713	Mastech	HY3003-3	0-30/3; 0-30/3; 5/3	300	115/230 ±10%	2-Digital LED	Y	N	10.4 x 6.5 x 14.4	29	299.95	269.95
211684	Mastech	HY3003D-3	0-30/3; 0-30/3; 5/3	195	115/230 ±10%	4-Digital LCD	Y	N	10.4 x 6.5 x 14.4	29	299.95	269.95
301955	Mastech	HY3005D-3A	0-30/5; 0-30/5; 5/3	315	115/230 ±10%	4-Digital LCD	Y	N	10.4 x 6.5 x 14.4	29	379.95	339.95
301938	Mastech	HY3005	0-30/5; 0-30/5; 5/3	315	115/230 ±10%	2-Digital LED	Y	N	10.5 x 6.5 x 14.3	10	199.95	179.95
197991	Extech	382213	0-30/3; 5/0.5; 12/0.5	98.5	110/120 @ 50-60 Hz	2-Digital LCD (3)	Y	Y	6 x 5.6 x 9.5	11	199.95	179.95
197982	Extech	382203	0-30/3; 5/0.5; 12/0.5	98.5	110/120 @ 50-60 Hz	2-Analog	Y	Y	6 x 5.6 x 9.5	11	169.95	159.95
1939618	Extech	382270	0-30/5; 0-30/5; 3-6/3; 8-15/1	334.5	110/120 @ 50-60 Hz*	4-Digital LED (4)	Y	Y	10.2 x 6.3 x 14.5	26.5	449.95	429.95

\* Selectable

\* For Complete Specs & Additional Product Listings Search [www.Jameco.com/More](http://www.Jameco.com/More) and Enter Web Code Listed Above