

12 Volt DC Fans

5 Volt DC Fans

24 Volt DC Fans

48 Volt DC Fans

Request a Large Quantity Quote



Jameco Part#	Manufacturer	Manufacturer Part #	Voltage (VDC)	Size mm (W x H x D)	Air Flow (CFM)	Bearing	Current (mA)	Power (Watts)	Agency Approvals	Noise (dBA)	Connection (Leads)	Price 1	Price 10+
2134299	ADDA Corporation	AD2012LB-K70	12	20 x 20 x 6	0.6	Ball	60	0.72	CE	19.5	5.5"	\$10.95	\$9.95
2095269	ADDA Corporation	AD2012LX-G70	12	20 x 20 x 10	0.6	Hypro	70	0.84	UL/CUL/CE	20	5.5"	\$7.95	\$6.95
2227655	ADDA Corporation	AD0212MX-K50	12	25 x 25 x 6	2.4	Hypro	60	0.72	UL/CUL	29	5.5"	\$11.95	\$10.95
2232198	ADDA Corporation	AD0212MX-K53	12	25 x 25 x 6	2.4	Hypro	90	1.08	UL/CUL/TUV/CE	29	(3) 5.5"	\$12.95	\$11.49
2179454	Jamicon Corporation	KF0210S1H	12	25 x 25 x 10	2.57	Sleeve	125	1.5	UL/TUV/CE	27	12"	\$3.95	\$3.49
2121316	ADDA Corporation	AD0212HB-G50GL	12	25 x 25 x 10	2.8	Hypro	90	1.08	UL/CUL/CE	23.1	5.5"	\$9.95	\$8.95
1951641	ADDA Corporation	AD0212MB-G50GL	12	25 x 25 x 10	2	Ball	80	0.96	UL/CUL/CE	25	(2) 5.5"	\$9.95	\$8.95
2224198	ADDA Corporation	AD0312LX-K73	12	30 x 30 x 6	2.6	Hypro	60	0.72	UL/CUL/TUV	20	5.3"	\$11.95	\$10.95
212783	Sunon	KDE1203PFB1-8	12	30 x 30 x 10	5.1	Ball	75	0.9	UL/CUL/TUV/CE/VDE	27	5.9"	\$6.95	\$5.95
2133860	ADDA Corporation	AD0312MB-G50	12	30 x 30 x 10	2.45	Hypro	60	0.72	UL/CE/TUV	20.3	5.5"	\$12.95	\$11.49
2131901	ADDA Corporation	AD0312HB-G53	12	30 x 30 x 10	4.5	Ball	80	0.96	UL/CSA/TUV/CUL/CE	34	(3) 5.5"	\$14.95	\$13.49
2233131	ADDA Corporation	AP3512LB-J70(S)	12	35 x 35 x 8	2.5	Ball	50	0.6	UL/CUL/TUV/CE	20	5"	\$9.95	\$8.95
2179411	Sunon	MF35101V1-10000-A99	12	35 x 35 x 10	7	Vapo	60	0.72	UL/CSA/TUV/CE	28	6"	\$11.95	\$10.95
212741	Sunon	KDE1235PFB2-8	12	35 x 35 x 10	4.5	Ball	60	0.72	UL/CUL/TUV/CE/VDE	21	3" with 2-pin connector	\$6.95	\$6.25
2276391	Evergreen	1404KL-04W-B59	12	35 x 35 x 10	5.6	Ball	80	0.96	UL/CUL/VDE	27	(3) 11"	\$11.95	\$10.95
2186224	Delta Electronics	FFB03812VHN-F00	12	38 x 38 x 28	20.2	Ball	65	0.78	UL/CSA/VDE/CE	58.5	(3) 13"	\$5.95	\$4.95
2215435	ADDA Corporation	AD0412HX-K96(X)	12	40 x 40 x 6	5.4	Hypro	72	0.864	UL/CUL/TUC/CE	30.5	5.5"	\$8.95	\$7.95
2167630	Sunon	HA40101V4-0000-999	12	40 x 40 x 10	5.3	Vapo	65	0.78	UL/TUV/CE	18.2	12"	\$6.95	\$6.25
1708473	Sunon	KDE1204PFVX11.MS.A	12	40 x 40 x 10	9.5	Vapo	150	1.8	UL/CUL/TUV	39	12"	\$8.95	\$7.95
2095314	ADDA Corporation	AD0412LX-G70	12	40 x 40 x 10	193	Ball	70	0.84	UL/CUL/TUV/CE	14	11"	\$5.95	\$5.39
2205384	ADDA Corporation	AD0412HB-G70(T)	12	40 x 40 x 10	6.7	Ball	100	1.2	UL/CUL/TUV	25	12"	\$9.95	\$8.95
2167234	Sunon	ME40101V1-0000-A99	12	40 x 40 x 10	8	Vapo	100	1.2	UL/CUL/TUV	32	12"	\$9.95	\$8.95
2224180	ADDA Corporation	AD0412LX-G76	12	40 x 40 x 10	4.7	Hypro	70	0.84	UL/CUL/TUV	14	(3) 12" (third wire is for speed sensor)	\$5.95	\$5.49
2132162	ADDA Corporation	AD0412LS-G70(T)	12	40 x 40 x 10	4.7	Sleeve	70	0.84	UL/CUL/TUV/CE/CSA	14	12"	\$4.95	\$4.49
2231777	ADDA Corporation	AD0412HB-G70	12	40 x 40 x 10	6.7	Ball	100	1.2	UL/CE	25	6" with connector	\$8.95	\$7.95
2232307	ADDA Corporation	AD0412LB-G71	12	40 x 40 x 10	5	Ball	70	0.84	UL/CUL/TUV/CE	34.5	(3) 12"	\$6.95	\$6.25
311968	ADDA Corporation	AD0412HB-G73	12	40 x 40 x 10	6.7	Ball	100	1.2	UL/CUL/TUV	25	(3) 12"	\$9.95	\$8.95
2132154	ADDA Corporation	AP0412MX-G70	12	40 x 40 x 10	4.7	Hypro	80	0.96	UL/CUL/TUV/CSA/CE	28	(2) 5"	\$9.95	\$8.95
2231769	ADDA Corporation	AD0412HB-D50	12	40 x 40 x 15	9.2	Ball	120	1.44	UL/CUL/CE	39.3	12"	\$5.95	\$4.95
2231793	ADDA Corporation	AD0412LB-D50	12	40 x 40 x 15	0.96	Ball	80	0.96	UL/TUV/CE	30.3	11"	\$5.95	\$4.95
1928118	ADDA Corporation	AD0412HB-C50	12	40 x 40 x 20	10.5	Ball	100	1.2	UL/CUL/TUV/CE	32	12"	\$8.95	\$7.95
2133907	ADDA Corporation	AD0412MB-C50	12	40 x 40 x 20	8.5	Ball	80	0.96	CE	28.5	11"	\$4.95	\$4.49
2151021	Sanyo Denki	109P0412H601	12	40 x 40 x 20	8	Ball	110	1.32	UL/CSA	33	7" with connector	\$4.95	\$4.49
2220218	ADDA Corporation	AD0412HB-C50(G)	12	40 x 40 x 20	10.5	Ball	100	1.2	UL/CUL/TUV/CE	36	10"	\$6.95	\$6.25
195899	Sunon	KDE1204PKS2	12	40 x 40 x 20	6.5	Sleeve	70	0.84	UL/TUV/CSA	25.5	12"	\$4.95	\$4.49
2228181	Delta Electronics	AFB0412LD	12	40 x 40 x 20	3.88	Ball	20	0.24	UL/TUV/CE/CSA	25	13"	\$3.95	\$3.59
2230969	Delta Electronics	EFB0412HHD	12	40 x 40 x 20	9.5	Ball	100	1.2	UL/CUL/CE/CSA	30.5	11"	\$6.95	\$6.25
2135380	ADDA Corporation	AD0412UB-C72GP(P)	12	40 x 40 x 20	10.6	Ball	170	2.04	UL/CUL/TUV/CE	34	12"	\$9.95	\$8.95
207052	ADDA Corporation	AD0412LB-C53	12	40 x 40 x 20	6.99	Ball	110	1.32	UL/CUL/TUV	30	(3) 11" (third wire is for speed sensor)	\$5.95	\$4.29
2227330	Eliana	HDF4020L-12HHB-4	12	40 x 40 x 20	10.9	Ball	165	1.98	UL/TUV	34	18"	\$7.95	\$6.95
2233924	Sunon	MF40201VX-10000-G99	12	40 x 40 x 20	10.8	Vapo	80	0.96	UL/CUL/TUV	27.5	(3) 12"	\$10.95	\$9.95
2233166	ADDA Corporation	AD0412MB-C71GP	12	40 x 40 x 20	8	Ball	120	1.44	UL/CUL/TUV/CE	26	11"	\$7.95	\$6.95
249375	ADDA Corporation	AD0412HB-C71GP	12	40 x 40 x 20	8.97	Ball	150	1.8	UL/CUL/TUV/CE	34	12"	\$6.95	\$6.25
136178	ADDA Corporation	AD0412HB-C56	12	40 x 40 x 20	9	Ball	100	1.2	UL/CSA/TUV	36	(3) 12"	\$7.95	\$6.95
2234863	Sunon	MB40201V3-0000-G99	12	40 x 40 x 20	6.3	Vapo	40	0.48	UL/CUL/TUV	18	(3) 6"	\$7.95	\$6.95
2231785	ADDA Corporation	AD0412HX-C56	12	40 x 40 x 20	9.6	Hypro	110	1.32	UL	31	(3) 11"	\$7.95	\$6.95
2082089	Sanyo Denki	109P0412H302	12	40 x 40 x 28	11.3	Ball	210	2.52	UL/TUV/CSA	37	3.75"	\$4.95	\$4.49
2186232	Delta Electronics	FFB0412HN-5T20	12	40 x 40 x 28	10.6	Ball	70	0.84	UL/C		3.5"	\$2.95	\$2.59
2099518	ADDA Corporation	AD0412UB-B33	12	40 x 40 x 28	16.6	Ball	230	2.76	UL/CUL/TUV	36.1	(3) 12"	\$12.95	\$11.49
2233158	ADDA Corporation	AD0412HB-B33	12	40 x 40 x 28	12.1	Ball	160	1.92	UL/CUL/TUV/CE	39	(3) 11"	\$12.95	\$11.49
2231751	ADDA Corporation	AD0412HB-B32	12	40 x 40 x 28	12.1	Ball	220	2.64	UL/CUL/TUV/CE	38.8	11"	\$7.95	\$6.95
2099500	ADDA Corporation	AD0412VB-B53GP(P)	12	40 x 40 x 28	21	Ball	800	9.6	UL/CUL/TUV/CE	58	(3) 12"	\$14.95	\$13.49

Jameco Part#	Manufacturer	Manufacturer Part #	Voltage (VDC)	Size mm (W x H x D)	Air Flow (CFM)	Bearing	Current (mA)	Power (Watts)	Agency Approvals	Noise (dBA)	Connection (Leads)	Price 1	Price 10+
2235348	ADDA Corporation	AD04012UB285300(LAP)	12	40 x 40 x 28	20.7	Ball	750	9	UL/CUL/TUV/CE	50.8	(3) 12" with connector	\$13.95	\$12.49
2235356	ADDA Corporation	AD0412HB-B32-380MM	12	40 x 40 x 28	12.1	Ball	220	2.64	UL/CUL/TUV/CE	38.8	(3) 14" with connector	\$6.95	\$6.25
2228800	Delta Electronics	GFB0412EHS-D	12	40 x 40 x 56	32.2	Ball	1.3	0.0156	UL/CUL/TUV/CE	64.5	(8) 3" with connector	\$9.95	\$8.95
2095322	ADDA Corporation	AD4512MX-G76	12	45 x 45 x 10	6.7	Hypro	70	0.84	UL/CUL/TUV/CE	22	11"	\$9.95	\$8.95
2232219	ADDA Corporation	AD4512HX-G70(T)	12	45 x 45 x 10	9.1	Hypro	90	1.08	UL/CUL/TUV/CE	27.4	11"	\$10.95	\$9.95
2095349	ADDA Corporation	AD0512MB-G76	12	50 x 50 x 10	10.5	Ball	120	1.44	UL/CUL/TUV/CE	24	11"	\$9.95	\$8.95
2202992	Sunon	ME50101V1-000U-A99	12	50 x 50 x 10	13.8	Vapo	110	1.32	UL/CUL/TUV	31	12"	\$7.95	\$6.95
2131936	ADDA Corporation	AD0512LB-G70(T)	12	50 x 50 x 10	8	Ball	80	0.96	UL/CUL/TUV/CE	20	(2) 12"	\$6.95	\$6.25
2258451	Sunon	KDE1205PHV1.MS.AF.GN	12	50 x 50 x 15	17	Vapo	83	0.996	UL/CUL	33	(3) 12", speed sensor	\$6.95	\$6.25
2203004	Sunon	MB50151V1-000U-A99	12	50 x 50 x 15	17	Vapo	87	1.044	UL/CUL/TUV/CE	33	12"	\$8.95	\$7.95
2133843	ADDA Corporation	AB5012MB-C03	12	50 x 50 x 20	4.6	Ball	90	1.08	UL/CUL/TUV/CE	32.5	(3) 12"	\$13.95	\$12.49
2100419	ADDA Corporation	AD0512HB-G70LF	12	51 x 51 x 10	11.8	Ball	90	1.08	UL/CUL/TUV/CE	27	11"	\$6.95	\$6.25
2220189	ADDA Corporation	AD0512HX-G70	12	51 x 51 x 10	11.2	Hypro	90	1.08	UL/CUL/TUV/CE	26	11"	\$10.95	\$7.89
2099534	ADDA Corporation	AD5012HB-D70	12	51 x 51 x 15	12.6	Hypro	100	1.2	UL/CUL/TUV/CE	29	5.5"	\$6.95	\$6.25
2220082	ADDA Corporation	AP5212MX-E70(8)	12	52 x 52 x 12	10.5	Hypro	70	0.84	UL/CUL/CE	20.8	(2) 5.5"	\$17.95	\$15.95
2228261	NMB Technologies	2106KL-04W-B39	12	52 x 52 x 15	9.9	Ball	70	0.84	UL/CUL/CE	21	12"	\$6.95	\$6.25
1946025	Evercool Thermal	EC6010M12CA	12	60 x 60 x 10	15.5	Ball	160	1.92	UL/CE/TUV	30	9"	\$8.95	\$7.95
1928126	ADDA Corporation	AD0612HX-G76(T)	12	60 x 60 x 10	14.5	Ball	150	1.8	UL/TUV/CE	31	(3) 12"	\$11.95	\$10.95
2205499	ADDA Corporation	AD0612HB-G90	12	60 x 60 x 10	14.06	Ball	140	1.68	UL/TUV	32.8	4.5"	\$4.95	\$4.49
2095357	ADDA Corporation	AD0612HB-G70	12	60 x 60 x 10	14.5	Ball	150	1.8	UL/CUL/TUV/CE	32	11"	\$7.95	\$6.95
2121332	ADDA Corporation	AD0612LX-G76(T)	12	60 x 60 x 10	10	Hypro	110	1.32	UL/CUL/TUV/CE	23	(3) 11" (third wire is speed sensor)	\$6.95	\$6.25
2217959	Thermactive Electronics	RDM6010B1	12	60 x 60 x 10	15.9	Ball	170	2.04	UL/CUL/TUV	31	12"	\$6.95	\$5.95
2233393	ADDA Corporation	AB6812MX-GCO	12	60 x 60 x 10	3.4	Hypro	90	1.08	CE	33.6	(2) 5"	\$9.95	\$8.95
144160	ADDA Corporation	AD0612LB-G76	12	60 x 60 x 10	11.7	Ball	80	0.96	UL/CUL/TUV	22.7	(3) 12"	\$11.95	\$10.95
2233609	ADDA Corporation	AD0612LS-G70	12	60 x 60 x 10	9.8	Sleeve	110	1.32	UL/CUL/TUV/CE	23	11"	\$8.95	\$7.95
2210909	Delta Electronics	AFB0612LB-TXNS	12	60 x 60 x 15	11.55	Ball	70	0.84	UL/TUV	24	6"	\$5.95	\$4.95
2233174	ADDA Corporation	AD0612LB-D9B	12	60 x 60 x 15	12.6	Ball	120	1.44	UL/CUL/TUV	25.8	(4) 5"	\$14.95	\$13.49
1928046	ADDA Corporation	AD0612MS-D70GL	12	60 x 60 x 15	14	Ball	110	1.32	UL/CUL/TUV/CE	28.8	5"	\$5.95	\$5.39
2121439	ADDA Corporation	AD0612DX-D70GL(T)	12	60 x 60 x 15	10.8	Hypro	70	0.84	UL/CSA/TUV/CE	23.8	(2) 5.5"	\$6.95	\$6.25
2270935	Sunon	MF60151V1-10000-A99	12	60 x 60 x 15	26.4	Vapo	147	1.764	UL/CUL/TUV/CE	34.2	12"	\$8.95	\$7.95
2231814	ADDA Corporation	AD0612MB-D71GL	12	60 x 60 x 15	14.3	Ball	80	0.96	UL/TUV/CE	28.8	5"	\$5.95	\$4.95
2233617	ADDA Corporation	AD0612LB-D70LF	12	60 x 60 x 15	12.6	Ball	90	1.08	UL/CUL/TUV/CE	25.3	5"	\$6.95	\$0.00
144161	ADDA Corporation	AD0612LB-C70GL-R	12	60 x 60 x 20	12.6	Ball	80	0.96	UL/CSA/TUV	22.7	12"	\$5.95	\$4.95
2133982	ADDA Corporation	AD0612LX-C70GL(T)	12	60 x 60 x 20	13.3	Sleeve	80	0.96	UL/CSA/TUV/CE	21.6	12"	\$6.95	\$6.25
2203389	ADDA Corporation	AD0612MB-C73GL(Q)	12	60 x 60 x 20	14.5	Ball	130	1.56	UL/CUL/CSA/TUV/CE	25.2	(3) 12"	\$6.95	\$6.25
2272671	Delta Electronics	DFB0612H	12	60 x 60 x 20	17.7	Ball	90	1.08	UL/CUL/TUV/CE	27	11"	\$5.95	\$5.39
2150766	ADDA Corporation	AD0612HB-A72GL	12	60 x 60 x 25	23.2	Ball	230	2.76	UL/CUL/TUV/CE	32.3	12"	\$7.95	\$6.95
2227719	ADDA Corporation	AD0612HB-A70GL	12	60 x 60 x 25	23.2	Ball	230	2.76	UL/CUL/TUV	32.3	12"	\$9.95	\$8.95
2205149	Sunon	MB60251V2-000U-G99	12	60 x 60 x 25	19.3	Vapo	74	0.888	UL/CUL	29	(3) 12"	\$9.95	\$8.95
2158311	Delta Electronics	AFB0612EH-BF00	12	60 x 60 x 25	38.35	Ball	480	5.76	UL/CSA/CE	46.5	8" with connector	\$11.95	\$10.95
2233078	ADDA Corporation	AD0612HB-A70GL4	12	60 x 60 x 25	24.8	Ball	230	2.76	UL/CUL/TUV	32.3	4" with connector	\$5.95	\$4.29
2227276	YS Tech Usa	NYWO60250125BL	12	60 x 60 x 25	15.8	Ball	80	0.96	UL/CUL/TUV	23.5	7"	\$4.95	\$4.49
2228818	Mitsubishi Electric and Electri	MMF-06D12DL	12	60 x 60 x 25	21.6	Ball	70	0.84	UL/CSA	23	8.5"	\$6.95	\$6.25
2217941	Thermactive Electronics	RDH6025B	12	60 x 60 x 25	20.3	Ball	140	1.68	UL/CUL	29	12"	\$6.95	\$6.25
2232260	NMB Technologies	2410W-04W-B30-2.5	12	60 x 60 x 25	19	Ball	120	1.44	UL/CUL/TUV/CSA/CE	31	2.5" with connector	\$5.95	\$5.39
2233051	ADDA Corporation	AQ0612LB-A70GL	12	60 x 60 x 25	13.2	Ball	80	0.96	UL/CUL	16.1	12"	\$10.95	\$9.95
2230766	Thermactive Electronics	RDH6025B-PWM	12	60 x 60 x 25	20.3	Ball	140	1.68	UL/CUL/TUV/CE	29	12"	\$7.95	\$6.95
2134205	ADDA Corporation	AD0612HB-GA6(GLS)	12	60 x 60 x 25	23.2	Ball	23	0.276	UL/TUV/CUL	35.2	(3) 12"	\$9.95	\$8.95
2133974	ADDA Corporation	AD0612XB-A72GL(P)	12	60 x 60 x 25	31.7		380	4.56	UL/CSA/TUV/CE	31.7	(3) 12"	\$11.95	\$10.95
2276567	Panasonic	FBA06A12L1A	12	60 x 60 x 25	14.1	HWB	100	1.2	UL/CSA	24	12"	\$7.95	\$6.95
2235276	ADDA Corporation	AD0712LX-DA6	12	70 x 70 x 10	29.2	Hypro	80	0.96	UL/CUL	32.7	(3) 12"	\$6.95	\$6.25
2125561	AVC America	DE07015R12U	12	70 x 70 x 15	43	Hydraulic	700	8.4	UL/CE/TUV	46	8" with connector	\$5.95	\$4.95
2232930	ADDA Corporation	AD0712HS-D73	12	70 x 70 x 15	32	Sleeve	250	3	UL/CUL/TUV/CE	40.3	(3) 12"	\$6.95	\$6.25
2233203	ADDA Corporation	AD0712HS-D71	12	70 x 70 x 15	34	Sleeve	250	3	UL/CUL/TUV/CE	40.3	(2) 12"	\$7.95	\$6.95
2227647	JMC Products	7025-12LS	12	70 x 70 x 25	22	Sleeve	100	1.2	UL/CUL/TUV	24.3	6" with connector	\$6.95	\$6.25
2233140	ADDA Corporation	AD7512HX(3)	12	75 x 75 x 30	10.3	Hypro	300	3.6	UL/CUL/CE	38.5	(3) 11"	\$7.95	\$6.95
2233035	ADDA Corporation	AD7512MS	12	75 x 75 x 30	7.8	Sleeve	200	2.4	UL/CUL/CE	34.9	15"	\$6.95	\$6.25
195936	ADDA Corporation	ADDA AD7512HB	12	75 x 75 x 30	10.3	Ball	240	2.88	UL/CUL/CE	38.5	(2) 12"	\$5.95	\$4.95
2099446	ADDA Corporation	AD7512LB(2A)	12	76 x 76 x 3	6.9	Ball	110	1.32	UL/CUL/TUV/CE	29	15"	\$6.95	\$6.25
2095365	ADDA Corporation	AD0812XX-D71	12	80 x 80 x 15	39.4	Hypro	350	4.2	UL/CSA/TUV/CE	42	11"	\$10.95	\$9.95
2132007	ADDA Corporation	AD0812HS-D70-LF	12	80 x 80 x 15	38.6	Sleeve	250	3	UL/CSA/TUV/CE	33	12"	\$5.95	\$5.49
2192561	ADDA Corporation	AD0812LB-D70(T)	12	80 x 80 x 15	20	Ball	90	1.08	UL/CSA/TUV/CE	19.6	12"	\$7.95	\$6.95
2230985	Delta Electronics	EFC0812DB	12	80 x 80 x 15	48.8	Ball	500	6	UL/CSA/CE	45	12"	\$9.95	\$8.95
2232948	ADDA Corporation	AD0812MX-D71	12	80 x 80 x 15	22.4	Sleeve	150	1.8	UL/CUL/TUV/CE	26	(2) 12"	\$8.95	\$7.95

Jameco Part#	Manufacturer	Manufacturer Part #	Voltage (VDC)	Size mm (W x H x D)	Air Flow (CFM)	Bearing	Current (mA)	Power (Watts)	Agency Approvals	Noise (dBA)	Connection (Leads)	Price 1	Price 10+
109081	ADDA Corporation	AD0812HB-D73(N)	12	80 x 80 x 15	29.9	Ball	190	2.28	UL/CUL/TUV	33.4	(3) 12"	\$9.95	\$8.95
141921	ADDA Corporation	AD0812HB-C70-R	12	80 x 80 x 20	27.3	Ball	240	2.88	UL/CSA/CE	34	12"	\$10.95	\$9.95
2232112	ADDA Corporation	AD0812UB-C7B	12	80 x 80 x 20	32.5	Ball	140	1.68	UL/CUL/TUV/CE	37.5	12"	\$12.95	\$11.49
2081078	Jamicon Corporation	JF0825B1UR-R	12	80 x 80 x 25	52	Dual Ball	370	4.44	UL/CUL/TUV/CE	40	12"	\$9.95	\$8.95
2210984	Sunon	EE80251B1-0000-A99	12	80 x 80 x 25	41	Ball	145	1.74	UL/TUV/CE	33	12"	\$7.95	\$7.49
2228113	Nidec Corporation	D08A-12TL	12	80 x 80 x 25	24.7	Ball	60	0.72	UL/CUL/TUV	19	8"	\$6.95	\$6.25
123530	ADDA Corporation	AD0812MS-A70GL-R	12	80 x 80 x 25	32	Sleeve	150	1.8	UL/CSA/TUV	28.3	12"	\$6.95	\$5.95
2233220	ADDA Corporation	AD0812UB-A70GL	12	80 x 80 x 25	48.8	Ball	300	3.6	UL/CUL/TUV/CE	37.4	12"	\$9.95	\$8.95
2135697	NMB Technologies	FBM-08A12H	12	80 x 80 x 25	39.6	Sleeve	220	2.64	UL/CSA	32	12" with connector	\$3.95	\$3.49
2209001	Sanyo Denki	9GV0812P4K03	12	80 x 80 x 25	74.8	Ball	870	10.44	UL/CUL/TUV	52	12"	\$7.95	\$6.95
2228148	Mechatronics	F8025S12B	12	80 x 80 x 25	26	Ball	75	0.9	UL/CUL/TUV	22	10"	\$6.95	\$6.25
2228121	NMB Technologies	3110GL-B4W-B14	12	80 x 80 x 25	24.7	Ball	10	0.12	UL/CUL	22	10"	\$6.95	\$6.25
2233385	ADDA Corporation	AD0812HB-A76GL	12	80 x 80 x 25	40.8	Ball	160	1.92	UL/CUL/TUV/CE	40.3	12"	\$9.95	\$0.00
234895	ADDA Corporation	AD0812HB-A73GL	12	80 x 80 x 25	38.6	Ball	250	3	UL/CSA/CE/TUV	38.6	(3) 12"	\$9.95	\$8.95
2234450	Sunon	EE80251B3-0000-G99	12	80 x 80 x 25	33	Ball	88	1.056	UL/CUL/TUV/CE	28	(3) 12"	\$8.95	\$7.95
2233238	ADDA Corporation	AD0812UX-A73GL	12	80 x 80 x 25	48.8	Hypro	300	3.6	UL/CUL/TUV/CE	40.8	12"	\$10.95	\$9.95
2187420	Velleman	PCBMF	12	80 x 80 x 25	34		233	2.796		30		\$19.95	\$0.00
1817864	NMB Technologies	3110KL-04W-B10-G00	12	80 x 80 x 25	24.7	Ball	100	1.2	UL/CSA/CE	22	Wire	\$13.95	\$12.75
2078194	ADDA Corporation	AD0812UB-A71GP	12	80 x 80 x 25	26.2	Ball	400	4.8	UL/CUL/TUV/CE	33.4	(2) 12"	\$8.95	\$7.95
107406	EBM Papst	8312GHL	12	80 x 80 x 32	39.4	Sleeve	330	3.96	UL/CSA/CE/VDE	43	12"	\$6.95	\$5.95
2228164	EBM Papst		8312 12	80 x 80 x 32	31.8	Ball	216	2.592	UL/CSA/TUV	36	12"	\$12.95	\$11.49
2134213	ADDA Corporation	AD0812MB-Y51	12	80 x 80 x 32	38	Ball	20	0.24	(IC)UL/CUL/TUV/CE	37	12"	\$14.95	\$13.49
1928100	ADDA Corporation	AD0812XB-F71DS(M)	12	80 x 80 x 38	99	Ball	1500	18	UL/CE/TUV	57	12"	\$9.95	\$8.95
2230758	Thermactive Electronics	RGM8038B1	12	80 x 80 x 38	83.4	Ball	850	10.2	UL/CUL/TUV/CE	57	12"	\$10.95	\$9.95
154641	Nidec Corporation	TA350DC-M33422-16	12	92 x 92 x 25	48	Ball	290	3.48	UL/CSA	34.8	12"	\$9.95	\$8.95
1952783	Nidec Corporation	TA350DC-M34138-34	12	92 x 92 x 25	35	Ball	160	1.92	UL/CSA	26.4	10"	\$3.95	\$3.49
2233094	ADDA Corporation	AQ0912LB-A70GL	12	92 x 92 x 25	40.7	Ball	150	1.8	UL/CUL/CE	29.2	12"	\$14.95	\$13.49
2228236	Sunon	1209PTB1-6	12	92 x 92 x 25	49	Ball	210	2.52	UL/CUL/TUV/CE	35	12"	\$9.95	\$8.95
1928302	ADDA Corporation	AD0912HS-A70GL(T)	12	92 x 92 x 25	57.9	Sleeve	210	2.52	UL/CSA/TUV/CE	38.6	12"	\$9.95	\$8.95
2232981	ADDA Corporation	AD0912LB-A72GL	12	92 x 92 x 25	37.7	Ball	130	1.56	UL/CUL/TUV/CE	42	(3) 12"	\$9.95	\$8.95
2228201	Mechatronics	E9225H12B2	12	92 x 92 x 25	51	Ball	360	4.32	UL/CUL/TUV	36	14"	\$9.95	\$8.95
2193942	Orion Fans	DPF92B012	12	92 x 92 x 25	50	Ball	290	3.48	UL/CUL	33	12"	\$7.95	\$6.95
1928097	ADDA Corporation	AD0912LX-A76GL(T)	12	92 x 92 x 25	32.8	Hypro	130	1.56	UL/CUL	23.5	(3) 12"	\$9.95	\$8.95
2134248	ADDA Corporation	AD0912US-A70GL	12	92 x 92 x 25	60	Sleeve	300	3.6	UL/CSA/TUV/CE	39.4	(2) 12"	\$12.95	\$11.49
1928003	ADDA Corporation	AD0912MS-A70GL	12	92 x 92 x 25	43	Sleeve	170	2.04	UL/CUL/TUV/CE	31	(2) 12"	\$13.95	\$12.49
2099796	Arndt	AD0912HB-A73GL(N)	12	92 x 92 x 25	52.5	Ball	250	3	UL/CUL/TUV	37.5	(3) 12"	\$7.95	\$6.95
2234871	Sunon	PMD1209PTB3-A(2).F.GN	12	92 x 92 x 25	65	Ball	300	3.6	UL/CUL/TUV/CE	43	(3) 12"	\$11.95	\$10.95
1928089	ADDA Corporation	AD0912HS-A76GL(T)	12	92 x 92 x 25	50	Sleeve	250	3	UL/CUL/TUV/CE	33.7	(3) 12"	\$9.95	\$8.95
1818605	NMB Technologies	3610KL-04W-B30	12	92 x 92 x 25	40.6	Ball	160	1.92	UL	34	Wire	\$10.95	\$9.95
2172711	Mechatronics	MC9238X12B	12	92 x 92 x 38	80.5	Ball			UL/CUL/TUV		12"	\$6.95	\$5.95
1819317	NMB Technologies	4710KL-04W-B50-E00	12	119 x 119 x 25.5	114.7	Ball	550	6.6		41.5	Wire	\$16.85	\$15.45
2170927	ADDA Corporation	AD1212US-A71GL-LF	12	120 x 120 x 25	99.12	Sleeve	500	6	UL/CUL/TUV/CE	43.3	11"	\$8.95	\$7.95
2228130	Delta Electronics	WFB1212H-BF05	12	120 x 120 x 25	86.5	Ball	360	4.32	UL/CSA/TUV/CE	37.6	11"	\$9.95	\$8.95
174140	Common Wealth	FP-108M-S3	12	120 x 120 x 25	54	Sleeve	140	1.68	UL/CSA/TUV/CE	25	12"	\$8.95	\$7.95
2228156	NMB Technologies	4710KL-04W-B19	12	120 x 120 x 25	63.5	Ball	120	1.44	UL/CUL/TUV	27	10"	\$9.95	\$8.95
2227866	YS Tech Usa	FD121225MB	12	120 x 120 x 25	87.8	Ball	290	3.48	UL/CUL/TUV	40.5	12"	\$12.95	\$11.95
2233246	ADDA Corporation	AD1212LS-A71GL	12	120 x 120 x 25	72	Sleeve	240	2.88	UL/CUL/TUV/CE	34.4	12"	\$10.95	\$9.95
1928020	ADDA Corporation	AD1212MB-Y51	12	120 x 120 x 25	97.5	Ball	370	4.44	UL/CUL/TUV/CE	41.1	11"	\$10.95	\$9.95
2228172	AVC America	F1225B12L	12	120 x 120 x 25	75.2	Ball	270	3.24	UL/CSA/TUV/CE	39.5	8"	\$9.95	\$8.95
2134264	ADDA Corporation	AD1212HX-A71GL(N)	12	120 x 120 x 25	85.2	Hypro	440	5.28	UL/CUL/TUVE/CE	39.1	(2) 12"	\$12.95	\$11.49
2233019	ADDA Corporation	AD1212LX-A71GL	12	120 x 120 x 25	72	Hypro	240	2.88	UL/CE	34.4	12"	\$9.95	\$8.95
2235321	ADDA Corporation	AS12012LB25A100	12	120 x 120 x 25	126	Ball	660	7.92	UL/CUL/TUV/CE	51	12"	\$10.95	\$9.95
2134053	ADDA Corporation	AD1212HB-A72GL(N)	12	120 x 120 x 25	85.2	Ball	370	4.44	UL/CUL/CE	39.1	(3) 12"	\$10.95	\$9.95
2270855	ADDA Corporation	AD1212HB-A71GL	12	120 x 120 x 25	87.8	Ball	370	4.44	UL/CUL	39.1	12"	\$13.95	\$12.49
2233060	ADDA Corporation	AQ1212HB-A71GL	12	120 x 120 x 28	87.9	Ball	290	3.48	UL/CUL/CE	39.1	12"	\$14.95	\$13.49
2203346	ADDA Corporation	AB1212MB-Y01	12	120 x 120 x 32	28	Sleeve	560	6.72	UL/CUL/TUV/CE	49	12"	\$9.95	\$8.95
2233254	ADDA Corporation	AD1212UB-Y51	12	120 x 120 x 32	130.8	Ball	510	6.12	UL/CUL/TUV/CE	48.4	12"	\$19.95	\$17.95
1928011	ADDA Corporation	AD2512MS-600MM	12	120 x 120 x 32	23.7		600	7.2	TUV/CE	51.1	(2) 12"	\$8.95	\$7.95
2173079	Sunon	EEC0381B2-0000-A99	12	120 x 120 x 38	108	Ball	421	5.052	UL/CUL/TUV/CE	44	12"	\$14.95	\$13.95
2211012	EBM Papst	4112GX	12	120 x 120 x 38	94	Sleeve	290	3.48	UL/CSA/CE	44	Terminal	\$9.95	\$8.95
2231478	ADDA Corporation	AD1212UB-F52	12	120 x 120 x 38	120	Ball	620	7.44	UL/CUL/TUV/CE	48	11"	\$12.95	\$11.95
2231697	Nidec Corporation	TA450DC-A31276-10A	12	120 x 120 x 38	104	Ball	440	5.28	UL/CSA	51.9	Terminals	\$11.95	\$10.95
2270871	ADDA Corporation	AD17212LB5151MD(OCW)	12	172 x 151 x 51	295	Ball	2300	27.6	UL/TUV/CSA/CE	60.6	12"	\$54.95	\$49.95
2228295	Sanyo Denki	109E1712K502	12	172 x 172 x 51	300	Ball	3200	38.4	UL/TUV/CSA	55	12"	\$29.95	\$26.95