

24 Volt DC Fans

5 Volt DC Fans

12 Volt DC Fans

48 Volt DC Fans

Request a Large Quantity Quote



Jameco Part#	Manufacturer	Manufacturer Part #	Voltage (VDC)	Size mm (W x H x D)	Air Flow (CFM)	Bearing	Current (mA)	Power (Watts)	Agency Approvals	Noise (dBA)	Connection (Leads)	Price 1	Price 10+
2167605	ADDA Corporation	AD0424HB-G70-LF	24	40 x 40 x 10	6.7	Ball	90	2.16	UL/CUL/TUV/CE	25	12"	\$9.95	\$8.95
2133931	ADDA Corporation	AD0424HB-G73	24	40 x 40 x 10	6.7	Ball	90	2.16	UL/CUL/TUV/CE	25	12"	\$10.95	\$9.95
2133940	ADDA Corporation	AD0424UB-C56	24	40 x 40 x 20	11	Ball	90	2.16	CE	31.9	11"	\$7.95	\$6.95
2158514	Sunon	MB40202V2-0000-A99	24	40 x 40 x 20	7.7	Vapo	33	0.792	UL/TUV/CE/CSA	21	12"	\$9.95	\$8.95
1928290	ADDA Corporation	AD0424HB-C50	24	40 x 40 x 20	10	Ball	90	2.16	UL/CE		12"	\$9.95	\$9.09
2231806	ADDA Corporation	AD0424LB-C50	24	40 x 40 x 20	1.4	Ball	60	1.44	UL/TUV/CE	25	12"	\$7.95	\$6.95
2121421	ADDA Corporation	AD0424MS-C50(T1)	24	40 x 40 x 20	7.7	Sleeve	70	1.68	UL/CSA/TUV/CE	27.5	(2) 12"	\$9.95	\$8.95
2233027	ADDA Corporation	AD4524HB-G70	24	45 x 45 x 10	8.7	Ball	80	1.92	UL/CUL/TUV/CE	28.6	12"	\$7.95	\$6.95
2235268	ADDA Corporation	AD0524HS-G70	24	52 x 52 x 10	11.2	Sleeve	90	2.16	UL/CUL/TUV/CE	26	12"	\$12.95	\$11.49
2188588	Sunon	ME60152V2-0000-A99	24	60 x 60 x 15	21.9	Vapo	85	2.04	UL/CUL/TUV/CE	32.5	12"	\$8.95	\$7.95
1708422	Sunon	KDE2406PHS3	24	60 x 60 x 15	15	Sleeve	50	1.2	UL/CUL/TUV/CE	31	12"	\$7.95	\$6.95
1816706	NMB Technologies	2406KL-05W-B50-L00	24	60 x 60 x 15	18.3	Ball	100	2.4	UL	34	Wire	\$13.95	\$12.79
1816693	NMB Technologies	2406KL-05W-B30-L00	24	60 x 60 x 15	18	Ball	56	1.344	UL/CUL/TUV/CE	31	11"	\$13.95	\$12.79
2134029	ADDA Corporation	AD0624MB-C70GL	24	60 x 60 x 20	14.5	Ball	40	0.96	UL/CUL/CE	25.7	12"	\$8.95	\$7.95
2233191	ADDA Corporation	AD0624HX-C70GL	24	60 x 60 x 20	16.3	Hypro	90	2.16	UL/CUL/TUV/CE	29.7	12"	\$9.95	\$8.95
189861	Jamicon Corporation	JF0625B2M-005-065R	24	60 x 60 x 25	18	Ball	130	3.12	UL/CSA/TUV/CE	31.3	10"	\$8.95	\$7.95
212628	ADDA Corporation	AD0624UB-A71GL-LF	24	60 x 60 x 25	23.2	Sleeve	150	3.6	UL/CSA/TUV/CE	32.3	17" with connector	\$7.95	\$6.95
2231831	ADDA Corporation	AD0624LB-A70GL	24	60 x 60 x 25	16.1	Ball	80	1.92	UL/TUV/CE	16.1	12"	\$6.95	\$6.25
2228244	Arndt	2406PTB1	24	60 x 60 x 25	23.5	Ball	110	2.64	UL/CSA/CE	33	12"	\$6.95	\$6.25
2132058	ADDA Corporation	AQ0624UB-A71GL(T)	24	60 x 60 x 25	28.3	Ball	160	3.84	UL/CUL/CE	40	(2) 12"	\$8.95	\$7.95
2132111	ADDA Corporation	AD0624HB-D71GL	24	60 x 60 x 25	18	Ball	80	1.92	UL/CSA/TUV/CUL/CE	28.3	12"	\$12.95	\$11.49
1816917	NMB Technologies	2410ML-05W-B40-E00	24	60 x 60 x 25	21.6	Ball	90	2.16	UL	33.5	Wire	\$13.69	\$12.55
1816925	NMB Technologies	2410ML-05W-B60-E00	24	60 x 60 x 25	25	Ball	56	1.344	UL/CSA/CE	31	11"	\$13.69	\$12.55
2121391	ADDA Corporation	AD06024MB257100	24	60 x 60 x 25	17.3	Ball	80	1.92	UL/CUL/TUV/CE	26.9	(2) 12"	\$7.95	\$6.95
1816888	NMB Technologies	2410ML-05W-B30-E00	24	60 x 60 x 25	19	Ball	60	1.44	UL	31	Wire	\$12.45	\$11.45
2235313	ADDA Corporation	AQ0624HB-70GL(T)	24	60 x 60 x 25	24.5	Ball	120	2.88	UL/CUL/CE	35.2	12"	\$11.95	\$10.95
2234492	ADDA Corporation	AG06024HB257002(00L5)	24	60 x 60 x 25	23.3	Ball	120	2.88	UL/CUL/TUV/CE	33	12"	\$9.95	\$8.95
2132066	ADDA Corporation	AD7524HB	24	75 x 75 x 30	9.1	Ball	160	3.84	UL/CUL/CE	38.5	12"	\$7.95	\$6.95
136161	Jamicon Corporation	JF0825B2H-005-065R	24	80 x 80 x 25	39.2	Ball	150	3.6	UL/CSA/TUV	31	12"	\$9.95	\$8.95
2158565	Sunon	EE80252B1-0000-A99	24	80 x 80 x 25	41	Ball	75	1.8	UL/CUL/TUV/CE	33		\$9.95	\$8.95
2134150	ADDA Corporation	AQ0824UB-A71GL	24	80 x 80 x 25	50	Ball	260	6.24	CE	41	12"	\$11.95	\$10.95
290029	Jamicon Corporation	JF0825B2M-005-065R	24	80 x 80 x 25	32.52	Ball	130	3.12	UL/CUL/TUV/CE	27.8	10"	\$9.95	\$8.95
2234847	ADDA Corporation	AD0824UB-A73GL(LN)	24	80 x 80 x 25	52.4	Ball	150	3.6	UL/CUL/TUV/CE	40.8	(3) 12"	\$11.95	\$10.95
2211160	NMB Technologies	3113PL05WB30	24	80 x 80 x 32	24	Ball	130	3.12	UL/CUL	31	12"	\$5.95	\$5.49
2220171	ADDA Corporation	AD0824UB-Y51	24	80 x 80 x 32	54.5	Ball	180	4.32	UL/CUL/CE/TUV	43.8	12"	\$12.95	\$11.95
2232964	ADDA Corporation	AD0824UB-F73DS	24	80 x 80 x 38	88	Ball	440	10.56	UL/CUL/CE	55	(3) 12"	\$8.95	\$7.95
2232067	ADDA Corporation	AD0824LB-F73	24	80 x 80 x 38	39	Ball	80	1.92	UL/CUL/TUV/CE	32.3	(3) 12"	\$7.95	\$0.00
2232075	ADDA Corporation	AD0924HB-C70	24	92 x 92 x 20	33	Ball	140	3.36	UL/CUL/TUV/CE/CSA	32.8	11"	\$10.95	\$7.89
2232999	ADDA Corporation	AD0924LB-A71GL	24	92 x 92 x 24	41.6	Ball	80	1.92	UL/CUL/TUV/CE	30	12"	\$9.95	\$8.95
2158303	Sunon	EE92252B1-0000-A99	24	92 x 92 x 25	51.5	Ball	87	2.088	UL/CE/TUV	34	12"	\$10.95	\$9.95
2203080	Nidec Corporation	A31394-55	24	92 x 92 x 25	42	Ball	140	3.36	UL/CSA		3" with connector	\$2.95	\$2.75
2230977	Delta Electronics	AFB0924VH	24	92 x 92 x 25	68	Ball	220	5.28	UL/CUL/CSA/CE	67.8	11"	\$9.95	\$8.95
2155065	Delta Electronics	AFB0924H-R00	24	92 x 92 x 25	51.2	Ball	100	2.4	UL/CSA/CE	34	12"	\$8.95	\$7.95
1928329	ADDA Corporation	AD0924XB-A71GL	24	92 x 92 x 25	67	Ball	250	6	UL/CUL/TUV/CE	42.6	12"	\$9.95	\$8.95
2215751	NMB Technologies	3610PL-05W-B20-100	24	92 x 92 x 25	43	Ball	150	3.6	UL/CUL	39	12"	\$4.95	\$4.49
1951051	Mechatronics	E9225L24B1-FS	24	92 x 92 x 25	35	Ball	85	2.04	UL/CUL	27	12"	\$4.95	\$3.95
2203071	NMB Technologies	3610PL-05W-B30	24	92 x 92 x 25	41	Ball	150	3.6	UL		12"	\$5.95	\$4.95
2233001	ADDA Corporation	AD0924MX-A70GL	24	92 x 92 x 25	47.2	Hypro	120	2.88	UL/CUL/TUV/CE	31.3	12"	\$8.95	\$7.95
2132082	ADDA Corporation	AD0924HX-A72GL	24	92 x 92 x 25	50	Hypro	150	3.6	UL/CSA/TUV/CUL/CE	33.7	(3) 12"	\$11.95	\$10.95
2236391	Sunon	MB60202V1-0000-A99	24	92 x 92 x 25	23	Vapo			UL/CUL	33	12"	\$10.95	\$9.95

Jameco													
Part#	Manufacturer	Manufacturer Part #	Voltage (VDC)	Size mm (W x H x D)	Air Flow (CFM)	Bearing	Current (mA)	Power (Watts)	Agency Approvals	Noise (dBA)	Connection (Leads)	Price 1	Price 10+
1819333	NMB Technologies	4710KL-05W-B50-B00	24	119 x 119 x 25.5	114	Ball	290	6.96		41.5	Wire	\$18.69	\$17.25
1819341	NMB Technologies	4710KL-05W-B50-E00	24	119 x 119 x 25.5	114	Ball	290	6.96		41.5	Wire	\$17.15	\$15.69
2121527	ADDA Corporation	AD1224MB-A71GL	24	120 x 120 x 25	80.5	Ball	170	4.08	UL/CUL/TUV/CE	38	11"	\$11.95	\$10.95
2197556	Coolmax Technology	1225M24B-ZD1	24	120 x 120 x 25	103.8	Dual Ball	300	7.2	UL/TUV	42.5	11"	\$8.95	\$7.95
2218046	ADDA Corporation	AD1224UB-A70GL	24	120 x 120 x 25	99	Ball	250	6	UL/CUL/TUV/CE	43.3	12"	\$12.95	\$11.95
2228199	Sunon	KDE2412PTB2-6A	24	120 x 120 x 25	80	Ball	170	4.08	UL/CUL/TUV	36.5	12"	\$11.95	\$10.95
2134070	ADDA Corporation	AD1224LB-F52(9TN)	24	120 x 120 x 25	72	Ball	140	3.36	UL/CUL/TUV/CE	34.4	11"	\$9.95	\$8.95
2235330	ADDA Corporation	AS12024LB25A100	24	120 x 120 x 25	126	Ball	280	6.72	UL/CUL/TUV/CE	51	12"	\$13.95	\$12.49
2233334	ADDA Corporation	AD1224UB-Y51(IP52)	24	120 x 120 x 32	59.5	Ball	50	1.2	UL/CUL/TUV/CE	26.9	11"	\$12.95	\$0.00
2235399	Sunon	PMB2412PLB2-A(2).GN	24	120 x 120 x 32	40	Ball	380	9.12	UL/CUL/TUV/CE	53.8	11"	\$20.95	\$18.95
2232104	ADDA Corporation	AD1224UB-Y5B	24	120 x 120 x 32	133	Ball	320	7.68	UL/CUL/TUV/CE	48.4	(3) 12"	\$16.95	\$14.95
694524	Jamicon Corporation	JF1238B2MR-R	24	120 x 120 x 38	101.3	Ball	220	5.28	UL/CSA/TUV/CE	39.1	9"	\$15.95	\$14.95
1809910	Sunon	KD2412PMSX-6A	24	120 x 120 x 38	119	Sleeve	300	7.2	UL/CE/TUV/CUL	45	12"	\$7.95	\$6.95
153411	Sunon	KD2412PMBX-6A	24	120 x 120 x 38	98	Ball	230	5.52	UL/CSA/TUV	36.5	12"	\$9.95	\$8.95
2134061	ADDA Corporation	AD1224HS-F51	24	120 x 120 x 38	104.8	Sleeve	320	7.68	UL/CSA/TUV/CE	42.8	10.5"	\$10.95	\$9.95
2215478	Comair Rotron	MD24B2	24	120 x 120 x 38	110	Ball	250	6	UL/CSA/TUV/CE	50	Terminal	\$10.95	\$9.95
2211021	EBM Papst	4124GX	24	120 x 120 x 38	94	Sleeve	138	3.312	UL/CSA/CE	43	Terminal	\$9.95	\$8.95
2236404	Sunon	MEC0382V1-0000-A99	24	120 x 120 x 38	138	Vapo	383	9.192	UL/CUL/TUV/CE	48	12"	\$12.95	\$11.95
2234919	ADDA Corporation	AD1324VB-F51	24	127 x 127 x 38	242.15	Ball	1100	26.4	UL/CUL/TUV/CE	64.5	(2) 12"	\$34.95	\$31.49
2270879	ADDA Corporation	AD17224MB5151M0(OCW)	24	172 x 151 x 51	327	Ball	1450	34.8	UL/TUV/CSA/CE	64	12"	\$54.95	\$49.95