



AC Fans

Jameco Part#	Manufacturer	Manufacturer Part #	Voltage (VAC)	Size mm (W x H x D)	Air Flow (CFM)	Bearing	Current (mA)	Power (Watts)	Agency Approvals	Noise (dBA)	Connection (Leads)	Price
213867	Fulltech Electric	UF-60D11HBWH-R	115	60 x 60 x 30	10.2	Ball	35	4.025	UL/CUL/VDE/CE	28	12	\$17.95
146078	Common Wealth	FP-108AX-S1-B-R(115)	115	80 x 80 x 25	23	Ball	140	16.1	UL/CE	29	12"	\$15.95
300557	Fulltech Electric	UF80B11SWH-R	115	80 x 80 x 25	24	Sleeve	140	16.1	UL/CUL/TUV/CE	35	12"	\$13.95
300600	Fulltech Electric	UF80A11BWH-R	115	80 x 80 x 38	29	Ball	120	13.8	UL/CUL/TUV/CE	36	12"	\$15.95
300389	Fulltech Electric	UF80A11BTH-R	115	80 x 80 x 38	30	Ball	120	13.8	UL/CUL/TUV/CE	36	Terminals	\$15.95
2228279	Mechatronics	80A12BWL	115	80 x 80 x 38	25	Ball	100	11.5	UL/CSA/CE	32	11"	\$14.95
2133819	ADDA Corporation	AA8381MS-AT	115	80 x 80 x 38	24	Sleeve	75	8.625	UL/CUL/TUV/CE	26.2	Terminals	\$13.95
303467	Sunon	SF11592A-1092HBL-GN	115	92 x 92 x 25	37	Ball	110	12.65	UL/CSA/TUV/CE	40	12"	\$12.95
2125931	Common Wealth	FP-108-1.	115	119 x 119 x 38	112	Ball	250	28.75	UL/CSA/TUV/CE	45	Terminals	\$13.95
1810048	Sunon	SP101AT1122HBL.GN	115	120 x 120 x 25	78	Ball	210	24.15	UL/CUL/TUV/CE	46	12"	\$16.95
124063	Sunon	SP101AT1122HBT-R	115	120 x 120 x 25	78	Ball	180	20.7	CSA/TUV/CE	46	Terminals	\$16.95
2131830	ADDA Corporation	AA1251MB-AW	115	120 x 120 x 25	69	Ball	240	27.6	UL/CSA/TUV/CE	38.7	(2) 12"	\$15.95
102884	Sunon	SP100A-1123XBT.GN	115	120 x 120 x 38	117	Ball	240	27.6	UL/CUL/TUV/CE	50	Terminals	\$14.95
106586	Common Wealth	FP-108-1-S1-S/T-R	115	120 x 120 x 38	105	Sleeve	180	20.7	UL/CSA/CE	47	Terminals	\$12.95
16935	Common Wealth	FP108-1-S1-B/T-R	115	120 x 120 x 38	105	Ball	240	27.6	UL/CSA	47	Terminals	\$13.95
1707163	Sunon	SP101A-1123HBL-GN	115	120 x 120 x 38	107	Ball	180	20.7	UL/CSA/TUV	50	12"	\$15.95
303361	Fulltech Electric	UF12A11BTL1-R	115	120 x 120 x 38	64	Ball	200	23	U/C/T/CE	37	Terminals	\$14.95
2258419	Fulltech Electric	UF-12A1223BWH	115	120 x 120 x 38	92	Ball	260	29.9	UL/CUL/TUV/CE	42	(4) 12"	\$15.95
2100427	ADDA Corporation	AA1281HS-AW	115	120 x 120 x 38		Sleeve	250	28.75	UL/CUL/TUV/CE	42.6	(2) 12"	\$11.95
2230141	Fulltech Electric	UF13A11BTH	115	127 x 127 x 38	120	Ball	160	18.4	UL/CUL/CE	50	Terminals	\$19.95
212582	Fulltech Electric	UF15PC11BWH-R	115	172 x 150 x 51	226	Ball	250	28.75	UL/CUL/TUV/CE	58	12" wires	\$32.95
189684	Fulltech Electric	UF15PC11BTH	115	172 x 150 x 51	226	Ball	250	28.75	UL/CUL/TUV/CE	58	Terminals	\$32.95
2230660	Thermocool Fans	G8025HAS	120	80 x 80 x 25	23	Sleeve			UL/CUL/TUV/CE		12"	\$10.95
2231734	ADDA Corporation	AA8251HB-AT	120	80 x 80 x 25	21	Ball	70	8.4	UL/CUL/TUV/CE	27	Terminals	\$12.95
2126096	Common Wealth	FP-108B	120	92 x 92 x 25	22	Ball	60	7.2	UL/CSA	24	15"	\$9.95
2230678	Thermocool Fans	G9225HAS	120	92 x 92 x 25	34	Sleeve	140	16.8	UL/CUL/TUV	40	Terminals	\$10.95
2234169	NMB Technologies	3610PS-12T-B20	120	92 x 92 x 25	28	Ball	90	10.8	CSA	35	Terminals	\$8.95
2135275	Common Wealth	FP-108JC	120	92 x 92 x 38	45	Sleeve	150	18	UL/CSA/CE	37	12"	\$13.95
2230694	Thermocool Fans	G12038MAB	120	120 x 120 x 38	85	Ball	220	26.4	UL/CUL/TUV	44	Terminals	\$12.95
2230686	Thermocool Fans	G12038HAS	120	120 x 120 x 38	198	Sleeve	340	40.8	UL/CUL/TUV	122	Terminals	\$11.95
2230379	EBM Papst	4800N	120	120 x 120 x 38	57.1	Sleeve	78	9.36	UL/CSA/CE	32	Terminals	\$14.95
2205392	ADDA Corporation	AA1281MB-AW	120	120 x 120 x 38	80	Ball	250	30	UL/CUL/TUV/CE	40	12"	\$10.95
2205405	ADDA Corporation	AA1281MB-AT(CF)	120	120 x 120 x 38	80	Ball	210	25.2	UL/CUL/TUV	41	Terminals	\$13.95
2231726	Sunon	SP100A-1123XBL.GN	120	120 x 120 x 38	117	Ball	240	28.8	UL/CUL/TUV/CE	50	12"	\$15.95
2231718	Sunon	SP102A-1123MBL.GN	120	120 x 120 x 38	88	Ball	160	19.2	UL/CUL/TUV/CE	40	12"	\$14.95
2230707	Thermocool Fans	G13538HAS	120	135 x 135 x 38	122	Sleeve	340	40.8	UL/CUL/TUV/CE	53	12"	\$13.95
2230715	Thermocool Fans	G15050HAS	120	150 x 150 x 50	198	Sleeve			UL/CUL/TUV/CE		12"	\$20.95
2230723	Thermocool Fans	G17050HASB	120	172 x 172 x 51	198	Ball	400	48	UL/CUL/TUV/CE/CCC	59	Terminals	\$20.95
100918	Sunon	SF23080A/2083HSL.GN	220	80 x 80 x 38	30	Sleeve	60	13.2	UL/CSA/CE/TUV	35	12"	\$15.95
355630	Fulltech Electric	UF-80A23-BTH-R	220	80 x 80 x 38	30	Ball	60	13.2	UL/CSA/VDE/CE	36	Terminals	\$12.95
2230117	ADDA Corporation	AA8252HB-AT	220	80 x 80 x 38	21	Ball	60	13.2	UL/CUL/CE/TUV	27.8	Terminals	\$12.95
2210837	Comair Rotron	SU3G1	220	80 x 80 x 38	32	Sleeve	70	15.4	UL/CSA	39	12"	\$8.95
2231566	ADDA Corporation	AA1252MB-AT	220	120 x 120 x 25	65	Ball	100	22	UL/CUL/TUV/CE	38	Terminals	\$14.95
102892	Sunon	DP200A-2123XBT-R	220	120 x 120 x 38	117	Ball	140	30.8	UL/CSA/TUV	50	Terminals	\$17.95
303459	Sunon	DP200A-2123XBL-ROHS	220	120 x 120 x 38	117	Ball	120	26.4	U/C/T/CE	50	12"	\$15.95
2133801	ADDA Corporation	AA1282UB-AT	220	120 x 120 x 38	103	Ball	140	30.8	UL/CUL/TUV/CE	46.4		\$15.95
2230424	Common Wealth	FP-108EX(S-1)	220	172 x 150 x 51	210	Ball	220	48.4	UL/CUL/TUV	50	Terminals	\$24.95
2265879	Orion Fans	OA172SAP-22-1TB	220	172 x 150 x 51	235	Ball	230	50.6	UL/CUL/TUV/CE	52	Terminals	\$29.95
2235241	ADDA Corporation	AA8382HX-AT	230	80 x 80 x 38	24	Hypro	70	16.1	UL/CUL/TUV/CE	26.2	Terminals	\$11.95
2234177	NMB Technologies	3115FS-23T-B10-A00	230	80 x 80 x 38	33	Ball	87	20.01	UL/CSA	36	Terminals	\$10.95
2234636	NMB Technologies	3610PS-23T-B20	230	92 x 92 x 25	28	Ball	50	11.5	UL/CSA	35	Terminals	\$12.95
2228287	EBM Papst	RER-125-19/56	230	138 x 138 x 40	61.2	Ball	83	19.09		65	12"	\$39.95
2231996	ADDA Corporation	AA1282HB-ATR2	240	120 x 120 x 38	95	Ball	130	31.2	UL/CUL/TUV	40	Terminals	\$10.95