

Request a Large Quantity Quote

MW MEAN WELL DIN-Rail Power Supplies



Fig. 1



Fig. 2



Fig. 3



Fig. 4



Fig. 5



Fig. 6



Fig. 7



Fig. 8



Jameco Part No.	Manufacturer Part No.	Fig.	Primary Output Voltage (VDC)	Output Current (A)	Max Output Power (W)	Input Voltage (VAC @ Hz)	Maximum Input Current (A)	Efficiency (%)	Operating Temp. Min (Cel)	Operating Temp. Max (Cel)	Size (H" x W" x D")	Price 1	Price 10
2101243	DR-15-5	2	5	2.4	12	85 to 264 @ 47-63	.88	77%	-20	60	0.98 x 3.66 x 2.20	\$12.25	\$10.95
2094952	DR-15-12	2	12	1.25	15	85 to 264 @ 47-63	.88	84%	-20	60	0.98 x 3.66 x 2.20	\$12.25	\$10.95
2101391	DR-15-15	2	15	1	15	85 to 264 @ 47-63	.88	84%	-20	60	0.98 x 3.66 x 2.20	\$13.00	\$10.95
2100873	DR-15-24	2	24	0.63	15.2	85 to 264 @ 47-63	.88	85%	-20	60	0.98 x 3.66 x 2.20	\$12.25	\$10.95
373174	DR-30-5	2	5	3	15	85 to 264 @ 47-63	.88	74%	-20	60	3.07 x 3.66 x 2.20	\$16.00	\$13.49
373182	DR-30-12	2	12	2	24	85 to 264 @ 47-63	.88	81%	-20	60	3.07 x 3.66 x 2.20	\$14.95	\$13.49
373191	DR-30-15	2	15	4	60	85 to 264 @ 47-63	.88	82%	-20	60	3.07 x 3.66 x 2.20	\$16.00	\$13.49
373203	DR-30-24	2	24	1.5	36	85 to 264 @ 47-63	.88	83%	-20	60	3.07 x 3.66 x 2.20	\$14.95	\$13.49
212303	DR-4505	2	5	5	25	85 to 264 @ 47-63	1.5	77%	-10	50	3.66 x 3.07 x 2.64	\$19.10	\$15.65
192699	DR-45-12	2	12	3.5	42	85 to 264 @ 47-63	1.5	77%	-10	50	3.66 x 3.07 x 2.64	\$18.69	\$15.65
221874	DR-45-15	2	15	2.8	42	85 to 264 @ 47-63	1.5	77%	-10	50	3.66 x 3.07 x 2.64	\$19.10	\$15.65
192681	DR-45-24	2	24	2	48	85 to 264 @ 47-63	1.5	80%	-10	50	3.66 x 3.07 x 2.64	\$19.10	\$15.65
373212	DR-60-5	2	5	6.5	32.5	85 to 264 @ 47-63	1.2	76%	-20	60	3.07 x 3.66 x 2.20	\$21.80	\$18.49
373230	DR-60-12	2	12	4.5	54	85 to 264 @ 47-63	1.2	82%	-20	60	3.07 x 3.66 x 2.20	\$21.49	\$17.49
373238	DR-60-15	2	15	4	60	85 to 264 @ 47-63	1.2	83%	-20	60	3.07 x 3.66 x 2.20	\$21.80	\$18.49
373246	DR-60-24	2	24	2.5	60	85 to 264 @ 47-63	1.2	84%	-20	60	3.07 x 3.66 x 2.20	\$20.49	\$18.49
212291	DR-75-12	4	12	6.3	75	85 to 264 @ 47-63	1.6	76%	-10	60	2.19 x 4.93 x 3.94	\$30.79	\$25.75
212282	DR-75-24	4	24	3.2	76.8	85 to 264 @ 47-63	1.6	80%	-10	60	2.19 x 4.93 x 3.94	\$30.79	\$25.75
221866	DR-75-48	4	48	1.6	76.8	85 to 264 @ 47-63	1.6	76%	-10	60	2.19 x 4.93 x 3.94	\$31.50	\$25.75
1943511	DR-100-12	2	12	7.5	90	88 to 264 @ 47-63	3.0	87%	-20	60	3.94 x 3.66 x 2.20	\$31.10	\$27.25
1943529	DR-100-15	2	15	6.5	97.5	88 to 264 @ 47-63	3.0	87%	-20	60	3.94 x 3.66 x 2.20	\$31.10	\$25.95
1943537	DR-100-24	2	24	4.2	100.8	88 to 264 @ 47-63	3.0	89%	-20	60	3.94 x 3.66 x 2.20	\$29.49	\$25.95
212274	DR-120-12	4	12	10	120	88 to 132 176 to 264 @ 47-63	2.6	80%	-10	60	2.58 x 4.93 x 3.94	\$37.89	\$31.49
212266	DR-120-24	4	24	5	120	88 to 132 176 to 264 @ 47-63	2.6	84%	-10	60	2.58 x 4.93 x 3.94	\$37.89	\$31.49
221904	DR-120-48	4	48	2.5	120	88 to 132 176 to 264 @ 47-63	2.6	89%	-20	70	8.94 x 4.93 x 3.94	\$37.89	\$31.49
2216788	DRA-40-12	1	12	3.34	40	90 to 264 @ 47-63	.80	85%	-30	70	1.57 x 3.54 x 3.94	\$20.20	\$16.55
2216796	DRA-40-24	1	24	1.7	40.8	90 to 264 @ 47-63	.80	87%	-30	70	1.57 x 3.54 x 3.94	\$20.20	\$16.55
2216809	DRA-60-12	1	12	5	60	90 to 264 @ 47-63	1.3	85%	-30	70	1.57 x 3.54 x 3.94	\$22.30	\$18.29
2216817	DRA-60-24	1	24	2.5	60	90 to 264 @ 47-63	1.3	87%	-30	70	1.57 x 3.54 x 3.94	\$22.30	\$18.29
2216745	DRC-40A	1	13.8	1.9	40.02	90 to 264 @ 47-63	.80	86%	-30	70	1.57 x 3.54 x 3.94	\$22.95	\$21.95
2216753	DRC-40B	1	27.6	0.95	40.02	90 to 264 @ 47-63	.80	87%	-30	70	1.57 x 3.54 x 3.94	\$22.95	\$21.95
2216761	DRC-60A	1	13.8	2.8	60	90 to 264 @ 47-63	1.3	86%	-30	70	1.57 x 3.54 x 3.94	\$26.95	\$25.25
2216770	DRC-60B	1	27.6	1.4	60	90 to 264 @ 47-63	1.3	88%	-30	70	1.57 x 3.54 x 3.94	\$26.95	\$24.95
2220841	DRC-100A	1	13.8	7	96.6	90 to 264 @ 47-63	1.8	87%	-30	70	2.17 x 3.54 x 3.94	\$37.95	\$34.95
2220859	DRC-100B	1	27.6	3.5	96.6	90 to 264 @ 47-63	1.8	89%	-30	70	2.17 x 3.54 x 3.94	\$37.95	\$34.95
1953727	DRH-120-24	4	24	5	120	340 to 550 @ 47-63	.65	85%	-20	60	2.58 x 4.93 x 3.94	\$55.80	\$45.49
1953735	DRH-120-48	4	48	2.5	120	340 to 550 @ 47-63	.65	86%	-20	60	2.58 x 4.93 x 3.94	\$55.80	\$45.49
221892	DRP-240-24	7	24	10	240	85 to 264 @ 47-63	2.8	84%	-10	70	4.94 x 4.93 x 3.94	\$58.29	\$48.49
221883	DRP-240-48	7	48	5	240	85 to 264 @ 47-63	2.8	85%	-10	70	4.94 x 4.93 x 3.94	\$58.29	\$48.49
252663	DRP-480-24	7	24	20	480	180 to 264 @ 47-63	4.0	89%	-20	70	8.94 x 4.93 x 3.94	\$100.59	\$83.95
252655	DRP-480-48	7	48	10	480	180 to 264 @ 47-63	4.0	89%	-20	70	8.94 x 4.93 x 3.94	\$99.95	\$89.95
295938	DRP-480S-24	7	24	20	480	90 to 132 180 to 264 @ 47-63	8.0	89%	-20	70	8.94 x 4.93 x 3.94	\$112.00	\$88.49
301306	DRP-480S-48	7	48	10	480	90 to 132 180 to 264 @ 47-63	8.0	89%	-20	70	8.94 x 4.93 x 3.94	\$112.00	\$88.49
373123	DRT-240-24	7	24	10	240	340 to 550 @ 47-63	1.7	89%	-20	70	8.94 x 4.93 x 3.94	\$73.80	\$60.49
373114	DRT-240-48	7	48	5	240	340 to 550 @ 47-63	1.7	90%	-20	70	8.94 x 4.93 x 3.94	\$73.80	\$60.49
372577	DRT-480-24	7	24	20	480	340 to 550 @ 47-63	1.7	89%	-20	70	8.94 x 4.93 x 3.94	\$117.00	\$95.49
373106	DRT-480-48	7	48	10	480	340 to 550 @ 47-63	1.7	90%	-20	70	8.94 x 4.93 x 3.94	\$117.00	\$95.49
373131	DRT-960-24	7	24	40	960	340 to 550 @ 47-63	2.0	91%	-20	60	10.97 x 4.93 x 3.94	\$220.00	\$179.95
373149	DRT-960-48	7	48	20	960	340 to 550 @ 47-63	2.0	92%	-20	60	10.97 x 4.93 x 3.94	\$220.00	\$179.95
2216649	EDR-75-12	6	12	6.3	75.6	90 to 264 @ 47-63	1.45	86%	-20	60	1.26 x 4.93 x 4.02	\$21.10	\$17.29
2216657	EDR-75-24	6	24	3.2	76.8	90 to 264 @ 47-63	1.45	88%	-20	60	1.26 x 4.93 x 4.02	\$21.10	\$17.29
2216665	EDR-75-48	6	48	1.6	76.8	90 to 264 @ 47-63	1.45	89%	-20	60	1.26 x 4.93 x 4.02	\$21.10	\$17.29
2218530	EDR-120-12	6	12	10	120	90 to 264 @ 47-63	2.25	85%	-20	60	1.57 x 4.93 x 4.47	\$24.30	\$19.89
2218548	EDR-120-24	6	24	5	120	90 to 264 @ 47-63	2.25	88%	-20	60	1.57 x 4.93 x 4.47	\$24.30	\$19.89

Jameco Part No.	Manufacturer Part No.	Fig.	Primary Output Voltage (VDC)	Output Current (A)	Max Output Power (W)	Input Voltage (VAC @ Hz)	Maximum Input Current (A)	Efficiency (%)	Operating Temp. Min (Cel)	Operating Temp. Max (Cel)	Size (H"x W"x D")	Price 1	Price 10
2218556	EDR-120-48	6	48	2.5	120	90 to 264 @ 47-63	2.25	89%	-20	60	1.57 x 4.93 x 4.47	\$24.30	\$19.89
2218564	EDR-150-24	6	24	5.2	150	90 to 264 @ 47-63	2.6	87%	-20	60	1.57 x 4.93 x 4.47	\$25.40	\$20.79
2251196	HDR-15-5	3	5	2.4	12	85 to 264 @ 47-63	.85	80%	-30	70	0.69 x 3.54 x 2.15	\$11.00	\$8.95
2251209	HDR-15-12	3	12	1.25	15	85 to 264 @ 47-63	.85	85%	-30	70	0.69 x 3.54 x 2.15	\$11.00	\$8.95
2251217	HDR-15-15	3	15	1	15	85 to 264 @ 47-63	.85	86%	-30	70	0.69 x 3.54 x 2.15	\$11.00	\$8.95
2251225	HDR-15-24	3	24	0.63	15.2	85 to 264 @ 47-63	.85	86%	-30	70	0.69 x 3.54 x 2.15	\$11.00	\$8.95
2251233	HDR-15-48	3	48	0.32	15.4	85 to 264 @ 47-63	.85	87%	-30	70	0.69 x 3.54 x 2.15	\$11.00	\$8.95
2251241	HDR-30-5	3	5	3	15	85 to 264 @ 47-63	.88	82%	-30	70	1.38 x 3.54 x 2.15	\$13.50	\$11.25
2251250	HDR-30-12	3	12	2	24	85 to 264 @ 47-63	.88	88%	-30	70	1.38 x 3.54 x 2.15	\$13.50	\$11.25
2251268	HDR-30-15	3	15	2	30	85 to 264 @ 47-63	.88	89%	-30	70	1.38 x 3.54 x 2.15	\$13.50	\$11.25
2251276	HDR-30-24	3	24	1.5	36	85 to 264 @ 47-63	.88	89%	-30	70	1.38 x 3.54 x 2.15	\$13.50	\$11.25
2251284	HDR-30-48	3	48	0.75	36	85 to 264 @ 47-63	.88	90%	-30	70	1.38 x 3.54 x 2.15	\$13.50	\$11.25
2251292	HDR-60-5	3	5	6.5	32.5	85 to 264 @ 47-63	1.2	85%	-30	70	2.07 x 3.54 x 2.15	\$18.40	\$15.09
2251305	HDR-60-12	3	12	4.5	54	85 to 264 @ 47-63	1.2	88%	-30	70	2.07 x 3.54 x 2.15	\$18.40	\$15.09
2251313	HDR-60-15	3	15	4	60	85 to 264 @ 47-63	1.2	89%	-30	70	2.07 x 3.54 x 2.15	\$18.40	\$15.09
2251321	HDR-60-24	3	24	2.5	60	85 to 264 @ 47-63	1.2	90%	-30	70	2.07 x 3.54 x 2.15	\$18.40	\$15.09
2251330	HDR-60-48	3	48	1.25	60	85 to 264 @ 47-63	1.2	91%	-30	70	2.07 x 3.54 x 2.15	\$18.40	\$15.09
2264327	HDR-100-12	3	12	7.1	85.2	85 to 264 @ 47-63	3.0	88%	-30	70	2.15 x 2.76 x 3.54	\$26.30	\$21.49
2264335	HDR-100-12N	3	12	7.5	90	85 to 264 @ 47-63	3.0	88%	-30	70	2.15 x 2.76 x 3.54	\$26.30	\$21.49
2264343	HDR-100-15	3	15	6.13	92	85 to 264 @ 47-63	3.0	89%	-30	70	2.15 x 2.76 x 3.54	\$26.30	\$21.49
2264351	HDR-100-15N	3	15	6.5	97.5	85 to 264 @ 47-63	3.0	89%	-30	70	2.15 x 2.76 x 3.54	\$26.30	\$21.49
2264359	HDR-100-24	3	24	3.83	92	85 to 264 @ 47-63	3.0	90%	-30	70	2.15 x 2.76 x 3.54	\$26.30	\$21.49
2264367	HDR-100-24N	3	24	4.2	100.8	85 to 264 @ 47-63	3.0	90%	-30	70	2.15 x 2.76 x 3.54	\$26.30	\$21.49
2264375	HDR-100-48	3	48	1.92	92.2	85 to 264 @ 47-63	3.0	90%	-30	70	2.15 x 2.76 x 3.54	\$26.30	\$21.49
2264383	HDR-100-48N	3	48	2.1	100.8	85 to 264 @ 47-63	3.0	90%	-30	70	2.15 x 2.76 x 3.54	\$26.30	\$21.49
2254493	KNX-20E-640	9	30	0.64	19.2	180 to 264 @ 47-63	.22	86%	-30	70	2.07 x 3.54 x 2.15	\$72.00	\$58.95
2103978	MDR-10-5	1	5	2	10	85 to 264 @ 47-63	.33	77%	-20	70	0.89 x 3.54 x 3.94	\$11.00	\$8.95
1952978	MDR-10-12	1	12	0.84	10	85 to 264 @ 47-63	.33	81%	-20	70	0.89 x 3.54 x 3.94	\$11.00	\$8.95
2103599	MDR-10-15	1	15	0.67	10	85 to 264 @ 47-63	.33	81%	-20	70	0.89 x 3.54 x 3.94	\$11.00	\$8.95
1952986	MDR-10-24	1	24	0.42	10	85 to 264 @ 47-63	.33	84%	-20	70	0.89 x 3.54 x 3.94	\$11.00	\$8.95
1943300	MDR-20-5	1	5	3	15	85 to 264 @ 47-63	.55	76%	-20	70	0.89 x 3.54 x 3.94	\$12.80	\$10.49
1943334	MDR-20-12	1	12	1.67	20	85 to 264 @ 47-63	.55	80%	-20	70	0.89 x 3.54 x 3.94	\$12.80	\$10.49
1943342	MDR-20-15	1	15	1.34	20	85 to 264 @ 47-63	.55	81%	-20	70	0.89 x 3.54 x 3.94	\$12.80	\$10.49
1943385	MDR-20-24	1	24	1	24	85 to 264 @ 47-63	.55	84%	-20	70	0.89 x 3.54 x 3.94	\$12.80	\$10.49
1943393	MDR-40-5	1	5	6	30	85 to 264 @ 47-63	1.1	78%	-20	70	1.57 x 3.54 x 3.94	\$17.10	\$13.95
1943406	MDR-40-12	1	12	3.33	40	85 to 264 @ 47-63	1.1	86%	-20	70	1.57 x 3.54 x 3.94	\$17.10	\$13.95
1943422	MDR-40-24	1	24	1.7	40.8	85 to 264 @ 47-63	1.1	88%	-20	70	1.57 x 3.54 x 3.94	\$17.10	\$13.95
1943431	MDR-40-48	1	48	0.83	39.8	85 to 264 @ 47-63	1.1	88%	-20	70	1.57 x 3.54 x 3.94	\$17.10	\$13.95
1943449	MDR-60-5	1	5	10	50	85 to 264 @ 47-63	1.8	78%	-20	70	1.57 x 3.54 x 3.94	\$18.40	\$15.09
1943457	MDR-60-12	1	12	5	60	85 to 264 @ 47-63	1.8	86%	-20	70	1.57 x 3.54 x 3.94	\$18.40	\$15.09
1943465	MDR-60-24	1	24	2.5	60	85 to 264 @ 47-63	1.8	88%	-20	70	1.57 x 3.54 x 3.94	\$18.40	\$15.09
1943473	MDR-60-48	1	48	1.25	60	85 to 264 @ 47-63	1.8	87%	-20	70	1.57 x 3.54 x 3.94	\$18.40	\$15.09
1943481	MDR-100-12	1	12	7.5	90	85 to 264 @ 47-63	1.3	85%	-10	60	2.17 x 3.54 x 3.94	\$31.90	\$25.95
1943490	MDR-100-24	1	24	4	90	85 to 264 @ 47-63	1.3	86%	-10	60	2.17 x 3.54 x 3.94	\$31.90	\$25.95
1943502	MDR-100-48	1	48	2	96	85 to 264 @ 47-63	1.3	88%	-10	60	2.17 x 3.54 x 3.94	\$31.90	\$25.95
2216673	NDR-75-12	6	12	6.3	75.6	90 to 264 @ 47-63	1.45	86%	-20	70	1.26 x 4.93 x 4.02	\$22.90	\$18.75
2216681	NDR-75-24	6	24	3.2	76.8	90 to 264 @ 47-63	1.45	88%	-20	70	1.26 x 4.93 x 4.02	\$22.90	\$18.75
2216690	NDR-75-48	6	48	1.6	76.8	90 to 264 @ 47-63	1.45	89%	-20	70	1.26 x 4.93 x 4.02	\$22.90	\$18.75
2218572	NDR-120-12	6	12	10	120	90 to 264 @ 47-63	2.25	86%	-20	70	1.57 x 4.93 x 4.47	\$26.80	\$21.95
2218581	NDR-120-24	6	24	5	120	90 to 264 @ 47-63	2.25	88%	-20	70	1.57 x 4.93 x 4.47	\$26.80	\$21.95
2218599	NDR-120-48	6	48	2.5	120	90 to 264 @ 47-63	2.25	89%	-20	70	1.57 x 4.93 x 4.47	\$26.80	\$21.95
2225060	NDR-240-24	6	24	10	240	90 to 264 @ 47-63	2.5	89%	-20	70	2.48 x 4.93 x 4.47	\$49.30	\$40.95
2225078	NDR-240-48	6	48	5	240	90 to 264 @ 47-63	2.5	90%	-20	70	2.48 x 4.93 x 4.47	\$49.30	\$40.95
2225086	NDR-480-24	6	24	20	480	90 to 264 @ 47-63	4.8	93%	-20	70	3.37 x 4.93 x 5.06	\$96.30	\$78.95
2225094	NDR-480-48	6	48	10	480	90 to 264 @ 47-63	4.8	93%	-20	70	3.37 x 4.93 x 5.06	\$96.30	\$78.95
2190311	SDR-75-12	5	12	6.3	75.6	88 to 264 @ 47-63	1.4	89%	-30	70	1.26 x 4.93 x 4.02	\$30.80	\$25.25
2190320	SDR-75-24	5	24	3.2	76.8	88 to 264 @ 47-63	1.4	89%	-30	70	1.26 x 4.93 x 4.02	\$30.80	\$25.25
2190338	SDR-75-48	5	48	1.6	76.8	88 to 264 @ 47-63	1.4	90%	-30	70	1.26 x 4.93 x 4.02	\$30.80	\$25.25
2099366	SDR-120-12	5	12	10	120	88 to 264 @ 47-63	1.4	89%	-25	70	1.57 x 4.93 x 4.47	\$49.50	\$40.49
2099374	SDR-120-24	5	24	5	120	88 to 264 @ 47-63	1.4	91%	-25	70	1.57 x 4.93 x 4.47	\$49.50	\$40.49
2107338	SDR-120-48	5	48	2.5	120	85 to 264 @ 47-63	1.4	90%	-25	70	1.57 x 4.93 x 4.47	\$49.50	\$40.49
2081086	SDR-240-24	5	24	10	240	88 to 264 @ 47-63	2.6	94%	-25	70	2.48 x 4.93 x 4.47	\$83.30	\$67.95
2094936	SDR-240-48	5	48	5	240	88 to 264 @ 47-63	2.6	94%	-25	70	2.48 x 4.93 x 4.47	\$83.30	\$67.95
2094944	SDR-480-24	5	24	20	480	90 to 264 @ 47-63	5.0	94%	-25	70	3.37 x 4.93 x 5.06	\$133.00	\$114.95
2107346	SDR-480-48	5	48	10	480	90 to 264 @ 47-63	5.0	94%	-25	70	3.37 x 4.93 x 5.06	\$133.00	\$114.95
2108947	SDR-480P-24	5	24	20	480	90 to 264 @ 47-63	5.0	94%	-25	70	3.37 x 4.93 x 5.06	\$133.00	\$114.95
2108955	SDR-480P-48	5	48	10	480	90 to 264 @ 47-63	5.0	94%	-25	70	3.37 x 4.93 x 5.06	\$133.00	\$114.95
2172156	SDR-960-24	5	24	40	960	180 to 264 @ 47-63	6.0	94%	-30	70	4.33 x 4.93 x 5.91	\$223.00	\$189.95

Jameco Part No.	Manufacturer Part No.	Fig.	Primary Output Voltage (VDC)	Output Current (A)	Max Output Power (W)	Input Voltage (VAC @ Hz)	Maximum Input Current (A)	Efficiency (%)	Operating Temp. Min (Cel)	Operating Temp. Max (Cel)	Size (H"x W"x D")	Price 1	Price 10
2172164	SDR-960-48	5	48	20	960	180 to 264 @ 47-63	6.0	94%	-30	70	4.33 x 4.93 x 5.91	\$223.00	\$189.95
2253044	TDR-480-24	8	24	20	480	340 to 550 @ 47-63	.85	93%	-30	70	3.37 x 4.93 x 5.06	\$117.00	\$95.49
2253052	TDR-480-48	8	48	10	480	340 to 550 @ 47-63	.85	93%	-30	70	3.37 x 4.93 x 5.06	\$117.00	\$95.49
2172375	TDR-960-24	8	24	40	960	340 to 550 @ 47-63	2.0	94%	-30	70	4.33 x 4.93 x 5.91	\$220.00	\$179.95
2172383	TDR-960-48	8	48	20	960	340 to 550 @ 47-63	2.0	95%	-30	70	4.33 x 4.93 x 5.91	\$220.00	\$179.95
2123047	WDR-120-12	8	12	10	120	180 to 550 @ 47-63	1.2	90%	-25	70	1.57 x 4.93 x 4.47	\$55.80	\$45.49
2123055	WDR-120-24	8	24	5	120	180 to 550 @ 47-63	1.2	91%	-25	70	1.57 x 4.93 x 4.47	\$55.80	\$45.49
2123063	WDR-120-48	8	48	2.5	120	180 to 550 @ 47-63	1.2	92%	-25	70	1.57 x 4.93 x 4.47	\$55.80	\$45.49
2150096	WDR-240-24	8	24	10	240	180 to 264 @ 47-63	2.0	91%	-30	70	2.48 x 4.93 x 4.47	\$107.00	\$87.49
2145182	WDR-240-48	8	48	5	240	180 to 550 @ 47-63	2.0	91%	-30	70	2.48 x 4.93 x 4.47	\$107.00	\$87.49
2127806	WDR-480-24	8	24	20	480	180 to 550 @ 47-63	4.0	92%	-30	70	3.37 x 4.93 x 5.06	\$156.00	\$127.49
2126977	WDR-480-48	8	48	10	480	180 to 550 @ 47-63	4.0	93%	-30	70	3.37 x 4.93 x 5.06	\$156.00	\$127.49