

We are happy to change any listed wall adapter or table-top power plug to overmolding on a connector of your choice for \$4.00 each. A 100 piece minimum order applies. Please call 1-800-794-9100 for details.



Request a Large Quantity Quote



Jameco Part#	Manufacturer	Manufacturer Part #	Body Type	Max Output Power (W)	Primary Output Voltage (VDC)	Output Current (A)	Input Voltage (VAC)	Output Connector Type	Output Connector Diameter ID x OD	Polarity	Efficiency (%)	Min Operating Temp (Cel)	Max Operating Temp (Cel)	Recommended Power Cord (Table Top Type Not Included)	Price 1	Price 10
2256982	MEAN WELL	GST18A05-P1J	Table-Top (A Version)	15	5	3	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	81	-30	70	Part # 38050	\$11.50	\$9.39
2257070	MEAN WELL	GST18B05-P1J	Table-Top (B Version)	15	5	3	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	81	-30	70	Part # 189587	\$11.50	\$9.65
2225529	MEAN WELL	GST18U05-P1J	Wall Adapter (U Version)	15	5	3	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	81	-30	70	--	\$11.50	\$9.39
2256991	MEAN WELL	GST18A07-P1J	Table-Top (A Version)	15	7.5	2	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	85	-30	70	Part # 38050	\$11.50	\$9.65
2257088	MEAN WELL	GST18B07-P1J	Table-Top (B Version)	15	7	2	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	85	-30	70	Part # 189587	\$11.50	\$9.65
2225596	MEAN WELL	GST18U07-P1J	Wall Adapter (U Version)	15	7.5	2	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	85	-30	70	--	\$11.50	\$9.39
2257002	MEAN WELL	GST18A09-P1J	Table-Top (A Version)	18	9	2	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	85	-30	70	Part # 38050	\$11.50	\$9.39
2257096	MEAN WELL	GST18B09-P1J	Table-Top (B Version)	18	9	2	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	85	-30	70	Part # 189587	\$11.50	\$9.65
2225609	MEAN WELL	GST18U09-P1J	Wall Adapter (U Version)	18	9	2	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	85	-30	70	--	\$11.50	\$9.39
2257011	MEAN WELL	GST18A12-P1J	Table-Top (A Version)	18	12	1.5	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	86	-30	70	Part # 38050	\$11.50	\$9.39
2257109	MEAN WELL	GST18B12-P1J	Table-Top (B Version)	18	12	1.5	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	86	-30	70	Part # 189587	\$11.50	\$9.39
2225537	MEAN WELL	GST18U12-P1J	Wall Adapter (U Version)	18	12	1.5	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	86	-30	70	--	\$11.50	\$9.39
2257029	MEAN WELL	GST18A15-P1J	Table-Top (A Version)	18	15	1.2	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	87	-30	70	Part # 38050	\$11.50	\$9.39
2257117	MEAN WELL	GST18B15-P1J	Table-Top (B Version)	18	15	1.2	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	87	-30	70	Part # 189587	\$11.50	\$9.39
2225617	MEAN WELL	GST18U15-P1J	Wall Adapter (U Version)	18	15	1.2	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	87	-30	70	--	\$11.50	\$9.39
2257037	MEAN WELL	GST18A18-P1J	Table-Top (A Version)	18	18	1	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	88	-30	70	Part # 38050	\$11.50	\$9.65
2257125	MEAN WELL	GST18B18-P1J	Table-Top (B Version)	18	18	1	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	88	-30	70	Part # 189587	\$11.50	\$9.65
2225625	MEAN WELL	GST18U18-P1J	Wall Adapter (U Version)	18	18	1	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	88	-30	70	--	\$11.50	\$9.39
2257045	MEAN WELL	GST18A24-P1J	Table-Top (A Version)	18	24	0.75	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	88	-30	70	Part # 38050	\$11.50	\$9.39
2257133	MEAN WELL	GST18B24-P1J	Table-Top (B Version)	18	24	0.75	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	88	-30	70	Part # 189587	\$11.50	\$9.65
2225545	MEAN WELL	GST18U24-P1J	Wall Adapter (U Version)	18	24	0.75	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	88	-30	70	--	\$11.50	\$9.39
2257053	MEAN WELL	GST18A28-P1J	Table-Top (A Version)	18	28	0.64	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	88.5	-30	70	Part # 38050	\$11.50	\$9.65
2257141	MEAN WELL	GST18B28-P1J	Table-Top (B Version)	18	28	0.64	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	88.5	-30	70	Part # 189587	\$11.50	\$9.65
2225633	MEAN WELL	GST18U28-P1J	Wall Adapter (U Version)	18	28	0.64	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	88.5	-30	70	--	\$11.50	\$9.39
2257061	MEAN WELL	GST18A48-P1J	Table-Top (A Version)	18	48	0.375	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	89	-30	70	Part # 38050	\$11.50	\$9.65
2257150	MEAN WELL	GST18B48-P1J	Table-Top (B Version)	18	48	0.375	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	89	-30	70	Part # 189587	\$11.50	\$9.65
2225641	MEAN WELL	GST18U48-P1J	Wall Adapter (U Version)	18	48	0.375	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	89	-30	70	--	\$11.50	\$9.39
2257168	MEAN WELL	GST25A05-P1J	Table-Top (A Version)	20	5	4	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	81.5	-30	70	Part # 38050	\$11.70	\$9.59
2257256	MEAN WELL	GST25B05-P1J	Table-Top (B Version)	20	5	4	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	81.5	-30	70	Part # 189587	\$11.70	\$9.59
2225650	MEAN WELL	GST25U05-P1J	Wall Adapter (U Version)	20	5	4	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	81.5	-30	70	--	\$11.70	\$9.59
2257176	MEAN WELL	GST25A07-P1J	Table-Top (A Version)	22	7.5	2.93	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	84.5	-30	70	Part # 38050	\$11.70	\$9.59
2257264	MEAN WELL	GST25B07-P1J	Table-Top (B Version)	22	7.5	2.93	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	84.5	-30	70	Part # 189587	\$11.70	\$9.59
2225668	MEAN WELL	GST25U07-P1J	Wall Adapter (U Version)	22	7.5	2.93	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	84.5	-30	70	--	\$11.70	\$9.59
2257184	MEAN WELL	GST25A09-P1J	Table-Top (A Version)	23	9	2.55	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	85	-30	70	Part # 38050	\$11.70	\$9.59
2257272	MEAN WELL	GST25B09-P1J	Table-Top (B Version)	23	9	2.55	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	85	-30	70	Part # 189587	\$11.70	\$9.59
2225676	MEAN WELL	GST25U09-P1J	Wall Adapter (U Version)	23	9	2.55	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	85	-30	70	--	\$11.70	\$9.59
2225553	MEAN WELL	GST25U12-P1J	Wall Adapter (U Version)	25	12	2.08	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	86.5	-30	70	--	\$11.70	\$9.59
2257205	MEAN WELL	GST25A15-P1J	Table-Top (A Version)	25	15	1.66	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	87	-30	70	Part # 38050	\$11.70	\$9.59
2257299	MEAN WELL	GST25B15-P1J	Table-Top (B Version)	25	15	1.66	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	87	-30	70	Part # 189587	\$11.70	\$9.59
2225684	MEAN WELL	GST25U15-P1J	Wall Adapter (U Version)	25	15	1.66	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	87	-30	70	--	\$11.70	\$9.59
2257213	MEAN WELL	GST25A18-P1J	Table-Top (A Version)	25	18	1.38	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	87	-30	70	Part # 38050	\$11.70	\$9.59
2257301	MEAN WELL	GST25B18-P1J	Table-Top (B Version)	25	18	1.38	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	87	-30	70	Part # 189587	\$11.70	\$9.59
2225692	MEAN WELL	GST25U18-P1J	Wall Adapter (U Version)	25	18	1.38	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	87	-30	70	--	\$11.70	\$9.59
2257221	MEAN WELL	GST25A24-P1J	Table-Top (A Version)	25	24	1.04	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	88	-30	70	Part # 38050	\$11.70	\$9.59
2257310	MEAN WELL	GST25B24-P1J	Table-Top (B Version)	25	24	1.04	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	88	-30	70	Part # 189587	\$11.70	\$9.59
2225561	MEAN WELL	GST25U24-P1J	Wall Adapter (U Version)	25	24	1.04	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	88	-30	70	--	\$11.70	\$9.59
2257230	MEAN WELL	GST25A28-P1J	Table-Top (A Version)	25	28	0.89	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	88	-30	70	Part # 38050	\$11.70	\$9.59
2257328	MEAN WELL	GST25B28-P1J	Table-Top (B Version)	25	28	0.89	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	88	-30	70	Part # 189587	\$11.70	\$9.59
2225705	MEAN WELL	GST25U28-P1J	Wall Adapter (U Version)	25	28	0.89	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	88	-30	70	--	\$11.70	\$9.59
2257248	MEAN WELL	GST25A48-P1J	Table-Top (A Version)	25	48	0.52	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	89	-30	70	Part # 38050	\$11.70	\$9.59
2257336	MEAN WELL	GST25B48-P1J	Table-Top (B Version)	25	48	0.52	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	89	-30	70	Part # 189587	\$11.70	\$9.59
2225713	MEAN WELL	GST25U48-P1J	Wall Adapter (U Version)	25	48	0.52	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	89	-30	70	--	\$11.70	\$9.59
2257344	MEAN WELL	GST36B05-P1J	Table-Top (B Version)	21.5	5	4.3	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	82	-30	70	Part # 189587	\$13.30	\$10.89
2225721	MEAN WELL	GST36U05-P1J	Wall Adapter (U Version)	21.5	5	4.3	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	82	-30	70	--	\$13.30	\$10.89
2257352	MEAN WELL	GST36B09-P1J	Table-Top (B Version)	28	9	3.11	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	86	-30	70	Part # 189587	\$13.30	\$10.89
2225730	MEAN WELL	GST36U09-P1J	Wall Adapter (U Version)	28	9	3.11	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	86	-30	70	--	\$13.30	\$10.89
2225570	MEAN WELL	GST36U12-P1J	Wall Adapter (U Version)	36	12	3	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	87.5	-30	70	--	\$13.30	\$10.89
2257379	MEAN WELL	GST36B24-P1J	Table-Top (B Version)	36	24	1.5	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	88.5	-30	70	Part # 189587	\$13.30	\$10.89
2225588	MEAN WELL	GST36U24-P1J	Wall Adapter (U Version)	36	24	1.5	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	88.5	-30	70	--	\$13.30	\$10.89
2257387	MEAN WELL	GST36B48-P1J	Table-Top (B Version)	36	48	0.75	85 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90	-30	70	Part # 189587	\$13.30	\$10.89
2225748	MEAN WELL	GST36U48-P1J	Wall Adapter (U Version)	36	48	0.75	90 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90	-30	70	--	\$13.30	\$10.89
2224278	MEAN WELL	GST40A05-P1J	Table-Top (A Version)	25	5	5	90 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	84.5	-30	70	Part # 38050	\$14.60	\$11.95

Jameco Part#	Manufacturer	Manufacturer Part #	Type	Max Output Power (W)	Primary Output Voltage (VDC)	Output Current (A)	Input Voltage (VAC)	Output Connector Type	Output Connector ID x OD	Polarity	Efficiency (%)	Min Operating Temp (Cel)	Max Operating Temp (Cel)	Recommended Power Cord (Table Top Type Not Included)	Price 1	Price 10
2224286	MEAN WELL	GST40A07-P1J	Table-Top (A Version)	40	7	5.34	90 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	87.5	-30	70	Part # 38050	\$14.60	\$11.95
2224294	MEAN WELL	GST40A09-P1J	Table-Top (A Version)	40	9	4.45	90 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	88.5	-30	70	Part # 38050	\$14.60	\$11.95
2224307	MEAN WELL	GST40A12-P1J	Table-Top (A Version)	40	12	3.34	90 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	89.5	-30	70	Part # 38050	\$14.60	\$11.95
2224315	MEAN WELL	GST40A15-P1J	Table-Top (A Version)	40	15	2.67	90 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90	-30	70	Part # 38050	\$14.60	\$11.95
2224323	MEAN WELL	GST40A18-P1J	Table-Top (A Version)	40	18	2.22	90 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90	-30	70	Part # 38050	\$14.60	\$11.95
2224331	MEAN WELL	GST40A24-P1J	Table-Top (A Version)	40	24	1.67	90 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	91	-30	70	Part # 38050	\$14.60	\$11.95
2224340	MEAN WELL	GST40A48-P1J	Table-Top (A Version)	40	48	0.84	90 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	92	-30	70	Part # 38050	\$14.60	\$11.95
2224358	MEAN WELL	GST60A05-P1J	Table-Top (A Version)	30	5	6	90 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	85.5	-30	70	Part # 38050	\$16.20	\$13.25
2224366	MEAN WELL	GST60A07-P1J	Table-Top (A Version)	45	7	6	90 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	88.5	-30	70	Part # 38050	\$16.20	\$13.25
2224374	MEAN WELL	GST60A09-P1J	Table-Top (A Version)	54	9	6	90 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	89	-30	70	Part # 38050	\$16.20	\$13.25
2224382	MEAN WELL	GST60A12-P1J	Table-Top (A Version)	60	12	5	90 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	89.5	-30	70	Part # 38050	\$16.20	\$13.25
2224391	MEAN WELL	GST60A15-P1J	Table-Top (A Version)	60	15	4	90 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	89.5	-30	70	Part # 38050	\$16.20	\$13.25
2224403	MEAN WELL	GST60A18-P1J	Table-Top (A Version)	60	18	3.33	90 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	89.5	-30	70	Part # 38050	\$16.20	\$13.25
2224411	MEAN WELL	GST60A24-P1J	Table-Top (A Version)	60	24	2.5	90 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90.5	-30	70	Part # 38050	\$16.20	\$13.25
2224420	MEAN WELL	GST60A48-P1J	Table-Top (A Version)	60	48	1.25	90 to 264	Cylindrical Female	2.1mm x 5.5mm	Center Positive	92	-30	70	Part # 38050	\$16.20	\$13.25
2223460	MEAN WELL	GST90A12-P1M	Table-Top (A Version)	80	12	6.67	90 to 264	Cylindrical Female	2.5mm x 5.5mm	Center Positive	89	-30	70	Part # 38050	\$26.60	\$21.79
2223478	MEAN WELL	GST90A15-P1M	Table-Top (A Version)	90	15	6	90 to 264	Cylindrical Female	2.5mm x 5.5mm	Center Positive	89.5	-30	70	Part # 38050	\$26.60	\$21.79
2223486	MEAN WELL	GST90A19-P1M	Table-Top (A Version)	90	19	4.74	90 to 264	Cylindrical Female	2.5mm x 5.5mm	Center Positive	90	-30	70	Part # 38050	\$26.60	\$21.79
2223494	MEAN WELL	GST90A24-P1M	Table-Top (A Version)	90	24	3.75	90 to 264	Cylindrical Female	2.5mm x 5.5mm	Center Positive	90	-30	70	Part # 38050	\$26.60	\$21.79
2223507	MEAN WELL	GST90A48-P1M	Table-Top (A Version)	90	48	1.87	90 to 264	Cylindrical Female	2.5mm x 5.5mm	Center Positive	91	-30	70	Part # 38050	\$26.60	\$21.79
2223582	MEAN WELL	GST120A12-R7B	Table-Top (A Version)	102	12	8.5	85 to 264	DIN Male	4-pin DIN	--	88.5	-30	70	Part # 38050	\$38.90	\$31.49
2223591	MEAN WELL	GST120A15-R7B	Table-Top (A Version)	105	15	7	85 to 264	DIN Male	4-pin DIN	--	89	-30	70	Part # 38050	\$38.90	\$31.49
2223603	MEAN WELL	GST120A20-R7B	Table-Top (A Version)	120	20	6	85 to 264	DIN Male	4-pin DIN	--	90	-30	70	Part # 38050	\$38.90	\$31.95
2223638	MEAN WELL	GST120A20-P1M	Table-Top (A Version)	120	20	6	85 to 264	Cylindrical Female	2.5mm x 5.5mm	Center Positive	89	-30	70	Part # 38050	\$38.90	\$31.95
2223611	MEAN WELL	GST120A24-R7B	Table-Top (A Version)	120	24	5	85 to 264	DIN Male	4-pin DIN	--	90.5	-30	70	Part # 38050	\$38.90	\$31.49
2223646	MEAN WELL	GST120A24-P1M	Table-Top (A Version)	120	24	5	85 to 264	Cylindrical Female	2.5mm x 5.5mm	Center Positive	89.5	-30	70	Part # 38050	\$38.90	\$31.49
2223654	MEAN WELL	GST120A48-P1M	Table-Top (A Version)	120	48	2.5	85 to 264	Cylindrical Female	2.5mm x 5.5mm	Center Positive	90.5	-30	70	Part # 38050	\$38.90	\$31.49
2223620	MEAN WELL	GST120A48-R7B	Table-Top (A Version)	120	48	2.5	85 to 264	DIN Male	4-pin DIN	--	91	-30	70	Part # 38050	\$38.90	\$31.49
2226425	MEAN WELL	GST160A12-R7B	Table-Top (A Version)	138	12	11.5	85 to 264	DIN Male	4-pin DIN	--	90	-30	70	Part # 38050	\$47.00	\$38.49
2226433	MEAN WELL	GST160A15-R7B	Table-Top (A Version)	144	15	9.6	85 to 264	DIN Male	4-pin DIN	--	91	-30	70	Part # 38050	\$47.00	\$38.49
2226441	MEAN WELL	GST160A20-R7B	Table-Top (A Version)	160	20	8	85 to 264	DIN Male	4-pin DIN	--	93	-30	70	Part # 38050	\$47.00	\$38.49
2226450	MEAN WELL	GST160A24-R7B	Table-Top (A Version)	160	24	6.67	85 to 264	DIN Male	4-pin DIN	--	93	-30	70	Part # 38050	\$47.00	\$38.49
2226468	MEAN WELL	GST160A48-R7B	Table-Top (A Version)	160	48	3.34	85 to 264	DIN Male	4-pin DIN	--	94	-30	70	Part # 38050	\$47.00	\$38.49
2226476	MEAN WELL	GST220A12-R7B	Table-Top (A Version)	180	12	15	85 to 264	DIN Male	4-pin DIN	--	90	-30	70	Part # 38050	\$66.60	\$56.29
2226484	MEAN WELL	GST220A15-R7B	Table-Top (A Version)	201	15	13.4	85 to 264	DIN Male	4-pin DIN	--	90	-30	70	Part # 38050	\$66.60	\$55.89
2278479	MEAN WELL	GST220A36-R7B	Table-Top (A Version)	219.6	36	6.1	86 to 264	DIN Male	4-pin DIN	--	90	-30	70	Part # 38050	\$66.60	\$55.89
2226492	MEAN WELL	GST220A20-R7B	Table-Top (A Version)	220	20	11	85 to 264	DIN Male	4-pin DIN	--	92	-30	70	Part # 38050	\$66.60	\$55.89
2226505	MEAN WELL	GST220A24-R7B	Table-Top (A Version)	221	24	9.2	85 to 264	DIN Male	4-pin DIN	--	93.5	-30	70	Part # 38050	\$66.60	\$55.89
2226513	MEAN WELL	GST220A48-R7B	Table-Top (A Version)	221	48	4.6	85 to 264	DIN Male	4-pin DIN	--	94.5	-30	70	Part # 38050	\$66.60	\$55.89
2226521	MEAN WELL	GST280A12-C6P	Table-Top (A Version)	252	12	21	85 to 264	MOLEX 39-01-2060	--	--	89.5	-30	70	Part # 38050	\$81.00	\$65.95
2226530	MEAN WELL	GST280A15-C6P	Table-Top (A Version)	255	15	15	85 to 264	MOLEX 39-01-2060	--	--	90	-30	70	Part # 38050	\$81.00	\$66.25
2226548	MEAN WELL	GST280A20-C6P	Table-Top (A Version)	260	20	20	85 to 264	MOLEX 39-01-2060	--	--	92	-30	70	Part # 38050	\$81.00	\$66.25
2226556	MEAN WELL	GST280A24-C6P	Table-Top (A Version)	280.08	24	24	85 to 264	MOLEX 39-01-2060	--	--	93	-30	70	Part # 38050	\$81.00	\$65.95
2226564	MEAN WELL	GST280A48-C6P	Table-Top (A Version)	280.32	48	48	85 to 264	MOLEX 39-01-2060	--	--	94	-30	70	Part # 38050	\$81.00	\$68.85