

Click Here to Request a Large Quantity Quote



DC BRUSHLESS FANS: 12 - 18 VOLTS

Jameco SKU	Mfr Name	Mfr P/N	Voltage (VDC)	Length (mm)	Width (mm)	Height (mm)	Air Flow (CFM)	Bearing	Current (mA)	Power (Watts)	Agency Approvals	Noise (dBA)	Connection (Leads)	Price 1
2134299	ADDA Corporation	AD2012LB-K70	12	20	20	6	0.6	Ball	60	0.72	CE	19.5	5.5"	10.95
2095269	ADDA Corporation	AD2012LX-G70	12	20	20	10	0.6	Hypro	70	0.72	UL/CUL/CE	20	5.5"	4.95
2227655	ADDA Corporation	AD0212MX-K50	12	25	25	6	2.4	Hypro	60	0.72	UL/CUL	29	5.5"	10.95
2232198	ADDA Corporation	AD0212MX-K53	12	25	25	6	2.4	Hypro	90	1.08	UL/CUL/TUV/CE	29	(3) 5.5" (speed sensor)	4.79
1951641	ADDA Corporation	AD0212MB-G50GL	12	25	25	10	2.0	Ball	80	0.95	UL/CUL/TUV/CE	25	5.5" (connector)	7.95
2179454	Jamicon Corporation	KF0210S1H	12	25	25	10	2.57	Sleeve	125	1.4	UL/TUV/CE	27	12"	3.95
2224198	ADDA Corporation	AD0312LX-K73	12	30	30	6	2.6	Hypro	60	0.75	UL/CUL/TUV	20	(3) 5.3" (speed sensor)	9.95
2133860	ADDA Corporation	AD0312MB-G50	12	30	30	10	3.3	Hypro	60	.600	UL/CE/TUV	20.3	5.5"	9.95
2233553	ADDA Corporation	AD0312LX-G50	12	30	30	10	3.21	Hypro	70	0.84	UL/CUL/TUV/CE	26	5.5"	5.95
2131901	ADDA Corporation	AD0312HB-G53	12	30	30	10	4.5	Ball	70	0.84	UL/CUL/TUV/CE	34	(3) 5.5" (speed sensor)	10.95
2233131	ADDA Corporation	AP3512LB-J70(S)	12	35	35	8	2.5	Ball	50	0.6	UL/CUL/TUV/CE	20	5"	7.95
212741	Sunon	KDE1235PFB2-8	12	35	35	10	4.5	Ball	60	0.8	UL/CUL/TUV/CE/VDE	21	3" (2-pin connector)	6.95
2276391	NMB/MAT	1404KL-04W-B59	12	35	35	10	5.6	Ball	80	0.96	UL/CUL/VDE	27	(3) 11" (speed sensor)	11.95
2179411	Sunon	MF35101V1-10000-A99	12	35	35	10	7	Vapo	60	0.72	UL/CSA/TUV/CE	28	6"	11.95
2186224	Delta Electronics	FFB03812VHN-F00	12	38	38	28	20.2	Ball	65	7.8	UL/CE/CSA	58.5	(3) 13" (speed sensor)	4.95
2215435	ADDA Corporation	AD0412HX-K96(X)	12	40	40	6	5.4	Hypro	72	0.96	UL/CUL/TUC/CE	30.5	(3) 5.5" (speed sensor)	7.65
2099500	ADDA Corporation	AD0412VB-B53GP(P)	12	40	40	28	21	Ball	80	0.72	UL/CUL/TUV/CE	31	(3) 5.5" (speed sensor)	7.95
2292607	ADDA Corporation	AD0412LX-G76(XT1)	12	40	40	10	4.7	Hypro	50	0.6	UL/CUL/TUV/CE	21	(3) 12" (speed sensor)	7.95
2224180	ADDA Corporation	AD0412LX-G76	12	40	40	10	4.7	Hypro	70	0.84	UL/CUL/TUV	14	(3) 12" (speed sensor)	5.95
2132162	ADDA Corporation	AD0412LS-G70(T)	12	40	40	10	4.7	Sleeve	70	0.84	UL/CUL/TUV/CE/CSA	14	12"	3.95
2232307	ADDA Corporation	AD0412LB-G71	12	40	40	10	5	Ball	70	0.35	UL/CUL/TUV/CE	34.5	12"	5.49
2167630	Sunon	HA40101V4-0000-999	12	40	40	10	5.3	Vapo	65	0.8	UL/TUV/CE	18.2	12"	6.95
2288943	Akasa	DFS401012M	12	40	40	10	5.62	Sleeve	66	\$24.80	UL/TUV/CE	24.8	(3) 13" (3P connector)	7.95
2290279	Common Wealth	FP-108HX/DC(S-2)12SW	12	40	40	10	6.5	Sleeve	90	1.08	UL/CUL/TUV/CE	27	12"	8.95
2205384	ADDA Corporation	AD0412HB-G70(T)	12	40	40	10	6.7	Ball	100	1.2	UL/CUL/TUV	25	12"	11.95
2231777	ADDA Corporation	AD0412HB-G70	12	40	40	10	6.7	Ball	100	1.2	UL/CE	25	6" (connector)	8.95
2167234	Sunon	ME40101V1-0000-A99	12	40	40	10	8	Vapo	100	1.08	UL/CUL/TUV	32	12"	9.95
1708473	Sunon	KDE1204PFVX11.MS.A	12	40	40	10	9.5	Vapo	150	1.8	UL/CUL/TUV	39	12"	7.95
2095314	ADDA Corporation	AD0412LX-G70	12	40	40	10	4.7	Ball	70	0.84	UL/CUL/TUV/CE	14	11"	5.95
2231793	ADDA Corporation	AD0412LB-D50	12	40	40	15	6.8	Ball	80	0.96	UL/TUV/CE	30.3	11"	4.95
2231769	ADDA Corporation	AD0412HB-D50	12	40	40	15	9.2	Ball	120	1.4	UL/CUL/CE	39.3	12"	4.95
2228181	Delta Electronics	AFB0412LD	12	40	40	20	3.88	Ball	20	0.24	UL/TUV/CE/CSA	25	13"	3.29
2234863	Sunon	MB40201V3-0000-G99	12	40	40	20	6.3	Vapo	40	0.48	UL/CUL/TUV	18	(3) 6" (speed sensor)	6.49
2289295	Sanyo Denki	109P0412F602	12	40	40	20	6.5	Ball	90	1.08	UL/CSA/TUV	28	12"	8.95
195899	Sunon	KDE1204PKS2	12	40	40	20	6.5	Sleeve	70	0.9	UL/TUV/CSA	25.5	12"	4.95
2289263	Arndt	280DH1LP11000	12	40	40	20	6.9	Ball	120	1.44	UL/CSA	33	2" (2P connector)	4.95
2134176	ADDA Corporation	AD0412LB-C50	12	40	40	20	7	Ball	70	0.84	UL/TUV/CSA	30	12"	8.95
2289279	Innovative	SP402012M	12	40	40	20	7.2	Sleeve	100	1.2	UL	28.4	7"	6.95
2289287	Sunon	KD1204PKS3	12	40	40	20	7.7	Sleeve	50	0.6	UL/CSA/TUV	19	6" (2P connector)	6.95
2151021	Sanyo Denki	109P0412H601	12	40	40	20	8	Ball	110	1.3	UL/CSA	33	(3) 7" (speed sensor)	4.49
2233166	ADDA Corporation	AD0412MB-C71GP	12	40	40	20	8	Ball	120	1.44	UL/CUL/TUV/CE	26	11"	6.49
2289271	Delta Electronics	DFB0412H	12	40	40	20	8.1	Ball	80	0.96	UL/CSA	29	2" (2P connector)	5.95
2230969	Delta Electronics	EFB0412HHD	12	40	40	20	9.5	Ball	100	1.2	UL/CUL/CE/CSA	30.5	13"	7.95
2231785	ADDA Corporation	AD0412HX-C56	12	40	40	20	9.6	Hypro	110	1.3	UL	31	(3) 11" (speed sensor)	6.49
2220218	ADDA Corporation	AD0412HB-C50(G)	12	40	40	20	8.8	Ball	100	1.2	UL/CUL/TUV/CE	36	10"	6.95
1928118	ADDA Corporation	AD0412HB-C50-LF	12	40	40	20	8.5	Ball	100	1.2	UL/CUL/TUV/CE	32	12"	9.95
2135380	ADDA Corporation	AD0412UB-C72GP(P)	12	40	40	20	10.6	Ball	170	2.4	UL/CUL/TUV/CE	34	(3) 12" (locked rotor)	8.45
2233924	Sunon	MF40201VX-10000-G99	12	40	40	20	10.8	Vapo	80	1.06	UL/CUL/TUV	27.5	(3) 12" (speed sensor)	8.95
2186232	Delta Electronics	FFB0412HN-5T20	12	40	40	28	10.6	Ball	70	0.84	UL/C	36	(3) 3.5" (speed sensor)	2.49
2082089	Sanyo Denki	109P0412H302	12	40	40	28	11.3	Ball	210	2.52	UL/TUV/CSA	37	3.75"	3.95
2235356	ADDA Corporation	AD0412HB-B32-380MM	12	40	40	28	12.1	Ball	220	2.64	UL/CUL/TUV/CE	38.8	(3) 14" (connector, alarm)	4.95
2099518	ADDA Corporation	AD0412UB-B33	12	40	40	28	16.6	Ball	230	2.76	UL/CUL/TUV	36.1	(3) 12" (speed sensor)	6.95
2235348	ADDA Corporation	AD04012UB285300(LAP)	12	40	40	28	20.7	Ball	750	9	UL/CUL/TUV/CE	50.8	(3) 12" (connector, speed sensor)	7.95
2288983	Sunon	PMD1204WQB1-A	12	40	40	28	24	Ball	330	4	UL/CUL/TUV	45	(3) 12" (3P connector, locke rotor)	14.95
2277823	Sanyo Denki	9CRB0412P5K001	12	40	40	56	26.83	Ball	880	10.56	UL, CUL, TUV, CSA	62	(8) 12" (speed sensor + PWM)	22.95
2277671	Sanyo Denki	9CRD0412P5J03	12	40	40	56	30.7	Ball	1150	13.8	UL, CUL, TUV, CSA	61	(8) 12" (speed sensor + PWM)	19.95
2228800	Delta Electronics	GFB0412EHS-C	12	40	40	56	32.2	Ball	1.3	15.6	UL/CUL/TUV/CE	64.5	(8) 3" (connector, speed sensor + PWM)	7.95
2233588	ADDA Corporation	AD4512DB-G70	12	45	45	10	5.8	Ball	50	0.6	UL/CUL/TUV/CE	30	11"	5.95





Click Here to Request a Large Quantity Quote

DC BRUSHLESS FANS: 12 - 18 VOLTS

Jameco SKU	Mfr Name	Mfr P/N	Voltage (VDC)	Length (mm)	Width (mm)	Height (mm)	Air Flow (CFM)	Bearing	Current (mA)	Power (Watts)	Agency Approvals	Noise (dBA)	Connection (Leads)	Price 1
2095322	ADDA Corporation	AD4512MX-G76	12	45	45	10	6.7	Hypro	70	0.84	UL/CUL/TUV/CE	22	(3) 11" (speed sensor)	7.95
2232219	ADDA Corporation	AD4512HX-G70(T)	12	45	45	10	9.1	Hypro	90	1.08	UL/CUL/TUV/CE	27.4	11"	7.95
2131936	ADDA Corporation	AD0512LB-G70(T)	12	50	50	10	8	Ball	80	0.96	UL/CUL/TUV/CE	20	12"	5.95
2202992	Sunon	ME50101V1-000U-A99	12	50	50	10	13.8	Vapo	110	1.32	UL/CUL/TUV	31	12"	6.49
2233596	ADDA Corporation	AD5012HX-D71-LF	12	50	50	15	15.1	Hypro	170	1.26	UL/CUL/TUV/CE	31.4	5.5"	5.59
2258451	Sunon	KDE1205PHV1.MS.AF.GN	12	50	50	15	17	Vapo	83	1	UL/CUL	33	(3) 12" (speed sensor)	5.95
2203004	Sunon	MB50151V1-000U-A99	12	50	50	15	17	Vapo	87	1.1	UL/CUL/TUV/CE	33	12"	7.95
2220189	ADDA Corporation	AD0512HX-G70	12	52	52	10	11.2	Hypro	90	1.1	UL/CUL/TUV/CE	26	11"	8.79
2099534	ADDA Corporation	AD5012HB-D70	12	50	50	15	12.6	Hypro	100	1.2	UL/CUL/TUV/CE	29	5.5"	5.95
2228261	NMB Technologies	2106KL-04W-B39	12	52	52	15	9.9	Ball	70	0.84	UL/CUL/CE	21	(3) 12" (speed sensor)	5.95
2233609	ADDA Corporation	AD0612LS-G70	12	60	60	10	9.8	Sleeve	110	1.32	UL/CUL/TUV/CE	23	11"	6.95
2121332	ADDA Corporation	AD0612LX-G76(T)	12	60	60	10	10	Hypro	110	1.32	UL/CUL/TUV/CE	23	(3) 11" (speed sensor)	5.95
144160	ADDA Corporation	AD0612LB-G76	12	60	60	10	11.7	Ball	80	1	UL/CUL/TUV	22.7	(3) 12" (speed sensor)	9.95
2205499	ADDA Corporation	AD0612HB-G90	12	60	60	10	14.06	Ball	140	1.68	UL/TUV	32.8	4.5"	3.95
2095357	ADDA Corporation	AD0612HB-G70	12	60	60	10	14.5	Ball	150	1.8	UL/CUL/TUV/CE	32	11"	7.95
1946025	Evercool Thermal	EC6010M12CA	12	60	60	10	15.5	Ball	160	1.9	UL/CE/TUV	30	(3) 9" (speed sensor)	8.95
2210909	Delta Electronics	AFB0612LB-TXNS	12	60	60	15	11.55	Ball	0.07	0.84	UL/TUV	24	6"	4.49
2233617	ADDA Corporation	AD0612LB-D70LF	12	60	60	15	12.6	Ball	90	1.08	UL/CUL/TUV/CE	25.3	5"	4.95
2270935	Sunon	MF60151V1-10000-A99	12	60	60	15	26.4	Vapo	147	1.58	UL/CUL/TUV/CE	34.2	12"	7.95
144161	ADDA Corporation	AD0612LB-C70GL-R	12	60	60	20	12.6	Ball	80	1	UL/CSA/TUV	22.7	12"	4.95
2133982	ADDA Corporation	AD0612LX-C70GL(T)	12	60	60	20	13.3	Sleeve	80	0.96	UL/CSA/TUV/CE	21.6	12"	5.49
1928126	ADDA Corporation	AD0612HX-G76(T)	12	60	60	10	16.3	Ball	160	1.92	UL/CE/TUV/CSA	31	(3) 12" (speed sensor)	7.95
2272671	Delta Electronics	DFD0612L	12	60	60	20	12.4	Ball	120	1.08	UL/CUL/TUV/CE	27	11"	5.05
2289303	Matsushita Electronic Comp.	FBP-06A12L	12	60	60	25	14.1	Hypro	120	1.44	—	24	12" (2P connector)	5.95
2288903	Delta Electronics	AUB0612LD	12	60	60	25	14.13	Ball	70	0.84	UL/CUL/VDE	24	3.5" (connector)	4.95
2288911	Delta Electronics	AFB0612L	12	60	60	25	14.13	Dual Ball	80	0.96	UL/CUL/VDE	26.5	20"	6.95
2289111	Max-Flow	MFD6025AD1	12	60	60	25	15.7	Ball	100	1.2	UL/CUL/TUV/CE	27	9" (2P connector)	5.95
2227276	YS Tech Usa	NYWO60250125BL	12	60	60	25	15.8	Ball	80	0.96	UL/CUL/TUV	23.5	7" (connector)	4.95
2288975	Jamicon Corporation	JF6025S	12	60	60	25	17.6	Sleeve	200	2.4	UL	31.5	7"	4.95
2288919	Sanyo Denki	109R0612H401	12	60	60	25	18.7	Ball	110	1.32	UL/CSA/VDE	28	(3) 4" (connector, speed sensor)	6.95
2205149	Sunon	MB60251V2-000U-G99	12	60	60	25	19.3	Vapo	74	0.89	UL/CUL	29	(3) 12" (speed sensor)	9.95
2217941	Thermactive Electronics	RDH6025B	12	60	60	25	20.3	Ball	140	1.68	UL/CUL	29	(3) 12" (speed sensor)	5.95
2230766	Thermactive Electronics	RDH6025B-PWM	12	60	60	25	20.3	Ball	140	1.86	UL/CUL/TUV/CE	29	(4) 12" (speed sensor + PWM)	6.49
2228818	Mitsubishi	MMF-06D12DL	12	60	60	25	21.6	Ball	70	0.84	UL/CSA	23	8.5"	5.95
2150766	ADDA Corporation	AD0612HB-A72GL	12	60	60	25	23.2	Ball	230	2.7	UL/CUL/TUV/CE	32.3	(3) 12" (alarm)	10.95
2133974	ADDA Corporation	AD0612XB-A72GL(P)	12	60	60	25	31.7	Hypro	230	2.76	UL/CSA/TUV/CE	32.3	(3) 12" (alarm)	10.95
2286215	Coolmax Technology	F126025BU	12	60	60	25	24.5	Ball	340	4.08	UL/TUV/CE	32.1	(3) 7.25" (PWM)	7.95
2292911	ADDA Corporation	AG06012HB257203(0L5)	12	60	60	25	24.8	Ball	230	2.76	UL/CUL/TUV	32.3	(3) 12" (alarm)	10.95
2279183	ADDA Corporation	AG06012HB257003(0L5)	12	60	60	25	24.8	Ball	230	2.76	UL/CUL/TUV	32.3	12"	10.95
2289103	Everflow	F1260025BU	12	60	60	25	34	Dual Ball	260	3.12	UL/TUV/CE	33.1	5" 3P connector	7.95
2158311	Delta Electronics	AFB0612EH-BF00	12	60	60	25	38.35	Ball	480	5.76	UL/CSA/CE	46.5	(3) 8" (connector, speed sensor)	11.95
2289215	Innovative	BP602512HH-03	12	60	60	25	38.4	Ball	390	4.68	UL/CUL/CE	46.7	(3) 12" (3P connector, speed sensor)	9.95
2289231	Nidec Corporation	A97578-001	12	60	60	38	27	Ball	1600	19	UL	31	(3) 11" (speed sensor)	10.95
2288927	Delta Electronics	FFB0612SHE-FOO	12	60	60	38	43.4	Ball	550	6.6	UL/CSA/VDE/CE	50.5	(3) 12" (speed sensor)	10.95
2232930	ADDA Corporation	AD0712HS-D73	12	70	70	15	32	Sleeve	250	3	UL/CUL/TUV/CE	40.3	(3) 12" (speed sensor)	5.95
2233203	ADDA Corporation	AD0712HS-D71	12	70	70	15	34	Sleeve	250	3	UL/CUL/TUV/CE	40.3	12"	6.49
2125561	AVC America	DE07015R12U	12	70	70	15	43	Hydraulic	700	8.4	UL/CE/TUV	46	(3) 8" connector (locked rotor)	6.95
2227647	JMC Products	7025-12LS	12	70	70	25	22	Sleeve	100	1.2	UL/CUL/TUV	24.3	6" connector	5.95
2192561	ADDA Corporation	AD0812LB-D70(T)	12	80	80	15	20	Ball	90	1.08	UL/CSA/TUV/CE	19.6	12"	6.75
2233641	ADDA Corporation	AD0812HB-D90	12	80	80	15	20	Ball	250	3	UL/CUL/TUV/CE	34.4	12"	4.95
2232948	ADDA Corporation	AD0812MX-D71	12	80	80	15	22.4	Hypro	150	1.8	UL/CUL/TUV/CE	26	12"	6.95
109081	ADDA Corporation	AD0812HB-D73(N)	12	80	80	15	29.9	Ball	190	2.28	UL/CUL/TUV	33.4	(3) 12" (speed sensor)	9.95
2132007	ADDA Corporation	AD0812HS-D70-LF	12	80	80	15	38.6	Sleeve	250	3	UL/CUL/TUV/CE	33	12"	4.95
2095365	ADDA Corporation	AD0812XX-D71	12	80	80	15	39.4	Hypro	350	4.2	UL/CSA/TUV/CE	42	11"	10.95
141921	ADDA Corporation	AD0812HB-C70-R	12	80	80	20	27.3	Ball	240	2.9	UL/CSA/CE	34	12"	9.35
2232112	ADDA Corporation	AD0812UB-C7B	12	80	80	20	32.5	Ball	140	1.68	UL/CUL/TUV/CE	37.5	(4) 12" (PWM + FG)	7.95
2228121	NMB Technologies	3110GL-B4W-B14	12	80	80	25	24.7	Ball	10	1.2	UL/CUL	22	10" (fan guard)	6.95
2228113	Nidec Corporation	D08A-12TL	12	80	80	25	24.7	Ball	60	0.72	—	19	8" (connector)	5.95
2228148	Mechatronics	F8025512B	12	80	80	25	26	Ball	75	0.9	UL/CUL/TUV	22	10"	6.95
2288935	NMB Technologies	3110KL-04W-B20	12	80	80	25	28.2	Ball	110	1.32	UL/CUL/CE/TUV	25	12" (connector)	8.95





[Click Here to Request a Large Quantity Quote](#)

**DC BRUSHLESS FANS: 12 - 18 VOLTS**

Jameco SKU	Mfr Name	Mfr P/N	Voltage (VDC)	Length (mm)	Width (mm)	Height (mm)	Air Flow (CFM)	Bearing	Current (mA)	Power (Watts)	Agency Approvals	Noise (dBA)	Connection (Leads)	Price 1
2289255	Arndt	DF1208SL	12	80	80	25	29.9	Sleeve	200	2.4	UL/CUL/TUV/CE	34	20"	5.95
2271511	ADDA Corporation	AD08012MX257304	12	80	80	25	30.9	Ball	150	1.8	UL/VDE/CE	26	(3) 11" (locked rotor)	9.95
2288951	Delta Electronics	AFB0812M	12	80	80	25	31.4	Ball	120	1.4	UL/CSA/VDE/CE	28	(3) 3" (speed sensor)	4.95
2234450	Sunon	EE80251B3-0000-G99	12	80	80	25	33	Ball	88	1.1	UL/CUL/TUV/CE	28	(3) 12" (speed sensor)	8.95
1776273	Delta Electronics	AFB0812H	12	80	80	25	35.3	Ball	160	1.92	UL/CUL/CE	37	12" (connector)	5.95
234895	ADDA Corporation	AD0812HB-A73GL	12	80	80	25	38.6	Ball	160	1.92	UL/CUL/TUV/CE	33.4	(3) 12" (speed sensor)	7.95
2078194	ADDA Corporation	AD0812UB-A71GP	12	80	80	25	40.2	Sleeve	250	3.0	UL/CSA/TUV/CE	34	12"	6.49
2135697	NMB Technologies	FBM-08A12H	12	80	80	25	39.6	Sleeve	220	2.1	UL/CSA	32	12" (connector)	3.29
2210984	Sunon	EE80251B1-0000-A99	12	80	80	25	41	Ball	145	1.74	UL/TUV/CE	33	12"	7.95
2233238	ADDA Corporation	AD0812UX-A73GL	12	80	80	25	48.8	Hypro	300	3.6	UL/CUL/TUV/CE	40.8	12" (speed sensor)	8.95
2081078	Jamicon Corporation	JF0825B1UR-R	12	80	80	25	52	Dual Ball	370	4.4	UL/CUL/TUV/CE	40	12"	9.95
2288967	Delta Electronics	QFR0812SH-FOO	12	80	80	25	54.6	Ball	330	3.96	UL/CUL/TUV/CE	41.2	12" (speed sensor)	14.95
2228164	EBM Papst	8312	12	80	80	32	31.8	Ball	216	2.6	UL/CSA/TUV	36	12"	12.95
2134213	ADDA Corporation	AD0812MB-Y51	12	80	80	32	44.6	Ball	20	5.08	UL/CUL/TUV/CE	37	12"	11.95
107406	EBM Papst	8312GHL	12	80	80	32	39.4	Sleeve	330	4	UL/CSA/CE/VDE	43	12"	5.95
2230758	Thermactive Electronics	RGM8038B1	12	80	80	38	83.4	Ball	850	11.7	UL/CUL/TUV/CE	57	12"	8.95
1928100	ADDA Corporation	AD0812XB-F71DS(M)	12	80	80	38	99	Ball	1500	18	UL/CE/TUV	57	12"	9.95
2233650	ADDA Corporation	AD0912HX-C70	12	92	92	20	32.8	Hypro	250	4	UL/CUL/TUV/CE	33	11"	4.95
1928089	ADDA Corporation	AD0912HS-A76GL(T)	12	92	92	25	50	Sleeve	130	1.6	UL/CUL/TUV/CE	23.5	(3) 12" (speed sensor)	7.95
1952783	Nidec Corporation	TA350DC-M34138-34	12	92	92	25	35	Ball	160	1.92	UL/CSA	26.4	(4) 10" (PWM)	3.95
2232981	ADDA Corporation	AD0912LB-A72GL	12	92	92	25	37.7	Ball	130	1.56	UL/CUL/TUV/CE	42	(3) 12" (alarm)	7.95
1928097	ADDA Corporation	AD0912LX-A76GL(T)	12	92	92	25	32.4	Hypro	120	1.44	UL/CSA/TUV/CE	26.5	(3) 12" (speed sensor)	7.95
1818605	NMB Technologies	3610KL-04W-B30	12	92	92	25	40.6	Ball	160	1.92	UL	34	24"	10.95
2233094	ADDA Corporation	AQ0912LB-A70GL	12	92	92	25	40.7	Ball	150	1.8	UL/CUL/CE	29.2	12"	12.75
1928003	ADDA Corporation	AD0912MS-A70GL	12	92	92	25	43	Sleeve	170	2.04	UL/CUL/TUV/CE	31	12"	10.95
154641	Nidec Corporation	TA350DC-M33422-16	12	92	92	25	48	Ball	290	3.5	UL/CSA	34.8	12"	9.95
2228236	Sunon	1209PTB1-6	12	92	92	25	49	Ball	210	2.5	UL/CUL/TUV/CE	35	12"	7.95
2193942	Orion Fans	DPF92B012	12	92	92	25	50	Ball	290	3.48	UL/CUL	33	12"	6.49
2228201	Mechatronics	E9225H12B2	12	92	92	25	51	Ball	360	4.32	UL/CUL/TUV	36	(3) 14" (speed sensor)	7.95
1928302	ADDA Corporation	AD0912HS-A70GL(T)	12	92	92	25	50	Sleeve	210	5.04	UL/CSA/TUV/CE	38.6	12"	7.95
2134248	ADDA Corporation	AD0912US-A70GL	12	92	92	25	60	Sleeve	300	3.6	UL/CSA/TUV/CE	39.4	12"	12.95
2234871	Sunon	PMD1209PTB3-A(2).F.GN	12	92	92	25	65	Ball	300	3.6	UL/CUL/TUV/CE	43	(3) 12" (speed sensor)	10.15
174140	Common Wealth	FP-108M/DC(S-3)12SW	12	120	120	25	54	Sleeve	140	1.7	UL/TUV/CE/CSA	25	12"	8.95
2233019	ADDA Corporation	AD1212LX-A71GL	12	120	120	25	72	Hypro	240	2.88	UL/CE	34.4	12"	9.95
2228172	AVC America	F1225B12L	12	120	120	25	75.2	Ball	270	3.24	UL/TUV/CE/CSA	39.5	8"	9.95
2134053	ADDA Corporation	AD1212HB-A72GL(N)	12	120	120	25	85.2	Ball	330	3.96	UL/TUV/CE/CE	38	(3) 12" (alarm)	8.95
2270855	ADDA Corporation	AD1212HB-A71GL	12	120	120	25	87.8	Ball	370	4.44	UL/CUL	39.1	12"	13.95
2271335	ADDA Corporation	AD1212HB-A73GL(N)	12	120	120	25	88.7	Ball	336	4.4	UL/CUL/TUV	39.1	(3) 11" (speed sensor)	10.95
1928020	ADDA Corporation	AD1212MB-Y51	12	120	120	32	99	Ball	370	3.36	UL/CUL/TUV/CE	41.1	11"	10.95
2170927	ADDA Corporation	AD1212US-A71GL-LF	12	120	120	25	99.12	Sleeve	500	6	UL/CUL/TUV/CE	43.3	11"	8.95
2235321	ADDA Corporation	AS12012LB25A100	12	120	120	25	126	Ball	660	7.92	UL/CUL/TUV/CE	51	12"	8.95
2233060	ADDA Corporation	AQ1212HB-A71GL	12	120	120	25	87.9	Ball	290	3.48	UL/CUL/CE	39.1	12" (water PRF)	14.95
2290303	Common Wealth	FP-108-32/DC(S-1)12BW	12	120	120	32	110	Ball	420	5.04	UL/TUV/CE	43	(3) 12" (3P connector, speed sensor)	11.95
2233254	ADDA Corporation	AD1212UB-Y51	12	120	120	32	130.8	Ball	510	6.12	UL/CUL/TUV/CE	48.4	12"	19.95
2231697	Nidec Corporation	TA450DC-A31276-10A	12	120	120	38	104	Ball	440	5.28	UL/CSA	51.9	Terminals	9.95
2134264	ADDA Corporation	AD1212HX-A71GL(N)	12	120	120	38	85.2	Ball	500	6	UL/CUL/TUV	46.7	12"	9.95
2290327	Common Wealth	FP-108/DC(S-1)12SW	12	120	120	38	105	Sleeve	600	7	UL/CSA	45	32" (0.25" QC plug)	12.95
2290335	Common Wealth	FP-108/DC(S-1)12SW*	12	120	120	38	105	Sleeve	600	7	UL/CSA	45	4" (2.1mm male jack)	12.95
2173079	Sunon	EEC0381B2-0000-A99	12	120	120	38	108	Ball	421	5.1	UL/CUL/TUV/CE	44	12"	14.95
2231478	ADDA Corporation	AD1212UB-F52	12	120	120	38	120	Ball	620	7.44	UL/CUL/TUV/CE	48	11"	12.95
2270871	ADDA Corporation	AD17212LB5151MD(OCW)	12	172	151	51	295	Ball	2300	27.6	UL/TUV/CSA/CE	60.6	12"	49.95
2288991	Panasonic	FBM06F18H	18	60	60	20	16.6	Hypro	130	2.34	UL/CSA	32	1.5" (2P connector)	4.95