



[Click Here to Request a Large Quantity Quote](#)

[12 to 14.3 Volt Table Top Switching Power Supplies](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	AC Power Cord	Input Voltage (VAC)	Input Frequency	Output Connector Type	Output Connector Diameters	Polarity	Agency Approvals	Price 1
1954244	MEAN WELL	GS15A-3P1J	12	1.25	15	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm right angle	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC	\$15.00
2229491	Dee Van Enterprise Usa	DSA-0151D-12-2.1	12	1.5	18	NOT INCLUDED, RECOMMEND 2271575	100 to 125	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CSA/TUV/CE	\$7.49
2229482	Dee Van Enterprise Usa	DSA-0151D-12-2.5	12	1.5	18	NOT INCLUDED, RECOMMEND 2271575	100 to 125	50 to 60	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CSA/TUV/CE	\$8.95
2257011	MEAN WELL	GST18A12-P1J	12	1.5	18	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$12.20
2270895	Phihong	PSA18U-120	12	1.5	18	NOT INCLUDED, RECOMMEND 2271583	100 to 240	50 to 60	DIN Male	4-Pin	N/A	UL/CUL/TUV/CE	\$8.95
2227381	Delta Electronics	EADP-24MB	12	2	24	NOT INCLUDED, RECOMMEND 2271583	100 to 240	50 to 60	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL/CCC/CE	\$7.95
2257192	MEAN WELL	GST25A12-P1J	12	2.08	25	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$12.40
2257361	MEAN WELL	GST36B12-P1J	12	3	36	NOT INCLUDED, RECOMMEND 2271583	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$14.10
2224307	MEAN WELL	GST40A12-P1J	12	3.34	40	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$15.40

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	AC Power Cord	Input Voltage (VAC)	Input Frequency	Output Connector Type	Output Connector Diameters	Polarity	Agency Approvals	Price 1
2271239	Jameco Reliapro	G99-KPL060F-L253	12	5	60	NOT INCLUDED, RECOMMEND 2271575	100 to 240	47 to 63	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL/TUV/CE/FCC/CCC	\$14.95
2208956	Jameco Reliapro	KPL-060F-VI	12	5	60	NOT INCLUDED, RECOMMEND 2271575	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CE	\$13.95
2236543	Lite-On Electronics	PA-1600-2A-LF	12	5	60	NOT INCLUDED, RECOMMEND 2271575	100 to 240	50 to 60	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL/TUV/CE	\$11.95
2272991	EDAC	EA1050A-120	12	5	60	NOT INCLUDED, RECOMMEND 2271575	100 to 240	50 to 60	DIN Male	4-pin DIN	N/A	UL/CUL/TUV/CE/FCC/CCC	\$12.95
2224382	MEAN WELL	GST60A12-P1J	12	5	60	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$17.10
1952370	MEAN WELL	GS60A12-P1J	12	5	60	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CEC	\$14.95
2223460	MEAN WELL	GST90A12-P1M	12	6.67	80	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$28.10
2223582	MEAN WELL	GST120A12-R7B	12	8.5	102	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	DIN Male	4-pin DIN	N/A	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$41.00
2226425	MEAN WELL	GST160A12-R7B	12	11.5	138	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	DIN Male	4-pin DIN	N/A	UL/CUL/TUV/CB/CE/FCC/EN/EAC	\$49.60
2226476	MEAN WELL	GST220A12-R7B	12	15	180	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	DIN Male	4-pin DIN	N/A	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$70.30
2226521	MEAN WELL	GST280A12-C6P	12	21	252	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	MOLEX 39-01-2060	6-Pin Molex	N/A	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$85.50