



[Click Here to Request a Large Quantity Quote](#)

[2 to 14.5 Volt LED Switching Power Supplies](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Input Voltage Range (VDC)	PFC Function	Agency Approvals	Maximum Input Current (A)	Output Connector Type	Maximum Output Power (W)	Price 1
2142053	MEAN WELL	APV-12-5	5	2		90 to 264		No	UL/CUL/CB/CE/EN/ENEC/EAC	0.35	Stripped and Tinned	10	\$6.10
2103222	MEAN WELL	LPV-20-5	5	3		90 to 264		No	UL/CUL/TUV/CE/EN/EAC	0.55	Stripped and Tinned	15	\$9.30
2103249	MEAN WELL	LPV-60-5	5	8		90 to 264		No	CB/CE/EN/EAC	1.2	Stripped and Tinned	40	\$14.80
2141190	MEAN WELL	LPV-100-5	5	12		90 to 264		No	UL/CUL/CE/EN/EAC	2.2	Stripped and Tinned	60	\$24.30
2226290	MEAN WELL	APV-8-12	12	0.67		90 to 264		No	UL/CUL/CE/EN/EAC	0.15	Stripped and Tinned	8	\$4.90
2142061	MEAN WELL	APV-12-12	12	1		90 to 264		No	UL/CUL/CB/CE/EN/ENEC/EAC	0.35	Stripped and Tinned	12	\$6.10
2142109	MEAN WELL	APV-16-12	12	1.25		90 to 264		No	UL/CUL/CB/CE/EN/ENEC/EAC	0.5	Stripped and Tinned	15	\$6.30
2165651	MEAN WELL	LPF-16D-12	12	1.34		90 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	0.4	Stripped and Tinned	16.08	\$20.90
2165562	MEAN WELL	LPF-16-12	12	1.34		90 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	0.4	Stripped and Tinned	16.08	\$19.00
2101059	MEAN WELL	LPL-18-12	12	1.5		90 to 132		No	CE/FCC/EN/EAC	0.5	Stripped and Tinned	18	\$8.60
2122423	MEAN WELL	PLN-20-12	12	1.6		90 to 277		Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	0.4	Stripped and Tinned	19.2	\$19.00
2102596	MEAN WELL	LPV-20-12	12	1.67		90 to 264		No	UL/CUL/TUV/CE/EN/EAC	0.55	Stripped and Tinned	20	\$9.30
2164076	MEAN WELL	APV-25-12	12	2.1		90 to 264		No	UL/CUL/CE/EN/EAC	0.8	Stripped and Tinned	25.2	\$10.60
2165749	MEAN WELL	LPF-25-12	12	2.1		90 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	0.4	Stripped and Tinned	25.2	\$21.30

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Input Voltage Range (VDC)	PFC Function	Agency Approvals	Maximum Input Current (A)	Output Connector Type	Maximum Output Power (W)	Price 1
2103610	MEAN WELL	PLC-30-12	12	2.5	11.4 to 13.2	90 to 264		Yes	CUL/TUV/CB/CE/EN/EAC/CCC	0.4	Screw Terminal Block	30	\$21.30
1954404	MEAN WELL	PLN-30-12	12	2.5		90 to 295		Yes	UL/CUL/CSA/TUV/CB/CE/EN/EAC/CCC	0.4	Stripped and Tinned	30	\$21.30
2103142	MEAN WELL	LPV-35-12	12	3		90 to 264		No	UL/CUL/CE/EN/EAC	1.1	Stripped and Tinned	36	\$13.30
2164121	MEAN WELL	APV-35-12	12	3		90 to 264		No	UL/CUL/CE/EN/EAC	0.75	Stripped and Tinned	36	\$11.80
2234783	EPtronics	LD40W-12-C3330	12	3.33	4 to 12	90 to 305			UL/CUL/FCC/CE	0.4	Stripped and Tinned	40	\$11.95
2148623	MEAN WELL	HLG-40H-12B	12	3.33		90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	0.43	Stripped and Tinned	39.96	\$30.40
2148957	MEAN WELL	HLN-40H-12A	12	3.33		90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	0.43	Stripped and Tinned	40	\$31.00
2148615	MEAN WELL	HLG-40H-12A	12	3.33		90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	0.43	Stripped and Tinned	39.96	\$29.60
2140470	MEAN WELL	LPF-40-12	12	3.34		90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	0.6	Stripped and Tinned	40.08	\$24.70
2140568	MEAN WELL	LPF-40D-12	12	3.34		90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	0.6	Stripped and Tinned	40.08	\$26.60
2220998	MEAN WELL	NPF-40-12	12	3.34		90 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	0.6	Stripped and Tinned	40.08	\$23.90
2263815	MEAN WELL	IDLV-65A-12	12	4.2	12	180 to 295		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	0.4	Terminal Block	50.4	\$20.90
1918833	MEAN WELL	PLN-100-12	12	5	10.2 to 12	90 to 264		Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	1.1	Stripped and Tinned	60	\$42.20
2196975	MEAN WELL	HVG-65-12A	12	5	10.8 to 13.5	180 to 528		Yes	UL/CUL/FCC/EN/EAC	0.22	Stripped and Tinned	60	\$52.30
2103901	MEAN WELL	PLC-60-12	12	5	11.5 to 13	90 to 264		Yes	CUL/TUV/CB/CE/EN/EAC/CCC	0.8	Screw Terminal Block	60	\$33.30
1918913	MEAN WELL	PLN-60-12	12	5	11.5 to 13	90 to 295		Yes	CUL/TUV/CB/CE/EN/EAC/CCC	0.8	Stripped and Tinned	60	\$33.30

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Input Voltage Range (VDC)	PFC Function	Agency Approvals	Maximum Input Current (A)	Output Connector Type	Maximum Output Power (W)	Price 1
2249723	MEAN WELL	ELG-75-12	12	5	6 to 12	100 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	0.7	Stripped and Tinned	60	\$29.50
2103169	MEAN WELL	LPV-60-12	12	5		90 to 264		No	CUL/CB/CE/EN/EAC	1.2	Stripped and Tinned	60	\$14.80
2221915	MEAN WELL	OWA-60U-12	12	5		90 to 264		No	CUL/FCC	1.2	Female Barrel Plug	60	\$27.70
2140656	MEAN WELL	LPF-60-12	12	5		90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	0.8	Stripped and Tinned	60	\$26.80
2140744	MEAN WELL	LPF-60D-12	12	5		90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	0.8	Stripped and Tinned	60	\$28.70
2121877	MEAN WELL	CEN-60-12	12	5		90 to 295		Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	0.8	Stripped and Tinned	60	\$31.95
2142264	MEAN WELL	HLG-80H-12B	12	5		90 to 305		Yes	CUL/TUV/CB/CE/EN/EAC/CCC	0.85	Stripped and Tinned	60	\$37.20
2220955	MEAN WELL	PWM-60-12	12	5		90 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	0.8	Stripped and Tinned	60	\$27.90
2224972	MEAN WELL	OWA-60E-12	12	5		90 to 264		No	CB/CE/EN/EAC	1.2	Female Barrel Plug	60	\$27.70
2293815	MEAN WELL	XLG-75-12-A	12	5		100 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	1	Stripped and Tinned	60	\$24.70
2142176	MEAN WELL	HLG-80H-12A	12	5		90 to 305		Yes	CUL/TUV/CB/CE/EN/EAC/CCC	0.85	Stripped and Tinned	60	\$36.10
2254311	MEAN WELL	LPFH-60D-12	12	5		200 to 400		Yes	UL/CUL/FCC/EN/EAC	0.4	Stripped and Tinned	60	\$32.50
2104954	MEAN WELL	PLP-60-12	12	5		90 to 264		Yes	CUL/TUV/CB/CE/EN/EAC/CCC	0.8	Screw Terminal Block	60	\$16.00
2197062	MEAN WELL	HVG-65-12B	12	5		180 to 528		Yes	UL/CUL/FCC/EN/EAC	0.22	Stripped and Tinned	60	\$53.80
2254240	MEAN WELL	LPFH-60-12	12	5		200 to 400		Yes	UL/CUL/FCC/EN/EAC	0.4	Stripped and Tinned	60	\$30.60
2304615	MEAN WELL	SLD-80-12	12	6.6		110 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	0.9	Screw Terminal Block	79.2	\$24.70

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Input Voltage Range (VDC)	PFC Function	Agency Approvals	Maximum Input Current (A)	Output Connector Type	Maximum Output Power (W)	Price 1
2215099	MEAN WELL	PWM-90-12	12	7.5		90 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	0.95	Stripped and Tinned	90	\$39.00
2215005	MEAN WELL	NPF-90-12	12	7.5		90 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	0.95	Stripped and Tinned	90	\$37.10
2214918	MEAN WELL	NPF-90D-12	12	7.5		90 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	0.95	Stripped and Tinned	90	\$39.00
2293863	MEAN WELL	XLG-100-12-A	12	8		100 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	1.1	Stripped and Tinned	96	\$27.60
2133131	MEAN WELL	LPV-100-12	12	8.5		90 to 264		No	UL/CUL/CE/EN/EAC	2.2	Stripped and Tinned	102	\$24.30
2148105	MEAN WELL	HLG-120H-12B	12	10	10.8 to 13.5	90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	1.4	Stripped and Tinned	120	\$46.60
2137529	MEAN WELL	HLG-120H-12A	12	10	10.8 to 13.5	90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	1.4	Stripped and Tinned	120	\$45.20
2215259	MEAN WELL	LPV-150-12	12	10		180 to 305		No	UL/CUL/CE/EN/EAC	1.7	Stripped and Tinned	120	\$33.30
2260535	MEAN WELL	LPVL-150-12	12	10		90 to 132		No	UL/CUL/CE/FCC/EN/EAC	1.7	Stripped and Tinned	120	\$33.30
2221827	MEAN WELL	OWA-120U-12	12	10		90 to 264		Yes	UL/CUL/FCC	1.3	4-pin DIN female	120	\$52.30
2222002	MEAN WELL	PWM-120-12	12	10		90 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	1.3	Stripped and Tinned	120	\$44.70
2221641	MEAN WELL	NPF-120-12	12	10		90 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	1.3	Stripped and Tinned	120	\$42.80
2249660	MEAN WELL	ELG-150-12	12	10		100 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	1.7	Stripped and Tinned	120	\$35.20
1954877	MEAN WELL	CLG-150-12A	12	11		90 to 295		Yes	UL/CUL/TUV/CB/CE/EN/EAC	2	Stripped and Tinned	132	\$47.95
2108699	MEAN WELL	CLG-150-12	12	11		90 to 295		Yes	UL/CUL/TUV/CB/CE/EN/EAC	4	Stripped and Tinned	132	\$42.95
2137609	MEAN WELL	HLG-150H-12A	12	12.5	10.8 to 13.5	90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	1.7	Stripped and Tinned	150	\$45.80
2147911	MEAN WELL	HLG-150H-12	12	12.5		90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	1.4	Stripped and Tinned	150	\$45.80

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Input Voltage Range (VDC)	PFC Function	Agency Approvals	Maximum Input Current (A)	Output Connector Type	Maximum Output Power (W)	Price 1
2147920	MEAN WELL	HLG-150H-12B	12	12.5		90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	1.4	Stripped and Tinned	150	\$47.10
2136690	MEAN WELL	HLG-185H-12A	12	13	10.8 to 13.5	90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	1.8	Stripped and Tinned	156	\$49.20
2102158	MEAN WELL	HLG-240H-12A	12	16	11.2 to 12.8	90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	4	Stripped and Tinned	192	\$61.00
2115004	MEAN WELL	HLG-240H-12	12	16	11.2 to 12.8	90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	4	Stripped and Tinned	192	\$61.00
2115098	MEAN WELL	HLG-240H-12B	12	16	11.2 to 12.8	90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	4	Stripped and Tinned	192	\$62.70
2251954	MEAN WELL	ELG-200-12	12	16		100 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	1.8	Stripped and Tinned	192	\$43.70
2252017	MEAN WELL	ELG-200-12A	12	16		100 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	1.8	Stripped and Tinned	192	\$43.70
2141780	MEAN WELL	HLG-320H-12A	12	22	10.8 to 13.5	90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	3.5	Stripped and Tinned	264	\$81.70
2141691	MEAN WELL	HLG-320H-12	12	22	10.8 to 13.5	90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	3.5	Stripped and Tinned	264	\$81.70
2141878	MEAN WELL	HLG-320H-12B	12	22	10.8 to 13.5	90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	3.5	Stripped and Tinned	264	\$84.60
2218311	MEAN WELL	HLG-600H-12A	12	40		90 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	7	Stripped and Tinned	480	\$179.00
2218329	MEAN WELL	HLG-600H-12B	12	40		90 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	7	Stripped and Tinned	480	\$182.00
2196983	MEAN WELL	HVG-65-15A	15	4.3	13.5 to 17	180 to 528		Yes	UL/CUL/FCC/EN/EAC	0.22	Stripped and Tinned	64.5	\$52.30
2189433	MEAN WELL	HBG-160-24B	24	6.5	14.5 to 24.0	90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/EAC	1.7	Stripped and Tinned	156	\$54.20
2189396	MEAN WELL	HBG-160-24A	24	6.5	14.5 to 24.0	90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/EAC	1.7	Stripped and Tinned	156	\$52.60
2100540	MEAN WELL	LPC-60-1750	34	1.75	9 to 34	90 to 264		No	CUL/CB/CE/EN/EAC	1.2	Stripped and Tinned	59.5	\$14.80
2101315	MEAN WELL	LPC-60-1400		1.4	9 to 42	90 to 264		No	UL/CUL/CB/CE/EN/EAC	1.2	Stripped and Tinned	58.8	\$14.80

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Input Voltage Range (VDC)	PFC Function	Agency Approvals	Maximum Input Current (A)	Output Connector Type	Maximum Output Power (W)	Price 1
2101121	MEAN WELL	LPC-20-350		0.35	9 to 48	90 to 264		No	UL/TUV/CE/EN/EAC	0.55	Stripped and Tinned	16.8	\$9.30
2101307	MEAN WELL	LPC-35-700		0.7	9 to 48	90 to 264		No	UL/CE/EN/EAC	1.1	Stripped and Tinned	33.6	\$13.30
2142150	MEAN WELL	APC-16-350		0.35	12 to 48	90 to 264		No	UL/CUL/CE/EN/EAC	0.5	Stripped and Tinned	16.8	\$6.30
2101147	MEAN WELL	LPC-60-1050		1.05	9 to 48	90 to 264		No	UL/CUL/CB/CE/EN/EAC	1.2	Stripped and Tinned	50.4	\$14.80
2101286	MEAN WELL	LPC-20-700		0.7	9 to 30	90 to 264		No	UL/CUL/TUV/CE/EN/EAC	0.55	Stripped and Tinned	21	\$9.30
2164050	MEAN WELL	APC-35-1050		1.05	11 to 33	90 to 264		No	CUL/CE/EN/EAC	0.75	Stripped and Tinned	34.7	\$11.80
2141026	MEAN WELL	PCD-16-1400A		1.4	8 to 12	90 to 135		Yes	CUL/FCC/EN/EAC	0.4	Stripped and Tinned	16.8	\$14.80
2142133	MEAN WELL	APC-12-350		0.35	9 to 36	90 to 264		No	UL/CUL/CE/EN/EAC	0.35	Stripped and Tinned	12.6	\$6.10
2164009	MEAN WELL	APC-25-700		0.7	11 to 36	90 to 264		No	CUL/CE/EN/EAC	0.8	Stripped and Tinned	25.2	\$10.60
2101139	MEAN WELL	LPC-35-1050		1.05	9 to 30	90 to 264		No	UL/CUL/CE/EN/EAC	1.1	Stripped and Tinned	31.5	\$13.30
2142168	MEAN WELL	APC-16-700		0.7	9 to 24	90 to 264		No	UL/CUL/CE/EN/EAC	0.5	Stripped and Tinned	16.8	\$6.30
2164017	MEAN WELL	APC-25-1050		1.05	9 to 24	90 to 264		No	CUL/CE/EN/EAC	0.8	Stripped and Tinned	25.2	\$10.60
2142141	MEAN WELL	APC-12-700		0.7	9 to 18	90 to 264		No	UL/CUL/CE/EN/EAC	0.35	Stripped and Tinned	12.6	\$6.10
2156009	MEAN WELL	LDD-700H		0.7	2 to 51		9 to 56		FCC/CE	0.65	PC Pins		\$5.69
2226337	MEAN WELL	APC-8-500		0.5	8 to 16	90 to 264		No	UL/CUL/CE/EN/EAC	0.15	Stripped and Tinned	8	\$4.90
2226345	MEAN WELL	APC-8-700		0.7	6 to 11	90 to 264		No	UL/CUL/CE/EN/EAC	0.15	Stripped and Tinned	7.7	\$4.90
2155911	MEAN WELL	LDD-350LW		0.35	2 to 31		9 to 32		FCC/CE	0.35	Wires		\$3.75
2226329	MEAN WELL	APC-8-350		0.35	11 to 23	90 to 264		No	UL/CUL/CE/EN/EAC	0.15	Stripped and Tinned	8.05	\$4.90

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Input Voltage Range (VDC)	PFC Function	Agency Approvals	Maximum Input Current (A)	Output Connector Type	Maximum Output Power (W)	Price 1
2155938	MEAN WELL	LDD-500HW		0.5	2 to 51		9 to 56		FCC/CE	0.45	Wires		\$5.69
2141018	MEAN WELL	PCD-16-1050A		1.05	12 to 16	90 to 135		Yes	CUL/FCC/EN/EAC	0.4	Stripped and Tinned	16.8	\$14.80
2101294	MEAN WELL	LPC-35-1400		1.4	9 to 24	90 to 264		No	UL/CUL/CE/EN/EAC	1.1	Stripped and Tinned	33.6	\$13.30
2155903	MEAN WELL	LDD-350L		0.35	2 to 31		9 to 32		FCC/CE	0.35	PC Pins		\$3.79
2155962	MEAN WELL	LDD-600H		0.6	2 to 51		9 to 56		FCC/CE	0.55	PC Pins		\$5.95
2216711	MEAN WELL	LCM-25DA		1.05	6 to 54	180 to 277		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	0.17	JST B2B-PH-KL	25.2	\$29.10
2174573	MEAN WELL	LCM-40		1.05	2 to 100	180 to 295		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	0.23	JST B2B-XH	42	\$28.50
2174581	MEAN WELL	LCM-40DA		1.05	2 to 100	180 to 295		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	0.23	JST B2B-XH	42	\$34.20
2174469	MEAN WELL	HVGC-150-1400A		1.4	12 to 107	180 to 528		Yes	UL/CUL/TUV/CB/CE/FCC/EN/EAC	0.5	Stripped and Tinned	149.8	\$70.30
2197257	MEAN WELL	HVGC-65-700B		0.7	9 to 93	180 to 528		Yes	UL/CUL/CB/CE/FCC/EN/ENEC/EAC	0.22	Stripped and Tinned	65.1	\$53.80
2216702	MEAN WELL	LCM-25		1.05	6 to 54	180 to 277		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	0.17	JST B2B-PH-KL	25.2	\$23.40
2174590	MEAN WELL	LCM-60		1.4	2 to 90	180 to 295		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	0.3	JST B2B-XH	60.3	\$31.40