

Click Here to Request a Large Quantity Quote



|        |      |      |      |      |      |      |      |      |      |      |      |      |      |      |      |      |      |      |      |      |      |      |      |      |      |      |      |      |
|--------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|
| mm     | 6    | 10   | 15   | 20   | 25   | 28   | 30   | 32   | 35   | 38   | 40   | 45   | 51   | 60   | 70   | 75   | 76   | 80   | 92   | 94   | 95   | 97   | 120  | 125  | 126  | 127  | 150  | 172  |
| Inches | 0.24 | 0.40 | 0.60 | 0.80 | 1.00 | 1.10 | 1.18 | 1.26 | 1.40 | 1.50 | 1.60 | 1.80 | 2.00 | 2.36 | 2.76 | 2.95 | 2.99 | 3.15 | 3.63 | 3.70 | 3.74 | 3.82 | 4.72 | 4.92 | 4.96 | 5.00 | 5.90 | 6.77 |

**DC BRUSHLESS FANS: 24 VOLTS**

| Jameco SKU | Mfr Name                | Mfr P/N               | Voltage (VDC) | Length (mm) | Width (mm) | Height (mm) | Air Flow (CFM) | Bearing   | Current (mA) | Power (Watts) | Agency Approvals  | Noise (dBA) | Connection (Leads)                | Price 1 |
|------------|-------------------------|-----------------------|---------------|-------------|------------|-------------|----------------|-----------|--------------|---------------|-------------------|-------------|-----------------------------------|---------|
| 2133931    | ADDA Corporation        | AD0424HB-G73          | 24            | 40          | 40         | 10          | 6.7            | Ball      | 90           | 2.16          | UL/CUL/TUV/CE     | 25          | (3) 12" (speed sensor)            | 10.95   |
| 2167605    | ADDA Corporation        | AD0424HB-G70-LF       | 24            | 40          | 40         | 10          | 6.7            | Ball      | 90           | 2.16          | UL/CUL/TUV/CE     | 25          | 12"                               | 9.95    |
| 2231806    | ADDA Corporation        | AD0424LB-C50          | 24            | 40          | 40         | 20          | 7.7            | Ball      | 60           | 1.4           | UL/TUV/CE         | 25          | 12"                               | 7.95    |
| 2158514    | Sunon                   | MF40202V2-10000-A99   | 24            | 40          | 40         | 20          | 7.7            | Vapo      | 33           | 2.16          | UL/TUV/CE/CSA     | 21          | 12"                               | 8.95    |
| 1928290    | ADDA Corporation        | AD0424HB-C50          | 24            | 40          | 40         | 20          | 10             | Ball      | 90           | 2.16          | UL/CE             | 31.9        | 12"                               | 11.95   |
| 2133940    | ADDA Corporation        | AD0424UB-C56          | 24            | 40          | 40         | 20          | 11             | Ball      | 90           | 2.16          | CE                | 31.9        | (3) 11" (speed sensor)            | 7.95    |
| 2235268    | ADDA Corporation        | AD0524HS-G70          | 24            | 52          | 52         | 10          | 11.2           | Sleeve    | 90           | 2.16          | UL/CUL/TUV/CE     | 26          | 12"                               | 9.95    |
| 1708422    | Sunon                   | KDE2406PHS3           | 24            | 60          | 60         | 15          | 15             | Sleeve    | 50           | 1.2           | UL/CUL/TUV/CE     | 31          | 12"                               | 6.95    |
| 2188588    | Sunon                   | MF60152V2-10000-A99   | 24            | 60          | 60         | 15          | 21.9           | Vapo      | 85           | 2.04          | UL/CUL/TUV/CE     | 32.5        | 12"                               | 8.95    |
| 2271135    | ADDA Corporation        | AG06024DB207000       | 24            | 60          | 60         | 20          | 15.1           | Dual Ball | 30           | 2.4           | UL/CUL/CE         | 30.9        | 12"                               | 9.95    |
| 2233191    | ADDA Corporation        | AD0624HX-C70GL        | 24            | 60          | 60         | 20          | 16.3           | Hypro     | 90           | 2.16          | UL/CUL/TUV/CE     | 29.7        | 12"                               | 7.95    |
| 2236391    | Sunon                   | MB60202V1-0000-A99    | 24            | 60          | 60         | 20          | 23             | Vapo      | 75           | 1.8           | UL/CUL            | 33          | 12" (with connector)              | 8.95    |
| 2231831    | ADDA Corporation        | AD0624LB-A70GL        | 24            | 60          | 60         | 25          | 13.2           | Ball      | 80           | 1.9           | UL/TUV/CE         | 16.1        | 12"                               | 5.95    |
| 2132111    | ADDA Corporation        | AD0624HB-D71GL        | 24            | 60          | 60         | 25          | 17             | Ball      | 80           | 1.8           | UL/CSA/TUV/CUL/CE | 28.3        | 12"                               | 9.95    |
| 2121391    | ADDA Corporation        | AD06024MB257100       | 24            | 60          | 60         | 25          | 17.3           | Ball      | 80           | 1.92          | UL/CUL/TUV/CE     | 26.9        | 12"                               | 6.49    |
| 189861     | Jamicon Corporation     | JF0625B2M-005-065R    | 24            | 60          | 60         | 25          | 18             | Ball      | 130          | 1.56          | UL/CSA/TUV/CE     | 31.3        | 10"                               | 8.95    |
| 2271295    | NMB Technologies        | 2410NL-05W-B30        | 24            | 60          | 60         | 25          | 19             | Ball      | 60           | 1.44          | CSA               | 31          | 4" (with 2P connector)            | 6.95    |
| 2234492    | ADDA Corporation        | AG06024HB257203(00L5) | 24            | 60          | 60         | 25          | 23.3           | Ball      | 120          | 2.8           | UL/CUL/TUV/CE     | 33          | 12"                               | 8.95    |
| 2228244    | Frilec                  | 2406PTB1              | 24            | 60          | 60         | 25          | 23.5           | Ball      | 110          | 2.6           | UL/CSA/CE         | 33          | 12"                               | 5.95    |
| 2235313    | ADDA Corporation        | AQ0624HB-70GL(T)      | 24            | 60          | 60         | 25          | 24.5           | Ball      | 120          | 2.88          | UL/CUL/CE         | 35.2        | 12"                               | 6.95    |
| 212628     | ADDA Corporation        | AD0624UB-A71GL-LF     | 24            | 60          | 60         | 25          | 27.8           | Sleeve    | 150          | 3.6           | UL/CSA/TUV/CE     | 32.3        | 12" (with connector)              | 7.95    |
| 136161     | Jamicon Corporation     | JF0825B2H-005-065R    | 24            | 80          | 80         | 25          | 39.2           | Ball      | 150          | 3.6           | UL/CSA/TUV        | 31          | 12"                               | 9.95    |
| 2158565    | Sunon                   | EE80252B1-0000-A99    | 24            | 80          | 80         | 25          | 41             | Ball      | 73           | 1.8           | UL/CUL/TUV        | 33          | 12"                               | 9.95    |
| 2271039    | Thermactive Electronics | RDH8025B2             | 24            | 80          | 80         | 25          | 41             | Ball      | 150          | 3.6           | UL/CUL/TUV/CE     | 35          | 12"                               | 8.95    |
| 2292639    | ADDA Corporation        | AD08024UB257104(05H3) | 24            | 80          | 80         | 25          | 47.31          | Ball      | 160          | 3.84          | UL/CUL/TUV/CE     | 41          | 11"                               | 9.95    |
| 2134150    | ADDA Corporation        | AQ0824UB-A71GL        | 24            | 80          | 80         | 25          | 50             | Ball      | 260          | 6.24          | CE                | 41          | 12"                               | 9.95    |
| 2234847    | ADDA Corporation        | AD0824UB-A73GL(LN)    | 24            | 80          | 80         | 25          | 52.4           | Ball      | 150          | 3.6           | UL/CUL/TUV/CE     | 40.8        | (3) 12" (speed sensor)            | 11.95   |
| 2211160    | NMB Technologies        | 3113PL05WB30          | 24            | 80          | 80         | 32          | 28             | Ball      | 130          | 3.1           | UL/CUL            | 31          | 12"                               | 4.95    |
| 2271287    | EBM Papst               | 8314/19H              | 24            | 80          | 80         | 32          | 47.1           | Ball      | 245          | 6             | UL/CSA            | 48          | (3) 11" (speed sensor)            | 14.95   |
| 2220171    | ADDA Corporation        | AD0824UB-Y51          | 24            | 80          | 80         | 32          | 55.3           | Ball      | 150          | 3.6           | UL/CUL/TUV/CE     | 43.8        | 12"                               | 12.95   |
| 2232067    | ADDA Corporation        | AD0824LB-F73          | 24            | 80          | 80         | 38          | 39             | Ball      | 80           | 1.92          | UL/VDE/CE         | 32.3        | (3) 12" (speed sensor)            | 6.95    |
| 2232964    | ADDA Corporation        | AD0824UB-F73DS        | 24            | 80          | 80         | 38          | 88             | Ball      | 440          | 10.56         | UL/VDE/CE         | 55          | (3) 12" (speed sensor)            | 6.95    |
| 2232075    | ADDA Corporation        | AD0924HB-C70-LF       | 24            | 92          | 92         | 20          | 33             | Ball      | 140          | 3.36          | UL/CUL/TUV/CE/CSA | 32.8        | 11"                               | 12.95   |
| 1951051    | Mechatronics            | E9225L24B1-FS         | 24            | 92          | 92         | 25          | 35             | Ball      | 85           | 2.04          | UL/CUL            | 27          | (3) 12" (speed sensor)            | 3.95    |
| 2289223    | Canon                   | CF92-H201N1D          | 24            | 92          | 92         | 25          | 35             | Ball      | 85           | 2.04          | UL/CSA            | 27          | 11"                               | 7.95    |
| 2203071    | NMB Technologies        | 3610PL-05W-B30        | 24            | 92          | 92         | 25          | 41             | Ball      | 150          | 3.6           | UL                | 47.2        | 12"                               | 4.95    |
| 2232999    | ADDA Corporation        | AD0924LB-A71GL        | 24            | 92          | 92         | 25          | 41.6           | Ball      | 80           | 1.92          | UL/CUL/TUV/CE     | 30          | 12"                               | 7.95    |
| 2203080    | Nidec Corporation       | A31394-55             | 24            | 92          | 92         | 25          | 42             | Ball      | 140          | 3.12          | UL/CSA            | 48          | 3" with connector                 | 2.95    |
| 2215751    | NMB Technologies        | 3610PL-05W-B20-100    | 24            | 92          | 92         | 25          | 43             | Ball      | 150          | 3.6           | UL/CUL            | 39          | 12"                               | 3.95    |
| 2233001    | ADDA Corporation        | AD0924MX-A70GL        | 24            | 92          | 92         | 25          | 47.2           | Hypro     | 120          | 2.88          | UL/CUL/TUV/CE     | 31.3        | 12"                               | 6.95    |
| 2132082    | ADDA Corporation        | AD0924HX-A72GL        | 24            | 92          | 92         | 25          | 50             | Ball      | 150          | 3.6           | UL/CSA/TUV/CUL/CE | 33.7        | (3) 12" (with alarm)              | 7.95    |
| 2155065    | Delta Electronics       | AFB0924H-R00          | 24            | 92          | 92         | 25          | 51.2           | Ball      | 100          | 2.4           | UL/CSA/CE         | 34          | (3) 12" (locked rotor protection) | 7.95    |
| 2158303    | Sunon                   | EE92252B1-0000-A99    | 24            | 92          | 92         | 25          | 51.5           | Ball      | 87           | 2.1           | UL/CE/TUV         | 34          | 12"                               | 10.95   |
| 2121527    | ADDA Corporation        | AD1224MB-A71GL        | 24            | 120         | 120        | 25          | 80.5           | Ball      | 170          | 4.08          | UL/CUL/TUV/CE     | 38          | 11"                               | 13.95   |
| 2218046    | ADDA Corporation        | AD1224UB-A70GL        | 24            | 120         | 120        | 25          | 99             | Ball      | 250          | 6             | UL/CUL/TUV/CE     | 43.3        | 12"                               | 12.95   |
| 2289015    | EBM Papst               | TYP4484F              | 24            | 120         | 120        | 25          | 100            | Ball      | 208          | 5             | UL/CSA/VDE        | 43          | 12"                               | 23.95   |
| 2235330    | ADDA Corporation        | AS12024LB25A100       | 24            | 120         | 120        | 25          | 126            | Ball      | 280          | 6.72          | UL/CUL/TUV/CE     | 51          | 12"                               | 13.95   |
| 2232104    | ADDA Corporation        | AD1224UB-Y5B          | 24            | 120         | 120        | 32          | 133            | Ball      | 320          | 7.68          | UL/CUL/TUV/CE     | 48.4        | (3) 12" (PWM + FG)                | 13.95   |
| 153411     | Sunon                   | KD2412PMBX-6A         | 24            | 120         | 120        | 38          | 98             | Ball      | 230          | 5.5           | UL/TUV/CSA        | 36.5        | 12" (with terminal)               | 7.95    |
| 694524     | Jamicon Corporation     | JF1238B2MR-R          | 24            | 120         | 120        | 38          | 101.3          | Ball      | 220          | 5.28          | UL/TUV/CE/CSA     | 39.1        | 9"                                | 15.95   |
| 2271167    | ADDA Corporation        | AD1224US-F51(FN)      | 24            | 120         | 120        | 38          | 120            | Sleeve    | 400          | 9.6           | UL/CUL/TUV/CE     | 48          | 12"                               | 12.95   |
| 2236404    | Sunon                   | MEC0382V1-0000-A99    | 24            | 120         | 120        | 38          | 138            | Vapo      | 383          | 9.2           | UL/CUL/TUV/CE     | 48          | 12"                               | 12.95   |
| 2234919    | ADDA Corporation        | AD1324VB-F51          | 24            | 127         | 127        | 38          | 242.15         | Ball      | 1100         | 26.4          | UL/CUL/TUV/CE     | 64.5        | 12"                               | 27.95   |
| 2270879    | ADDA Corporation        | AD17224MB5151M0(0CW)  | 24            | 172         | 151        | 51          | 327            | Ball      | 1450         | 34.8          | UL/TUV/CSA/CE     | 64          | 12"                               | 49.95   |