



[Click Here to Request a Large Quantity Quote](#)

mm	6	10	15	20	25	28	30	32	35	38	40	45	51	60	70	75	76	80	92	94	95	97	120	125	126	127	150	172
Inches	0.24	0.40	0.60	0.80	1.00	1.10	1.18	1.26	1.40	1.50	1.60	1.80	2.00	2.36	2.76	2.95	2.99	3.15	3.63	3.70	3.74	3.82	4.72	4.92	4.96	5.00	5.90	6.77

DC BRUSHLESS FANS: 5 VOLTS

Jameco SKU	Mfr Name	Mfr P/N	Voltage (VDC)	Length (mm)	Width (mm)	Height (mm)	Air Flow (CFM)	Bearing	Current (mA)	Power (Watts)	Agency Approvals	Noise (dBA)	Connection (Leads)	Price 1
2095277	ADDA Corporation	AD2005LX-G70	5	20	20	10	0.6	Hypro	80	0.4	UL/CUL/TUV/CE/CSA	20	5.5"	\$ 10.15
2233490	ADDA Corporation	AD0205LB-G50GL	5	25	25	10	1.8	Ball	80	.4	UL/CUL/TUV/CE	15.6	5.5"	\$ 7.95
131247	ADDA Corporation	AD0205LX-G50-R	5	25	25	10	1.8	Sleeve	100	0.5	UL/CE/CSA	15.6	5.5"	\$ 6.75
2289247	SEPA	MFB25A-05	5	25	25	10	1.9	Ball	85	0.45	—	17	2" (with 2P connector)	\$ 5.95
2132197	ADDA Corporation	AD0205MB-G50GL	5	25	25	10	2.2	Ball	120	0.6	UL/CUL/TUV/CE/CSA	23	5.5"	\$ 5.95
2233502	ADDA Corporation	ADF0212MX-G50	5	25	25	10	2.2	Hypro	70	0.6	UL/CUL/TUV/CE	18.3	5.5"	\$ 6.95
2276575	Toshiba	D25MO5P-1	5	25	25	10	2.3	Ball	70	0.35	—	9.5	2.5"	\$ 5.95
695050	Sunon	MC25100V2-0000-99	5	25	25	10	3.0	Vapo	80	0.4	UL/CUL	16	5.5"	\$ 8.95
2234695	Sunon	MC30060V1-0000-A99	5	30	30	6	4.9	Vapo	112	0.56	UL/CUL/TUV	28	6"	\$ 8.45
2188924	ADDA Corporation	AD0305HX-K70(TX)	5	30	30	6.8	3.5	Ball	120	0.6	UL/CUL/TUV	32	12"	\$ 8.95
2270983	ADDA Corporation	AD0405LX-K90(X)	5	40	40	6.8	3.78	Hypro	50	0.25	UL/TUV	19.5	5.5"	\$ 10.95
2231742	ADDA Corporation	AD0405LB-G70	5	40	40	10	4.7	Ball	80	0.4	UL/CUL/TUV/CE	21	11"	\$ 4.95
2133886	ADDA Corporation	AD0405LX-G70	5	40	40	10	4.7	Hypro	80	0.4	UL/CUL/TUV/CE	14	11"	\$ 9.95
2258814	ADDA Corporation	AD0405MB-G76-LF	5	40	40	10	5	Ball	110	0.55	UL/CE	22	(3) 4" (with connector)	\$ 2.95
2131928	ADDA Corporation	AD0405MX-G76-LF	5	40	40	10	5.7	Hypro	110	0.55	UL/CUL/TUV/CE	20	(3) 11" (speed sensor)	\$ 3.95
2220091	ADDA Corporation	AD0405MX-G70	5	40	40	10	5.7	Hypro	110	0.55	UL/CUL/TUV/CE	19	4"	\$ 5.95
1928353	ADDA Corporation	AD0405HX-G70	5	40	40	10	6.7	Hypro	190	0.95	UL/CUL/TUV/CE	30	11"	\$ 5.95
2229933	Sunon	EE40100S1-0000-999	5	40	40	10	8	Sleeve	271	1.36	UL/CUL/TUV	32	12"	\$ 6.95
2132189	ADDA Corporation	AD0405HB-G70(TS)	5	40	40	10	8.7	Ball	100	0.8	UL/CUL/TUV/CE/CSA	25	12 with connector	\$ 3.95
2230993	Delta Electronics	FBK04F05L	5	40	40	20	3.9	Ball	120	0.006	UL	24	11"	\$ 5.95
1928361	ADDA Corporation	AD0405DS-C50(T1)	5	40	40	20	4.7	Sleeve	120	0.6	UL/TUV/CE	10	12"	\$ 5.95
2120057	Sunon	KD0504PKB2(2).GN	5	40	40	20	7.7	Ball	142	0.142	UL/CUL/TUV	29	12"	\$ 5.95
2121295	ADDA Corporation	AD0405HB-C50	5	40	40	20	9.9	Ball	110	0.55	UL/TUV/CSA	20	11"	\$ 8.95
2233318	ADDA Corporation	AD4505MX-G70	5	45	45	10	7	Hypro	120	0.6	UL/CUL/TUV/CE	22	12"	\$ 7.95
136494	Delta Electronics	AFB0505LA	5	50	50	10	7.42	Ball	80	0.4	UL/CE/CSA/VDE	26	11"	\$ 4.95
2121324	ADDA Corporation	AD0505MB-G76(S)LF	5	50	50	10	10.5	Ball	180	0.9	UL/CUL/TUV/CE	25	(3) 11" (locked rotor)	\$ 4.95
2150774	ADDA Corporation	AD0505MB-G70	5	50	50	10	10.5	Ball	180	0.9	UL/CUL/TUV/CE	24	12"	\$ 8.95
2233537	ADDA Corporation	AD0505HB-G76	5	50	50	10	11.8	Ball	230	1.15	UL/CUL/TUV/CE	27.5	(3) 12" (speed sensor)	\$ 6.95
2132120	ADDA Corporation	AD0605LB-A72GL-LF	5	60	60	25	13.82	Ball	250	1	UL/CSA/TUV	16.1	(3) 12" (with alarm)	\$ 4.95
2271127	ADDA Corporation	AG06005MB257103	5	60	60	25	23.3	Ball	300	1.5	UL/CUL/TUV/CE	37.1	12"	\$ 8.95
2131952	ADDA Corporation	AD0605HB-A72GL	5	60	60	25	24.3	Ball	250	1.25	UL/CSA/TUV/CE	28.8	(3) 12" (with alarm)	\$ 5.95
2258671	ADDA Corporation	AD0805HB-D71-LF	5	80	80	15	29.9	Ball	430	2.15	UL/CUL/TUV	33	12"	\$ 8.95
2233211	ADDA Corporation	AD0805HS-D71	5	80	80	15	29.9	Sleeve	430	2.15	UL/CUL/TUV/CE	31.4	12"	\$ 6.95