



[Click Here to Request a Large Quantity Quote](#)

AC-DC SWITCHING DIN RAIL POWER SUPPLIES 5V - 13.8V

Jameco SKU	Mfr Name	Mfr P/N	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	Input Voltage (VAC)	Maximum Input Current (A)	Low Power Source (LPS)	PFC Function	Efficiency (%)	Length (in)	Width (in)	Height (in)	Weight (lbs.)	Agency Approvals	Price 1
2103978	MEAN WELL	MDR-10-5	5.0	2.0	10.0	85 to 264	0.33	No	No	77	0.89	3.54	3.94	0.4	UL/CUL/TUV/CB/CE/EN	\$ 11.60
2251196	MEAN WELL	HDR-15-5	5.0	2.4	12.0	85 to 264	0.50	Yes	No	80	0.69	3.54	2.15	0.2	UL/CUL/TUV/CB/CE/EN	\$ 11.60
2101243	MEAN WELL	DR-15-5	5.0	2.4	12.0	85 to 264	0.88	No	No	77	0.98	3.66	2.2	0.2	UL/CUL/TUV/CB/CE/EN	\$ 12.95
1943300	MEAN WELL	MDR-20-5	5.0	3.0	15.0	85 to 264	0.55	No	No	76	0.89	3.54	3.94	0.4	UL/CUL/TUV/CB/CE/EN	\$ 13.50
2251241	MEAN WELL	HDR-30-5	5.0	3.0	15.0	85 to 264	0.88	Yes	No	82	1.38	3.54	2.15	0.3	UL/CUL/TUV/CB/CE/EN	\$ 14.30
212303	MEAN WELL	DR-4505	5.0	5.0	25.0	85 to 264	1.50	No	No	72	3.66	3.07	2.64	0.7	UL/CUL/TUV/CB/CE/EN	\$ 14.95
1943393	MEAN WELL	MDR-40-5	5.0	6.0	30.0	85 to 264	1.10	No	No	78	1.57	3.54	3.94	0.6	UL/CUL/TUV/CB/CE/EN/EAC	\$ 18.10
2251292	MEAN WELL	HDR-60-5	5.0	6.5	32.5	85 to 264	1.20	Yes	No	85	2.07	3.54	2.15	0.5	UL/CUL/TUV/CB/CE/EN	\$ 19.40
373212	MEAN WELL	DR-60-5	5.0	6.5	32.5	88 to 264	1.20	No	No	76	3.07	3.66	2.2	0.6	UL/CUL/TUV/CB/CE/EN	\$ 22.99
1943449	MEAN WELL	MDR-60-5	5.0	10.0	50.0	85 to 264	1.80	No	No	78	1.57	3.54	3.94	0.7	UL/CUL/TUV/CB/CE/EN/EAC	\$ 19.40
1952978	MEAN WELL	MDR-10-12	12.0	0.8	10.0	85 to 264	0.33	No	No	81	0.89	3.54	3.94	0.4	UL/CUL/TUV/CB/CE/EN	\$ 11.60
2251209	MEAN WELL	HDR-15-12	12.0	1.3	15.0	85 to 264	0.50	Yes	No	85	0.69	3.54	2.15	0.2	UL/CUL/TUV/CB/CE/EN	\$ 11.60
2094952	MEAN WELL	DR-15-12	12.0	1.3	15.0	85 to 264	0.88	No	No	84	0.98	3.66	2.2	0.2	UL/CUL/TUV/CB/CE/EN	\$ 12.95
1943334	MEAN WELL	MDR-20-12	12.0	1.7	20.0	85 to 264	0.55	No	No	80	0.89	3.54	3.94	0.4	UL/CUL/TUV/CB/CE/EN	\$ 13.50
2251250	MEAN WELL	HDR-30-12	12.0	2.0	24.0	85 to 264	0.88	Yes	No	88	1.38	3.54	2.15	0.3	UL/CUL/TUV/CB/CE/EN	\$ 14.30
373182	MEAN WELL	DR-30-12	12.0	2.0	24.0	85 to 264	0.88	No	No	81	3.07	3.66	2.2	0.6	UL/CUL/TUV/CB/CE/EN	\$ 14.95
1943406	MEAN WELL	MDR-40-12	12.0	3.3	40.0	85 to 264	1.10	No	No	86	1.57	3.54	3.94	0.6	UL/CUL/TUV/CB/CE/EN/EAC	\$ 18.10
2216788	MEAN WELL	DRA-40-12	12.0	3.3	40.1	90 to 264	0.80	Yes	No	85	1.57	3.54	3.94	0.6	UL/CUL/TUV/CB/CE/EN	\$ 21.30
192699	MEAN WELL	DR-4512	12.0	3.5	42.0	85 to 264	1.50	No	No	77	3.66	3.07	2.64	0.7	UL/CUL/TUV/CB/CE/EN	\$ 19.10
2251305	MEAN WELL	HDR-60-12	12.0	4.5	54.0	85 to 264	1.20	Yes	No	88	2.07	3.54	2.15	0.5	UL/CUL/TUV/CB/CE/EN	\$ 19.40
1943457	MEAN WELL	MDR-60-12	12.0	5.0	60.0	85 to 264	1.80	No	No	86	1.57	3.54	3.94	0.7	UL/CUL/TUV/CB/CE/EN/EAC	\$ 19.40
2216809	MEAN WELL	DRA-60-12	12.0	5.0	60.0	90 to 264	1.30	No	No	85	1.57	3.54	3.94	0.6	UL/CUL/TUV/CB/CE/EN	\$ 23.60
2190311	MEAN WELL	SDR-75-12	12.0	6.3	75.6	88 to 264	1.40	No	No	89	1.26	4.93	4.02	1.2	UL/CUL/TUV/CB/CE/EN/EAC/SEMI	\$ 33.40
2216673	MEAN WELL	NDR-75-12	12.0	6.3	75.6	90 to 264	1.45	No	No	86	1.26	4.93	4.02	1.1	UL/CUL/TUV/CB/CE/EN	\$ 24.10
2216649	MEAN WELL	EDR-75-12	12.0	6.3	75.6	90 to 264	1.45	No	No	86	1.26	4.93	4.02	1.1	UL/CUL/TUV/CB/CE/EN	\$ 22.20
212291	MEAN WELL	DR-75-12	12.0	6.3	76.0	85 to 264	1.60	No	No	76	2.19	4.93	3.94	1.5	UL/CUL/TUV/CB/CE/EN	\$ 30.95
2264327	MEAN WELL	HDR-100-12	12.0	7.1	85.2	85 to 264	3.00	Yes	No	88	2.15	2.76	3.54	0.6	UL/CUL/TUV/CB/CE/EN	\$ 27.70
1943481	MEAN WELL	MDR-100-12	12.0	7.5	90.0	85 to 264	1.30	No	Yes	85	2.17	3.54	3.94	1.0	UL/CUL/TUV/CE/EN/EAC	\$ 33.60
2264335	MEAN WELL	HDR-100-12N	12.0	7.5	90.0	85 to 264	3.00	No	No	88	2.15	2.76	3.54	0.6	UL/CUL/TUV/CB/CE/EN	\$ 27.70
1943511	MEAN WELL	DR-100-12	12.0	7.5	90.0	88 to 264	3.00	No	No	87	3.94	3.66	2.2	0.8	UL/CUL/TUV/CB/CE/EN	\$ 28.49
212274	MEAN WELL	DR-120-12	12.0	10.0	120.0	88 to 132, 176 to 264	2.60	No	No	80	2.58	4.93	3.94	1.9	UL/CUL/TUV/CB/CE/EN	\$ 37.89
2099366	MEAN WELL	SDR-120-12	12.0	10.0	120.0	88 to 264	1.40	No	Yes	89	1.57	4.93	4.47	1.5	UL/CUL/TUV/CB/CE/EN/EAC/SEMI	\$ 54.00
2218530	MEAN WELL	EDR-120-12	12.0	10.0	120.0	90 to 264	2.25	No	No	85	1.57	4.93	4.47	1.4	UL/CUL/TUV/CB/CE/EN	\$ 25.70
2218572	MEAN WELL	NDR-120-12	12.0	10.0	120.0	90 to 264	2.25	No	No	86	1.57	4.93	4.47	1.4	UL/CUL/TUV/CB/CE/EN	\$ 28.30
2123047	MEAN WELL	WDR-120-12	12.0	10.0	120.0	180 to 550	1.20	No	No	90	1.57	4.93	4.47	1.4	UL/CUL/CB/CE/EN/EAC	\$ 60.80
2284527	MEAN WELL	HDR-150-12	12.0	10.2	122.4	85 to 264	3.00	No	No	89	4.13	3.54	2.15	0.8	UL/CUL/TUV/CB/CE/EAC	\$ 35.20
2216745	MEAN WELL	DRC-40A	13.8	2.9	40.0	90 to 264	0.80	No	No	86	1.57	3.54	3.94	0.6	UL/CUL/TUV/CB/CE/EN	\$ 21.95
2216761	MEAN WELL	DRC-60A	13.8	4.3	59.3	90 to 264	1.30	No	No	86	1.57	3.54	3.94	0.7	UL/CUL/TUV/CB/CE/EN	\$ 27.95
2220841	MEAN WELL	DRC-100A	13.8	7.0	96.6	90 to 264	1.80	No	No	87	2.17	3.54	3.94	0.9	UL/CUL/TUV/CB/CE/EN	\$ 39.95